

Coaxial High Pass Filter

50Ω 1650 to 5000 MHz

VHFG-1600+



Generic photo used for illustration purposes only

CASE STYLE: FF704

The Big Deal

- Excellent power handling, 4W
- Temperature stable
- Rugged unibody construction
- Good rejection, 53 dB typical

Product Overview

VHFG-1600+ is a 50Ω high pass filter built in rugged unibody construction. Covering 1650-5000 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VHFG-1600+ offer low insertion loss, and excellent power handling capability. It handles up to 4W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
4W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High Pass Filter

50Ω 1650 to 5000 MHz

VHFG-1600+



Features

- Temperature stable
- Excellent power handling, 4W
- Connectorized package
- Rugged unibody construction

Generic photo used for illustration purposes only
CASE STYLE: FF704

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Applications

- Transmitters / Receivers
- Global positioning system(GPS)
- Satellite broadcast applications

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	DC - 700	40	53	-	dB
		DC-F2	DC - 950	22	33	-	dB
	Freq. Cut-Off	F3*	1530	-	3.0	-	dB
Pass Band	Insertion Loss	F4-F8	1650 - 5000	-	2.0	-	dB
	Return Loss	F5-F7	1700 - 4000	-	14	-	dB

In Applications where DC voltage is present at either input or output ports, DC blocks are required.


* Typically, a $\pm 5\%$ frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings


Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	4W max. @25°C

*Passband rating, derate linearly to 0.8W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Functional Schematic






Typical Frequency Response



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	87.69	0.17
250	65.12	0.30
700	58.54	0.50
950	32.78	0.65
1000	29.36	0.70
1160	19.40	0.95
1200	17.06	1.07
1300	11.50	1.66
1400	6.63	3.21
1530	2.64	8.65
1550	2.31	9.97
1600	1.72	13.84
1650	1.39	18.31
1700	1.20	21.86
2000	0.81	21.17
3500	0.47	31.52
3750	0.48	25.51
4000	0.53	18.72
4500	0.79	11.81
5000	1.26	8.10



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C	@-55°C	@+25°C	@+125°C
10	67.33	68.17	65.77	0.16	0.19	0.24	0.15	0.20	0.24
100	68.25	68.45	72.62	0.19	0.23	0.29	0.19	0.24	0.30
180	64.69	64.56	64.96	0.22	0.26	0.33	0.23	0.28	0.34
270	60.59	60.69	60.59	0.23	0.28	0.35	0.25	0.31	0.38
340	58.40	58.32	58.22	0.26	0.32	0.39	0.27	0.34	0.41
420	56.34	56.22	56.11	0.27	0.34	0.42	0.28	0.36	0.43
500	54.98	55.08	55.17	0.28	0.35	0.44	0.30	0.38	0.47
580	55.09	55.31	55.70	0.30	0.38	0.48	0.31	0.40	0.49
660	58.31	59.24	60.18	0.33	0.42	0.52	0.34	0.43	0.53
700	63.46	64.45	64.15	0.34	0.43	0.54	0.35	0.45	0.55
820	48.54	47.17	45.72	0.37	0.48	0.60	0.39	0.50	0.61
950	35.95	35.07	34.05	0.42	0.54	0.69	0.45	0.57	0.71
1010	31.51	30.68	29.73	0.45	0.58	0.74	0.48	0.61	0.77
1060	28.12	27.33	26.40	0.49	0.63	0.81	0.51	0.66	0.83
1140	23.05	22.27	21.36	0.55	0.71	0.93	0.61	0.77	0.99
1170	21.23	20.46	19.55	0.59	0.77	1.00	0.65	0.83	1.07
1300	13.72	12.97	12.12	0.94	1.24	1.64	1.08	1.37	1.78
1530	3.36	3.12	2.95	5.22	6.40	7.90	5.98	7.28	8.98
1550	2.87	2.69	2.59	6.11	7.41	9.02	7.04	8.49	10.38
1600	1.96	1.92	1.96	8.70	10.25	12.06	10.29	12.20	14.59
1650	1.43	1.49	1.60	11.54	13.18	14.89	14.25	16.60	19.31
1700	1.14	1.25	1.40	13.91	15.31	16.60	17.77	19.81	21.41
1750	0.99	1.11	1.27	15.14	16.15	17.04	18.64	19.60	20.13
1860	0.83	0.95	1.11	15.48	16.23	17.09	16.63	17.24	17.89
1940	0.76	0.87	1.01	15.73	16.60	17.64	16.15	16.94	17.83
2000	0.70	0.81	0.95	16.25	17.26	18.44	16.36	17.28	18.32
2100	0.61	0.72	0.86	17.68	18.93	20.33	17.31	18.45	19.65
2180	0.56	0.66	0.80	19.21	20.64	22.08	18.46	19.72	20.99
2260	0.50	0.61	0.75	20.92	22.36	23.57	19.83	21.11	22.32
2340	0.46	0.57	0.71	22.51	23.61	24.27	20.98	22.03	22.96
2420	0.43	0.54	0.68	23.38	23.81	23.94	21.52	22.20	22.85
2500	0.41	0.52	0.66	23.30	23.20	23.08	21.73	22.04	22.49
2580	0.39	0.51	0.64	22.74	22.33	22.18	21.46	21.51	21.90
2660	0.38	0.49	0.63	22.23	21.69	21.61	21.13	21.03	21.44
2740	0.37	0.48	0.61	21.73	21.16	21.20	20.94	20.74	21.21
2820	0.35	0.47	0.60	21.43	20.87	21.02	20.74	20.52	21.06
2900	0.34	0.46	0.59	21.36	20.82	21.06	20.78	20.56	21.20
2980	0.33	0.44	0.58	21.66	21.10	21.47	21.12	20.88	21.62
3060	0.31	0.43	0.56	22.03	21.50	21.96	21.66	21.42	22.26
3140	0.30	0.42	0.55	22.69	22.19	22.70	22.40	22.21	23.16
3220	0.29	0.40	0.54	23.78	23.26	23.86	23.51	23.33	24.45
3300	0.27	0.39	0.53	25.20	24.65	25.32	25.11	24.99	26.37
3380	0.26	0.38	0.52	27.17	26.57	27.22	27.46	27.43	29.18
3460	0.25	0.37	0.51	29.47	28.82	29.26	31.43	31.55	34.13
3540	0.25	0.36	0.51	31.80	31.20	30.68	36.96	38.65	42.95
3620	0.24	0.36	0.50	31.02	30.82	29.56	38.30	43.04	36.87
3700	0.24	0.36	0.51	27.77	27.78	26.78	30.88	31.47	29.76
3780	0.25	0.36	0.51	24.91	24.89	24.26	26.34	26.47	25.66
3860	0.26	0.37	0.52	22.38	22.33	21.99	23.32	23.34	22.92
3940	0.27	0.39	0.54	20.29	20.25	20.07	20.91	20.90	20.68
4000	0.28	0.40	0.55	19.02	18.93	18.87	19.42	19.36	19.27
4100	0.31	0.43	0.58	17.09	17.00	17.03	17.41	17.33	17.36
4180	0.34	0.46	0.61	15.74	15.66	15.75	16.04	15.97	16.06
4260	0.38	0.50	0.65	14.65	14.56	14.70	14.83	14.75	14.89
4340	0.42	0.55	0.69	13.64	13.55	13.73	13.79	13.71	13.90
4420	0.47	0.59	0.75	12.70	12.61	12.83	12.86	12.79	13.02
4500	0.52	0.64	0.79	11.88	11.80	12.02	12.00	11.92	12.15
4580	0.57	0.70	0.84	11.19	11.11	11.34	11.28	11.21	11.44
4660	0.63	0.77	0.91	10.51	10.43	10.68	10.58	10.51	10.77
5000	0.93	1.09	1.25	8.20	8.14	8.39	8.22	8.17	8.42






* Temperature test data was based on the underlying chip

Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-55°C	@+25°C	@+125°C
1000	0.24	0.25	0.26
1100	0.32	0.33	0.35
1200	0.41	0.43	0.46
1300	0.55	0.58	0.63
1400	0.75	0.78	0.83
1500	0.92	0.92	0.92
1600	0.88	0.85	0.81
1650	0.79	0.76	0.72
1700	0.70	0.66	0.63
1750	0.61	0.58	0.56
2000	0.38	0.37	0.36
2100	0.33	0.32	0.32
2200	0.30	0.29	0.29
2300	0.27	0.26	0.26
2400	0.25	0.24	0.24
2500	0.23	0.22	0.22
2600	0.21	0.20	0.20
2700	0.19	0.19	0.19
2800	0.18	0.18	0.18
2900	0.17	0.17	0.17
3000	0.16	0.16	0.16
3100	0.15	0.15	0.15
3200	0.15	0.15	0.15
3300	0.14	0.14	0.14
3400	0.14	0.14	0.14
3550	0.13	0.13	0.13
3600	0.13	0.13	0.13
3700	0.13	0.12	0.13
3800	0.12	0.12	0.12
3900	0.12	0.12	0.12
4000	0.12	0.12	0.12
4100	0.11	0.11	0.12
4200	0.11	0.11	0.11
4300	0.11	0.11	0.11
4400	0.11	0.11	0.11
4500	0.11	0.11	0.11
4650	0.10	0.10	0.10
4700	0.10	0.10	0.10
4800	0.10	0.10	0.10
4900	0.10	0.10	0.10
5000	0.09	0.09	0.10


* Temperature test data was based on the underlying chip

Typical Performance Curves



* Temperature test data was based on the underlying chip

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 125° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 125°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, Except +125°C