

Low Pass Filter

VLF-1200

50Ω

*DC to 1200 MHz



CASE STYLE: FF704

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C
DC Current Input to Output	0.5A max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 10W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications

- harmonic rejection
- transmitters/receivers
- lab use


Connectors	Model
SMA	VLF-1200
Price: Contact Sales Dept.	

Electrical Specifications at 25°C

PASSBAND (MHz)	f _{co} , MHz Nom.	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
(loss < 1 dB)	(loss 3 dB)	f 20	30	fr 20	Stopband	Passband	
Max.	Typ.	Min.	Typ.	Typ.	Typ.	Typ.	
*DC-1200	1530	1865	2000-5000	6200	20	1.2	7

* Not for use with DC voltage at input and output ports


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	gra
.410	1.43	.312	1
10.41	36.32	7.92	

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.07	1.01
250	0.14	1.05
700	0.32	1.15
1200	0.69	1.06
1400	1.45	1.48
1530	3.63	2.20
1600	7.44	3.56
1700	17.61	7.70
1865	30.16	14.87
2000	30.80	19.11
3500	37.28	38.61
5000	37.80	45.72
6000	27.00	34.75
6200	16.43	16.56
7000	15.93	32.18



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

VLF-1200

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.07	0.08	47.31	44.57	42.43	44.97	41.64	39.81
100	0.07	0.10	0.11	40.05	41.64	41.71	39.18	38.58	38.13
200	0.07	0.11	0.14	36.86	34.62	33.30	33.56	32.13	31.40
500	0.19	0.24	0.29	27.20	25.90	24.91	24.92	23.83	22.84
1000	0.38	0.49	0.58	25.64	25.80	25.93	24.78	24.55	24.25
1200	0.53	0.69	0.82	33.17	30.61	28.65	29.57	27.65	25.91
1250	0.61	0.81	0.94	25.62	24.11	22.91	24.42	22.92	21.65
1300	0.72	0.93	1.11	21.05	19.98	19.20	19.89	18.80	17.86
1315	0.77	0.99	1.17	19.80	18.87	18.16	18.71	17.75	16.86
1350	0.89	1.14	1.36	17.39	16.74	16.18	16.45	15.63	14.86
1400	1.14	1.45	1.72	14.57	14.21	13.88	13.46	12.84	12.18
1450	1.56	1.95	2.32	12.22	12.10	11.93	10.82	10.29	9.73
1500	2.27	2.81	3.35	9.98	9.96	9.90	8.27	7.79	7.30
1505	2.33	2.92	3.48	9.73	9.72	9.66	8.03	7.56	7.08
1530	2.92	3.63	4.35	8.52	8.52	8.44	6.74	6.29	5.87
1560	3.96	4.92	5.83	7.02	6.98	6.90	5.24	4.86	4.54
1600	6.11	7.44	8.69	5.03	5.02	4.96	3.51	3.33	3.18
1630	8.43	10.04	11.51	3.79	3.85	3.88	2.56	2.52	2.51
1675	12.91	14.77	16.41	2.54	2.69	2.78	1.73	1.86	1.97
1700	15.70	17.61	19.28	2.09	2.27	2.40	1.49	1.68	1.82
1720	18.01	19.91	21.57	1.83	2.02	2.14	1.38	1.57	1.74
1780	24.40	26.01	27.27	1.33	1.52	1.66	1.16	1.38	1.57
1800	26.12	27.51	28.57	1.24	1.43	1.56	1.11	1.35	1.54
1830	28.11	29.16	29.88	1.09	1.28	1.42	1.08	1.31	1.49
1865	30.99	31.12	31.23	0.93	1.09	1.27	0.93	1.11	1.31
2000	30.51	30.80	31.08	0.74	0.91	1.03	0.88	1.07	1.24
2350	40.32	41.76	43.25	0.46	0.66	0.81	0.53	0.68	0.77
2495	57.72	54.94	52.03	0.42	0.62	0.77	0.43	0.55	0.62
3000	37.13	37.20	37.16	0.37	0.55	0.66	0.25	0.36	0.43
3500	37.08	37.28	37.38	0.28	0.45	0.55	0.18	0.29	0.36
4000	37.70	37.86	38.01	0.21	0.38	0.47	0.14	0.26	0.34
4500	37.47	37.66	37.77	0.19	0.35	0.47	0.12	0.26	0.38
5000	37.60	37.80	38.09	0.18	0.38	0.50	0.13	0.28	0.42
5610	48.45	51.65	51.68	0.14	0.35	0.54	0.10	0.28	0.46
5780	43.02	39.65	37.25	0.15	0.39	0.59	0.10	0.31	0.49
5940	32.05	30.02	28.34	0.18	0.43	0.66	0.13	0.35	0.55
6120	22.86	20.87	19.08	0.34	0.69	1.03	0.27	0.56	0.90
6200	18.63	16.43	14.44	0.54	1.05	1.72	0.43	0.87	1.46
6330	10.59	8.53	8.05	2.19	4.46	5.63	1.88	3.78	4.82
6490	7.91	9.97	11.56	2.83	1.88	1.60	2.51	1.70	1.45
7000	15.60	15.93	16.18	0.27	0.54	0.76	0.27	0.48	0.69

REV. X1

VLF-1200

080720

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-1200


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VLF-1200
080720
Page 1 of 1

Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I