

Coaxial Low Pass Filter

50Ω

*DC to 1450 MHz

VLF-1450+



Generic photo used for illustration purposes only

CASE STYLE: FF704

Connectors	Model
SMA	VLF-1450+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C
DC Current Input to Output	0.5A max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 10W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications


- harmonic rejection
- transmitters/receivers
- lab use

Electrical Specifications at 25°C

PASSBAND (MHz) (loss < 1 dB)	fco, MHz Nom. (loss 3 dB)	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
		f 20 Min.	30 Typ.	fr 20 Typ.	Stopband Typ.	Passband Typ.	
Max.	Typ.	Min.	Typ.	Typ.	Typ.	Typ.	
*DC-1450	1825	2025	2050-6600	6700	20	1.2	7

* Not for use with DC voltage at input and output ports


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.09	1.03
500	0.22	1.05
1000	0.41	1.09
1450	0.79	1.10
1600	1.36	1.35
1790	7.31	5.59
1825	10.28	8.08
1880	16.05	13.09
2025	36.64	23.49
2050	40.77	24.14
3500	42.15	46.96
5000	40.48	49.64
6600	41.43	41.37
6700	29.08	38.61
7000	18.74	33.42



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/VCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
M151777
VLF-1450+
ED-11960/2
AD/TD/CP/AM
200522
Page 1 of 1

Coaxial Low Pass Filter

VLF-1450+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.05	0.09	0.09	39.31	36.79	35.90	39.73	37.20	36.31
100	0.07	0.09	0.11	36.65	34.68	33.75	36.95	34.86	33.82
500	0.17	0.22	0.25	30.35	32.31	34.66	29.14	30.08	30.86
1000	0.29	0.41	0.46	27.65	27.05	26.97	26.89	26.01	25.59
1450	0.61	0.79	0.91	26.09	26.76	27.11	24.72	24.63	24.45
1530	0.76	1.00	1.14	24.49	23.77	23.03	22.57	21.93	21.39
1685	1.95	2.49	2.89	9.88	9.15	8.66	10.53	10.09	9.82
1700	2.26	2.88	3.31	8.72	8.04	7.57	9.46	9.05	8.81
1740	3.47	4.31	4.95	5.94	5.46	5.13	6.81	6.54	6.37
1825	8.79	10.28	11.39	2.22	2.16	2.14	3.02	3.10	3.13
1860	12.10	13.80	15.03	1.49	1.55	1.58	2.30	2.45	2.53
1910	17.82	19.74	21.15	0.98	1.11	1.20	1.65	1.84	1.93
1960	24.37	26.53	28.10	0.77	0.92	1.00	1.34	1.53	1.64
1975	26.49	28.72	30.38	0.72	0.87	0.97	1.25	1.45	1.54
2000	30.22	32.60	34.34	0.65	0.79	0.91	1.14	1.33	1.43
2025	34.18	36.64	38.45	0.58	0.74	0.83	1.06	1.25	1.33
2040	36.68	39.14	41.00	0.55	0.72	0.82	1.03	1.19	1.30
2050	38.35	40.77	42.68	0.57	0.72	0.84	1.00	1.16	1.26
2125	47.07	47.32	47.25	0.45	0.62	0.69	0.83	0.99	1.08
2660	33.18	33.39	33.48	0.25	0.39	0.50	0.44	0.58	0.68
3000	35.37	35.70	35.96	0.25	0.38	0.47	0.33	0.49	0.60
3500	41.56	42.15	42.51	0.25	0.37	0.44	0.34	0.49	0.58
4000	53.74	54.95	56.25	0.21	0.33	0.40	0.26	0.42	0.50
4160	68.10	68.65	65.88	0.20	0.33	0.43	0.29	0.43	0.50
4230	65.18	61.83	59.74	0.21	0.36	0.43	0.30	0.44	0.51
4300	57.86	56.17	55.18	0.20	0.38	0.45	0.28	0.41	0.49
4500	49.47	48.73	48.19	0.20	0.36	0.44	0.23	0.39	0.45
5000	40.77	40.48	40.29	0.19	0.35	0.46	0.23	0.37	0.46
6500	36.91	38.78	40.53	0.21	0.41	0.57	0.19	0.40	0.59
6600	42.01	41.43	38.01	0.22	0.42	0.61	0.24	0.51	0.74
6630	42.60	38.09	34.14	0.19	0.40	0.59	0.28	0.56	0.83
6700	34.24	29.08	25.72	0.21	0.45	0.68	0.40	0.85	1.35
6890	13.83	15.49	17.02	0.90	0.81	0.82	5.26	2.55	1.77
7000	17.18	18.74	19.62	0.37	0.52	0.64	0.83	0.78	0.84
8000	21.04	21.02	21.12	0.16	0.40	0.56	0.16	0.39	0.59
10000	15.77	15.79	15.73	0.24	0.53	0.72	0.35	0.56	0.68
11000	12.65	12.86	12.91	0.58	0.90	1.13	0.63	0.90	1.04
12000	9.22	9.27	9.37	1.27	1.83	2.28	1.41	2.03	2.57
12240	8.26	8.35	8.91	1.71	2.49	3.01	2.38	4.03	5.90
13000	12.97	15.15	15.60	8.51	10.34	8.04	1.42	1.65	1.91

REV. X1
VLF-1450+
070924
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-1450+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VLF-1450+
070924
Page 1 of 1

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I