

Low Pass Filter

50Ω

*DC to 2750 MHz

VLF-2750



CASE STYLE: FF704

Connectors	Model
SMA	VLF-2750

Price: Contact Sales Dept.

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	10W max. at 25°C
DC Current Input to Output	0.5A max. at 25°C

* Passband rating, derate linearly to 3.5W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- rugged unibody construction, small size
- 7 sections
- excellent power handling, 10W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications


- harmonic rejection
- transmitters/receivers
- lab use

Electrical Specifications at 25°C

PASSBAND (MHz) (loss < 1 dB)	fco, MHz Nom. (loss 3 dB)	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
		F 20 Min.	30 Typ.	Fr 20 Typ.	Stopband Typ.	Passband Typ.	
*DC-2750	3150	4000	4150-6800	8400	20	1.2	7

* Not for use with DC voltage at input and output ports


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50	0.08	1.03
200	0.13	1.02
500	0.18	1.02
1000	0.28	1.10
2000	0.54	1.32
2750	0.79	1.16
3150	1.83	1.97
4000	33.61	23.18
4200	53.15	27.59
5150	39.36	40.41
6000	55.34	45.72
6800	32.46	46.96
7500	26.91	46.96
8400	22.87	46.96
9900	18.62	29.96



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

VLF-2750

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.06	0.08	0.07	44.14	38.02	34.78	44.89	38.48	35.07
200	0.10	0.13	0.14	35.82	39.27	38.86	34.96	38.30	38.59
500	0.12	0.18	0.21	44.67	39.75	33.22	36.88	34.25	30.76
1000	0.20	0.28	0.32	26.73	26.24	26.24	24.71	24.37	24.04
1500	0.31	0.41	0.48	19.61	19.39	19.42	19.56	19.21	19.05
2000	0.42	0.54	0.63	17.07	17.31	17.53	17.35	17.39	17.41
2500	0.52	0.66	0.77	19.63	20.57	21.28	18.93	20.01	20.77
2700	0.58	0.74	0.88	23.33	23.02	22.76	20.97	21.38	21.71
2750	0.61	0.79	0.93	23.55	22.68	22.09	21.03	21.15	21.28
2900	0.76	0.96	1.14	19.50	18.62	17.90	18.32	18.10	17.85
3150	1.47	1.83	2.15	10.42	9.70	9.29	10.66	10.14	9.81
3260	2.43	2.92	3.39	6.79	6.37	6.09	7.16	6.85	6.59
3370	4.29	4.97	5.63	3.98	3.83	3.72	4.35	4.26	4.13
3540	9.26	10.21	11.14	1.63	1.71	1.79	1.96	2.05	2.09
3660	14.08	15.18	16.23	1.05	1.18	1.30	1.29	1.43	1.52
3775	19.25	20.54	21.77	0.74	0.91	1.04	0.96	1.13	1.26
3850	23.03	24.45	25.81	0.68	0.84	0.97	0.84	1.02	1.16
3900	25.76	27.28	28.74	0.68	0.83	0.96	0.84	1.01	1.15
3950	28.62	30.26	31.85	0.58	0.74	0.88	0.76	0.95	1.11
4000	31.81	33.61	35.34	0.60	0.75	0.88	0.74	0.93	1.09
4070	36.87	38.96	41.01	0.57	0.74	0.85	0.73	0.93	1.09
4150	43.18	45.33	46.81	0.57	0.72	0.84	0.74	0.94	1.16
4200	49.82	53.15	56.52	0.46	0.63	0.76	0.68	0.87	1.06
4700	45.73	44.52	43.70	0.39	0.55	0.66	0.69	0.91	1.11
4900	40.77	40.27	40.02	0.31	0.48	0.58	0.65	0.86	1.05
5150	39.34	39.36	39.34	0.28	0.43	0.55	0.62	0.80	0.95
6000	56.41	55.34	52.90	0.31	0.38	0.54	0.43	0.60	0.71
6800	32.77	32.46	32.16	0.42	0.37	0.58	0.25	0.47	0.64
7500	27.00	26.91	26.86	0.23	0.37	0.57	0.20	0.44	0.66
8400	22.70	22.87	23.00	0.22	0.37	0.51	0.23	0.45	0.69
9900	18.86	18.62	18.58	0.08	0.58	0.78	0.32	0.53	0.67
11000	16.78	16.74	16.58	0.34	0.55	0.71	0.35	0.61	0.77
12100	14.41	14.49	14.51	0.38	0.65	0.89	0.33	0.52	0.69
13000	12.55	12.14	11.98	0.51	0.94	1.41	0.53	0.82	1.09
14000	11.58	11.98	12.17	1.27	1.44	1.80	0.91	1.15	1.43
15200	9.32	9.98	10.83	1.93	1.77	1.76	1.91	1.93	2.15
16300	14.72	15.51	16.12	0.63	0.91	1.15	0.73	0.90	1.08
17400	19.48	19.98	20.33	0.59	0.86	1.47	0.38	0.76	0.89
18500	21.76	19.66	19.77	5.81	3.65	2.51	0.25	0.67	1.00
19400	18.32	18.56	19.10	0.63	1.09	1.48	0.46	0.94	1.44
20000	16.39	16.35	16.27	1.07	1.90	2.88	0.98	1.69	2.66

REV. X1

VLF-2750

080720

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-2750


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1
VLF-2750
080720
Page 1 of 1

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I