

# Coaxial Low Pass Filter

50Ω

\*DC to 2750 MHz

VLF-2750+



Generic photo used for illustration purposes only

CASE STYLE: FF704

| Connectors | Model     |
|------------|-----------|
| SMA        | VLF-2750+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

## Maximum Ratings

|                            |                   |
|----------------------------|-------------------|
| Operating Temperature      | -55°C to 100°C    |
| Storage Temperature        | -55°C to 100°C    |
| RF Power Input*            | 10W max. at 25°C  |
| DC Current Input to Output | 0.5A max. at 25°C |

\* Passband rating, derate linearly to 3.5W at 100°C ambient.  
Permanent damage may occur if any of these limits are exceeded.

## Features

- rugged unibody construction, small size
- 7 sections
- excellent power handling, 10W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

## Applications


- harmonic rejection
- transmitters/receivers
- lab use

## Electrical Specifications at 25°C

| PASSBAND<br>(MHz)<br>(loss < 1 dB) | fco, MHz<br>Nom.<br>(loss 3 dB) | STOP BAND (MHz)<br>(loss, dB) |            |               | VSWR<br>(:1)     |                  | NO. OF<br>SECTIONS |
|------------------------------------|---------------------------------|-------------------------------|------------|---------------|------------------|------------------|--------------------|
|                                    |                                 | F 20<br>Min.                  | 30<br>Typ. | Fr 20<br>Typ. | Stopband<br>Typ. | Passband<br>Typ. |                    |
| Max.                               | Typ.                            |                               |            |               |                  |                  |                    |
| *DC-2750                           | 3150                            | 4000                          | 4150-6800  | 8400          | 20               | 1.2              | 7                  |

\* Not for use with DC voltage at input and output ports


## Outline Drawing



## Outline Dimensions (inch/mm)

| B     | D     | E    | wt    |
|-------|-------|------|-------|
| .410  | 1.43  | .312 | grams |
| 10.41 | 36.32 | 7.92 | 10.0  |

## typical frequency response




## electrical schematic



## Typical Performance Data at 25°C

| Frequency<br>(MHz) | Insertion Loss<br>(dB) | VSWR<br>(:1) |
|--------------------|------------------------|--------------|
| 50                 | 0.08                   | 1.03         |
| 200                | 0.13                   | 1.02         |
| 500                | 0.18                   | 1.02         |
| 1000               | 0.28                   | 1.10         |
| 2000               | 0.54                   | 1.32         |
| 2750               | 0.79                   | 1.16         |
| 3150               | 1.83                   | 1.97         |
| 4000               | 33.61                  | 23.18        |
| 4200               | 53.15                  | 27.59        |
| 5150               | 39.36                  | 40.41        |
| 6000               | 55.34                  | 45.72        |
| 6800               | 32.46                  | 46.96        |
| 7500               | 26.91                  | 46.96        |
| 8400               | 22.87                  | 46.96        |
| 9900               | 18.62                  | 29.96        |



## Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E  
M151777  
VLF-2750+  
EDR-6783/4  
AD/TD/CP/AM  
200522  
Page 1 of 1

# Coaxial Low Pass Filter

VLF-2750+

## Typical Performance Data

| FREQ.<br>(MHz) | INSERTION LOSS<br>(dB) |          |           | INPUT RETURN LOSS<br>(dB) |          |           | OUTPUT RETURNLOSS<br>(dB) |          |           |
|----------------|------------------------|----------|-----------|---------------------------|----------|-----------|---------------------------|----------|-----------|
|                | @ -55° C               | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C | @ -55° C                  | @ +25° C | @ +100° C |
| 50             | 0.06                   | 0.08     | 0.07      | 44.14                     | 38.02    | 34.78     | 44.89                     | 38.48    | 35.07     |
| 200            | 0.10                   | 0.13     | 0.14      | 35.82                     | 39.27    | 38.86     | 34.96                     | 38.30    | 38.59     |
| 500            | 0.12                   | 0.18     | 0.21      | 44.67                     | 39.75    | 33.22     | 36.88                     | 34.25    | 30.76     |
| 1000           | 0.20                   | 0.28     | 0.32      | 26.73                     | 26.24    | 26.24     | 24.71                     | 24.37    | 24.04     |
| 1500           | 0.31                   | 0.41     | 0.48      | 19.61                     | 19.39    | 19.42     | 19.56                     | 19.21    | 19.05     |
| 2000           | 0.42                   | 0.54     | 0.63      | 17.07                     | 17.31    | 17.53     | 17.35                     | 17.39    | 17.41     |
| 2500           | 0.52                   | 0.66     | 0.77      | 19.63                     | 20.57    | 21.28     | 18.93                     | 20.01    | 20.77     |
| 2700           | 0.58                   | 0.74     | 0.88      | 23.33                     | 23.02    | 22.76     | 20.97                     | 21.38    | 21.71     |
| 2750           | 0.61                   | 0.79     | 0.93      | 23.55                     | 22.68    | 22.09     | 21.03                     | 21.15    | 21.28     |
| 2900           | 0.76                   | 0.96     | 1.14      | 19.50                     | 18.62    | 17.90     | 18.32                     | 18.10    | 17.85     |
| 3150           | 1.47                   | 1.83     | 2.15      | 10.42                     | 9.70     | 9.29      | 10.66                     | 10.14    | 9.81      |
| 3260           | 2.43                   | 2.92     | 3.39      | 6.79                      | 6.37     | 6.09      | 7.16                      | 6.85     | 6.59      |
| 3370           | 4.29                   | 4.97     | 5.63      | 3.98                      | 3.83     | 3.72      | 4.35                      | 4.26     | 4.13      |
| 3540           | 9.26                   | 10.21    | 11.14     | 1.63                      | 1.71     | 1.79      | 1.96                      | 2.05     | 2.09      |
| 3660           | 14.08                  | 15.18    | 16.23     | 1.05                      | 1.18     | 1.30      | 1.29                      | 1.43     | 1.52      |
| 3775           | 19.25                  | 20.54    | 21.77     | 0.74                      | 0.91     | 1.04      | 0.96                      | 1.13     | 1.26      |
| 3850           | 23.03                  | 24.45    | 25.81     | 0.68                      | 0.84     | 0.97      | 0.84                      | 1.02     | 1.16      |
| 3900           | 25.76                  | 27.28    | 28.74     | 0.68                      | 0.83     | 0.96      | 0.84                      | 1.01     | 1.15      |
| 3950           | 28.62                  | 30.26    | 31.85     | 0.58                      | 0.74     | 0.88      | 0.76                      | 0.95     | 1.11      |
| 4000           | 31.81                  | 33.61    | 35.34     | 0.60                      | 0.75     | 0.88      | 0.74                      | 0.93     | 1.09      |
| 4070           | 36.87                  | 38.96    | 41.01     | 0.57                      | 0.74     | 0.85      | 0.73                      | 0.93     | 1.09      |
| 4150           | 43.18                  | 45.33    | 46.81     | 0.57                      | 0.72     | 0.84      | 0.74                      | 0.94     | 1.16      |
| 4200           | 49.82                  | 53.15    | 56.52     | 0.46                      | 0.63     | 0.76      | 0.68                      | 0.87     | 1.06      |
| 4700           | 45.73                  | 44.52    | 43.70     | 0.39                      | 0.55     | 0.66      | 0.69                      | 0.91     | 1.11      |
| 4900           | 40.77                  | 40.27    | 40.02     | 0.31                      | 0.48     | 0.58      | 0.65                      | 0.86     | 1.05      |
| 5150           | 39.34                  | 39.36    | 39.34     | 0.28                      | 0.43     | 0.55      | 0.62                      | 0.80     | 0.95      |
| 6000           | 56.41                  | 55.34    | 52.90     | 0.31                      | 0.38     | 0.54      | 0.43                      | 0.60     | 0.71      |
| 6800           | 32.77                  | 32.46    | 32.16     | 0.42                      | 0.37     | 0.58      | 0.25                      | 0.47     | 0.64      |
| 7500           | 27.00                  | 26.91    | 26.86     | 0.23                      | 0.37     | 0.57      | 0.20                      | 0.44     | 0.66      |
| 8400           | 22.70                  | 22.87    | 23.00     | 0.22                      | 0.37     | 0.51      | 0.23                      | 0.45     | 0.69      |
| 9900           | 18.86                  | 18.62    | 18.58     | 0.08                      | 0.58     | 0.78      | 0.32                      | 0.53     | 0.67      |
| 11000          | 16.78                  | 16.74    | 16.58     | 0.34                      | 0.55     | 0.71      | 0.35                      | 0.61     | 0.77      |
| 12100          | 14.41                  | 14.49    | 14.51     | 0.38                      | 0.65     | 0.89      | 0.33                      | 0.52     | 0.69      |
| 13000          | 12.55                  | 12.14    | 11.98     | 0.51                      | 0.94     | 1.41      | 0.53                      | 0.82     | 1.09      |
| 14000          | 11.58                  | 11.98    | 12.17     | 1.27                      | 1.44     | 1.80      | 0.91                      | 1.15     | 1.43      |
| 15200          | 9.32                   | 9.98     | 10.83     | 1.93                      | 1.77     | 1.76      | 1.91                      | 1.93     | 2.15      |
| 16300          | 14.72                  | 15.51    | 16.12     | 0.63                      | 0.91     | 1.15      | 0.73                      | 0.90     | 1.08      |
| 17400          | 19.48                  | 19.98    | 20.33     | 0.59                      | 0.86     | 1.47      | 0.38                      | 0.76     | 0.89      |
| 18500          | 21.76                  | 19.66    | 19.77     | 5.81                      | 3.65     | 2.51      | 0.25                      | 0.67     | 1.00      |
| 19400          | 18.32                  | 18.56    | 19.10     | 0.63                      | 1.09     | 1.48      | 0.46                      | 0.94     | 1.44      |
| 20000          | 16.39                  | 16.35    | 16.27     | 1.07                      | 1.90     | 2.88      | 0.98                      | 1.69     | 2.66      |

REV. X1  
VLF-2750+  
080720  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




# Coaxial Low Pass Filter


## Typical Performance Curves

VLF-2750+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X1  
VLF-2750+  
080720  
Page 1 of 1

**Mini-Circuits®**

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



### Outline Dimensions



| CASE #. | A  | B               | C  | D               | E              | WT GRAMS |
|---------|----|-----------------|----|-----------------|----------------|----------|
| FF704   | -- | .410<br>(10.41) | -- | 1.43<br>(36.32) | .312<br>(7.92) | 10.0     |

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

#### Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                              | Reference/Spec                       |
|----------------------------|----------------------------------------------------------------------------------------|--------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                   | Individual Model Data Sheet          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                                  | Individual Model Data Sheet          |
| Barometric Pressure        | 100,000 Feet                                                                           | MIL-STD-202, Method 105, Condition D |
| Humidity                   | 90% RH, 65°C<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103              |
| Thermal Shock              | -65° to 125°C, 5 cycles                                                                | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)    | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock           | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)                          | MIL-STD-202, Method 213, Condition I |