

Coaxial Low Pass Filter

50Ω *DC to 575 MHz

VLF-575+ VLF-575



Generic photo used for illustration purposes only

CASE STYLE: FF704

| | |
|------------|----------|
| Connectors | Model |
| SMA | VLF-575+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

| | |
|----------------------------|-------------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| RF Power Input* | 8.5W max. at 25°C |
| DC Current Input to Output | 0.5A max. at 25°C |

* Passband rating, derate linearly to 3.5W at 100°C ambient. Permanent damage may occur if any of these limits are exceeded.

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 8.5W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications


- harmonic rejection
- transmitters/receivers
- lab use

Electrical Specifications at 25°C

| PASSBAND (MHz) (loss < 1.2 dB) | f _{co} , MHz Nom. (loss 3 dB) | STOP BAND (MHz) (loss, dB) | | | VSWR (:1) | | NO. OF SECTIONS |
|-----------------------------------|----------------------------------------------|-------------------------------|------------|---------------|------------------|------------------|-----------------|
| | | f 20 Min. | 40 Typ. | fr 20 Typ. | Stopband Typ. | Passband Typ. | |
| Max. | Typ. | | | | | | |
| *DC-575 | 770 | 900 | 1050-3200 | 5500 | 20 | 1.2 | 7 |

* Not for use with DC voltage at input and output ports


Outline Drawing




Outline Dimensions (inch/mm)

| B | D | E | wt |
|-------|-------|------|-------|
| .410 | 1.43 | .312 | grams |
| 10.41 | 36.32 | 7.92 | 10.0 |

typical frequency response





electrical schematic



Typical Performance Data at 25°C

| Frequency (MHz) | Insertion Loss (dB) | VSWR (:1) |
|-----------------|---------------------|-----------|
| 1 | 0.05 | 1.01 |
| 100 | 0.21 | 1.03 |
| 350 | 0.47 | 1.11 |
| 575 | 0.84 | 1.06 |
| 700 | 1.63 | 1.53 |
| 770 | 3.23 | 2.25 |
| 810 | 6.80 | 4.13 |
| 840 | 13.17 | 7.73 |
| 870 | 22.75 | 11.61 |
| 900 | 35.71 | 14.26 |
| 1050 | 50.67 | 20.95 |
| 2000 | 59.09 | 45.72 |
| 3200 | 40.27 | 56.04 |
| 4500 | 31.35 | 46.96 |
| 5500 | 22.64 | 42.38 |



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. J
M151107
VLF-575
EDR-6588/6
RVN/AD/CP/AM
200522
Page 1 of 1

Coaxial Low Pass Filter

VLF-575

Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS (dB) | | | INPUT RETURN LOSS (dB) | | | OUTPUT RETURN LOSS (dB) | | |
|----------------|------------------------|----------|-----------|---------------------------|----------|-----------|----------------------------|----------|-----------|
| | @ -55° C | @ +25° C | @ +100° C | @ -55° C | @ +25° C | @ +100° C | @ -55° C | @ +25° C | @ +100° C |
| 50 | 0.12 | 0.15 | 0.17 | 38.54 | 35.73 | 34.72 | 37.70 | 35.28 | 34.27 |
| 60 | 0.12 | 0.14 | 0.16 | 39.41 | 36.87 | 35.19 | 36.04 | 33.90 | 33.04 |
| 70 | 0.11 | 0.16 | 0.18 | 38.88 | 36.23 | 34.79 | 35.84 | 33.72 | 32.91 |
| 75 | 0.15 | 0.17 | 0.20 | 38.80 | 36.20 | 35.03 | 35.39 | 33.66 | 32.85 |
| 80 | 0.17 | 0.20 | 0.22 | 38.35 | 35.97 | 34.74 | 34.40 | 32.90 | 32.04 |
| 85 | 0.18 | 0.22 | 0.25 | 38.81 | 36.85 | 35.31 | 34.61 | 33.00 | 32.28 |
| 90 | 0.13 | 0.18 | 0.20 | 39.59 | 37.44 | 36.03 | 34.06 | 32.59 | 31.97 |
| 95 | 0.16 | 0.23 | 0.26 | 39.82 | 37.51 | 36.15 | 33.78 | 32.38 | 31.78 |
| 100 | 0.17 | 0.20 | 0.22 | 39.31 | 37.02 | 35.69 | 33.25 | 32.04 | 31.47 |
| 150 | 0.19 | 0.24 | 0.26 | 42.91 | 39.18 | 36.92 | 30.39 | 29.40 | 28.95 |
| 200 | 0.24 | 0.30 | 0.34 | 43.54 | 37.40 | 33.69 | 27.91 | 26.84 | 26.22 |
| 250 | 0.24 | 0.31 | 0.38 | 35.32 | 32.45 | 29.70 | 25.94 | 24.86 | 24.12 |
| 300 | 0.32 | 0.42 | 0.46 | 30.26 | 28.88 | 27.07 | 24.44 | 23.42 | 22.64 |
| 350 | 0.36 | 0.46 | 0.53 | 26.57 | 25.95 | 24.93 | 22.76 | 22.03 | 21.35 |
| 400 | 0.44 | 0.55 | 0.64 | 24.41 | 24.13 | 23.66 | 22.08 | 21.56 | 21.01 |
| 450 | 0.48 | 0.60 | 0.68 | 23.35 | 23.30 | 23.21 | 21.92 | 21.63 | 21.30 |
| 500 | 0.52 | 0.68 | 0.78 | 24.51 | 24.71 | 25.05 | 22.64 | 22.55 | 22.45 |
| 575 | 0.66 | 0.84 | 0.98 | 28.99 | 30.42 | 31.58 | 25.99 | 25.93 | 25.56 |
| 600 | 0.74 | 0.93 | 1.06 | 28.85 | 28.74 | 28.09 | 25.57 | 24.86 | 24.04 |
| 650 | 0.94 | 1.19 | 1.40 | 20.35 | 19.40 | 18.54 | 19.93 | 19.06 | 18.31 |
| 700 | 1.36 | 1.71 | 1.99 | 14.00 | 13.39 | 12.80 | 14.71 | 14.37 | 14.09 |
| 770 | 2.85 | 3.57 | 4.26 | 8.14 | 7.63 | 7.16 | 12.20 | 13.12 | 14.10 |
| 810 | 6.06 | 7.66 | 9.28 | 4.17 | 3.77 | 3.44 | 8.37 | 8.18 | 7.75 |
| 840 | 12.33 | 14.80 | 17.03 | 2.01 | 2.01 | 1.98 | 4.22 | 4.26 | 4.22 |
| 870 | 21.93 | 25.04 | 27.84 | 1.19 | 1.35 | 1.44 | 2.49 | 2.70 | 2.82 |
| 900 | 35.91 | 37.89 | 37.87 | 0.94 | 1.10 | 1.21 | 1.85 | 2.08 | 2.24 |
| 950 | 36.04 | 36.30 | 36.65 | 0.76 | 0.92 | 1.04 | 1.39 | 1.64 | 1.81 |
| 1000 | 39.69 | 41.05 | 42.37 | 0.65 | 0.79 | 0.89 | 1.17 | 1.40 | 1.57 |
| 1050 | 51.55 | 52.33 | 51.33 | 0.57 | 0.71 | 0.82 | 1.04 | 1.27 | 1.43 |
| 1500 | 46.70 | 47.36 | 48.03 | 0.29 | 0.42 | 0.53 | 0.51 | 0.66 | 0.76 |
| 2000 | 58.02 | 57.66 | 57.22 | 0.20 | 0.32 | 0.41 | 0.27 | 0.37 | 0.44 |
| 2500 | 49.34 | 49.13 | 48.90 | 0.21 | 0.31 | 0.39 | 0.21 | 0.29 | 0.34 |
| 3000 | 41.61 | 41.38 | 41.22 | 0.18 | 0.27 | 0.35 | 0.16 | 0.26 | 0.31 |
| 3200 | 39.24 | 39.06 | 38.89 | 0.19 | 0.29 | 0.37 | 0.15 | 0.26 | 0.31 |
| 3500 | 36.15 | 36.07 | 35.91 | 0.17 | 0.28 | 0.38 | 0.13 | 0.22 | 0.29 |
| 4000 | 32.41 | 32.38 | 32.33 | 0.16 | 0.29 | 0.38 | 0.10 | 0.22 | 0.29 |
| 4500 | 30.28 | 30.42 | 30.56 | 0.12 | 0.29 | 0.43 | 0.11 | 0.27 | 0.37 |
| 5000 | 20.33 | 21.58 | 22.33 | 0.44 | 0.50 | 0.60 | 0.32 | 0.40 | 0.51 |
| 5500 | 22.36 | 22.52 | 22.63 | 0.23 | 0.40 | 0.59 | 0.15 | 0.32 | 0.49 |
| 6000 | 22.26 | 21.96 | 21.98 | 0.37 | 0.49 | 0.70 | 0.24 | 0.37 | 0.55 |
| 6500 | 21.45 | 21.63 | 21.60 | 0.28 | 0.55 | 0.77 | 0.17 | 0.37 | 0.58 |
| 7000 | 19.97 | 20.04 | 20.10 | 0.23 | 0.43 | 0.65 | 0.18 | 0.38 | 0.56 |
| 7500 | 18.87 | 18.92 | 18.98 | 0.23 | 0.43 | 0.62 | 0.21 | 0.39 | 0.55 |
| 8000 | 17.97 | 18.12 | 18.23 | 0.32 | 0.53 | 0.72 | 0.22 | 0.41 | 0.53 |
| 8500 | 17.05 | 17.24 | 17.50 | 0.34 | 0.52 | 0.65 | 0.25 | 0.43 | 0.53 |
| 9000 | 16.34 | 16.61 | 16.86 | 0.36 | 0.56 | 0.69 | 0.31 | 0.52 | 0.64 |
| 9500 | 15.88 | 16.02 | 16.16 | 0.41 | 0.72 | 0.94 | 0.34 | 0.60 | 0.77 |
| 10000 | 15.62 | 15.81 | 16.02 | 0.67 | 1.08 | 1.46 | 0.63 | 1.11 | 1.37 |
| 10500 | 15.69 | 16.24 | 16.63 | 1.42 | 1.92 | 2.45 | 0.63 | 1.00 | 1.33 |
| 11000 | 17.14 | 18.25 | 19.36 | 2.39 | 3.09 | 3.75 | 0.84 | 1.38 | 1.92 |
| 11500 | 23.23 | 25.83 | 28.38 | 2.93 | 3.83 | 4.40 | 1.93 | 3.02 | 4.24 |
| 12000 | 32.16 | 29.50 | 27.43 | 2.35 | 2.85 | 3.20 | 8.66 | 10.80 | 10.86 |
| 12500 | 20.85 | 20.08 | 19.75 | 1.97 | 2.17 | 2.42 | 3.04 | 3.08 | 3.22 |
| 13000 | 16.32 | 17.54 | 19.62 | 1.79 | 2.31 | 2.64 | 1.74 | 2.21 | 2.30 |

REV. X2
VLF-575
101128
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE




Case Style

FF

FF704

Outline Dimensions



| CASE #. | A | B | C | D | E | WT GRAMS |
|---------|----|-----------------|----|-----------------|----------------|----------|
| FF704 | -- | .410 (10.41) | -- | 1.43 (36.32) | .312 (7.92) | 10.0 |

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|----------------------------------------------------------------------------------------|--------------------------------------|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Barometric Pressure | 100,000 Feet | MIL-STD-202, Method 105, Condition D |
| Humidity | 90% RH, 65°C Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103 |
| Thermal Shock | -65° to 125°C, 5 cycles | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18) | MIL-STD-202, Method 213, Condition I |