

Coaxial Low Pass Filter

50Ω

*DC to 6000 MHz

VLF-6000+
VLF-6000



Generic photo used for illustration purposes only

CASE STYLE: FF704

Connectors	Model
SMA	VLF-6000(+)

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	9W max. at 25°C
DC Current Input to Output	0.5A max. at 25°C

* Passband rating, derate linearly to 3W at 100°C ambient.
Permanent damage may occur if any of these limits are exceeded.

Features

- rugged uni-body construction, small size
- 7 sections
- excellent power handling, 9W
- temperature stable
- low cost
- protected by U.S. Patent 6,943,646

Applications


- harmonic rejection
- transmitters/receivers
- lab use

Electrical Specifications at 25°C

PASSBAND (MHz)	fco, MHz Nom.	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
(loss < 1.2 dB)	(loss 3 dB)	F 20	30	Fr 20	Stopband	Passband	
Max.	Typ.	Min.	Typ.	Typ.	Typ.	Typ.	
*DC-6000	6800	8500	8700-10500	18000	20	1.3	7

* Not for use with DC voltage at input and output ports


Outline Drawing




Outline Dimensions (inch/mm)

B	D	E	wt
.410	1.43	.312	grams
10.41	36.32	7.92	10.0

typical frequency response





electrical schematic



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
50.00	0.10	1.01
100.00	0.02	1.01
1000.00	0.10	1.03
3000.00	0.19	1.07
5000.00	0.57	1.37
6000.00	0.75	1.24
6800.00	2.80	3.31
8000.00	21.90	15.96
8720.00	44.10	17.22
10000.00	58.33	19.76
12000.00	30.77	15.26
13700.00	27.55	1.37
15000.00	27.44	8.72
18000.00	21.31	10.02
20000.00	26.23	7.44



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. K
M151107
VLF-6000
EDR-6706
RVN/AD/CP/AM
200522
Page 1 of 1

Coaxial Low Pass Filter

VLF-6000+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURN LOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
50	0.02	0.03	0.04	45.83	42.21	40.25	45.67	41.68	40.50
100	0.02	0.03	0.05	45.59	42.38	39.84	46.33	41.39	38.75
200	0.04	0.05	0.07	39.92	40.39	40.38	40.93	41.19	41.58
300	0.04	0.07	0.09	37.10	38.50	39.64	36.92	39.17	43.64
400	0.05	0.09	0.11	35.05	36.34	37.74	36.62	38.26	42.73
500	0.06	0.09	0.12	33.51	35.05	37.12	35.26	36.97	40.22
600	0.04	0.09	0.12	33.77	35.40	38.01	33.82	35.79	39.06
700	0.06	0.10	0.14	33.56	34.91	36.91	33.64	36.04	40.19
800	0.07	0.11	0.14	34.01	35.70	37.40	34.08	36.96	42.30
900	0.06	0.13	0.19	33.30	35.19	36.98	33.90	36.72	42.20
1000	0.06	0.14	0.19	33.69	35.89	38.16	34.48	37.67	43.78
1200	0.08	0.15	0.19	35.38	37.92	39.91	37.41	40.83	45.42
1400	0.08	0.17	0.21	37.67	41.57	42.83	42.36	49.90	43.23
1500	0.08	0.18	0.22	38.29	40.52	39.72	44.85	48.92	41.74
2000	0.10	0.21	0.27	36.57	33.32	33.05	35.11	32.20	31.37
2200	0.11	0.22	0.31	30.95	29.44	29.72	31.00	29.46	29.10
2500	0.09	0.22	0.31	27.50	26.29	26.68	27.12	25.72	25.51
3000	0.17	0.31	0.43	23.11	22.91	23.29	23.28	22.55	22.40
3200	0.19	0.31	0.43	22.38	22.32	22.45	22.03	21.47	21.16
3500	0.20	0.36	0.46	20.83	21.18	21.54	20.57	20.45	20.33
4000	0.24	0.41	0.53	20.18	20.20	20.11	19.79	19.60	19.27
4200	0.24	0.43	0.57	20.37	20.20	19.86	19.84	19.56	19.16
4500	0.25	0.45	0.61	20.90	20.30	19.30	20.38	19.83	19.09
5000	0.29	0.52	0.67	21.42	20.67	19.38	21.29	20.76	20.06
5200	0.35	0.56	0.74	21.40	20.95	19.79	21.47	21.23	20.74
5500	0.36	0.60	0.79	20.82	20.97	20.38	21.48	21.77	21.47
6000	0.52	0.79	1.01	18.77	18.51	18.00	20.68	20.00	19.31
6200	0.64	0.94	1.19	16.45	15.78	15.18	18.47	17.40	16.80
6500	1.05	1.42	1.75	11.45	10.98	10.38	12.65	11.97	11.58
6800	2.20	2.70	3.22	6.42	6.25	5.91	7.15	6.83	6.63
7000	3.74	4.38	5.05	3.95	3.93	3.73	4.55	4.32	4.20
7200	5.95	6.80	7.65	2.31	2.40	2.37	2.72	2.64	2.62
7500	10.47	11.56	12.60	1.12	1.32	1.44	1.33	1.41	1.45
8000	19.84	21.13	22.38	0.50	0.81	1.06	0.58	0.75	0.83
8200	24.13	25.60	26.90	0.43	0.76	1.07	0.45	0.63	0.73
8500	31.73	33.76	35.41	0.39	0.74	1.06	0.37	0.57	0.70
8720	39.22	42.70	45.73	0.40	0.73	1.06	0.33	0.52	0.68
9000	53.55	54.43	50.55	0.37	0.71	1.04	0.28	0.51	0.70
9200	45.41	46.17	45.13	0.37	0.67	1.00	0.26	0.50	0.70
9500	41.07	44.11	44.07	0.35	0.67	0.94	0.27	0.51	0.75
10000	39.19	45.38	46.80	0.29	0.60	0.85	0.30	0.57	0.84
10200	39.72	44.52	46.33	0.25	0.58	0.82	0.30	0.62	0.89
10500	43.18	44.29	44.67	0.19	0.56	0.79	0.26	0.66	0.95
10800	47.91	45.12	43.82	0.15	0.51	0.77	0.21	0.56	0.90
11000	45.48	42.74	41.97	0.15	0.52	0.75	0.21	0.53	0.86
12000	32.68	32.75	32.66	0.16	0.49	0.68	0.15	0.42	0.66
13000	26.97	27.76	27.95	0.38	0.83	1.17	0.13	0.40	0.58
13700	25.84	26.01	27.60	3.93	8.93	13.00	0.22	0.42	0.58
14000	30.91	29.68	29.58	7.03	4.20	3.32	0.03	0.30	0.47
15000	28.55	28.62	28.09	0.05	0.60	1.08	0.03	0.30	0.45
16000	24.87	24.92	24.72	0.09	0.58	1.09	0.05	0.32	0.51
17000	21.63	22.01	22.21	0.13	0.63	1.16	0.14	0.43	0.69
18000	20.57	21.19	21.40	0.41	1.01	1.46	0.26	0.68	1.07
19000	18.28	19.21	19.92	0.67	1.09	1.35	0.42	0.73	1.09

REV. X2

VLF-6000+

101129

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-6000+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE




OUTPUT RETURN LOSS vs. TEMPERATURE



REV. X2
VLF-6000+
101129
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I