

Low Pass Filter

50Ω

*DC to 6400 MHz

VLF-6400+

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power Input*	8W at 25°C
DC Current Input to Output	0.5A max. at 25°C

*Passband rating, derate linearly to 3 W at 100°C ambient
Permanent damage may occur if any of these limits are exceeded.

Features

- Rugged uni-body construction, small size
- 7 sections
- Excellent power handling, 8W
- Temperature stable
- Low cost
- Protected by US patent 6,943,646

Applications

- Harmonic rejection
- Transmitters/receivers
- Lab use




CASE STYLE: FF704

Connectors	Model
SMA	VLF-6400+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Outline Drawing




Low Pass Filter Electrical Specifications (T_{AMB} = 25°C)


PASSBAND (MHz) (loss < 2 dB) Max.	fco, MHz Nom. (loss 3 dB) Typ.	STOP BAND (MHz) (loss, dB)			VSWR (:1)		NO. OF SECTIONS
		F 20 Min.	30 Typ.	FR 20 Typ.	Stopband Typ.	Passband Typ.	
*DC - 6400	7200	8300	7770 - 10200	12500	17	1.2	7

* Not for use with DC voltage at input and output ports

Typical frequency response



Electrical schematic




Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
40	0.06	1.04
500	0.08	1.03
2000	0.22	1.17
4000	0.39	1.28
5500	0.48	1.11
6400	0.79	1.33
7000	1.41	1.25
7200	2.73	1.92
7350	5.61	3.58
7500	11.17	6.94
7680	22.01	11.77
7770	30.63	13.81
8300	26.96	20.70
10200	34.63	31.03
11000	39.63	40.41
12500	37.94	69.49
15000	26.38	57.91


Outline Dimensions (inch mm)

B	D	E	wt.
.410	1.43	.312	grams
10.41	36.32	7.92	10

VLF-6400+
INSERTION LOSS



VLF-6400+
VSWR



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial Low Pass Filter

VLF-6400+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)			INPUT RETURN LOSS (dB)			OUTPUT RETURNLOSS (dB)		
	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C	@ -55° C	@ +25° C	@ +100° C
40	0.05	0.09	0.09	43.58	45.28	40.91	44.25	46.93	41.93
100	0.00	0.01	0.03	41.28	48.47	40.84	39.91	45.79	40.47
200	0.00	0.01	0.03	44.39	43.70	41.11	41.92	41.48	40.03
400	0.03	0.05	0.08	41.27	36.99	30.00	43.27	37.21	29.92
600	0.04	0.07	0.10	33.78	32.77	30.07	36.69	33.69	30.43
800	0.05	0.09	0.13	30.45	29.48	28.09	31.24	29.93	28.24
1000	0.06	0.10	0.15	28.26	27.47	27.12	29.33	27.92	27.56
1500	0.07	0.12	0.17	25.67	25.06	24.85	25.67	25.21	25.36
2000	0.11	0.17	0.23	21.75	21.65	21.41	21.92	21.84	21.74
2500	0.16	0.22	0.28	19.62	19.65	20.21	19.62	19.77	20.45
3000	0.18	0.25	0.33	18.51	18.76	19.74	18.46	18.74	19.69
3500	0.24	0.32	0.41	17.22	17.45	17.78	17.40	17.75	18.09
4000	0.25	0.36	0.49	17.97	17.30	16.41	17.96	17.51	16.74
4500	0.22	0.33	0.47	20.44	19.55	18.68	19.96	19.43	18.72
5000	0.24	0.36	0.49	23.83	23.88	24.26	23.56	23.60	23.51
5200	0.24	0.36	0.49	26.90	27.96	27.68	25.66	27.23	26.17
6000	0.35	0.51	0.68	24.49	21.22	19.95	24.69	21.92	21.09
6400	0.47	0.66	0.88	19.03	17.60	16.63	19.02	17.71	16.78
6750	0.69	0.87	1.11	15.61	16.43	16.28	16.16	17.17	16.90
7150	1.49	1.88	2.34	10.92	10.45	9.80	14.43	13.38	12.52
7200	1.76	2.22	2.76	9.49	8.98	8.40	12.39	11.44	10.69
7300	2.81	3.50	4.26	6.49	6.11	5.75	8.18	7.65	7.21
7450	6.13	7.15	8.33	2.90	2.92	2.94	3.71	3.72	3.67
7550	9.93	11.14	12.57	1.61	1.77	1.94	2.20	2.33	2.40
7630	13.76	15.27	17.00	1.05	1.27	1.50	1.56	1.71	1.81
7700	17.89	19.83	21.94	0.79	1.01	1.26	1.24	1.39	1.51
7740	20.67	22.88	25.28	0.69	0.90	1.13	1.07	1.19	1.29
7770	23.18	25.73	28.40	0.62	0.83	1.06	1.05	1.18	1.29
7790	24.90	27.70	30.46	0.58	0.79	1.02	0.99	1.11	1.22
7850	31.53	33.79	33.74	0.47	0.68	0.91	0.90	1.02	1.11
8000	29.23	28.32	27.65	0.39	0.53	0.71	0.82	0.87	0.96
8300	25.89	26.53	26.94	0.28	0.34	0.46	0.70	0.73	0.83
8850	36.19	37.49	38.91	0.26	0.24	0.33	0.52	0.70	0.90
9500	37.80	37.13	36.87	0.32	0.33	0.45	0.39	0.68	1.00
10200	34.24	34.13	34.13	0.32	0.41	0.63	0.19	0.51	0.91
11000	41.36	40.91	41.77	0.34	0.48	0.67	0.10	0.60	0.88
12000	42.33	40.32	39.58	0.07	0.36	0.54	0.07	0.02	0.18
12500	36.20	38.65	38.94	0.02	0.34	0.53	0.01	0.03	0.19
14000	30.54	28.80	28.26	0.16	0.07	0.35	0.25	0.18	0.25
16000	22.30	23.03	22.93	0.02	0.05	0.25	0.24	0.65	0.94
18000	20.11	18.02	18.96	0.22	0.11	0.41	0.36	0.52	1.30
20000	15.06	14.49	13.96	1.02	0.61	0.92	0.41	0.04	0.74

REV. X1
VLF-6400+
071009
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Coaxial Low Pass Filter


Typical Performance Curves

VLF-6400+


INSERTION LOSS vs. TEMPERATURE



INPUT RETURN LOSS vs. TEMPERATURE



OUTPUT RETURN LOSS vs. TEMPERATURE



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



REV. X1
VLF-6400+
071009
Page 1 of 1

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	--	.410 (10.41)	--	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I