Coaxial

Low Pass Filter

VLFG-1200+

50Ω DC to 1200 MHz

Generic photo used for illustration purposes only

CASE STYLE: FF704

The Big Deal

- Excellent power handling, 5.5W
- Temperature stable
- Rugged unibody construction
- Good rejection, 50 dB typical

Product Overview

VLFG-1200+ is a 50Ω low pass filter built in rugged unibody construction. Covering DC-1200 MHz bandwidth, these units offer good matching within the passband and good rejection in stopband. VLFG-1200+ offer low insertion loss, and excellent power handling capability. It handles up to 5.5W RF input power and provides a wide operating temperature range from -55°C to 125°C.

Key Features

Feature	Advantages
Low passband insertion loss	Suitable for high performance application.
5.5W Power handling	Supports a range of system power requirements.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial

Low Pass Filter

VLFG-1200+

50Ω DC to 1200 MHz

Generic photo used for illustration purposes only
CASE STYLE: FF704

+RoHS Compliant
The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Features

- Low loss, 1.0 dB typical
- Good rejection 50 dB typical
- Excellent power handling, 5.5W
- Temperature stable
- Connectorized package
- Rugged unibody construction

Applications

- Military radar applications
- Test and measurement
- Telecommunication and broadband wireless applications

Functional Schematic



Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC - 1200	—	1.0	1.8	dB
	Freq. Cut-Off	F2*	1470	—	3.0	—	dB
	Return Loss	DC-F1	DC - 1200	—	24	—	dB
Stop Band	Rejection Loss	F3-F4	1865 - 2000	20	50	—	dB
		F4-F5	2000 - 3700	40	50	—	dB
		F5-F6	3700 - 7000	28	40	—	dB
		F6-F7	7000 - 10000	—	30	—	dB

In Application where DC voltage is present at either input or output port, DC blocks are required.
* Typically, a ±5% frequency deviation from the stated value may occur on a unit-to-unit basis.

Maximum Ratings	
Operating Temperature	-55°C to 125°C
Storage Temperature	-55°C to 125°C
RF Power Input*	5.5W max.@25°C

*Passband rating, derate linearly to 1W at 125°C ambient
Permanent damage may occur if any of these limits are exceeded.

Typical Frequency Response



Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)
10	0.07	42.12
100	0.14	36.51
400	0.30	41.00
600	0.40	29.78
1000	0.67	26.07
1200	0.94	31.75
1300	1.23	21.58
1470	3.02	8.01
1650	13.39	1.87
1700	21.50	1.28
1750	31.72	1.03
1865	58.83	0.78
1900	59.68	0.73
2000	57.95	0.64
3700	55.26	0.39
5000	50.52	0.41
7000	51.55	0.45
8000	40.70	0.46
9000	35.93	0.46
10000	32.14	0.58







Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions (inch / mm)

B	D	E	wt.
.410	**1.43**	**.312**	grams
10.41	36.32	7.92	10

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Low Pass Filter VLFG-1200+

Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C	@-55°C	@+25°C	@+100°C
10	0.05	0.07	0.08	43.46	42.12	39.40	43.11	42.16	39.77
60	0.09	0.11	0.12	41.21	37.82	34.92	39.84	36.71	33.94
100	0.11	0.14	0.15	38.56	36.51	34.53	35.92	34.36	32.58
140	0.14	0.16	0.18	34.95	36.27	36.11	32.02	32.86	32.76
180	0.16	0.18	0.20	31.95	36.51	37.25	29.12	31.37	32.23
200	0.17	0.20	0.21	30.97	36.84	36.95	28.13	30.76	31.74
240	0.19	0.22	0.24	30.22	38.20	35.98	27.11	29.71	30.46
300	0.21	0.25	0.28	31.77	40.69	36.44	27.07	28.18	28.70
400	0.24	0.30	0.33	40.14	41.00	42.31	27.52	26.39	26.41
500	0.27	0.35	0.39	34.11	34.06	34.74	26.07	25.12	24.81
800	0.42	0.52	0.59	25.75	25.77	25.47	25.01	24.70	23.78
1000	0.55	0.67	0.77	25.78	26.07	26.04	28.15	28.09	27.94
1100	0.64	0.78	0.90	27.53	28.30	28.11	29.88	30.85	31.15
1150	0.70	0.85	0.98	29.15	30.35	29.68	30.63	32.63	32.50
1200	0.77	0.94	1.08	32.10	31.75	30.28	32.45	33.34	32.30
1250	0.87	1.06	1.22	29.98	27.54	26.63	30.21	28.85	28.20
1300	1.01	1.23	1.41	23.21	21.58	21.13	23.84	22.78	22.54
1400	1.60	1.92	2.21	13.37	12.46	12.13	14.02	13.40	13.22
1450	2.21	2.63	3.02	9.75	9.13	8.82	10.51	10.16	10.03
1470	2.55	3.02	3.45	8.52	8.01	7.72	9.38	9.15	9.08
1500	3.19	3.74	4.27	6.92	6.54	6.29	8.01	7.99	8.04
1560	5.01	5.84	6.67	4.48	4.26	4.08	6.73	7.21	7.75
1600	6.93	8.19	9.43	3.24	3.05	2.92	7.14	7.94	8.80
1650	11.25	13.39	15.37	1.95	1.87	1.86	7.28	7.24	7.21
1700	18.61	21.50	24.03	1.20	1.28	1.36	4.60	4.39	4.28
1750	28.27	31.72	34.73	0.89	1.03	1.14	2.77	2.76	2.78
1800	40.23	44.67	48.55	0.73	0.89	1.02	1.88	1.96	2.02
1865	58.66	58.83	59.48	0.62	0.78	0.91	1.30	1.41	1.49
1900	58.37	59.68	61.44	0.57	0.73	0.86	1.11	1.23	1.31
2000	60.27	57.95	56.43	0.47	0.64	0.76	0.80	0.92	1.00
2100	53.31	52.96	52.75	0.41	0.57	0.68	0.65	0.75	0.82
2200	52.76	53.14	53.41	0.36	0.52	0.63	0.55	0.65	0.71
2300	54.98	55.65	56.44	0.32	0.48	0.58	0.48	0.58	0.64
2400	59.30	60.57	62.08	0.30	0.45	0.55	0.44	0.53	0.59
2500	67.34	69.96	73.78	0.27	0.43	0.52	0.41	0.49	0.55
2600	77.90	74.70	71.28	0.25	0.41	0.51	0.38	0.47	0.52
2700	67.34	66.46	65.75	0.24	0.40	0.50	0.36	0.44	0.49
2800	64.97	64.86	64.30	0.23	0.39	0.50	0.34	0.43	0.48
2900	64.78	65.41	65.11	0.22	0.38	0.50	0.32	0.41	0.46
3000	66.67	67.68	67.70	0.22	0.38	0.50	0.31	0.40	0.45
3700	55.75	55.26	55.07	0.21	0.39	0.50	0.24	0.34	0.41
4000	52.23	52.06	51.95	0.23	0.38	0.47	0.21	0.34	0.42
4500	50.09	50.01	49.93	0.25	0.39	0.46	0.20	0.34	0.46
5000	50.51	50.52	50.49	0.21	0.41	0.54	0.20	0.36	0.51
5500	52.88	53.46	53.84	0.17	0.43	0.67	0.22	0.40	0.58
6000	60.17	62.16	63.57	0.15	0.44	0.74	0.27	0.46	0.65
6500	60.54	59.29	58.71	0.17	0.45	0.74	0.33	0.52	0.73
7000	51.49	51.55	52.01	0.20	0.45	0.68	0.38	0.60	0.81
7500	43.40	43.49	43.74	0.21	0.45	0.62	0.42	0.65	0.85
8000	40.84	40.70	40.99	0.18	0.46	0.65	0.44	0.69	0.89
8100	40.50	40.61	40.55	0.16	0.46	0.66	0.47	0.70	0.87
8200	40.37	40.01	39.92	0.15	0.46	0.67	0.44	0.68	0.86
8300	39.75	39.42	39.32	0.14	0.46	0.69	0.43	0.67	0.86
8400	39.18	38.87	38.75	0.14	0.46	0.72	0.43	0.67	0.86
8500	38.66	38.35	38.22	0.13	0.46	0.73	0.43	0.67	0.85
8600	38.17	37.85	37.68	0.12	0.46	0.75	0.42	0.67	0.85
8700	37.68	37.35	37.19	0.11	0.45	0.76	0.41	0.66	0.84
8800	37.18	36.87	36.70	0.12	0.45	0.78	0.41	0.66	0.84
9000	36.22	35.93	35.78	0.12	0.46	0.80	0.39	0.64	0.82
10000	32.34	32.14	32.00	0.34	0.58	0.76	0.30	0.53	0.70

Typical Performance Data

FREQ. (MHz)	GROUP DELAY (nsec)		
	@-55°C	@+25˚C	@+100˚C
10	0.55	0.55	0.55
20	0.55	0.55	0.55
40	0.54	0.54	0.54
60	0.54	0.54	0.53
80	0.54	0.53	0.53
100	0.54	0.53	0.52
120	0.53	0.53	0.52
140	0.53	0.53	0.52
160	0.53	0.53	0.52
180	0.53	0.53	0.52
200	0.53	0.53	0.52
220	0.53	0.53	0.52
240	0.53	0.53	0.52
260	0.54	0.53	0.52
280	0.54	0.53	0.52
300	0.54	0.53	0.53
320	0.54	0.53	0.53
340	0.54	0.53	0.53
360	0.54	0.54	0.53
380	0.55	0.54	0.53
400	0.55	0.54	0.53
420	0.55	0.54	0.54
440	0.55	0.55	0.54
460	0.56	0.55	0.54
480	0.56	0.55	0.55
500	0.56	0.55	0.55
520	0.57	0.56	0.55
540	0.57	0.56	0.56
560	0.57	0.56	0.56
580	0.58	0.57	0.56
600	0.58	0.57	0.57
620	0.59	0.58	0.57
640	0.59	0.58	0.58
660	0.59	0.59	0.58
680	0.60	0.59	0.59
700	0.60	0.60	0.59
800	0.64	0.63	0.62
900	0.68	0.67	0.67
1000	0.73	0.72	0.72
1100	0.81	0.81	0.81
1200	0.92	0.93	0.93

Typical Performance Curves

INSERTION LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



INSERTION LOSS vs. TEMPERATURE (Zoomed)
INPUT POWER = 0 dBm



INPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS vs. TEMPERATURE
INPUT POWER = 0 dBm



GROUP DELAY vs. TEMPERATURE
INPUT POWER = 0 dBm



Case Style FF

FF704

Outline Dimensions



CASE #.	A	B	C	D	E	WT GRAMS
FF704	-- --	.410 (10.41)	-- --	1.43 (36.32)	.312 (7.92)	10.0

Dimensions are in inches (mm). Tolerances: 2Pl. ± .04; 3Pl. ± .030

Notes:

1. Case material: Stainless steel.
2. Case finish: Gold plated.
3. Round Flange may have .312 Across Flats in some models.

This document and its contents are the property of Mini-Circuits.

Mini-Circuits

Environmental Specifications ENV113

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Thermal Shock	-55° to 100°C, 5 cycles	MIL-STD-202, Method 107, Condition A, Except +100°C

This document and its contents are the property of Mini-Circuits.