



Instrumentation Test Cable **VNAX-2FT-KMVRF+**

50Ω 2 ft DC to 40 GHz Low Loss 2.92 mm Male to 2.4 mm Rugged Female

THE BIG DEAL

- Ultra-Wideband Operation, DC to 40 GHz
- 2.4 mm Rugged Female Connector for Direct Interface With 40 GHz VNA Ports
- Low Insertion Loss and Excellent Return Loss
- Rugged Construction, Crush and Torque Resistant



Generic photo used for illustration purposes only

Model No.	VNAX-2FT-KMVRF+
Case Style	RH2514-2
Connectors	2.92 mm Male to 2.4 mm Rugged Female

APPLICATIONS

- Military and Defense Applications
- Research & Development Labs
- Precision Testing

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

PRODUCT OVERVIEW

Mini-Circuits' VNAX-2FT-KMVRF+ is an ultra-wideband precision instrumentation cable specially designed for use with 40 GHz VNA equipment in test environments. The cable provides excellent VSWR and very low insertion loss over its entire frequency range. 2.4 mm rugged female to 2.92 mm male connector configuration provides direct connection from the ports of a 40 GHz VNA to 2.92 mm connectorized devices without the need for adapters. The cable features a rugged crush and torque resistant outer sheath that protects the cable from damage in demanding lab settings.

KEY FEATURES

Features	Advantages
DC to 40 GHz Operation Designed for Use With Vector Network Analyzers (VNA)	Covers a wide range of test applications; rugged 2.4 mm connector interfaces directly with VNA without the need for an adapter for improved VSWR performance and lower cost.
Rugged Cable-Connector Interface	Chrome-plated metal back shell maintains integrity of the cable-connector interface improving the reliability and extending life of use.
Extra Rugged Yet Flexible Armored Cable Construction	100% coverage, non-interleaved, stainless steel spiral sheath provides crush resistance and captured, opposing force steel braid provides torque resistance. PET monofilament yarn outer cover eliminates conductivity and allows easy handling.
2 ft Length	Standard VNA cable length makes this model a high performing, cost-effective replacement for expensive OEM cables.





Mini-Circuits



Instrumentation Test Cable **VNAX-2FT-KMVRF+**

50Ω 2 ft DC to 40 GHz Low Loss 2.92 mm Male to 2.4 mm Rugged Female

ELECTRICAL SPECIFICATIONS AT +25 °C

Parameter	Frequency (GHz)	Min.	Typ.	Max.	Units
Frequency Range		DC		40	GHz
Length		2			ft
Insertion Loss	DC-6	-	0.8	1.1	dB
	6-18	-	1.3	1.7	
	18-26.5	-	1.6	2.0	
	26.5-40	-	2.0	2.6	
Return Loss	DC-6	23	28	-	dB
	6-18	20	21	-	
	18-26.5	17	20	-	
	26.5-40	16	19	-	

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	+18 °C to +28 °C
Storage Temperature	-40 °C to +50 °C
Power Handling at +25 °C, Sea Level	140 W at 2 GHz
	46 W at 18 GHz
	38 W at 26.5 GHz
	30 W at 40 GHz

Permanent damage may occur if any of these limits are exceeded.

Product Guarantee

Mini-Circuits® will repair or replace your test cable at its option if the connector attachment fails within six months of shipment. This guarantee excludes cable or connector interface damage from misuse or abuse.





Instrumentation Test Cable **VNAX-2FT-KMVRF+**


50Ω 2 ft DC to 40 GHz Low Loss 2.92 mm Male to 2.4 mm Rugged Female

CABLE CONSTRUCTION



- **Center Conductor:** Solid SPC
- **Dielectric:** ND-PTFE
- **Outer Conductor:** SPC Strip
- **Interlayer:** LD-PTFE
- **Outer Shield:** SPC Braid
- **Jacket:** FEP
- **Armor Spiral:** SUS304
- **Armor Braid:** Nylon Braid
- **Armor Jacket:** Nylon Braid (Black)

OUTLINE DRAWING



OUTLINE DIMENSIONS (Inch/mm)

A		B	C	D	E	F	T	wt
Feet	Meters	0.79	.315	0.83	.75	.602	Inch	grams
2.00	0.61	20.07	8.00	21.08	19.05	15.29	+ .787/-0	+20/-0







Instrumentation Test Cable VNAX-2FT-KMVRF+

50Ω 2 ft DC to 40 GHz Low Loss 2.92 mm Male to 2.4 mm Rugged Female

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Insertion Loss (dB)	Return Loss (dB)	
		2.92 mm Male	2.4 mm Female
100	0.10	41.55	38.08
1000	0.31	35.47	38.02
4000	0.61	29.62	30.33
6000	0.74	31.45	31.36
10000	0.94	28.37	27.94
14000	1.09	37.70	41.91
18000	1.26	31.46	29.97
22000	1.41	23.84	22.34
26500	1.58	24.87	22.43
30000	1.67	41.80	27.44
32000	1.73	29.56	28.46
34000	1.78	40.38	35.34
36000	1.84	31.93	32.44
38000	1.90	35.56	39.19
40000	1.97	27.75	27.57



* Typical phase change over flexure performed on VNAX-3FT-KMVRF+ by wrapping cable 360° around 2" and 3" radii mandrels referenced to normalized straight position.
 ** Setup is flipped and measurement is repeated.

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html





Instrumentation Test Cable

Typical Performance Data


FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm MALE RETURN LOSS (dB)	2.4mm FEMALE Ruggedized RETURN LOSS (dB)
100	0.10	41.55	38.08
1000	0.31	35.47	38.02
2000	0.43	45.36	43.95
4000	0.61	29.62	30.33
6000	0.74	31.45	31.36
8000	0.84	30.83	29.14
10000	0.94	28.37	27.94
12000	1.02	39.24	36.95
14000	1.09	37.70	41.91
15000	1.14	31.72	30.68
15500	1.15	48.23	37.19
16000	1.17	31.85	31.05
16500	1.19	35.27	38.31
17000	1.21	38.84	34.48
17500	1.24	28.52	27.10
18000	1.26	31.46	29.97
18500	1.28	31.05	27.01
19000	1.31	24.99	23.39
19500	1.31	32.14	31.70
20000	1.33	29.78	26.51
20500	1.37	24.19	22.91
21000	1.37	28.18	25.29
21500	1.39	26.40	23.85
22000	1.41	23.84	22.34
22500	1.41	29.34	25.03
23000	1.44	25.69	22.26
23500	1.49	21.89	20.64
24000	1.49	30.22	24.09
24500	1.53	22.80	21.11
25000	1.55	22.42	21.00
25500	1.54	31.40	24.67
26000	1.56	24.96	22.24
26500	1.58	24.87	22.43
28000	1.62	26.47	24.24
30000	1.67	41.80	27.44
32000	1.73	29.56	28.46
34000	1.78	40.38	35.34
36000	1.84	31.93	32.44
38000	1.90	35.56	39.19
40000	1.97	27.75	27.57

Flex Test, 2.92mm-Male/2.4mm-Female Ruggedized VNAX-2FT-KMVRF+ Instrumentation Test Cable

Typical Performance Curves



Outline Dimensions



RH2514 SERIES

2.92mm MALE (CONN-1)

2.4mm FEMALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS			
	FEET	METERS						INCH	MM				
RH2514-2	2.00	.61	.79 (20.0)	.315 (8.00)	.83 (21.00)	.75 (19.00)	.602 (15.3)	+.787/-0	+20.0/-0	328			

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. High Performance rugged Cable.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	+18°C to 28°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 50°C Ambient Environment	Individual Model Data Sheet