



MMIC REFLECTIONLESS


Low Pass Filter

XLF-332+

50Ω DC to 3250 MHz

THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature sData, up to +105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our website for methodologies and qualifications

APPLICATIONS

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

PRODUCT OVERVIEW

Mini-Circuits' XLF-332+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

KEY FEATURES

Features	Advantages
Reflectionless Technology	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
50Ω Match in Stopband	Reflectionless filters maintain good impedance matching in the stopband, allowing for integration with high gain, wideband amplifiers without the risk of creating out-of-band instabilities.
Excellent RF Performance Repeatability	Fabricated on a GaAs process, X-series filters are inherently repeaData for large-volume production.
Excellent Stability over temperature	With ±0.3 dB variation over temperature, is ideal for use in wide temperature range applications without the need for additional temperature compensation.
Excellent Power Handling in a Compact Package	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.

REV. B
 ECO-020722
 XLF-332+
 MCL NY
 250407





ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Passband	Insertion Loss	DC - F1	—	1.4	1.8	dB
	Frequency Cut-off	F2	—	3.0	—	dB
	VSWR	DC - F1	—	1.2	—	:1
Stopband	Rejection	F3 - F4	12	15	—	dB
		F4 - F5	—	19	—	dB
	VSWR	F3 - F4	—	1.2	—	:1
		F4 - F5	—	2.0	—	:1

1. Measured on Mini-Circuits Characterization Test Board TB-844-332+

ABSOLUTE MAXIMUM RATINGS²


Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C
RF Power Input, Passband (DC-F1) ³	2 W at +25°C
RF Power Input, Stopband (F2-F5) ⁴	0.2 W at +25°C

2. Permanent damage may occur if any of these limits are exceeded.

3. Passband rating derates linearly to 1 W at 105°C ambient



4. Stopband rating derates linearly to 0.1 W at 105°C ambient

SPECIFICATION DEFINITION






SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	2	RF Input Pad
RF-OUT	8	RF Output Pad
GND	1,3,7,9, Paddle	Connected to ground
NC (GND Externally)	4,5,6,10,11,12	No internal connection

PRODUCT MARKING





Marking may contain other features or characters for internal lot control



TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.51	1.02
100	0.47	1.02
200	0.47	1.04
400	0.49	1.08
800	0.55	1.17
1600	0.68	1.24
3250	1.34	1.08
4120	3.03	1.07
5900	15.59	1.22
8000	19.18	1.25
10000	15.91	1.24
12000	15.55	1.05
14500	15.84	1.11
17000	15.25	1.19
19000	13.06	1.96
21000	12.79	2.61
23000	18.96	1.62
25000	22.23	1.72
27500	23.07	1.84
30000	24.44	2.89





MMIC REFLECTIONLESS

Low Pass Filter

XLF-332+

50Ω DC to 3250 MHz

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500 ,1000, 2000, 3000 devices
Suggested Layout for PCB Design	PL-451
Evaluation Board	TB-844-332+ (without connectors) TB-844-332C+ (with connectors) B20-118-F1+ Connector sold separately
Environmental Ratings	ENV82

ESD RATING

Human body model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1-2001


MSL RATING

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D



REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter





Figure 2. IF output reflection spectrum with conventional filter



An application circuit was assembled to measure the IF reflection spectrum at the output of a mixer when the mixer was paired with a conventional filter versus a reflectionless filter.

While the conventional filter reduces the reflections present when the mixer is used alone (no filter), the reflectionless filter virtually eliminates those reflections altogether.

The reflected signal at marker 1 in the figures above exhibits a reduction of more than 20 dB from -28.7 dBm to -50.3 dBm when the reflectionless filter is used as compared to the conventional filter, thus eliminating unwanted spurious mixing products and improving system dynamic range.

For more information, refer to application note [AN-75-007](#)

- NOTES
- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)					GROUP DELAY (nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	10	0.48	0.49	0.52	0.58	0.57	0.13	0.13	0.12	0.17
20	0.39	0.41	0.44	0.50	0.50	0.12	0.12	0.12	0.15	0.15
40	0.40	0.43	0.46	0.50	0.51	0.11	0.11	0.10	0.13	0.13
50	0.40	0.40	0.45	0.49	0.51	0.10	0.10	0.10	0.12	0.12
60	0.39	0.40	0.46	0.49	0.51	0.10	0.10	0.09	0.11	0.11
70	0.40	0.41	0.46	0.50	0.52	0.09	0.09	0.09	0.10	0.10
80	0.39	0.41	0.45	0.48	0.51	0.08	0.08	0.08	0.09	0.09
90	0.40	0.41	0.45	0.50	0.52	0.08	0.08	0.08	0.09	0.09
100	0.41	0.41	0.46	0.51	0.52	0.08	0.08	0.08	0.09	0.09
200	0.39	0.41	0.46	0.52	0.54	0.08	0.08	0.08	0.08	0.08
300	0.40	0.42	0.47	0.53	0.56	0.08	0.08	0.08	0.08	0.08
400	0.39	0.41	0.49	0.54	0.55	0.08	0.08	0.08	0.08	0.08
500	0.41	0.43	0.49	0.55	0.58	0.08	0.08	0.07	0.08	0.08
600	0.42	0.45	0.52	0.58	0.60	0.08	0.08	0.07	0.08	0.08
700	0.43	0.45	0.52	0.59	0.61	0.07	0.07	0.07	0.08	0.08
800	0.44	0.46	0.54	0.61	0.64	0.08	0.08	0.08	0.08	0.08
900	0.45	0.47	0.56	0.62	0.65	0.08	0.08	0.07	0.08	0.08
1000	0.46	0.48	0.57	0.64	0.67	0.08	0.07	0.07	0.08	0.08
1100	0.47	0.50	0.58	0.66	0.69	0.08	0.08	0.07	0.08	0.08
1200	0.48	0.51	0.60	0.68	0.71	0.08	0.08	0.07	0.08	0.08
1300	0.50	0.52	0.62	0.70	0.73	0.08	0.08	0.07	0.08	0.08
1400	0.51	0.54	0.64	0.72	0.75	0.08	0.08	0.07	0.08	0.08
1500	0.51	0.55	0.65	0.73	0.76	0.08	0.08	0.08	0.08	0.08
1600	0.53	0.56	0.67	0.75	0.79	0.08	0.08	0.08	0.08	0.08
1700	0.55	0.58	0.69	0.77	0.81	0.08	0.08	0.08	0.08	0.08
1800	0.56	0.59	0.70	0.79	0.82	0.08	0.08	0.08	0.08	0.08
1900	0.57	0.60	0.72	0.81	0.84	0.08	0.08	0.08	0.08	0.08
2000	0.58	0.61	0.73	0.82	0.86	0.08	0.08	0.08	0.08	0.08
2200	0.62	0.66	0.78	0.87	0.91	0.08	0.08	0.08	0.09	0.09
2400	0.66	0.70	0.83	0.93	0.97	0.09	0.09	0.09	0.09	0.09
2600	0.71	0.76	0.90	1.00	1.04	0.09	0.09	0.09	0.09	0.10
2800	0.80	0.84	1.00	1.11	1.15	0.10	0.10	0.10	0.10	0.10
3000	0.91	0.95	1.12	1.24	1.29	0.10	0.10	0.10	0.10	0.10
3250	1.10	1.15	1.34	1.47	1.53	0.11	0.11	0.11	0.11	0.11
3400	1.26	1.31	1.51	1.65	1.71	0.11	0.11	0.11	0.11	0.11
3500	1.38	1.44	1.65	1.80	1.86	0.11	0.11	0.11	0.11	0.12
3600	1.53	1.59	1.81	1.97	2.03	0.11	0.11	0.11	0.11	0.12
3700	1.69	1.75	1.98	2.15	2.22	0.12	0.12	0.12	0.12	0.12
3800	1.88	1.94	2.18	2.37	2.43	0.12	0.12	0.12	0.12	0.12
3900	2.09	2.16	2.41	2.61	2.68	0.12	0.12	0.12	0.12	0.12
4000	2.33	2.41	2.67	2.88	2.96	0.12	0.12	0.12	0.12	0.13
4120	2.67	2.74	3.03	3.25	3.33	0.12	0.12	0.12	0.12	0.12
4500	4.06	4.16	4.49	4.77	4.87	0.13	0.13	0.12	0.12	0.12
5000	6.83	6.95	7.36	7.69	7.81	0.12	0.11	0.11	0.11	0.11
5900	14.89	15.04	15.60	16.04	16.19	0.05	0.05	0.04	0.03	0.03
6000	16.12	16.26	16.83	17.31	17.45	0.04	0.04	0.03	0.02	0.02
6500	24.12	24.21	24.68	24.96	24.98	-0.15	-0.16	-0.21	-0.23	-0.25
7000	28.13	27.92	26.90	26.10	25.88	-0.35	-0.33	-0.27	-0.23	-0.21
7500	22.27	22.18	21.87	21.59	21.52	-0.01	-0.01	-0.01	-0.01	-0.01
8000	19.25	19.22	19.19	19.09	19.10	0.03	0.03	0.03	0.03	0.03
8500	17.62	17.64	17.67	17.66	17.71	0.04	0.04	0.03	0.04	0.04
9000	16.64	16.68	16.78	16.82	16.86	0.04	0.04	0.04	0.04	0.04
9500	16.05	16.08	16.25	16.31	16.35	0.04	0.04	0.04	0.04	0.04
10000	15.65	15.71	15.89	16.02	16.05	0.04	0.04	0.04	0.04	0.05
10500	15.42	15.49	15.69	15.82	15.88	0.04	0.04	0.04	0.04	0.04
11000	15.30	15.36	15.57	15.72	15.81	0.04	0.04	0.04	0.04	0.04
11500	15.21	15.28	15.52	15.69	15.75	0.04	0.04	0.04	0.04	0.04
12000	15.21	15.27	15.52	15.70	15.79	0.04	0.04	0.04	0.04	0.04
13000	15.30	15.36	15.65	15.82	15.91	0.04	0.04	0.04	0.04	0.04
14000	15.42	15.51	15.79	15.97	16.04	0.04	0.04	0.04	0.04	0.04
15000	15.46	15.54	15.84	16.02	16.10	0.04	0.04	0.04	0.05	0.05
16000	15.32	15.40	15.69	15.87	15.95	0.04	0.04	0.04	0.05	0.05
17000	14.89	14.96	15.24	15.40	15.46	0.05	0.05	0.05	0.05	0.05
18000	13.96	14.03	14.32	14.45	14.52	0.06	0.06	0.06	0.07	0.07
19000	12.57	12.64	13.02	13.25	13.32	0.09	0.09	0.09	0.09	0.09
20000	11.81	11.90	11.99	12.38	12.57	0.08	0.07	0.12	0.13	0.13
22000	14.74	14.99	16.02	16.79	17.05	0.08	0.09	0.08	0.08	0.08
24000	20.11	20.26	20.95	21.45	21.62	0.05	0.05	0.04	0.05	0.05
26000	22.09	22.24	22.82	23.22	23.35	0.04	0.03	0.04	0.05	0.05
28000	22.38	22.58	23.10	23.61	23.84	0.05	0.05	0.05	0.05	0.04
30000	23.37	23.59	24.21	24.63	24.81	0.05	0.04	0.05	0.08	0.05
32000	26.66	26.77	27.44	27.96	28.06	0.02	0.00	0.00	0.02	0.01
34000	30.88	30.65	30.14	29.86	30.28	-0.15	-0.13	-0.01	0.08	0.01
36000	28.01	28.31	28.66	29.28	29.32	-0.02	0.02	-0.04	0.01	-0.04
38000	25.32	25.42	25.90	26.06	26.02	0.04	0.08	0.07	0.03	0.07
40000	24.46	24.76	25.40	26.08	26.39	0.16	-0.05	0.17	0.12	-0.09











Typical Performance Data


FREQ. (MHz)	INPUT RETURN LOSS					OUTPUT RETURN LOSS				
	(dB)					(dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
10	40.97	41.96	43.81	41.82	41.12	48.07	48.97	46.02	44.34	42.42
20	40.10	41.79	48.64	50.98	49.72	42.60	43.00	51.45	52.64	49.33
40	41.63	43.14	49.63	46.46	44.90	40.00	40.81	50.44	51.20	48.68
50	38.60	38.87	43.93	47.71	45.96	40.03	41.04	48.42	46.12	44.07
60	38.88	39.75	45.08	45.75	44.50	38.05	38.43	42.81	43.64	43.33
70	38.78	39.75	43.50	43.50	42.99	38.96	39.43	45.10	45.07	43.99
80	38.91	39.27	44.56	45.54	45.46	37.49	38.62	41.61	42.68	41.65
90	37.35	37.88	40.98	43.15	42.84	39.20	39.90	43.50	41.42	41.22
100	37.88	38.09	40.87	40.86	40.34	37.07	37.59	39.98	40.43	40.31
200	35.82	36.03	34.94	34.40	34.25	35.73	35.62	34.57	34.61	34.37
300	31.70	31.50	30.54	30.26	30.29	31.02	30.92	30.25	30.11	30.17
400	28.12	27.97	27.80	27.64	27.56	28.66	28.49	28.13	28.09	28.08
500	26.22	26.13	25.69	25.53	25.39	26.42	26.35	25.84	25.83	25.71
600	24.61	24.55	24.17	24.02	23.96	24.52	24.45	24.11	23.98	23.90
700	23.59	23.49	23.15	23.09	23.15	23.59	23.50	23.23	23.18	23.18
800	22.89	22.83	22.45	22.48	22.47	22.73	22.65	22.31	22.32	22.34
900	21.90	21.85	21.62	21.63	21.65	21.77	21.72	21.48	21.49	21.51
1000	21.03	21.00	20.83	20.71	20.77	20.94	20.89	20.68	20.61	20.65
1100	20.61	20.61	20.43	20.31	20.28	20.64	20.61	20.41	20.26	20.26
1200	20.36	20.35	20.20	20.06	20.03	20.32	20.31	20.12	19.96	19.98
1300	19.98	19.98	19.82	19.70	19.70	19.96	19.94	19.78	19.67	19.70
1400	19.70	19.68	19.52	19.40	19.36	19.75	19.74	19.57	19.44	19.42
1500	19.64	19.68	19.56	19.39	19.37	19.67	19.71	19.55	19.40	19.39
1600	19.55	19.57	19.60	19.50	19.51	19.55	19.58	19.57	19.49	19.50
1700	19.37	19.44	19.58	19.52	19.53	19.56	19.60	19.70	19.66	19.68
1800	19.44	19.50	19.66	19.59	19.58	19.56	19.62	19.72	19.67	19.64
1900	19.63	19.68	19.84	19.75	19.73	19.79	19.84	20.03	19.92	19.91
2000	20.05	20.13	20.34	20.36	20.31	20.19	20.27	20.49	20.49	20.48
2200	20.58	20.69	21.09	21.13	21.11	20.77	20.85	21.30	21.38	21.30
2400	21.80	21.90	22.34	22.45	22.39	22.06	22.17	22.51	22.80	22.74
2600	23.08	23.18	23.28	23.37	23.22	23.34	23.46	23.75	23.91	23.85
2800	24.49	24.63	24.73	24.71	24.57	25.02	25.17	25.39	25.67	25.60
3000	26.32	26.39	26.11	25.78	25.64	26.82	26.97	26.91	26.85	26.73
3250	29.15	29.13	28.40	27.78	27.46	29.73	29.72	28.79	28.42	28.42
3400	29.95	29.83	28.90	27.76	27.45	31.04	31.02	30.55	29.28	29.03
3500	30.66	30.62	29.65	28.21	27.88	32.28	32.17	31.65	29.74	29.51
3600	31.24	31.28	30.20	28.52	28.20	33.64	33.52	32.51	30.37	29.88
3700	31.09	31.17	30.01	28.27	27.91	34.35	34.11	32.75	30.52	30.04
3800	31.70	31.62	30.14	28.57	28.35	35.87	35.44	33.66	31.07	30.56
3900	32.17	31.93	30.34	28.95	28.82	35.86	35.32	33.71	30.84	30.12
4000	31.46	31.40	30.16	28.76	28.37	35.38	34.71	33.05	30.36	29.70
4120	30.28	30.20	29.15	27.69	27.31	33.97	33.49	31.96	29.83	29.23
4500	27.42	27.49	26.79	25.88	25.80	28.10	27.86	27.34	26.24	25.92
5000	22.35	22.45	22.60	22.32	22.24	22.32	22.33	22.30	21.94	21.84
5900	19.33	19.50	19.99	20.49	20.62	18.71	18.87	19.42	19.99	20.23
6000	19.25	19.40	20.08	20.96	21.30	18.73	18.86	19.44	20.01	20.31
6500	18.55	18.71	19.86	20.71	20.81	18.94	19.14	19.92	20.77	21.05
7000	19.05	19.17	20.07	20.43	20.48	19.58	19.82	20.93	21.63	21.63
7500	18.67	18.84	19.71	20.09	20.21	19.85	20.12	21.38	21.66	21.56
8000	18.10	18.24	19.27	19.88	19.92	19.62	19.89	20.99	21.43	21.39
8500	17.58	17.74	18.43	19.28	19.49	19.17	19.38	19.98	20.72	20.88
9000	17.55	17.68	18.21	18.85	19.15	18.68	18.81	19.09	19.93	20.38
9500	17.76	17.87	18.42	18.87	19.08	18.60	18.67	18.71	19.50	20.00
10000	18.52	18.63	19.07	19.32	19.54	18.91	19.00	19.02	19.60	19.96
10500	19.93	20.08	20.56	20.64	20.66	19.64	19.72	19.80	19.96	20.11
11000	22.39	22.62	23.36	22.81	22.61	20.73	20.85	21.36	21.07	20.85
11500	24.82	25.26	26.89	26.21	25.68	22.35	22.62	23.91	22.76	22.08
12000	28.74	29.68	33.09	31.72	30.11	25.04	25.35	27.37	24.83	23.73
13000	28.41	29.06	30.91	33.32	32.91	40.20	39.40	37.14	28.58	26.42
14000	26.46	26.46	26.87	26.86	26.39	27.43	27.76	29.22	25.70	24.37
15000	25.82	25.61	25.88	26.15	25.93	24.91	25.24	26.11	24.62	24.28
16000	25.90	25.43	25.27	25.76	25.71	25.10	25.16	24.28	24.36	24.71
17000	22.77	22.40	21.64	21.45	21.21	22.50	22.30	20.63	20.81	21.33
18000	16.61	16.27	15.41	14.82	14.64	16.82	16.61	15.29	15.01	15.10
19000	10.26	10.15	9.81	9.33	9.21	10.55	10.52	10.19	9.69	9.51
20000	5.71	5.92	6.69	6.82	6.86	6.59	6.63	6.78	6.74	6.67
22000	9.30	9.52	10.51	11.16	11.47	10.69	10.83	11.36	12.36	12.84
24000	11.95	12.11	12.61	13.26	13.70	11.65	11.72	12.16	12.49	12.71
26000	10.18	10.35	10.97	11.24	11.36	9.72	9.78	9.99	10.42	10.63
28000	10.38	10.41	10.37	10.31	10.28	9.24	9.38	9.77	9.41	9.19
30000	6.25	6.24	6.33	6.34	6.30	6.22	6.26	6.24	6.47	6.58
32000	2.78	2.85	3.16	3.57	3.81	2.62	2.74	3.17	3.32	3.40
34000	1.50	1.60	2.17	2.41	2.48	1.63	1.74	2.04	2.50	2.65
36000	1.25	1.36	1.93	2.22	2.40	1.30	1.44	2.00	2.13	2.09
38000	1.73	1.92	2.81	3.32	3.46	2.24	2.39	2.91	3.53	3.88
40000	2.69	2.84	3.46	3.96	4.19	2.39	2.57	3.23	3.50	3.51




Typical Performance Curves



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN $\pm .002$

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.

Mini-Circuits®


Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf

Mini-Circuits®


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152656	NEW RELEASE	09/11/15	ITG	MY

SUGGESTED MOUNTING CONFIGURATION
FOR DQ1225 CASE STYLE, "12FL02" PIN CODE




NOTES:

- TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS $.0066 \pm .0007$ ". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
- BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

UNLESS OTHERWISE SPECIFIED	INITIALS		DATE
DIMENSIONS ARE IN INCHES TOLERANCES ON: 2 PL DECIMALS ± 3 PL DECIMALS ± .005 ANGLES ± FRACTIONS ±	DRAWN	ITG	09/10/15
	CHECKED	GF	09/11/15
	APPROVED	MY	09/11/15



Mini-Circuits® 13 Neptune Avenue
 Brooklyn NY 11235


PL, 12FL02, DQ1225, TB-844+

Mini-Circuits®
 THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


SIZE A	CODE IDENT 15542	DRAWING NO: 98-PL-451	REV: OR
FILE: 98PL451	SCALE: 16:1	SHEET: 1 OF 1	

Evaluation Board and Circuit

To be used with Mini-Circuits 50 Ohm 2.92 connectors B20-118-F1+.
Connectors are sold separately.




TB-844-332+





Schematic Diagram

Note:

PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**


Evaluation Board and Circuit



Schematic Diagram

Notes:

1. 50 Ohm 2.92 mm Female connectors.
2. PCB Material: R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215