

## Engineering Development Model


# Power Splitter/Combiner

# WP4-ED12616B

## 4 Way-0°

### Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : DQ1225

| ELECTRICAL SPECIFICATIONS 50Ω @ +25°C |                 |      |      |       |
|---------------------------------------|-----------------|------|------|-------|
| Parameter                             | Min.            | Typ. | Max. | Units |
| Frequency                             | 2700            |      | 3800 | MHz   |
| Isolation                             | 2700 - 3800 MHz | 27   |      | dB    |
| Insertion Loss Above 6.0 dB           | 2700 - 3800 MHz | 0.80 |      | dB    |
| Phase Unbalance                       | 2700 - 3800 MHz | 2.60 |      | deg.  |
| Amplitude Unbalance                   | 2700 - 3800 MHz | 0.15 |      | dB    |
| VSWR                                  | SUM Port        | 1.60 |      | (:1)  |
|                                       | OUT Ports       | 1.35 |      | (:1)  |

| MAXIMUM RATINGS       |                |
|-----------------------|----------------|
| Operating Temperature | -40°C to 85°C  |
| Storage Temperature   | -65°C to 150°C |

| PIN CONNECTIONS |                        |
|-----------------|------------------------|
| SUM PORT        | 2                      |
| PORT 1          | 12                     |
| PORT 2          | 10                     |
| PORT 3          | 6                      |
| PORT 4          | 4                      |
| GROUND          | 1,3,5,7,8,9,11, paddle |

### Functional Diagram



# 4 Way-0° Power Splitter/Combiner

WP4-ED12616B

## Typical Performance Data

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      |      |      | AMP.<br>UNBAL.<br>(dB) | ISOLATION<br>(dB) |       |       | PHASE<br>UNBAL.<br>(deg.) | FREQ.<br>(MHz) | VSWR<br>(:1) |      |      |      |      |
|----------------|---------------------------------|------|------|------|------------------------|-------------------|-------|-------|---------------------------|----------------|--------------|------|------|------|------|
|                | S-1                             | S-2  | S-3  | S-4  |                        | 1-2               | 1-3   | 3-4   |                           |                | S            | 1    | 2    | 3    | 4    |
| 2700.0         | 7.15                            | 7.19 | 7.14 | 7.10 | 0.09                   | 28.23             | 24.14 | 29.48 | 0.92                      | 2700.0         | 1.78         | 1.42 | 1.46 | 1.45 | 1.40 |
| 2750.0         | 7.07                            | 7.10 | 7.05 | 7.02 | 0.08                   | 29.72             | 25.04 | 31.18 | 0.63                      | 2750.0         | 1.68         | 1.41 | 1.45 | 1.42 | 1.38 |
| 2800.0         | 6.99                            | 7.02 | 6.97 | 6.95 | 0.07                   | 31.23             | 25.92 | 32.73 | 0.59                      | 2800.0         | 1.61         | 1.40 | 1.42 | 1.41 | 1.37 |
| 2850.0         | 6.94                            | 6.95 | 6.90 | 6.89 | 0.06                   | 32.53             | 26.78 | 33.74 | 0.62                      | 2850.0         | 1.53         | 1.39 | 1.40 | 1.39 | 1.36 |
| 2900.0         | 6.88                            | 6.89 | 6.84 | 6.83 | 0.06                   | 33.16             | 27.39 | 33.85 | 0.86                      | 2900.0         | 1.48         | 1.38 | 1.39 | 1.37 | 1.35 |
| 2950.0         | 6.84                            | 6.83 | 6.78 | 6.79 | 0.06                   | 33.13             | 27.98 | 33.12 | 1.12                      | 2950.0         | 1.42         | 1.37 | 1.37 | 1.35 | 1.34 |
| 3000.0         | 6.81                            | 6.79 | 6.74 | 6.76 | 0.07                   | 32.33             | 28.17 | 32.00 | 1.42                      | 3000.0         | 1.40         | 1.37 | 1.36 | 1.34 | 1.34 |
| 3050.0         | 6.79                            | 6.75 | 6.70 | 6.74 | 0.09                   | 31.37             | 28.28 | 30.78 | 1.67                      | 3050.0         | 1.36         | 1.37 | 1.33 | 1.32 | 1.33 |
| 3100.0         | 6.77                            | 6.73 | 6.67 | 6.72 | 0.10                   | 30.06             | 27.91 | 29.66 | 1.97                      | 3100.0         | 1.36         | 1.36 | 1.34 | 1.31 | 1.33 |
| 3150.0         | 6.77                            | 6.69 | 6.65 | 6.72 | 0.12                   | 29.13             | 27.62 | 28.65 | 2.18                      | 3150.0         | 1.35         | 1.36 | 1.31 | 1.30 | 1.32 |
| 3200.0         | 6.76                            | 6.68 | 6.62 | 6.71 | 0.14                   | 27.97             | 26.97 | 27.76 | 2.46                      | 3200.0         | 1.37         | 1.36 | 1.30 | 1.28 | 1.32 |
| 3250.0         | 6.77                            | 6.66 | 6.61 | 6.72 | 0.16                   | 27.22             | 26.47 | 26.98 | 2.71                      | 3250.0         | 1.38         | 1.35 | 1.30 | 1.27 | 1.32 |
| 3300.0         | 6.77                            | 6.66 | 6.60 | 6.72 | 0.17                   | 26.30             | 25.82 | 26.28 | 2.93                      | 3300.0         | 1.41         | 1.35 | 1.28 | 1.26 | 1.31 |
| 3350.0         | 6.79                            | 6.65 | 6.60 | 6.74 | 0.19                   | 25.73             | 25.30 | 25.65 | 3.14                      | 3350.0         | 1.44         | 1.35 | 1.28 | 1.25 | 1.31 |
| 3400.0         | 6.80                            | 6.65 | 6.60 | 6.75 | 0.20                   | 24.98             | 24.69 | 25.10 | 3.35                      | 3400.0         | 1.48         | 1.35 | 1.25 | 1.24 | 1.31 |
| 3450.0         | 6.82                            | 6.66 | 6.61 | 6.77 | 0.22                   | 24.46             | 24.11 | 24.60 | 3.56                      | 3450.0         | 1.52         | 1.34 | 1.26 | 1.24 | 1.31 |
| 3500.0         | 6.85                            | 6.67 | 6.62 | 6.80 | 0.23                   | 23.93             | 23.65 | 24.15 | 3.74                      | 3500.0         | 1.56         | 1.35 | 1.24 | 1.22 | 1.30 |
| 3550.0         | 6.88                            | 6.69 | 6.64 | 6.83 | 0.24                   | 23.45             | 23.09 | 23.73 | 3.94                      | 3550.0         | 1.62         | 1.34 | 1.25 | 1.22 | 1.31 |
| 3600.0         | 6.91                            | 6.71 | 6.66 | 6.86 | 0.25                   | 23.09             | 22.74 | 23.35 | 4.10                      | 3600.0         | 1.66         | 1.34 | 1.23 | 1.21 | 1.30 |
| 3650.0         | 6.94                            | 6.74 | 6.69 | 6.90 | 0.25                   | 22.63             | 22.23 | 22.99 | 4.29                      | 3650.0         | 1.72         | 1.34 | 1.22 | 1.21 | 1.30 |
| 3700.0         | 6.98                            | 6.77 | 6.72 | 6.93 | 0.26                   | 22.35             | 21.89 | 22.66 | 4.45                      | 3700.0         | 1.77         | 1.33 | 1.23 | 1.20 | 1.30 |
| 3750.0         | 7.02                            | 6.81 | 6.76 | 6.97 | 0.26                   | 21.97             | 21.48 | 22.35 | 4.60                      | 3750.0         | 1.83         | 1.33 | 1.21 | 1.19 | 1.30 |
| 3800.0         | 7.05                            | 6.84 | 6.80 | 7.01 | 0.25                   | 21.71             | 21.13 | 22.06 | 4.76                      | 3800.0         | 1.88         | 1.33 | 1.22 | 1.19 | 1.30 |

<sup>1</sup>Total Loss = Insertion Loss + 6dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)






IF/RF MICROWAVE COMPONENTS

REV. X2  
 WP4-ED12616B  
 9/14/2010  
 Page 1 of 1


# 4 Way-0° Power Splitter/Combiner

WP4-ED12616B


## Typical Performance Curves



### Outline Dimensions



### PCB Land Pattern



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm 0.002$

**Weight: .02 Grams**

**Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .004$**

### Notes:

- Case material: Plastic.
- Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F66



| Tape Width,<br>mm | Device Cavity<br>Pitch, mm | Reel Size,<br>inches | Devices per Reel<br>see note  |                  |
|-------------------|----------------------------|----------------------|-------------------------------|------------------|
| 8                 | 4                          | 7                    | Small<br>quantity<br>standard | 20               |
|                   |                            |                      |                               | 50               |
|                   |                            |                      |                               | 100              |
|                   |                            |                      |                               | 200              |
|                   |                            |                      |                               | 500              |
|                   |                            | 7                    | Standard                      | 1000, 2000, 3000 |

Note: Please consult individual model data sheet to determine device per reel availability.


Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661  
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010  
Mini-Circuits ISO 9001 & ISO 14001 Certified

# Evaluation Board and Circuit




TB-395+



Schematic Diagram

## Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.020 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification                 | Test/Inspection Condition                                                                                                 | Reference/Spec                                |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------|
| Operating Temperature         | -40° to 85° C<br>Ambient Environment                                                                                      | Individual Model Data Sheet                   |
| Storage Temperature           | -65° to 150° C<br>Ambient Environment                                                                                     | Individual Model Data Sheet                   |
| Autoclave                     | 15 psig, 100% RH, 121°C, 96 hours                                                                                         | JESD22-A102-C, Condition C                    |
| Temperature Cycling           | -65° to 150°C, 100 cycles                                                                                                 | JESD22-A104                                   |
| Temperature Humidity          | 85°C/ 85% RH, 168 hours                                                                                                   | JESD22-113                                    |
| Solder Reflow Heat            | Sn-Pb Eutetic Process: 240°C peak<br>Pb-Free Process: 260°C peak                                                          | J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1 |
| Moisture Sensitivity: Level 1 | Bake at 125°C for 24 hours<br>Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS) | J-STD-020                                     |
| Solderability                 | 10X magnification, 95% coverage                                                                                           | JESD22-B102, Method 1: Dip and Look Test      |
| Mechanical Shock              | 50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes                                                         | MIL-STD-202, Method 213, Condition A          |
| Vibration (High Frequency)    | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)                                       | MIL-STD-202, Method 204, Condition D          |