



Mini-Circuits

MMIC SURFACE MOUNT


Power Splitter/Combiner

WP4W+

4 Way-0° 50Ω 3300 to 3800 MHz

FEATURES

- Excellent Isolation, Typ. 26 dB
- Good Phase Unbalance, Max. 8 deg.
- Good Amplitude Unbalance, Max. 0.4 dB
- Small Size, 3x3 mm
- High ESD Level
- Aqueous Washable



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS CompliantThe +Suffix identifies RoHS Compliance.
See our website for methodologies and qualifications

APPLICATIONS

- WIMAX

ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range		3300		3800	MHz
Insertion Loss* (Above 6.0 dB)	3300-3800		0.8	1.4	dB
Isolation	3300-3800	18	26		dB
Amplitude Unbalance	3300-3800			0.4	dB
Phase Unbalance	3300-3800			8	deg.
VSWR (Port S)	3300-3800		1.5		:1
VSWR (Ports 1,2,3,4)	3300-3800		1.3		:1


*Includes test fixture loss, 0.27 dB typ.

ABSOLUTE MAXIMUM RATINGS

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C
Power Input (as a Splitter)	1.5 W max.
Internal Dissipation	0.375 W max.

Permanent damage may occur if any of these limits are exceeded.

ELECTRICAL SCHEMATIC



Mini-Circuits

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. E
ECO-026468
WP4W+
MCL NY
250806

PAGE 1 OF 3



Power Splitter/Combiner

WP4W+

4 Way-0° 50Ω 3300 to 3800 MHz

OUTLINE DRAWING

SUM PORT	2
PORT 1	12
PORT 2	10
PORT 3	6
PORT 4	4
GROUND	1,3,5,7,8,9,11, Paddle

Figure 1: Dimensions of the package outline. The drawing shows a top-down view of a square package with a complex internal layout. The package is outlined in blue with a red border. Internal features include a central square area with a cross-hatch pattern, four circular pads at the corners, and various rectangular and circular features. Dimensions are provided in inches. Key dimensions include: overall width .236, overall height .255, distance from top edge to center line .105, distance from center line to bottom edge .224, distance from left edge to center line .148, distance from center line to right edge .085, distance from top edge to top of central area .015, distance from center line to left edge of central area .007, distance from center line to right edge of central area .003 (typical), and distance from center line to bottom edge of central area .007. The package is labeled "PACKAGE OUTLINE" and "11X Ø.020 PTH FOR GROUND". The central area is labeled "COPLANAR WAVEGUIDE, .035 TRACE WIDTH, .008 GAP, 5 PL. (SEE NOTE 1)". The bottom edge is labeled "PIN 1" and "SEE NOTE 3".


1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" ± .0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. SIGNAL TRACES ARE NOT ALLOWED INSIDE HATCHED AREAS (APPROX. .030 X .030) AT 4 PLACES AS SHOWN.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC
 (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

The diagram shows a black rectangular label with white text. The text is arranged in four lines: a small white circle, the text 'MCL', 'WP4W', and 'XXXX'. An arrow points from the word 'Index' to the small white circle. Two other arrows point from the text 'Black Body' and 'Model Family Designation' to the text 'MCL' and 'XXXX' respectively.

Marking may contain other features or characters for internal lot control.

PCB Land Pattern



Weight: .02 Grams
Dimensions are in inches [mm]. Tolerances in inches: 2 Pl. $\pm .01$; 3 Pl. $\pm .004$ inches

TAPE & REEL INFORMATION: F66



Mini-Circuits

MMIC SURFACE MOUNT

Power Splitter/Combiner




WP4W+

4 Way-0° 50Ω 3300 to 3800 MHz

TYPICAL PERFORMANCE DATA AND CHARTS

Frequency (MHz)	Total Loss ¹ (dB)				Amplitude Unbalance (dB)	Isolation (dB)			Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4						
3300.00	6.91	6.88	6.81	6.88	0.10	31.79	31.04	31.98	0.99	1.53	1.40	1.32	1.34	1.41
3350.00	6.89	6.85	6.78	6.86	0.11	31.72	31.54	31.75	1.00	1.50	1.39	1.31	1.33	1.40
3400.00	6.87	6.82	6.75	6.84	0.12	30.97	31.12	30.82	1.02	1.49	1.39	1.30	1.32	1.40
3450.00	6.86	6.80	6.73	6.83	0.13	30.39	30.78	30.15	1.19	1.48	1.38	1.29	1.31	1.39
3500.00	6.85	6.79	6.72	6.83	0.13	29.59	29.95	29.26	1.36	1.49	1.37	1.28	1.30	1.38
3550.00	6.85	6.77	6.71	6.83	0.14	28.87	29.14	28.52	1.57	1.49	1.37	1.27	1.29	1.38
3600.00	6.86	6.77	6.71	6.83	0.15	28.23	28.36	27.83	1.74	1.51	1.36	1.26	1.28	1.38
3625.00	6.86	6.77	6.71	6.84	0.15	27.81	27.84	27.41	1.83	1.52	1.36	1.26	1.28	1.37
3650.00	6.86	6.77	6.71	6.84	0.16	27.47	27.42	27.07	1.94	1.53	1.36	1.25	1.27	1.37
3675.00	6.87	6.77	6.71	6.85	0.16	27.23	27.11	26.84	2.02	1.54	1.36	1.25	1.27	1.37
3700.00	6.88	6.78	6.72	6.86	0.16	26.94	26.74	26.53	2.09	1.55	1.35	1.24	1.26	1.37
3725.00	6.89	6.78	6.73	6.87	0.16	26.59	26.29	26.18	2.18	1.57	1.35	1.24	1.26	1.37
3750.00	6.90	6.79	6.73	6.87	0.17	26.29	25.90	25.89	2.28	1.59	1.35	1.24	1.26	1.36
3775.00	6.91	6.79	6.74	6.88	0.17	26.11	25.65	25.71	2.39	1.60	1.35	1.23	1.25	1.36
3800.00	6.92	6.80	6.75	6.89	0.17	25.87	25.35	25.47	2.47	1.62	1.35	1.23	1.25	1.36

1. Total Loss = Insertion Loss + 6 dB splitter loss.



NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



4 Way-0° Power Splitter/Combiner

WP4W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +25°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.20	10.43	10.36	10.13	0.30	6.22	16.64	15.73	16.66	5.23	1.68	1.71	1.71	1.66
2300	9.56	9.76	9.69	9.49	0.27	5.60	17.43	16.42	17.47	4.41	1.65	1.68	1.67	1.63
2400	9.01	9.19	9.12	8.93	0.26	5.08	18.33	17.19	18.41	3.76	1.62	1.63	1.63	1.59
2500	8.54	8.69	8.62	8.46	0.23	4.64	19.37	18.09	19.51	3.22	1.58	1.59	1.59	1.55
2600	8.14	8.26	8.19	8.05	0.21	4.17	20.58	19.14	20.77	2.78	1.55	1.55	1.55	1.52
2700	7.81	7.91	7.84	7.72	0.19	3.76	21.91	20.31	22.22	2.44	1.51	1.50	1.51	1.48
2800	7.56	7.63	7.56	7.46	0.17	3.39	23.37	21.59	23.85	2.18	1.48	1.46	1.46	1.45
2900	7.34	7.39	7.32	7.26	0.14	3.02	25.06	23.08	25.67	1.96	1.45	1.42	1.42	1.42
3000	7.19	7.21	7.14	7.10	0.11	2.63	26.82	24.71	27.57	1.79	1.42	1.39	1.39	1.40
3050	7.12	7.14	7.07	7.04	0.10	2.43	27.72	25.57	28.51	1.72	1.41	1.37	1.37	1.39
3100	7.07	7.08	7.01	6.99	0.09	2.26	28.55	26.44	29.36	1.67	1.41	1.35	1.35	1.38
3150	7.03	7.02	6.95	6.94	0.08	2.12	29.42	27.39	30.05	1.61	1.39	1.34	1.34	1.37
3200	6.99	6.97	6.90	6.90	0.09	1.96	30.16	28.34	30.50	1.57	1.39	1.32	1.32	1.36
3250	6.95	6.93	6.85	6.87	0.10	1.79	30.71	29.20	30.66	1.53	1.37	1.30	1.30	1.36
3300	6.93	6.89	6.82	6.85	0.11	1.60	30.89	29.92	30.56	1.50	1.37	1.29	1.29	1.35
3350	6.91	6.87	6.80	6.83	0.12	1.42	30.69	30.24	30.24	1.49	1.35	1.28	1.28	1.34
3400	6.90	6.85	6.78	6.82	0.13	1.25	30.37	30.31	29.75	1.48	1.35	1.26	1.26	1.34
3450	6.90	6.84	6.76	6.82	0.14	1.08	29.91	30.07	29.18	1.48	1.34	1.26	1.25	1.33
3500	6.90	6.82	6.75	6.82	0.15	0.90	29.42	29.73	28.57	1.48	1.33	1.24	1.24	1.33
3550	6.90	6.82	6.75	6.82	0.15	0.72	28.75	29.07	27.96	1.49	1.33	1.23	1.23	1.32
3600	6.91	6.82	6.75	6.83	0.16	0.59	28.12	28.34	27.37	1.50	1.32	1.23	1.22	1.32
3650	6.92	6.82	6.75	6.84	0.17	0.49	27.44	27.50	26.80	1.53	1.32	1.22	1.22	1.32
3700	6.93	6.83	6.76	6.86	0.18	0.62	26.88	26.81	26.27	1.56	1.32	1.21	1.21	1.31
3750	6.95	6.84	6.77	6.87	0.18	0.75	26.32	26.09	25.76	1.58	1.31	1.20	1.20	1.31
3800	6.97	6.85	6.78	6.89	0.19	0.90	25.83	25.48	25.28	1.61	1.31	1.20	1.20	1.30
3850	6.98	6.86	6.79	6.91	0.20	1.06	25.35	24.92	24.85	1.63	1.30	1.19	1.19	1.30
3900	7.01	6.88	6.81	6.93	0.20	1.22	24.87	24.31	24.43	1.66	1.30	1.19	1.19	1.30
3950	7.03	6.90	6.83	6.95	0.20	1.37	24.43	23.77	24.05	1.69	1.29	1.18	1.18	1.30
4000	7.06	6.92	6.85	6.98	0.21	1.50	23.96	23.23	23.70	1.74	1.30	1.18	1.18	1.30
4050	7.08	6.94	6.87	7.00	0.21	1.65	23.64	22.77	23.36	1.77	1.29	1.18	1.18	1.30
4100	7.12	6.97	6.90	7.03	0.22	1.79	23.27	22.28	23.03	1.81	1.29	1.18	1.18	1.29
4150	7.14	6.99	6.92	7.06	0.22	1.93	22.99	21.88	22.71	1.84	1.28	1.18	1.17	1.29
4200	7.17	7.02	6.95	7.09	0.23	2.07	22.68	21.46	22.43	1.87	1.27	1.17	1.17	1.29
4250	7.21	7.05	6.98	7.12	0.23	2.23	22.42	21.07	22.17	1.91	1.28	1.17	1.17	1.29
4300	7.24	7.08	7.01	7.15	0.23	2.35	22.16	20.69	21.90	1.95	1.26	1.17	1.17	1.29
4400	7.31	7.15	7.07	7.22	0.23	2.61	21.67	19.98	21.42	2.03	1.26	1.17	1.17	1.28
4500	7.37	7.21	7.14	7.29	0.23	2.88	21.31	19.38	21.00	2.11	1.25	1.17	1.17	1.28
4600	7.45	7.29	7.21	7.36	0.24	3.14	20.93	18.79	20.58	2.20	1.24	1.17	1.17	1.27
4800	7.60	7.44	7.36	7.50	0.24	3.69	20.27	17.72	19.90	2.38	1.22	1.18	1.18	1.26
5000	7.75	7.62	7.52	7.64	0.23	4.21	19.63	16.80	19.29	2.58	1.20	1.20	1.20	1.25
5200	7.89	7.78	7.68	7.77	0.21	4.67	19.09	16.03	18.78	2.76	1.19	1.22	1.22	1.24
5400	8.05	7.96	7.86	7.92	0.19	5.23	18.59	15.27	18.33	2.98	1.18	1.24	1.25	1.24
5600	8.18	8.12	8.03	8.05	0.15	5.70	18.22	14.63	17.93	3.17	1.18	1.28	1.29	1.25
5800	8.31	8.28	8.19	8.18	0.13	6.17	17.81	14.00	17.48	3.36	1.18	1.32	1.33	1.25
6000	8.39	8.41	8.32	8.28	0.14	6.79	17.41	13.49	17.02	3.48	1.19	1.37	1.38	1.27
6200	8.48	8.54	8.48	8.40	0.14	7.14	16.94	12.98	16.56	3.61	1.21	1.43	1.44	1.30
6400	8.54	8.66	8.60	8.48	0.18	7.66	16.49	12.60	16.09	3.71	1.24	1.51	1.52	1.34
6600	8.58	8.74	8.71	8.55	0.19	7.93	16.04	12.28	15.59	3.78	1.28	1.58	1.60	1.39
6800	8.62	8.82	8.81	8.61	0.20	8.21	15.54	12.00	15.13	3.80	1.33	1.67	1.69	1.45
7000	8.63	8.87	8.88	8.63	0.25	8.36	15.03	11.70	14.63	3.79	1.37	1.76	1.78	1.50
7200	8.67	8.96	8.96	8.66	0.30	8.35	14.43	11.48	14.09	3.82	1.44	1.88	1.88	1.56
7400	8.69	9.03	9.01	8.66	0.37	8.67	13.93	11.34	13.64	3.80	1.51	1.97	1.97	1.62
7600	8.76	9.14	9.08	8.69	0.45	9.08	13.38	11.14	13.13	3.82	1.59	2.08	2.07	1.67
8000	8.82	9.27	9.07	8.67	0.61	9.59	12.59	11.07	12.35	3.72	1.73	2.27	2.21	1.78

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W+

100627

Page 1 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = -40°C

FREQ. (MHz)	TOTAL LOSS ¹				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION			VSWR				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.12	10.35	10.27	10.06	0.29	8.77	16.43	15.52	16.43	5.68	1.67	1.70	1.70	1.66
2300	9.46	9.67	9.59	9.40	0.27	8.21	17.21	16.20	17.23	4.72	1.64	1.67	1.67	1.62
2400	8.92	9.09	9.02	8.83	0.26	7.79	18.10	16.95	18.16	4.01	1.61	1.63	1.63	1.59
2500	8.43	8.58	8.50	8.34	0.24	7.54	19.15	17.87	19.24	3.40	1.58	1.59	1.59	1.56
2600	8.01	8.13	8.05	7.92	0.21	7.18	20.39	18.95	20.49	2.89	1.54	1.54	1.55	1.53
2700	7.69	7.79	7.71	7.60	0.19	6.82	21.66	20.08	21.92	2.54	1.51	1.50	1.52	1.49
2800	7.44	7.51	7.43	7.35	0.17	6.59	23.02	21.28	23.53	2.27	1.47	1.46	1.48	1.46
2900	7.21	7.27	7.19	7.14	0.13	6.31	24.72	22.77	25.34	2.02	1.44	1.42	1.44	1.44
3000	7.05	7.08	7.00	6.97	0.10	5.97	26.42	24.36	27.25	1.84	1.41	1.38	1.39	1.41
3050	6.98	7.00	6.92	6.91	0.10	5.82	27.27	25.16	28.20	1.77	1.40	1.36	1.37	1.39
3100	6.93	6.94	6.85	6.85	0.09	5.69	28.10	26.01	29.07	1.71	1.39	1.34	1.35	1.38
3150	6.87	6.87	6.79	6.80	0.09	5.59	29.08	26.99	29.80	1.64	1.38	1.32	1.33	1.37
3200	6.83	6.81	6.73	6.75	0.10	5.48	29.97	28.04	30.29	1.58	1.37	1.30	1.31	1.36
3250	6.79	6.77	6.68	6.71	0.11	5.35	30.69	29.07	30.50	1.54	1.36	1.28	1.29	1.35
3300	6.77	6.73	6.64	6.68	0.12	5.21	30.90	29.90	30.44	1.50	1.35	1.27	1.28	1.35
3350	6.75	6.71	6.62	6.67	0.13	5.09	30.68	30.26	30.13	1.49	1.34	1.26	1.27	1.34
3400	6.74	6.69	6.60	6.65	0.14	4.97	30.31	30.35	29.65	1.49	1.34	1.24	1.25	1.33
3450	6.74	6.67	6.58	6.65	0.15	4.86	29.83	30.12	29.08	1.49	1.33	1.24	1.24	1.32
3500	6.73	6.66	6.57	6.64	0.16	4.74	29.34	29.78	28.47	1.49	1.32	1.22	1.22	1.31
3550	6.73	6.65	6.56	6.65	0.17	4.63	28.66	29.14	27.86	1.50	1.32	1.22	1.21	1.30
3600	6.74	6.65	6.56	6.65	0.18	4.56	28.03	28.39	27.25	1.51	1.31	1.21	1.20	1.30
3650	6.75	6.66	6.57	6.66	0.19	4.48	27.35	27.51	26.67	1.54	1.31	1.20	1.19	1.30
3700	6.76	6.66	6.57	6.67	0.19	4.39	26.76	26.79	26.13	1.57	1.30	1.19	1.18	1.29
3750	6.78	6.67	6.58	6.69	0.20	4.51	26.16	26.06	25.62	1.60	1.30	1.19	1.18	1.29
3800	6.80	6.69	6.59	6.71	0.20	4.72	25.69	25.41	25.14	1.63	1.30	1.19	1.17	1.29
3850	6.81	6.70	6.61	6.73	0.21	4.92	25.22	24.84	24.69	1.65	1.30	1.18	1.17	1.29
3900	6.84	6.71	6.62	6.75	0.22	5.14	24.78	24.30	24.28	1.68	1.30	1.18	1.17	1.28
3950	6.85	6.73	6.64	6.77	0.22	5.34	24.36	23.78	23.91	1.70	1.29	1.17	1.16	1.29
4000	6.88	6.75	6.66	6.80	0.22	5.52	23.91	23.22	23.55	1.75	1.29	1.17	1.16	1.29
4050	6.91	6.77	6.68	6.82	0.23	5.72	23.54	22.75	23.22	1.78	1.29	1.17	1.16	1.29
4100	6.94	6.80	6.71	6.85	0.23	5.92	23.12	22.21	22.89	1.83	1.28	1.17	1.16	1.28
4150	6.97	6.83	6.74	6.87	0.23	6.11	22.80	21.78	22.57	1.86	1.28	1.17	1.16	1.28
4200	7.00	6.86	6.76	6.90	0.24	6.31	22.50	21.35	22.28	1.90	1.27	1.17	1.16	1.28
4250	7.03	6.88	6.79	6.93	0.24	6.52	22.26	21.01	22.02	1.94	1.27	1.17	1.15	1.27
4300	7.05	6.90	6.81	6.96	0.24	6.69	22.03	20.65	21.76	1.96	1.26	1.17	1.15	1.27
4400	7.12	6.97	6.87	7.03	0.25	7.05	21.51	19.93	21.29	2.05	1.25	1.17	1.15	1.27
4500	7.19	7.04	6.95	7.10	0.25	7.41	21.08	19.28	20.86	2.14	1.25	1.17	1.16	1.27
4600	7.27	7.12	7.02	7.16	0.25	7.78	20.75	18.69	20.45	2.23	1.25	1.17	1.16	1.26
4800	7.40	7.26	7.15	7.30	0.25	8.53	20.12	17.64	19.77	2.40	1.22	1.17	1.18	1.26
5000	7.57	7.44	7.33	7.45	0.24	9.26	19.41	16.66	19.14	2.63	1.20	1.20	1.19	1.25
5200	7.69	7.59	7.47	7.58	0.22	9.92	18.95	15.90	18.63	2.80	1.19	1.23	1.22	1.25
5400	7.85	7.76	7.64	7.71	0.21	10.64	18.42	15.13	18.15	3.04	1.19	1.26	1.24	1.23
5600	7.97	7.92	7.80	7.83	0.17	11.36	18.09	14.53	17.74	3.23	1.19	1.30	1.30	1.26
5800	8.12	8.10	7.99	7.99	0.14	11.97	17.63	13.83	17.29	3.50	1.19	1.34	1.33	1.26
6000	8.13	8.16	8.04	8.02	0.14	12.79	17.37	13.39	16.85	3.52	1.20	1.39	1.39	1.29
6200	8.23	8.30	8.19	8.14	0.16	13.27	16.91	12.85	16.40	3.70	1.22	1.46	1.44	1.31
6400	8.29	8.42	8.31	8.20	0.22	14.13	16.41	12.46	15.94	3.82	1.25	1.54	1.53	1.36
6600	8.37	8.55	8.46	8.31	0.24	14.72	15.90	12.07	15.45	4.01	1.30	1.62	1.62	1.41
6800	8.43	8.65	8.58	8.39	0.26	15.30	15.41	11.78	15.00	4.09	1.35	1.70	1.72	1.47
7000	8.41	8.68	8.62	8.40	0.27	15.80	14.95	11.51	14.54	4.04	1.40	1.81	1.85	1.54
7200	8.45	8.77	8.73	8.46	0.32	15.99	14.32	11.28	14.00	4.12	1.47	1.92	1.97	1.62
7400	8.43	8.79	8.78	8.46	0.35	16.13	13.80	11.09	13.57	4.06	1.54	2.01	2.08	1.68
7600	8.49	8.88	8.85	8.50	0.39	16.25	13.25	10.89	13.05	4.08	1.62	2.11	2.17	1.74
8000	8.54	8.97	8.81	8.59	0.44	17.26	12.50	10.68	12.23	3.94	1.74	2.27	2.28	1.82

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W+

100627

Page 2 of 3



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



4 Way-0° Power Splitter/Combiner

WP4W+

Typical Performance Data

TEST CONDITIONS: INPUT POWER = -10dBm @Temperature = +85°C

FREQ. (MHz)	TOTAL LOSS ¹ (dB)				AMP. UNBAL. (dB)	PHASE UNBAL. (deg.)	ISOLATION (dB)			VSWR (:1)				
	S-1	S-2	S-3	S-4			1-2	2-3	3-4	S	1	2	3	4
2200	10.26	10.48	10.41	10.19	0.29	7.90	16.75	15.84	16.80	4.98	1.68	1.71	1.70	1.66
2300	9.63	9.82	9.75	9.56	0.26	7.46	17.56	16.53	17.62	4.21	1.65	1.68	1.66	1.63
2400	9.08	9.24	9.17	9.00	0.24	7.05	18.50	17.33	18.58	3.58	1.62	1.64	1.62	1.59
2500	8.60	8.74	8.67	8.52	0.22	6.64	19.58	18.27	19.69	3.08	1.59	1.60	1.58	1.55
2600	8.21	8.32	8.24	8.12	0.19	6.28	20.81	19.34	20.98	2.67	1.55	1.55	1.53	1.51
2700	7.88	7.97	7.89	7.79	0.17	5.94	22.21	20.55	22.45	2.35	1.52	1.50	1.49	1.48
2800	7.63	7.69	7.61	7.54	0.15	5.57	23.74	21.89	24.11	2.10	1.48	1.46	1.45	1.44
2900	7.43	7.46	7.39	7.34	0.12	5.21	25.44	23.41	25.96	1.90	1.45	1.43	1.41	1.42
3000	7.28	7.29	7.22	7.19	0.10	4.94	27.23	25.06	27.91	1.74	1.43	1.39	1.37	1.39
3050	7.22	7.22	7.15	7.13	0.09	4.82	28.15	25.94	28.86	1.68	1.41	1.37	1.36	1.38
3100	7.17	7.16	7.09	7.09	0.08	4.67	28.96	26.84	29.71	1.63	1.41	1.35	1.34	1.37
3150	7.12	7.11	7.03	7.04	0.09	4.65	29.76	27.75	30.38	1.58	1.39	1.34	1.33	1.37
3200	7.09	7.06	6.99	7.01	0.10	4.69	30.39	28.63	30.78	1.54	1.39	1.32	1.31	1.36
3250	7.06	7.02	6.95	6.98	0.11	4.75	30.82	29.40	30.90	1.51	1.37	1.31	1.30	1.35
3300	7.04	6.99	6.92	6.96	0.12	4.84	30.94	30.06	30.74	1.48	1.37	1.29	1.29	1.35
3350	7.03	6.97	6.90	6.95	0.13	4.92	30.71	30.30	30.36	1.47	1.35	1.28	1.28	1.34
3400	7.02	6.95	6.88	6.94	0.14	5.00	30.37	30.30	29.83	1.46	1.35	1.26	1.27	1.34
3450	7.01	6.94	6.87	6.94	0.15	5.06	29.85	29.97	29.23	1.46	1.34	1.26	1.26	1.33
3500	7.01	6.92	6.86	6.94	0.15	5.16	29.32	29.54	28.61	1.46	1.33	1.24	1.25	1.33
3550	7.02	6.92	6.85	6.95	0.16	5.24	28.63	28.88	27.99	1.47	1.33	1.23	1.24	1.33
3600	7.02	6.92	6.86	6.96	0.17	5.40	28.02	28.16	27.39	1.48	1.32	1.23	1.23	1.32
3650	7.04	6.93	6.86	6.97	0.18	5.63	27.37	27.33	26.82	1.51	1.32	1.22	1.22	1.32
3700	7.05	6.93	6.87	6.99	0.18	5.92	26.81	26.65	26.28	1.53	1.31	1.21	1.22	1.32
3750	7.07	6.94	6.88	7.00	0.19	6.19	26.24	25.99	25.78	1.55	1.30	1.20	1.21	1.32
3800	7.09	6.95	6.89	7.02	0.20	6.41	25.75	25.34	25.31	1.58	1.30	1.20	1.21	1.31
3850	7.11	6.97	6.90	7.04	0.20	6.64	25.27	24.76	24.87	1.60	1.29	1.19	1.20	1.31
3900	7.13	6.99	6.92	7.06	0.21	6.83	24.79	24.19	24.46	1.64	1.30	1.19	1.20	1.31
3950	7.15	7.00	6.94	7.09	0.21	7.05	24.37	23.68	24.09	1.66	1.29	1.19	1.19	1.31
4000	7.18	7.03	6.97	7.12	0.22	7.34	23.93	23.12	23.73	1.70	1.29	1.18	1.19	1.31
4050	7.21	7.05	6.99	7.14	0.22	7.57	23.61	22.68	23.39	1.73	1.28	1.18	1.19	1.30
4100	7.24	7.07	7.01	7.17	0.23	7.80	23.24	22.19	23.06	1.77	1.28	1.18	1.18	1.30
4150	7.27	7.10	7.04	7.20	0.23	8.00	22.95	21.78	22.74	1.81	1.27	1.18	1.18	1.30
4200	7.30	7.13	7.07	7.23	0.24	8.19	22.66	21.36	22.46	1.84	1.27	1.17	1.18	1.30
4250	7.34	7.17	7.10	7.27	0.24	8.40	22.39	20.98	22.21	1.89	1.27	1.17	1.18	1.30
4300	7.37	7.20	7.13	7.30	0.24	8.63	22.16	20.62	21.94	1.92	1.26	1.17	1.18	1.30
4400	7.45	7.27	7.20	7.37	0.25	9.12	21.68	19.94	21.46	2.01	1.25	1.17	1.17	1.29
4500	7.52	7.34	7.27	7.44	0.25	9.51	21.32	19.33	21.04	2.09	1.25	1.17	1.17	1.28
4600	7.60	7.42	7.35	7.51	0.25	9.92	20.96	18.74	20.62	2.19	1.24	1.17	1.17	1.27
4800	7.75	7.57	7.49	7.65	0.25	10.81	20.32	17.71	19.96	2.37	1.22	1.18	1.18	1.26
5000	7.89	7.73	7.65	7.79	0.25	11.57	19.72	16.85	19.37	2.56	1.20	1.20	1.19	1.25
5200	8.03	7.89	7.80	7.92	0.23	12.31	19.18	16.07	18.88	2.73	1.18	1.22	1.21	1.24
5400	8.19	8.07	7.97	8.07	0.21	12.95	18.69	15.32	18.44	2.95	1.16	1.24	1.23	1.23
5600	8.32	8.24	8.14	8.21	0.18	13.60	18.32	14.69	18.05	3.14	1.15	1.27	1.27	1.23
5800	8.46	8.41	8.31	8.35	0.15	14.22	17.88	14.06	17.63	3.32	1.15	1.31	1.31	1.24
6000	8.56	8.56	8.46	8.46	0.10	14.71	17.46	13.52	17.17	3.45	1.17	1.35	1.36	1.26
6200	8.66	8.69	8.63	8.60	0.09	15.54	16.99	13.03	16.72	3.58	1.18	1.39	1.42	1.29
6400	8.72	8.80	8.77	8.69	0.11	16.31	16.57	12.68	16.26	3.65	1.20	1.46	1.49	1.33
6600	8.76	8.87	8.89	8.76	0.13	17.29	16.13	12.37	15.76	3.68	1.24	1.53	1.57	1.37
6800	8.78	8.93	8.98	8.80	0.20	18.30	15.66	12.11	15.28	3.65	1.29	1.60	1.66	1.41
7000	8.79	8.99	9.06	8.83	0.27	19.38	15.12	11.83	14.75	3.61	1.33	1.70	1.74	1.46
7200	8.82	9.07	9.12	8.83	0.30	20.52	14.57	11.66	14.19	3.58	1.40	1.82	1.81	1.50
7400	8.85	9.16	9.16	8.82	0.34	21.40	14.07	11.51	13.71	3.55	1.48	1.93	1.89	1.55
7600	8.92	9.29	9.21	8.83	0.46	22.23	13.52	11.43	13.19	3.52	1.56	2.05	1.98	1.61
8000	9.04	9.50	9.24	8.83	0.67	23.01	12.68	11.37	12.42	3.48	1.72	2.27	2.15	1.74

¹ Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2

WP4W+

100627

Page 3 of 3

Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see




4 Way-0° Power Splitter/Combiner


WP4W+

Typical Performance Curves


Total Loss




Total Loss S-1 vs. TEMPERATURE




Amplitude Unbalance vs. TEMPERATURE




Phase Unbalance vs. TEMPERATURE



Isolation



Isolation 1-2 vs. TEMPERATURE






REV. X2
WP4W+
100627
Page 1 of 2

4 Way-0° Power Splitter/Combiner

WP4W+

Typical Performance Curves



REV. X2
WP4W+
100627
Page 2 of 2




Mini-Circuits®

IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661


The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Outline Dimensions



PCB Land Pattern



SUGGESTED LAYOUT,
TOLERANCE TO BE WITHIN ± 0.002

Weight: .02 Grams

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .01$; 3 Pl. $\pm .004$

Notes:

- Case material: Plastic.
- Termination finish:
 - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix. See Data sheet.
 - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Tape & Reel Packaging TR-F66



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: www.minicircuits.com/pages/pdfs/tape.pdf




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


THIRD ANGLE PROJECTION



REVISIONS


REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M109251	NEW RELEASE	01/11/07	PW	WP
A	M112849	UPDATED NOTE 3	08/03/07	AV	WP

SUGGESTED MOUNTING CONFIGURATION FOR DQ1225 CASE STYLE, "rx" PIN CONNECTION



NOTES:

1. TRACE WIDTH IS SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS .020" $\pm$.0015"; COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.
3. SIGNAL TRACES ARE NOT ALLOWED INSIDE HATCHED AREAS (APPROX. .030 X .030) AT 4 PLACES AS SHOWN.

-  DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)
 DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED

INITIALS

DATE

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS $\pm$ 3 PL DECIMALS $\pm$.005ANGLES $\pm$ 1°FRACTIONS $\pm$

DRAWN

PW

01/10/07

CHECKED

IL

01/11/07

APPROVED

WP

01/11/07



Mini-Circuits®

13 Neptune Avenue
Brooklyn NY 11235

PL, rx, DQ1225, WP4, TB-395+

SIZE
ACODE IDENT
15542DRAWING NO:
98-PL-259REV:
A

FILE: 98PL259

SCALE: 10:1


SHEET: 1 OF 1

 Mini-Circuits®


THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THEREON. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95

Evaluation Board and Circuit




TB-395+



Schematic Diagram

Notes:

1. SMA Female connectors.
2. PCB Material: Rogers R04350 or equivalent,
Dielectric Constant=3.5, Thickness=.020 inch.





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D