

DC Pass

Matching Transformer

Z7550-BMBF+

50/75Ω

DC to 3000 MHz



Generic photo used for illustration purposes only

CASE STYLE: QP1876-1

The Big Deal

- Low Insertion loss 0.6 dB typ.
- 2W Power Handling
- BNC-F (50Ω) to BNC-M (75Ω) Connectors

Product Overview

Mini-Circuits' Z7550-BMBF+ is a coaxial 50/75Ω matching transformer covering the DC to 3000 MHz frequency range, supporting impedance matching in a wide range of systems including CATV, broadband networks, matching antenna systems and more. This model is ideal for 50/75Ω impedance matching in systems where minimizing overall signal loss is a priority. The transformer handles RF input power up to 2W and comes housed in a rugged, compact aluminum alloy case (1.25 x 1.25 x 0.94") with BNC-F (50Ω) to BNC-M (75Ω) connectors.

Key Features

Feature	Advantages
Wideband, DC to 3000 MHz	Supports a wide variety of applications including CATV and DOCSIS® 3.1 systems and equipment.
Low insertion loss, 0.6 dB typ.	Enables excellent signal power transmission from input to output, minimizing overall system losses.
2W Power handling	Supports a range of system power requirements.
Compact size, 1.25 x 1.25 x 0.94"	Accommodates tight space requirements for crowded system layouts.
Connectorized package BNC-F (50Ω) to BNC-M (75Ω) connectors	Supports connections between components with different connector types.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



DC Pass Matching Transformer

Z7550-BMBF+

50/75Ω DC to 3000 MHz

Maximum Ratings


Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
DC Current	5A max.
DC Resistance	0.2Ω max.

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

PORT - 1	BNC-Male(75Ω)
PORT - 2	BNC-Female(50Ω)

Outline Drawing




Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	Wt.
1.25	1.25	.94	.63	.47	1.00	.13	.13	grams
31.75	31.75	23.88	16.00	11.94	25.40	3.30	3.30	51

Note: Please refer to case style drawing for details

Functional Schematic



Features

- Low loss (0.6 dB typ.) matching device
- Wide band coverage, DC-3000 MHz
- Connectorized package

Applications

- Impedance matching
- CATV
- Matching antenna systems



Generic photo used for illustration purposes only

CASE STYLE: QP1876-1
Connectors Model
75Ω BNC-M Z7550-BMBF+
50Ω BNC-F

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range	-	DC	-	3000	MHz
Insertion Loss	10	-	-	0.5	dB
	950 - 2500	-	0.5	1.0	
VSWR	10	-	-	1.8	:1
	950 - 2500	-	-	1.6	
Power	2500 - 3000	-	1.6	-	W
	DC - 3000	-	-	2	


Typical Performance Data

Frequency (MHz)	Insertion Loss (dB)	VSWR	
		50 Ω	75 Ω
10	0.01	1.50	1.47
100	0.07	1.49	1.46
250	0.18	1.44	1.44
500	0.31	1.34	1.36
950	0.21	1.22	1.18
1500	0.30	1.10	1.12
1750	0.38	1.08	1.12
2300	0.47	1.29	1.21
2500	0.50	1.25	1.12
3000	0.71	1.30	1.38

Z7550-BMBF+ INSERTION LOSS



Z7550-BMBF+ VSWR



Notes




- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/VCLStore/terms.jsp



Typical Performance Data


FREQ.	INSERTION LOSS	INPUT RETURN LOSS (50Ω)	OUTPUT RETURN LOSS (75Ω)
(MHz)	(dB)	(dB)	(dB)
1	0.01	14.05	14.43
10	0.01	13.92	14.44
15	0.01	13.91	14.46
20	0.01	13.90	14.46
30	0.02	13.89	14.47
40	0.03	13.88	14.50
50	0.03	13.89	14.51
60	0.04	13.89	14.53
70	0.05	13.90	14.55
80	0.05	13.91	14.57
90	0.06	13.92	14.59
100	0.07	13.93	14.62
150	0.10	14.04	14.74
200	0.14	14.20	14.86
250	0.18	14.41	14.96
300	0.21	14.66	15.12
350	0.24	14.97	15.34
400	0.27	15.32	15.60
450	0.29	15.70	15.90
500	0.31	16.12	16.33
525	0.32	17.12	16.61
550	0.33	16.57	16.90
600	0.34	17.03	17.47
650	0.33	17.51	18.02
700	0.32	17.98	18.71
750	0.30	18.45	19.42
800	0.26	18.91	19.97
850	0.23	19.34	20.47
900	0.21	19.74	21.12
950	0.21	20.09	21.72
1000	0.22	20.41	22.12
1025	0.23	21.41	22.31
1050	0.24	20.66	22.50
1100	0.26	20.85	22.74
1150	0.27	20.98	22.65
1200	0.28	21.04	22.37
1225	0.28	22.04	22.23
1250	0.28	21.03	22.12
1300	0.28	20.97	22.07
1350	0.28	20.85	22.32
1400	0.28	20.66	22.90
1450	0.29	20.41	23.82
1500	0.30	20.10	24.99
1550	0.31	19.74	26.14
1600	0.32	19.35	26.91
1650	0.34	18.94	27.15
1700	0.36	18.52	26.52
1750	0.38	18.14	25.09
1800	0.40	17.79	23.40
1850	0.41	17.48	21.98
1900	0.42	17.24	21.02
1925	0.41	18.24	20.65
1950	0.41	17.09	20.32
2000	0.41	17.02	19.79
2050	0.40	17.04	19.52
2100	0.40	17.18	19.54
2150	0.41	17.41	19.52
2200	0.43	17.74	19.46
2250	0.45	18.13	19.80
2300	0.47	18.51	20.58

Typical Performance Curves



Outline Dimensions

QP1876-1



CASE#	A	B	C	D	E	F	G	H	WT.GRAMS
QP1876-1	1.25 (31.75)	1.25 (31.75)	.94 (23.88)	.63 (16.00)	.47 (11.94)	1.000 (25.40)	.13 (3.30)	.13 (3.30)	51

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:

For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I