



MMIC REFLECTIONLESS


# High Pass Filter

**XHF-581M+**

50Ω 580 to 3000 MHz

## THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Good stopband rejection, 35 dB typ.
- Temperature stable, up to 105°C
- Small size, 5 x 5 mm
- Protected by US Patents 8,392,495; 9,705,467, additional patent pending
- Protected by China Patent 201080014266.1
- Protected by Taiwan Patent I581494

*Generic photo used for illustration purposes only*

CASE STYLE: DG1677-2

### +RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Cellular
- WiFi
- GPS
- Radio astronomy
- Radio location

## PRODUCT OVERVIEW

Mini-Circuits' XHF-581M+ two-section reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

## KEY FEATURES

Feature	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals falling in filter stopband, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
High stopband rejection, up to 50 dB	Ideal for applications where suppression of strong spurious signals and intermodulation products is needed.
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stopband; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect passband signals. Low & highpass filters can be cascaded to realize bandpass filters.
Excellent power handling in a tiny surface mount device up to 7W in passband	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.
Small size, 5x5mm QFN	Allows replacement of filter/attenuator pairs with a single reflectionless filter, saving board space.
Excellent repeatability of RF performance	Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.
Operating temperature up to 105 °C	Suitable for operation close to high power components.

IPD – Integrated Passive Device, is a GaAs semiconductor process





MMIC REFLECTIONLESS

## High Pass Filter

XHF-581M+

50Ω 580 to 3000 MHz

ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	DC - F'	DC - 280	28	35	—	dB
	F' - F1	280 - 330	20	27	—	
	Frequency Cut-off	F2	—	3.0	—	:1
	VSWR	DC - F1	—	1.3	—	
Pass Band	Insertion Loss	F3 - F5	—	0.6	2.1	dB
	VSWR	F3 - F4	—	1.2	—	:1
		F4 - F5	—	1.6	—	

1. Measured on Mini-Circuits Characterization Test Board TB-944-581M+

ABSOLUTE MAXIMUM RATINGS<sup>2</sup>


Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C
RF Power Input, Passband (F3-F5) <sup>3</sup>	+32 dBm at +25°C
RF Power Input, Stopband (DC-F3) <sup>4</sup>	+35 dBm at +25°C

2. Permanent damage may occur if any of these limits are exceeded.

3. Passband rating derates linearly to +29 dBm at +105°C ambient



4. Stopband rating derates linearly to +32 dBm at +105°C ambient

## SPECIFICATION DEFINITION






### SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	3	RF Input Pad
RF-OUT	22	RF Output Pad
GND	2,4,21,23	Connected to ground
NC (GND Externally)	1,5-20,24-32 & paddle	No internal connection

### PRODUCT MARKING



Marking may contain other features or characters for internal lot control



MMIC REFLECTIONLESS



# High Pass Filter

**XHF-581M+**

50Ω 580 to 3000 MHz

## TYPICAL PERFORMANCE DATA AT +25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	43.12	2.05
50	32.03	1.87
100	33.36	1.54
200	33.77	1.16
280	30.86	1.17
300	27.81	1.15
330	23.56	1.15
470	3.12	1.09
500	2.47	1.11
580	1.56	1.14
600	1.43	1.14
800	0.77	1.09
1000	0.54	1.08
1200	0.45	1.14
1400	0.40	1.21
1600	0.39	1.29
2000	0.42	1.43
2400	0.49	1.57
3000	0.61	1.77
3200	0.66	1.83





MMIC REFLECTIONLESS

# High Pass Filter

**XHF-581M+**

50Ω 580 to 3000 MHz


ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASHBOARD. TO ACCESS [CLICK HERE](#)

Performance Data	Data Table
	Swept Graphs
	S-Parameter (S3P Files) Data Set (.zip file)
Case Style	DG1677-2 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F68 7" reels with 20, 50, 100, 200, 500 ,1000 devices 13" reels with 2000, 3000, 4000 devices
Suggested Layout for PCB Design	PL-518
Evaluation Board	TB-944-581M+
Environmental Ratings	ENV82

## ESD RATING

Human body model (HBM): Class 2 (Pass 2000V) in accordance with ANSI/ESD 5.1-2001

## MSL TEST FLOW CHART





MMIC REFLECTIONLESS


# High Pass Filter

XHF-581M+

50Ω 580 to 3000 MHz

## REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter




Figure 2. IF output reflection spectrum with conventional filter




Figure 3. IF output reflection spectrum with reflectionless filter

### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)






# MMIC Reflectionless High Pass Filter

**XHF-581M+**

## Typical Performance Data


FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-55°C	@25°C	@+105°C	@-55°C	@+25°C	@+105°C	@-55°C	@+25°C	@+105°C
10	46.20	43.45	42.51	11.37	9.44	8.22	11.05	9.25	8.07
50	31.65	32.03	32.35	12.07	10.47	9.45	11.88	10.34	9.36
100	32.47	33.36	33.76	14.53	13.43	12.64	14.65	13.51	12.78
200	33.81	33.78	33.40	26.10	22.74	20.38	25.86	22.49	20.32
280	32.53	30.86	29.42	23.06	22.05	20.82	23.68	22.27	21.12
300	28.80	27.81	26.65	24.44	23.06	21.79	25.44	23.41	22.19
400	5.85	7.08	7.97	38.33	33.35	29.75	40.46	34.33	30.05
470	2.38	3.12	3.76	31.64	28.50	26.29	30.28	27.72	25.72
500	1.86	2.47	3.00	28.82	26.15	24.39	27.74	25.49	23.88
580	1.15	1.56	1.93	25.81	24.15	22.59	25.45	23.62	22.15
700	0.72	1.00	1.25	26.57	25.28	23.78	26.53	24.86	23.87
1000	0.35	0.54	0.72	31.32	27.88	25.31	29.80	28.12	24.90
1400	0.22	0.40	0.56	21.55	20.33	19.86	21.26	20.57	19.74
1500	0.21	0.39	0.56	19.92	19.08	18.45	19.63	19.31	18.24
2000	0.22	0.42	0.60	15.68	15.00	14.62	15.56	15.14	14.55
2500	0.31	0.51	0.70	12.48	12.67	12.76	12.36	12.78	12.74
3000	0.41	0.61	0.81	10.80	11.16	11.37	10.83	11.21	11.37
3500	0.49	0.73	0.95	9.76	10.00	10.48	9.76	10.01	10.49
4000	0.59	0.88	1.11	8.89	8.97	9.42	8.92	8.96	9.46
4500	0.67	1.05	1.41	8.32	8.04	7.94	8.38	8.02	8.01
5000	0.85	1.31	1.73	7.46	7.18	7.16	7.53	7.27	7.36
5500	1.22	1.60	2.05	6.01	6.23	6.12	6.09	6.22	6.17
6000	1.65	1.95	2.36	5.01	5.56	5.88	5.05	5.58	6.02
6500	2.25	2.58	3.04	4.46	5.18	5.64	4.58	5.29	5.84
7000	4.95	5.58	5.46	5.52	6.42	7.19	6.33	6.96	7.46
7500	2.31	2.57	2.87	6.41	6.28	6.16	6.41	6.38	6.33
8000	1.50	2.17	2.75	6.05	5.48	5.37	6.08	5.60	5.37
8500	1.31	1.98	2.54	5.91	5.66	5.71	5.94	5.81	5.95
9000	1.16	1.74	2.31	6.52	6.44	6.70	6.60	6.63	6.66
9500	1.12	1.47	1.85	6.57	7.96	9.99	6.76	8.24	10.60
10000	0.97	1.27	1.74	8.12	10.73	14.72	8.43	11.39	14.80
10500	0.76	1.37	2.05	13.18	15.22	18.80	15.05	18.82	24.74
11000	1.36	2.28	3.34	13.13	12.89	12.92	20.06	16.40	13.77
11500	3.49	5.05	6.48	7.45	7.54	8.91	8.26	8.64	9.54
12000	8.52	10.06	10.57	5.26	6.05	7.69	5.29	6.64	8.09
12500	11.36	9.28	8.14	6.87	8.44	9.05	6.99	8.79	9.50
13000	4.92	4.61	4.72	10.35	11.88	12.68	11.24	13.02	14.26
13500	2.43	3.00	3.75	13.55	13.02	12.73	16.21	14.48	12.41
14000	2.00	2.94	3.99	10.17	8.49	7.34	10.70	8.71	8.10
14500	2.71	3.65	4.71	5.51	5.31	5.85	5.41	5.32	5.84
15000	3.98	4.58	5.83	2.76	3.69	3.71	3.03	3.61	3.81
15500	4.87	5.39	6.43	2.41	2.91	3.35	2.00	2.80	3.74
16000	5.46	5.86	6.74	1.60	2.68	3.30	1.54	2.54	3.41
16500	4.98	5.40	6.62	2.35	3.67	3.86	2.35	3.55	3.99
17000	18.94	17.66	17.31	1.25	2.21	3.48	1.51	2.18	3.43
17500	11.01	12.37	13.54	1.13	2.06	2.55	1.38	1.90	2.48
18000	11.23	12.31	12.62	2.08	2.56	3.68	1.51	2.43	3.86
18500	10.03	11.41	12.95	3.66	2.77	2.19	2.55	2.71	2.17
19000	9.69	10.66	11.83	2.10	2.24	3.29	2.56	2.24	3.18
19500	10.72	10.82	12.41	0.66	1.74	2.10	0.76	1.81	2.54
20000	11.68	11.34	12.66	0.51	1.49	2.63	0.65	1.63	3.13
20500	12.36	11.93	12.65	0.09	1.44	2.66	0.37	1.61	2.79
21000	11.71	12.53	13.42	0.58	1.51	3.58	0.93	1.76	3.48
21500	11.96	13.16	14.42	0.57	1.71	2.83	0.93	2.09	3.25
22000	12.09	13.86	15.18	1.23	2.04	3.32	1.53	2.52	4.54
22500	12.59	14.59	16.04	1.81	2.56	3.24	1.93	3.15	4.49
23000	13.90	15.13	15.57	2.59	3.32	4.40	2.91	3.86	4.93
23500	15.12	14.23	14.43	2.72	4.16	4.59	3.60	4.52	5.08
24000	13.34	12.19	13.28	3.62	4.32	3.84	3.46	4.37	3.87
24500	11.33	11.04	12.87	2.58	3.58	3.25	3.36	3.39	3.72
25000	11.07	11.02	12.53	1.54	2.66	3.50	1.54	2.39	2.96
25500	11.43	11.48	12.62	0.99	2.00	3.36	0.88	1.77	3.07
26000	11.52	11.92	12.42	0.69	1.66	3.39	0.28	1.48	3.26

Typical Performance Curves






## Outline Dimensions



## PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm .002$

CASE #	A	B	C MAX	C MIN	D	E	F	G	H	J
DG1677-2	.197 (5.00)	.197 (5.00)	.039 (1.00)	.031 (0.80)	.008 (0.20)	.142 (3.60)	.142 (3.60)	.009 (0.23)	- -	.016 (0.40)
CASE #	K	L	M	N	P	Q	R	S	WT. GRAM	
DG1677-2	.020 (0.50)	.193 (4.90)	.193 (4.90)	.110 (2.79)	.012 (0.30)	.035 (0.89)	.110 (2.79)	.008 (0.20)	.05	

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .005$

### Notes:

- Case material: Plastic.
- Termination finish:

For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier transitioning to Matte-Tin.

All models, (+) suffix. See Data sheet.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



RF/IF MICROWAVE COMPONENTS

# Tape & Reel Packaging TR-F68



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
12	8	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000
		13	Standard	2000
				3000
				4000

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M162495	NEW RELEASE	06/15/17	GF	RS

SUGGESTED MOUNTING CONFIGURATION FOR  
DG1677-2 CASE STYLE, "32FL01" PIN CONNECTION

NOTES:

1. TRACE WIDTH & GAP ARE SHOWN FOR ROGERS RO4350B WITH DIELECTRIC THICKNESS .010"  $\pm$  .001"; COPPER: 1/2 OZ. EACH SIDE.  
FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.




DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER)



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

UNLESS OTHERWISE SPECIFIED	INITIALS	DATE
DIMENSIONS ARE IN INCHES	DRAWN GF	06/14/17
TOLERANCES ON:	CHECKED IL	06/15/17
2 PL DECIMALS $\pm$	APPROVED RS	06/15/17
3 PL DECIMALS $\pm$ .005		
ANGLES $\pm$		
FRACTIONS $\pm$		

 Mini-Circuits®

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS. EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO. THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.

ASHEETA1.DWG REV:A DATE:01/12/95




**Mini-Circuits®**

13 Neptune Avenue  
Brooklyn NY 11235


PL, 32FL01, DG1677-2, TB-944+

SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-518	OR
FILE:	98PL518	SCALE:	10:1
		SHEET:	1 OF 1

# Evaluation Board and Circuit



TB-944-581M+




PINS 1,5-8,9-20,24-32 - NOT CONNECTED.

Schematic Diagram

## Notes:

1. 50 Ohm SMA Female connectors.
2. PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.010 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215