

DC Pass Bi-Directional Coupler

75Ω Up to 100W 700 to 2500 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

* Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	4
COUPLED (forward)	2
COUPLED (reverse)	3

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G
2.00	2.00	.88	.90	.156	1.688	.125
50.80	50.80	22.35	22.86	3.96	42.88	3.18
H	J	K	L	M	wt	
.38	---	.50	1.00	1.25	grams	
9.65	---	12.70	25.40	31.75	225	

Features

- excellent mainline loss, 0.15 dB typ.
- excellent directivity, 25 dB typ.
- high power, up to 100W
- rugged shielded case
- DC current through input to output 2.0A Max. at 50 watt RF input power

Applications

- cable tv
- power leveling & monitoring
- VSWR measurement



Generic photo used for illustration purposes only

CASE STYLE: DD477-1

Connectors	Model
N-TYPE	ZABDC20-25H75+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Bi-Directional Coupler Electrical Specifications

FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT (W)
f_L - f_U	Nom.	Flatness	Typ.	Max.	Typ.	Min.	Typ.	Max.
700-2500			0.15	0.35	25	15	1.08	25
800-1000	21.5±1.0	±0.95	0.10	0.30	27	22	1.08	100
1000-1300	20±0.8	±0.95	0.15	0.35	27	20	1.08	50
1300-2200	18.5±1.0	±0.7	0.15	0.35	25	17	1.08	50
2200-2500	18.5±1.0	±0.7	0.15	0.35	18	15	1.08	25


1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
700.00	0.07	23.45	23.45	27.55	27.50	34.81	34.65	33.64	33.85
800.00	0.07	22.41	22.41	27.34	27.33	32.60	32.55	31.58	31.93
1000.00	0.09	20.85	20.86	26.91	27.33	29.85	29.89	29.17	29.13
1100.00	0.10	20.24	20.25	26.77	27.44	29.14	29.39	28.78	28.99
1300.00	0.12	19.29	19.29	26.66	27.95	28.17	28.04	27.88	28.11
1500.00	0.16	18.72	18.71	26.90	28.73	29.02	29.00	30.31	30.70
1700.00	0.18	18.26	18.24	27.53	29.85	31.79	32.85	40.91	40.80
2000.00	0.16	18.13	18.11	26.08	27.79	41.10	43.50	31.19	30.29
2200.00	0.13	18.33	18.32	22.74	23.99	33.31	33.65	24.74	24.89
2500.00	0.20	19.29	19.29	18.56	19.52	27.08	27.97	22.95	23.50



Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. B
M151107
ED-13230
ZABDC20-25H75+
WP/CP/AM
200505
Page 1 of 1

Bi-Directional Coupler

ZABDC20-25H75+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
700.0	0.07	0.07	23.45	23.45	27.50	27.55	34.81	34.65	33.64	33.85
750.0	0.07	0.07	23.13	23.13	27.43	27.49	34.11	33.80	32.73	33.02
800.0	0.07	0.07	22.41	22.41	27.33	27.34	32.60	32.55	31.58	31.93
850.0	0.07	0.07	21.97	21.97	27.27	27.18	31.98	32.42	31.29	31.70
900.0	0.08	0.08	21.56	21.57	27.24	27.05	31.56	31.30	30.84	30.62
950.0	0.08	0.08	21.20	21.20	27.26	26.96	30.09	30.68	29.16	29.71
1000.0	0.09	0.09	20.85	20.86	27.33	26.91	29.85	29.89	29.17	29.13
1050.0	0.09	0.09	20.54	20.54	27.38	26.86	28.93	29.19	28.22	28.51
1100.0	0.10	0.09	20.24	20.25	27.44	26.77	29.14	29.39	28.78	28.99
1150.0	0.10	0.09	19.97	19.98	27.54	26.70	28.73	28.89	28.59	28.74
1200.0	0.10	0.10	19.72	19.73	27.68	26.70	28.60	28.85	28.47	28.78
1250.0	0.12	0.11	19.50	19.50	27.82	26.69	28.51	28.44	28.26	28.35
1300.0	0.12	0.11	19.29	19.29	27.95	26.66	28.17	28.04	27.88	28.11
1350.0	0.14	0.12	19.10	19.09	28.15	26.68	28.67	28.46	28.65	28.79
1400.0	0.16	0.14	18.81	18.81	28.56	26.83	28.79	28.67	29.44	29.83
1500.0	0.16	0.14	18.72	18.71	28.73	26.90	29.02	29.00	30.31	30.70
1600.0	0.17	0.15	18.42	18.41	29.34	27.22	30.08	30.43	33.54	33.96
1700.0	0.18	0.16	18.26	18.24	29.85	27.53	31.79	32.85	40.91	40.80
1800.0	0.18	0.16	18.15	18.14	29.94	27.63	33.93	35.78	43.45	41.26
1900.0	0.17	0.15	18.11	18.09	29.26	27.19	37.77	41.02	37.26	35.39
2000.0	0.16	0.15	18.13	18.11	27.79	26.08	41.10	43.50	31.19	30.29
2100.0	0.15	0.15	18.20	18.19	25.89	24.49	39.36	38.88	27.35	27.13
2200.0	0.13	0.14	18.33	18.32	23.99	22.74	33.31	33.65	24.74	24.89
2250.0	0.14	0.15	18.38	18.37	23.46	22.25	32.78	32.98	24.40	24.61
2300.0	0.15	0.16	18.51	18.50	22.27	21.22	31.52	31.72	24.04	24.24
2350.0	0.15	0.17	18.63	18.62	21.56	20.50	29.56	29.79	23.32	23.46
2400.0	0.17	0.19	18.78	18.77	20.91	19.90	28.86	29.55	23.06	23.48
2450.0	0.19	0.22	18.93	18.93	20.33	19.36	28.67	29.03	23.31	23.62
2500.0	0.20	0.23	19.29	19.29	19.52	18.56	27.08	27.97	22.95	23.50



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site.
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINN-CIRCUITS At: www.minicircuits.com

RF/MW MICROWAVE COMPONENTS



REV. X1

ZABDC20-25H75+





12/31/2008

Page 1 of 1

Bi-Directional Coupler

ZABDC20-25H75+

Typical Performance Curves



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS




REV. X1

ZABDC20-25H75+

12/31/2008

Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
DD477-1	2.00 (50.80)	2.00 (50.80)	.88 (22.35)	.90 (22.86)	.156 (3.96)	1.688 (42.88)	.125 (3.18)	.38 (9.65)	-- --	.50 (12.70)	1.00 (25.40)	1.25 (31.75)	225

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I