

DC Pass

Bi-Directional Coupler

75Ω Up to 100W 700 to 2500 MHz

ZABDC20-25H75F+

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

* Case temperature is defined as temperature on ground leads.
Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

INPUT	1
OUTPUT	4
COUPLED (forward)	2
COUPLED (reverse)	3


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
2.00	2.00	.88	.90	.156	1.688	.125
50.80	50.80	22.35	22.86	3.96	42.88	3.18
H	J	K	L	M		wt
.38	---	.50	1.00	1.25		grams
9.65	---	12.70	25.40	31.75		225

Electrical Schematic



Features

- excellent mainline loss, 0.3 dB typ.
- excellent directivity, 25 dB typ.
- high power, up to 100W
- rugged shielded case
- DC current through input to output 2.0A Max. at 50 watt RF input power

Applications

- cable tv
- power leveling & monitoring
- VSWR measurement



Generic photo used for illustration purposes only

CASE STYLE: DD477-1

Connectors Model
F-TYPE ZABDC20-25H75F+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications

Parameter	Condition (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		700	—	2500	MHz
Mainline Loss	700 - 1000	—	0.2	0.4	dB
	1000 - 1300	—	0.3	0.5	
	1300 - 2200	—	0.3	0.5	
	2200 - 2500	—	0.3	0.5	
Coupling	700 - 800	—	22.7±1.0	—	dB
	800 - 1000	—	21.5±1.0	—	
	1000 - 1300	—	20±0.8	—	
	1300 - 2200	—	18.5±1.0	—	
Coupling Flatness(±)	2200 - 2500	—	18.5±1.0	—	dB
	700 - 800	—	±0.7	—	
	800 - 1000	—	±0.95	—	
	1000 - 1300	—	±0.95	—	
Directivity	1300 - 2200	—	±0.9	—	dB
	2200 - 2500	—	±0.7	—	
	700 - 1000	22	27	—	dB
	1000 - 1300	20	27	—	
Return Loss (Input)	1300 - 2200	17	25	—	
	2200 - 2500	15	18	—	
Return Loss (Output)	700 - 2500	—	23.0	—	dB
Return Loss (Coupling)	700 - 2500	—	23.0	—	dB
Input Power	700 - 1000	—	—	100	W
	1000 - 1300	—	—	50	
	1300 - 2200	—	—	50	
	2200 - 2500	—	—	25	

1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB)		Coupling (dB)		Directivity (dB)		Return Loss (dB)		
	In-Out	In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
700.0	0.13	23.27	23.28	28.60	29.60	29.95	29.66	28.43	26.83
800.0	0.14	22.24	22.26	28.66	29.74	29.57	28.82	27.18	26.99
1000.0	0.21	20.69	20.71	27.91	29.22	26.40	26.71	24.50	24.83
1100.0	0.22	20.09	20.10	27.59	29.06	25.39	25.63	24.00	23.48
1200.0	0.22	19.60	19.57	26.95	28.56	25.72	25.55	23.29	23.58
1700.0	0.37	18.21	18.27	24.40	24.57	24.75	24.27	22.64	23.81
1900.0	0.31	17.87	17.96	23.13	24.92	23.66	26.58	24.29	24.24
2000.0	0.30	17.82	17.95	22.36	24.01	24.70	27.01	24.93	24.84
2200.0	0.37	17.96	18.16	21.16	22.30	29.43	29.09	27.65	28.37
2300.0	0.37	18.06	18.30	20.55	21.49	29.94	31.59	31.64	32.62
2500.0	0.32	18.50	18.82	19.55	19.94	33.91	31.78	38.42	32.19



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. A
M151107
ED-13230A
ZABDC20-25H75F+
WP/CP/AM
200505
Page 1 of 1

DC PASS Bi-Directional Coupler

ZABDC20-25H75F+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
100.0	0.01	0.01	39.60	39.69	28.89	29.67	46.05	45.52	46.86	42.19
300.0	0.05	0.04	30.18	30.20	29.15	29.21	38.35	37.89	37.78	34.68
500.0	0.10	0.10	25.93	25.97	29.33	29.51	33.15	33.22	31.96	30.35
600.0	0.13	0.13	24.47	24.51	29.50	28.97	31.15	30.48	29.46	29.89
700.0	0.13	0.13	23.27	23.28	29.60	28.60	29.95	29.66	28.43	26.83
750.0	0.14	0.14	22.74	22.76	29.48	28.56	29.55	29.09	27.42	26.83
800.0	0.14	0.14	22.24	22.26	29.74	28.66	29.57	28.82	27.18	26.99
850.0	0.15	0.15	21.80	21.81	29.70	28.35	28.80	28.24	26.39	25.71
900.0	0.16	0.16	21.40	21.41	29.51	28.14	27.93	27.93	25.89	25.30
950.0	0.19	0.17	21.02	21.05	29.56	28.09	27.17	27.53	25.20	24.92
1000.0	0.21	0.18	20.69	20.71	29.22	27.91	26.40	26.71	24.50	24.83
1050.0	0.23	0.21	20.39	20.39	29.24	27.92	25.70	26.03	24.13	25.34
1100.0	0.22	0.22	20.09	20.10	29.06	27.59	25.39	25.63	24.00	23.48
1150.0	0.23	0.22	19.84	19.81	28.87	27.22	25.56	25.68	23.54	24.02
1200.0	0.22	0.22	19.60	19.57	28.56	26.95	25.72	25.55	23.29	23.58
1250.0	0.22	0.21	19.45	19.31	28.32	26.63	25.43	25.39	23.40	24.02
1300.0	0.23	0.22	19.48	19.10	28.06	25.96	25.10	25.21	23.09	22.15
1350.0	0.23	0.22	19.29	18.91	27.83	25.81	24.70	25.13	22.49	23.35
1400.0	0.26	0.26	19.00	18.75	27.52	25.56	24.02	24.60	22.16	23.05
1450.0	0.28	0.28	18.79	18.60	27.28	25.37	23.33	24.21	21.96	23.17
1500.0	0.32	0.34	18.64	18.49	26.74	24.86	23.19	23.68	21.93	22.84
1600.0	0.37	0.41	18.43	18.40	25.91	24.00	23.61	23.57	21.68	23.99
1700.0	0.37	0.39	18.21	18.27	24.57	24.40	24.75	24.27	22.64	23.81
1800.0	0.35	0.33	18.01	17.90	23.31	24.00	24.31	25.56	23.23	24.16
1900.0	0.31	0.29	17.87	17.96	24.92	23.13	23.66	26.58	24.29	24.24
2000.0	0.30	0.27	17.82	17.95	24.01	22.36	24.70	27.01	24.93	24.84
2050.0	0.31	0.28	17.84	17.97	23.66	22.08	25.88	27.97	25.61	25.62
2100.0	0.33	0.32	17.88	18.02	23.25	21.77	28.13	27.83	25.85	27.01
2150.0	0.35	0.34	17.91	18.09	22.72	21.46	29.33	28.53	27.39	26.86
2200.0	0.37	0.34	17.96	18.16	22.30	21.16	29.43	29.09	27.65	28.37
2250.0	0.37	0.35	18.00	18.24	21.87	20.82	30.12	30.23	29.28	27.75
2300.0	0.37	0.32	18.06	18.30	21.49	20.55	29.94	31.59	31.64	32.62
2350.0	0.37	0.31	18.15	18.41	21.11	20.27	29.44	31.93	33.26	27.22
2400.0	0.36	0.32	18.26	18.54	20.75	19.96	29.77	31.92	34.85	29.55
2450.0	0.35	0.32	18.39	18.66	20.39	19.73	31.24	31.56	35.65	33.39
2500.0	0.32	0.30	18.50	18.82	19.94	19.55	33.91	31.78	38.42	32.19
2600.0	0.28	0.28	18.85	19.17	19.08	19.09	38.91	30.70	37.26	30.94
2700.0	0.28	0.26	19.37	19.66	18.21	18.60	40.28	29.06	32.15	34.56
2800.0	0.38	0.27	20.04	20.24	17.26	17.95	34.93	28.16	30.66	34.73
2900.0	0.44	0.33	20.83	20.93	16.15	17.17	34.49	29.19	29.15	34.73
3000.0	0.44	0.43	21.70	21.77	14.92	16.01	40.89	28.90	30.97	32.33



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com





IF/RF MICROWAVE COMPONENTS

REV. OR
ZABDC20-25H75F+
12/30/2014
Page 1 of 1

DC PASS Bi-Directional Coupler

ZABDC20-25H75F+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. OR
ZABDC20-25H75F+
12/30/2014
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
DD477-1	2.00 (50.80)	2.00 (50.80)	.88 (22.35)	.90 (22.86)	.156 (3.96)	1.688 (42.88)	.125 (3.18)	.38 (9.65)	-- --	.50 (12.70)	1.00 (25.40)	1.25 (31.75)	225

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I