

Engineering Development Model

DC PASS

Bi-Directional Coupler

ZABDC20-ED11579/4

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



SMA version shown
CASE STYLE : DD477-1


ELECTRICAL SPECIFICATIONS 50 Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		800		2500	MHz
Coupling	Nominal		21.35 $\pm$ 0.9		dB
	Flatness		$\pm$ 0.9		dB
Mainline Loss*	800-2500 MHz		0.20		dB
Directivity	800-2500 MHz		28		dB
VSWR	800-2500 MHz		1.05		(:1)
RF Power Input	800-2500 MHz			50	W
	800-1000 MHz			100	
	1300-2500 MHz			50	

Note: * Mainline loss includes theoretical coupled power loss of 0.029 dB at 21.7 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

COAXIAL CONNECTIONS	
INPUT	1
OUTPUT	4
COUPLED FORWARD	2
COUPLED REVERSE	3

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.

Bi-Directional Coupler

ZABDC20-ED11579/4

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)		COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
700.0	0.11	0.13	24.88	24.87	37.59	33.60	38.66	35.17	48.63	42.23
800.0	0.11	0.14	23.88	23.85	36.66	32.78	39.78	35.40	47.06	42.20
825.0	0.11	0.15	23.67	23.63	35.30	32.40	40.00	35.66	46.02	41.34
850.0	0.11	0.15	23.45	23.41	34.60	31.88	40.06	35.47	43.98	40.47
875.0	0.11	0.15	23.23	23.20	34.23	31.68	40.30	35.28	42.61	40.10
900.0	0.11	0.15	23.03	22.99	33.68	31.23	40.31	35.34	42.11	40.11
925.0	0.11	0.16	22.85	22.81	33.05	30.87	40.17	35.62	41.92	39.84
950.0	0.11	0.16	22.67	22.63	32.46	30.53	39.98	35.75	40.95	39.20
975.0	0.12	0.17	22.49	22.45	32.43	30.20	39.63	35.81	39.75	38.28
1000.0	0.12	0.17	22.32	22.28	32.23	30.17	39.27	35.77	38.27	37.38
1200.0	0.13	0.18	21.22	21.15	32.87	31.42	35.59	36.09	34.59	34.96
1400.0	0.15	0.21	20.43	20.38	36.13	35.46	32.74	34.79	33.78	35.02
1600.0	0.17	0.22	19.92	19.86	35.55	42.35	30.21	33.34	31.94	33.00
1800.0	0.19	0.23	19.63	19.58	29.28	32.79	29.43	33.84	33.22	32.26
1900.0	0.20	0.24	19.58	19.54	27.91	30.13	30.35	34.34	35.41	34.12
2000.0	0.20	0.25	19.58	19.54	26.99	28.91	30.64	33.90	36.72	35.98
2100.0	0.21	0.25	19.65	19.61	26.48	28.36	30.48	34.27	38.92	36.56
2200.0	0.21	0.25	19.77	19.73	26.09	28.11	31.14	35.70	41.69	36.37
2300.0	0.22	0.24	19.96	19.91	25.73	27.46	32.97	36.69	43.05	35.56
2400.0	0.21	0.24	20.21	20.16	25.13	27.14	35.33	36.16	49.29	35.25
2500.0	0.21	0.25	20.53	20.48	24.97	27.45	37.60	37.56	38.44	34.58
3000.0	0.20	0.24	23.38	23.35	19.12	19.98	39.81	33.98	28.75	28.00



ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350168, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

minicircuits.com

REV. X1

ZABDC20-ED11579/4





12/31/2008

Page 1 of 1

Bi-Directional Coupler

ZABDC20-ED11579/4

Typical Performance Curves



P.O. Box 350168, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4951 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

RF/MICROWAVE COMPONENTS




REV. X1

ZABDC20-ED11579/4

12/31/2008

Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
DD477-1	2.00 (50.80)	2.00 (50.80)	.88 (22.35)	.90 (22.86)	.156 (3.96)	1.688 (42.88)	.125 (3.18)	.38 (9.65)	-- --	.50 (12.70)	1.00 (25.40)	1.25 (31.75)	225

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I