



Mini-Circuits

THIN FILM COAXIAL

Bandpass Filter

ZABF-7R625G-S+

50Ω 7.45 to 7.8 GHz SMA Male/Female

KEY FEATURES

- Low Passband Insertion Loss, 2.3 dB Typ.
- High Rejection, 48 dB Typ.
- Small Size

APPLICATIONS

- Weather Radar and Satellite Communication Systems
- Test and Measurement Equipment


PRODUCT OVERVIEW

Mini-Circuits' Connectorized Thin-Film filters offer low insertion loss and high rejection realized via Thin-Film on Alumina substrate, using a sputtering process that can guarantee an enhanced Q and repeatable performance. Low pass, high pass, and bandpass connectorized thin-film designs can be realized with this technology up to 40 GHz in a small form factor helping customers achieve their SWaP objectives. Using our high quality thin-film manufacturing process we can guarantee repeatability on large batches of filters.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM

ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency ²	—	—	—	7.625	—	GHz
	Insertion Loss	F1-F2	7.45 - 7.8	—	2.3	3.0	dB
	Return Loss	F1-F2	7.45 - 7.8	—	10	—	dB
Stopband, Lower	Rejection	DC-F3	DC - 6	40	45	—	dB
		F3-F4	6 - 6.5	25	35	—	
Stopband, Upper	Rejection	F5-F6	9 - 11	20	28	—	dB
		F6-F7	11 - 14	42	48	—	
		F7-F8	14 - 18	—	35	—	

1. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

2. Typical variation $\pm 3\%$


ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁴	1W at 25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE



REV. OR
ECO-027956
EDU5135
ZABF-7R625G-S+
URJ
251212





Mini-Circuits





THIN FILM COAXIAL

Bandpass Filter

ZABF-7R625G-S+

50Ω 7.45 to 7.8 GHz SMA Male/Female

TYPICAL PERFORMANCE GRAPHS AT +25°C





THIN FILM COAXIAL

Bandpass Filter

ZABF-7R625G-S+


50Ω 7.45 to 7.8 GHz SMA Male/Female

CONNECTOR DESCRIPTION

Function	Connector
RF1 ⁵	SMA Male
RF2 ⁵	SMA Female

5. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

CASE STYLE DRAWING



Unit weight: 24grams

Dimensions are in inches (mm). Tolerances: 2 Pl.±.050"; 3 Pl.±.015"

PRODUCT MARKING*: ZABF-7R625G-S+

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

THIN FILM COAXIAL

Bandpass Filter

ZABF-7R625G-S+

50Ω 7.45 to 7.8 GHz SMA Male/Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	UK3042
RoHS Status	Compliant
Environmental Ratings	ENV144

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html




Coaxial Thin-Film Bandpass Filter

ZABF-7R625G-S+

Typical Performance Data


FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
10	72.85	0.06	0.10	7450	1.40
15	75.05	0.07	0.11	7455	1.39
50	94.00	0.12	0.17	7460	1.39
100	95.19	0.15	0.22	7465	1.39
150	112.19	0.17	0.26	7470	1.38
200	91.91	0.19	0.28	7475	1.38
300	93.87	0.21	0.32	7480	1.37
400	99.38	0.23	0.36	7485	1.37
500	87.94	0.25	0.38	7490	1.37
600	91.57	0.26	0.40	7495	1.36
700	102.45	0.28	0.42	7500	1.36
800	92.98	0.29	0.44	7505	1.35
900	88.18	0.31	0.45	7510	1.35
1000	92.10	0.32	0.46	7515	1.35
1500	91.75	0.40	0.47	7520	1.34
2000	87.04	0.44	0.45	7525	1.34
2200	86.41	0.44	0.44	7530	1.33
3000	82.17	0.36	0.36	7535	1.33
3500	81.81	0.26	0.29	7540	1.33
4000	81.59	0.15	0.25	7545	1.32
5000	71.37	0.09	0.24	7550	1.32
6000	54.37	0.34	0.40	7555	1.32
6500	39.46	0.59	0.62	7560	1.31
6700	30.93	0.74	0.79	7565	1.31
6850	22.68	0.97	1.06	7570	1.31
7000	11.87	1.97	2.17	7575	1.30
7130	3.18	12.90	14.55	7580	1.30
7200	2.52	13.33	13.95	7585	1.30
7450	1.82	26.86	31.46	7590	1.30
7500	1.79	24.48	25.84	7595	1.29
7550	1.82	19.24	19.84	7600	1.29
7600	1.84	17.27	17.87	7605	1.29
7625	1.87	16.94	17.61	7610	1.29
7650	1.87	16.95	17.66	7615	1.29
7700	1.87	17.83	18.73	7620	1.29
7750	1.86	19.78	21.02	7625	1.28
7800	1.85	23.20	25.14	7630	1.28
8195	3.37	10.16	10.05	7635	1.28
8260	4.88	6.45	6.46	7640	1.28
8350	8.61	3.25	3.35	7645	1.28
8500	17.57	1.53	1.65	7650	1.28
8650	28.72	1.22	1.33	7655	1.28
9000	33.16	1.38	1.44	7660	1.28
9500	33.88	1.12	1.22	7665	1.28
10000	41.13	0.64	0.75	7670	1.28
10500	48.14	0.53	0.57	7675	1.28
11000	54.03	0.58	0.56	7680	1.28
11500	59.54	0.68	0.62	7685	1.28
12000	64.95	0.77	0.71	7690	1.28
12500	70.81	0.81	0.81	7700	1.28
13000	78.22	0.79	0.90	7710	1.28
13500	82.62	0.70	0.94	7720	1.28
14000	78.28	0.57	0.91	7730	1.28
14500	74.94	0.46	0.79	7740	1.28
15000	68.81	0.40	0.63	7750	1.29
15500	62.95	0.40	0.47	7760	1.29
16000	58.16	0.46	0.35	7770	1.29
16500	54.27	0.55	0.31	7780	1.29
17000	50.62	0.66	0.37	7790	1.30
18000	44.07	0.77	0.74	7800	1.30

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours Units may require bake-out after humidity to restore full performance.	MIL-STD-202. method 103. Condition B
Thermal Shock	-40°C to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -40°C and +100°C