



THIN FILM COAXIAL

Bandpass Filter

ZABF-9R3G-S+

50Ω 9.2 to 9.4 GHz SMA Male/Female

KEY FEATURES

- Low Passband Insertion Loss, 2.4 dB Typ.
- High Rejection, 53 dB Typ.
- Small Size

APPLICATIONS

- Satcom
- Ground Antenna for weather satellites
- Test and Measurement


PRODUCT OVERVIEW

Mini-Circuits' Connectorized Thin-Film filters offer low insertion loss and high rejection realized via Thin-Film on Alumina substrate, using a sputtering process that can guarantee an enhanced Q and repeatable performance. Low pass, high pass, and bandpass connectorized thin-film designs can be realized with this technology up to 40 GHz in a small form factor helping customers achieve their SWaP objectives. Using our high quality thin-film manufacturing process we can guarantee repeatability on large batches of filters.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS^{1,2} AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency ²	—	—	—	9.3	—	GHz
	Insertion Loss	F1-F2	9.2 - 9.4	—	2.4	3.0	dB
	Return Loss	F1-F2	9.2 - 9.4	—	12	—	dB
Stopband, Lower	Rejection	DC-F3	DC - 6.5	43	53	—	dB
		F3-F4	6.5 - 7.8	20	35	—	
Stopband, Upper	Rejection	F5-F6	10.7 - 12	20	32	—	dB
		F6-F7	12 - 13	33	42	—	
		F7-F8	13 - 17	—	45	—	
		F8-F9	17-19	—	40	—	

1. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

2. Typical variation $\pm 3\%$


ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁴	1W at 25°C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals within the passband.

TYPICAL FREQUENCY RESPONSE





THIN FILM COAXIAL





Bandpass Filter

ZABF-9R3G-S+

Mini-Circuits

50 Ω 9.2 to 9.4 GHz SMA Male/Female

TYPICAL PERFORMANCE GRAPHS AT +25°C





THIN FILM COAXIAL

Bandpass Filter

ZABF-9R3G-S+

Mini-Circuits


50Ω 9.2 to 9.4 GHz SMA Male/Female

CONNECTOR DESCRIPTION

Function	Connector
RF1 ⁵	SMA Male
RF2 ⁵	SMA Female

5. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

CASE STYLE DRAWING



Unit weight: 24grams

Dimensions are in inches (mm). Tolerances: 2 Pl.±.050"; 3 Pl.±.015"

PRODUCT MARKING*: ZABF-9R3G-S+

*Marking may contain other features or characters for internal lot control.





Mini-Circuits

THIN FILM COAXIAL

Bandpass Filter

ZABF-9R3G-S+

50Ω 9.2 to 9.4 GHz SMA Male/Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	UK3042
RoHS Status	Compliant
Environmental Ratings	ENV144

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial Thin-Film Bandpass Filter


ZABF-9R3G-S+

Typical Performance Data

FREQ.	Insertion Loss	Input Return Loss	Output Return Loss
(MHz)	(dB)	(dB)	(dB)
10	85.85	0.09	0.09
20	83.08	0.10	0.12
40	96.21	0.13	0.16
100	86.65	0.18	0.22
160	84.34	0.22	0.27
200	86.24	0.24	0.29
260	80.96	0.27	0.32
400	79.29	0.31	0.36
600	78.06	0.34	0.41
800	75.43	0.37	0.44
900	74.37	0.37	0.45
1000	74.19	0.38	0.46
1500	70.22	0.40	0.46
2000	67.96	0.36	0.43
2500	66.26	0.32	0.37
3000	64.80	0.19	0.31
3500	63.38	0.11	0.26
4000	62.54	0.03	0.23
4500	61.45	0.03	0.22
5000	60.50	0.07	0.23
5500	59.25	0.14	0.28
6000	57.52	0.25	0.38
6500	54.50	0.35	0.47
6700	53.00	0.40	0.49
6900	51.08	0.42	0.52
7800	37.53	0.56	0.62
8000	32.81	0.61	0.67
8300	23.40	0.75	0.84
8720	3.40	7.59	7.64
9200	1.41	28.34	24.99
9210	1.41	28.09	24.69
9250	1.41	26.02	23.35
9270	1.41	25.22	22.92
9300	1.41	24.67	22.66
9350	1.41	25.46	23.33
9370	1.41	26.45	24.02
9380	1.41	27.12	24.45
9400	1.41	28.89	25.46
10000	3.17	11.59	13.51
10210	20.82	1.29	1.64
10700	33.17	0.68	0.72
11000	36.20	0.63	0.70
12000	44.63	0.35	0.77
13000	50.66	0.06	0.62
14500	57.81	0.17	0.30
15000	59.26	0.21	0.30
15200	59.68	0.28	0.32
15300	59.95	0.32	0.33
15800	60.31	0.31	0.42
16500	59.20	0.31	0.63
17000	57.39	0.24	0.79
17500	55.11	0.35	0.91
17600	54.61	0.33	0.92
17800	53.43	0.29	0.93
18000	52.31	0.23	0.91
18500	49.23	0.18	0.80
18600	48.57	0.15	0.77
18700	47.97	0.16	0.75
18800	47.33	0.21	0.72
19000	46.07	0.16	0.65


FREQ.	Group Delay
(MHz)	(ns)
9200	1.04
9205	1.03
9210	1.03
9215	1.03
9220	1.03
9225	1.03
9230	1.03
9235	1.03
9240	1.02
9245	1.02
9250	1.02
9255	1.02
9255	1.02
9270	1.02
9275	1.02
9280	1.02
9285	1.02
9290	1.02
9295	1.02
9300	1.01
9305	1.01
9310	1.01
9315	1.01
9320	1.01
9325	1.01
9330	1.01
9335	1.01
9340	1.01
9345	1.01
9350	1.01
9355	1.01
9360	1.01
9365	1.01
9370	1.01
9375	1.02
9380	1.02
9385	1.02
9390	1.02
9395	1.02
9400	1.02

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours Units may require bake-out after humidity to restore full performance.	MIL-STD-202. method 103. Condition B
Thermal Shock	-40°C to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -40°C and +100°C