



THIN FILM COAXIAL

Bandpass Filter

ZABF-K10R125G+

50Ω 9.35 to 10.9 GHz 2.92mm Female

KEY FEATURES

- Low Passband Insertion Loss 2 dB Typ.
- High Rejection 53 dB Typ.
- Small Size

APPLICATIONS

- X-band Radar
- Test and Measurement




Generic photo used for illustration purposes only

PRODUCT OVERVIEW

Mini-Circuits' Connectorized Thin-Film filters offer low insertion loss and high rejection realized via Thin-Film on Alumina substrate, using a sputtering process that can guarantee an enhanced Q and repeatable performance. Low pass, high pass, and bandpass connectorized thin-film designs can be realized with this technology up to 40 GHz in a small form factor helping customers achieve their SWaP objectives. Using our high quality thin-film manufacturing process we can guarantee repeatability on large batches of filters.

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS¹ AT +25°C

Parameter		F#	Frequency (GHz)	Min.	Typ.	Max.	Units
Passband	Center Frequency ²	—	—	—	10.125	—	GHz
	Insertion Loss	F1-F2	9.35 - 10.9	—	2	2.5	dB
	Return Loss	F1-F2	9.35 - 10.9	—	10	—	dB
Stopband, Lower	Rejection	DC-F3	DC - 6	40	50	—	dB
		F3-F4	6 - 7.5	20	30	—	
Stopband, Upper	Rejection	F5-F6	13 - 15	20	30	—	dB
		F6-F7	15 - 18	40	53	—	
		F7-F8	18 - 23	—	30	—	

1. This component should not be used as a DC-block. In applications where DC voltage and/or current is present at either the input or output ports, external DC blocking capacitors are required.

2. Typical variation $\pm 3\%$


ABSOLUTE MAXIMUM RATINGS³

Parameter	Ratings
Operating Temperature	-55°C to +125°C
Storage Temperature	-55°C to +125°C
Input Power ⁴	8 W at 25 °C

3. Permanent damage may occur if any of these limits are exceeded.

4. Power rating applies only to signals with in the passband.

TYPICAL FREQUENCY RESPONSE AT +25°C





THIN FILM COAXIAL

Bandpass Filter

ZABF-K10R125G+





Mini-Circuits

50 Ω

9.35 to 10.9 GHz

2.92mm Female

TYPICAL PERFORMANCE GRAPHS AT +25°C





THIN FILM COAXIAL

Bandpass Filter

ZABF-K10R125G+


50Ω 9.35 to 10.9 GHz 2.92mm Female

CONNECTOR DESCRIPTION

Function	Connector
RF1 ⁵	2.92mm Female
RF2 ⁵	2.92mm Female

5. This filter is bi-directional RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

CASE STYLE DRAWING



Unit weight: 24grams

Dimensions are in inches (mm). Tolerances: 2 Pl.±.050"; 3 Pl.±.015"

PRODUCT MARKING*: ZABF-K10R125G+

*Marking may contain other features or characters for internal lot control.



Mini-Circuits

THIN FILM COAXIAL

Bandpass Filter

ZABF-K10R125G+

50Ω 9.35 to 10.9 GHz 2.92mm Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	UK3042
RoHS Status	Compliant
Environmental Ratings	ENV144

NOTES




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Typical Performance Data


FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
10	78.01	0.07	0.07	9350	0.73
100	91.93	0.17	0.19	9380	0.73
200	83.79	0.22	0.25	9400	0.73
300	82.80	0.25	0.28	9420	0.73
500	78.91	0.31	0.33	9440	0.74
700	75.09	0.37	0.37	9460	0.74
1000	72.26	0.44	0.41	9480	0.74
1500	68.87	0.46	0.43	9500	0.75
2000	66.08	0.38	0.41	9520	0.75
2500	64.31	0.28	0.36	9540	0.75
3000	62.59	0.23	0.31	9560	0.75
3500	61.04	0.24	0.26	9580	0.75
4000	59.99	0.23	0.22	9600	0.76
4500	58.85	0.17	0.19	9620	0.76
5000	57.71	0.11	0.19	9640	0.76
6000	54.56	0.17	0.28	9660	0.76
7000	45.74	0.41	0.45	9680	0.75
7500	36.84	0.54	0.54	9700	0.75
8000	22.61	0.72	0.73	9720	0.75
8500	1.50	22.82	25.94	9740	0.75
9000	1.07	23.64	24.85	9760	0.74
9350	1.39	11.60	11.74	9780	0.74
9400	1.33	12.41	12.60	9800	0.73
9500	1.16	15.84	16.18	9820	0.73
9600	1.05	24.57	26.53	9840	0.72
9700	1.05	22.56	23.12	9860	0.72
9800	1.18	15.15	15.23	9880	0.71
9900	1.36	12.02	12.09	9900	0.71
10000	1.50	10.67	10.76	9920	0.70
10125	1.55	10.48	10.63	9940	0.70
10800	1.41	14.00	14.21	9960	0.70
10900	1.54	12.45	12.73	9980	0.70
11420	3.20	7.41	7.81	10000	0.69
11875	20.26	1.03	1.04	10050	0.69
12150	30.91	0.70	0.68	10100	0.69
13000	53.53	0.44	0.46	10125	0.69
13200	51.26	0.45	0.48	10130	0.69
13400	50.55	0.47	0.51	10140	0.69
13600	50.46	0.50	0.54	10150	0.70
13800	50.69	0.54	0.57	10160	0.70
14000	51.00	0.58	0.62	10180	0.70
14200	51.53	0.62	0.65	10190	0.70
14400	52.13	0.67	0.69	10200	0.70
14600	52.70	0.70	0.73	10210	0.70
14800	53.43	0.74	0.77	10220	0.71
15000	54.15	0.77	0.80	10230	0.71
16000	58.97	0.80	0.86	10240	0.71
17000	67.85	0.69	0.71	10250	0.71
18000	78.61	0.48	0.44	10300	0.72
18200	75.84	0.43	0.39	10400	0.75
18400	75.23	0.38	0.35	10500	0.77
18600	76.47	0.34	0.31	10550	0.78
18800	78.47	0.30	0.30	10600	0.78
19000	75.25	0.27	0.29	10650	0.79
19500	61.94	0.25	0.31	10700	0.79
20000	53.65	0.32	0.41	10720	0.79
20500	47.49	0.47	0.58	10740	0.79
21000	42.37	0.68	0.78	10800	0.79
22000	33.74	1.13	1.09	10850	0.79
23000	24.72	1.33	1.21	10900	0.80

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 100° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours Units may require bake-out after humidity to restore full performance.	MIL-STD-202. method 103. Condition B
Thermal Shock	-40°C to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except -40°C and +100°C