


MMIC

REFLECTIONLESS FILTER DICE

50Ω DC to 21 GHz



X-Series

Available in Low Pass, High Pass and Band Pass designs

The Big Deal

- Patented design eliminates in band spurs
- Pass band cut-off up to 21 GHz
- Stop band up to 35 GHz
- Excellent repeatability through IPD* process
- Unpackaged Die Form

Product Overview

Mini-Circuits' X-Series reflectionless filters employ a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level which interact with neighboring components and often result in intermodulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolators, isolation amplifiers or attenuators.

Key Features	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
Enables stable integration of wideband amplifiers	Because reflectionless filters maintain good impedance in the stop band; they can be integrated with high gain, wideband amplifiers without the risk of creating instabilities in these out of band regions.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.
Excellent power handling in a tiny surface mount device	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.
Excellent repeatability of RF performance	Through semiconductor IPD process, X-series filters are inherently repeatable for large volume production.
Excellent stability over temperature	With ± 0.3 dB variation over temperature ideal for use in wide temperature range applications without the need for additional temperature compensation.
Operating Temperature up to 105°C	Suitable for operation close to high power components
Unpackaged Die form	Enables direct integration into customer hybrids

*IPD – Integrated Passive Device, is a GaAs semiconductor process



Reflectionless Low Pass Filter Die

XLF-252-D+

50Ω DC to 2500 MHz

Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Protected by US Patent No. 8,392,495



Applications

- Harmonics Rejection
- Wideband Matching
- Transmitters / Receivers

+RoHS Compliant


The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Ordering Information: Refer to Last Page

General Description

Mini-Circuits' XLF-252-D+ reflectionless filter die employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

Simplified Schematic



Pad	Description
RF-IN	RF Input Pad
RF-OUT	RF Output Pad
Ground	Ground Bonding Pad



Electrical Specifications¹ at 25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 2500	1.3		dB
	Frequency Cut-off	F2	3220	3.0		dB
	VSWR	DC - F1	DC - 2500	1.3		:1
Stop Band	Rejection	F3 - F4	4550 - 16000	15		dB
		F4 - F5	16000 - 30000	18		dB
	VSWR	F3 - F4	4550 - 16000	1.2		:1
		F4 - F5	16000 - 30000	1.8		:1

¹ Measured on Mini-Circuits Characterization test board. Die packaged in 3mm x 3mm, 12-lead MCLP package and soldered on TB-844-252+


Specification Definition**Absolute Maximum Ratings^{1,4}**

Parameter	Ratings
Operating Temperature	-55°C to +105°C
RF Power Input, Passband (DC-F1) ²	2W at 25°C
RF Power Input, Stopband (F2-F5) ³	0.5W at 25°C


² Passband rating derates linearly to 1W at 105°C ambient

³ Stopband rating derates linearly to 0.25W at 105°C ambient

⁴ Permanent damage may occur if any of these limits are exceeded.

**Typical Performance Data at 25°C¹**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.41	1.01
100	0.40	1.01
200	0.40	1.03
400	0.41	1.07
800	0.47	1.18
1600	0.70	1.35
2500	1.27	1.33
3220	3.01	1.15
4550	15.78	1.44
6000	19.73	1.21
8000	15.26	1.22
10000	15.84	1.27
12000	16.27	1.24
14000	16.36	1.09
16000	15.82	1.14
19000	11.48	2.40
22000	19.48	1.71
25000	20.90	1.82
27500	19.91	1.73
30000	21.78	2.26



Die Layout

Fig 1. Die Layout


Bonding Pad Position
(Dimensions in μm , Typical)

Fig 2. Bonding Pad Positions

Critical Dimensions

Parameter	Values
Die Thickness, μm	100
Die Width, μm	1000
Die Length, μm	550
Bond Pad Size (Ground pad), μm	75 x 75

Assembly and Handling Procedure

1. Storage

Dice should be stored in a dry nitrogen purged desiccators or equivalent.

2. ESD

MMIC Gallium Arsenide (GaAs) filter dice are susceptible to electrostatic and mechanical damage. Die are supplied in antistatic protected material, which should be opened in clean room conditions at an appropriately grounded anti-static workstation. Devices need careful handling using correctly designed collets, vacuum pickup tips or sharp antistatic tweezers to deter ESD damage to dice.


3. Die Attach

The die mounting surface must be clean and flat. Using conductive silver filled epoxy, recommended epoxies are DieMat DM6030Hk-PT/H579/H579 or Ablestik 84-1LMISR4. Apply sufficient epoxy to meet required epoxy bond line thickness, epoxy fillet height and epoxy coverage around total die periphery. Parts shall be cured in a nitrogen filled atmosphere per manufacturer's cure condition. It is recommended to use antistatic die pick up tools only.

4. Wire Bonding

Bond pad openings in the surface passivation above the bond pads are provided to allow wire bonding to the dice gold bond pads. Thermosonic bonding is used with minimized ultrasonic content. Bond force, time, ultrasonic power and temperature are all critical parameters. Suggested wire is pure gold, 1 mil diameter. Bonds must be made from the bond pads on the die to the package or substrate. All bond wires should be kept as short as reasonable to minimize performance degradation due to undesirable series inductance.

Assembly Diagram



Recommended Wire Length, Typical

Wire	Wire Length (mm)	Wire Loop Height (mm)
All wires	1.0	0.15

Note: Use double bond wire at RF IN & RF OUT

Additional Detailed Technical Information

additional information is available on our dash board.

*Known Good Dice (“KGD”) means that the dice are taken from PCM good wafer and visually inspected according to Mini-Circuits inspection criteria. While this is not definitive, it does help to provide a higher degree of confidence that dice are capable of meeting typical RF electrical parameters specified by Mini-Circuits.

ESD Rating**

Human Body Model (HBM): Class 1A (250V) in accordance with ANSI/ESD STM 5.1 - 2001

** Tested in industry standard MCLP 3x3mm 12 lead package.

Additional Notes

- EXCLUSIONS**

 - A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 - B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 - C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp
 - D. Mini-Circuits does not warrant the accuracy or completeness of the information, text, graphics and other items contained within this document and same are provided as an accommodation and on an "As is" basis, with all faults.
 - E. Purchasers of this part are solely responsible for proper storing, handling, assembly and processing of Known Good Dice (including, without limitation, proper ESD preventative measures, die preparation, die attach, wire bonding and related assembly and test activities), and Mini-Circuits assumes no responsibility therefor or for environmental effects on Known Good Dice.
 - F. Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation by any such third-party of Mini-Circuits or its products.



Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)					GROUP DELAY (nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	0.40	0.42	0.46	0.51	0.52	0.27	0.29	0.26	0.28	0.28
10	0.36	0.37	0.43	0.47	0.48	0.27	0.28	0.26	0.27	0.28
20	0.36	0.37	0.43	0.46	0.48	0.27	0.28	0.26	0.27	0.28
30	0.36	0.37	0.42	0.46	0.48	0.27	0.28	0.26	0.27	0.28
40	0.37	0.38	0.44	0.48	0.49	0.27	0.27	0.26	0.27	0.27
50	0.36	0.37	0.42	0.48	0.49	0.26	0.27	0.26	0.26	0.27
60	0.35	0.37	0.43	0.48	0.49	0.26	0.26	0.26	0.26	0.26
70	0.36	0.37	0.43	0.48	0.50	0.26	0.26	0.25	0.26	0.26
80	0.36	0.38	0.43	0.48	0.49	0.26	0.25	0.25	0.25	0.25
90	0.36	0.38	0.43	0.48	0.50	0.25	0.25	0.25	0.25	0.25
100	0.36	0.37	0.44	0.48	0.50	0.25	0.25	0.25	0.25	0.25
200	0.37	0.39	0.45	0.51	0.53	0.25	0.25	0.24	0.24	0.25
300	0.39	0.40	0.48	0.54	0.56	0.25	0.25	0.24	0.24	0.24
400	0.40	0.42	0.50	0.56	0.59	0.25	0.25	0.24	0.24	0.24
500	0.42	0.44	0.53	0.59	0.62	0.25	0.25	0.24	0.24	0.24
600	0.44	0.46	0.56	0.63	0.65	0.25	0.25	0.24	0.24	0.24
700	0.46	0.49	0.59	0.66	0.68	0.25	0.25	0.24	0.24	0.24
800	0.49	0.51	0.62	0.69	0.72	0.25	0.25	0.24	0.24	0.24
900	0.51	0.54	0.65	0.73	0.76	0.25	0.25	0.24	0.24	0.24
1000	0.54	0.56	0.68	0.76	0.79	0.25	0.25	0.24	0.24	0.24
1100	0.57	0.60	0.72	0.80	0.83	0.25	0.25	0.24	0.24	0.24
1200	0.60	0.63	0.76	0.85	0.88	0.25	0.25	0.24	0.24	0.24
1300	0.64	0.67	0.80	0.89	0.92	0.25	0.25	0.25	0.25	0.25
1400	0.68	0.71	0.84	0.94	0.97	0.25	0.25	0.25	0.25	0.25
1500	0.71	0.75	0.89	0.98	1.01	0.25	0.25	0.25	0.25	0.25
1600	0.76	0.79	0.93	1.03	1.07	0.25	0.25	0.25	0.25	0.25
1700	0.81	0.84	0.99	1.09	1.12	0.26	0.26	0.25	0.25	0.25
1800	0.85	0.89	1.03	1.14	1.18	0.26	0.26	0.25	0.25	0.25
1900	0.90	0.94	1.09	1.20	1.24	0.26	0.26	0.26	0.26	0.26
2000	0.95	0.99	1.15	1.26	1.30	0.26	0.26	0.26	0.26	0.26
2100	1.01	1.05	1.22	1.33	1.37	0.27	0.27	0.26	0.26	0.26
2200	1.07	1.12	1.29	1.41	1.45	0.27	0.27	0.26	0.26	0.26
2300	1.14	1.19	1.37	1.50	1.54	0.27	0.27	0.27	0.27	0.27
2400	1.22	1.27	1.46	1.60	1.64	0.28	0.28	0.27	0.27	0.27
2500	1.32	1.37	1.58	1.72	1.77	0.28	0.28	0.28	0.28	0.28
2600	1.43	1.49	1.70	1.85	1.91	0.29	0.29	0.28	0.28	0.28
2700	1.57	1.63	1.86	2.02	2.08	0.29	0.29	0.29	0.29	0.29
2800	1.74	1.80	2.05	2.23	2.29	0.30	0.30	0.29	0.29	0.29
2900	1.95	2.01	2.28	2.46	2.53	0.30	0.30	0.30	0.30	0.30
3000	2.20	2.27	2.55	2.75	2.83	0.31	0.31	0.30	0.30	0.30
3200	2.87	2.95	3.27	3.50	3.58	0.32	0.32	0.31	0.31	0.31
3220	2.95	3.03	3.35	3.58	3.67	0.32	0.32	0.31	0.31	0.31
3500	4.38	4.47	4.84	5.12	5.21	0.32	0.32	0.31	0.31	0.31
4000	8.40	8.51	8.97	9.32	9.45	0.29	0.29	0.28	0.28	0.28
4500	14.48	14.62	15.22	15.70	15.86	0.25	0.24	0.23	0.22	0.22
4550	15.24	15.40	16.01	16.52	16.69	0.24	0.24	0.22	0.21	0.20
6000	20.44	20.42	20.37	20.24	20.24	0.20	0.20	0.19	0.18	0.19
6500	17.79	17.81	17.91	17.94	17.96	0.21	0.21	0.20	0.20	0.20
7000	16.52	16.57	16.75	16.84	16.87	0.21	0.21	0.20	0.20	0.20
7500	15.91	15.96	16.20	16.33	16.40	0.21	0.21	0.20	0.20	0.20
8000	15.64	15.71	16.00	16.19	16.26	0.21	0.21	0.20	0.20	0.20
8500	15.63	15.68	16.03	16.30	16.38	0.20	0.20	0.20	0.19	0.19
9000	15.81	15.89	16.29	16.58	16.64	0.20	0.20	0.19	0.18	0.18
9500	16.29	16.38	16.58	16.61	16.65	0.18	0.17	0.17	0.19	0.19
10000	16.37	16.35	16.52	16.67	16.73	0.18	0.18	0.19	0.19	0.19
10500	16.31	16.37	16.62	16.84	16.91	0.20	0.20	0.19	0.19	0.19
11000	16.44	16.51	16.84	17.08	17.17	0.20	0.19	0.19	0.19	0.19
11500	16.64	16.73	17.09	17.36	17.44	0.19	0.19	0.19	0.19	0.19
12000	16.86	16.96	17.35	17.62	17.73	0.19	0.19	0.19	0.18	0.18
12500	17.07	17.16	17.58	17.88	18.00	0.19	0.19	0.18	0.19	0.18
13000	17.25	17.35	17.81	18.12	18.25	0.20	0.20	0.19	0.19	0.19
13500	17.46	17.58	18.05	18.39	18.51	0.20	0.19	0.19	0.19	0.18
14000	17.63	17.73	18.28	18.64	18.77	0.20	0.20	0.19	0.18	0.19
15000	17.93	18.01	18.50	18.71	18.84	0.20	0.20	0.19	0.18	0.18
16000	17.11	17.19	17.62	17.86	17.96	0.20	0.20	0.20	0.20	0.20
18000	12.89	12.97	13.38	13.66	13.81	0.28	0.28	0.29	0.29	0.29
20000	14.95	15.24	16.26	17.12	17.40	0.27	0.27	0.26	0.26	0.26
22000	19.78	19.97	21.04	21.87	22.18	0.22	0.22	0.22	0.22	0.22
24000	21.77	21.87	22.17	22.68	22.92	0.20	0.20	0.21	0.21	0.21
26000	21.21	21.37	21.98	22.33	22.47	0.20	0.20	0.19	0.20	0.20
28000	20.79	20.84	21.38	22.07	22.41	0.21	0.21	0.21	0.20	0.20
30000	21.40	21.63	22.52	22.81	22.92	0.21	0.21	0.18	0.22	0.21
31000	21.96	22.19	23.73	24.44	24.56	0.22	0.20	0.17	0.18	0.19
32000	24.30	24.26	25.14	26.37	27.05	0.24	0.22	0.19	0.15	0.10
33000	26.15	26.08	25.59	26.60	26.97	0.15	0.14	0.20	0.17	0.18
34000	26.97	26.85	26.32	26.59	26.99	0.10	0.08	0.18	0.18	0.21
35000	25.66	25.93	27.14	27.14	26.90	0.20	0.18	0.16	0.18	0.17

 Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com


Typical Performance Data

FREQ. (MHz)	INPUT RETURN LOSS (dB)					OUTPUT RETURN LOSS (dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	39.24	40.54	44.62	46.28	44.14	40.28	41.58	46.13	43.92	43.51
20	41.04	42.24	51.54	49.26	45.32	39.30	40.85	47.91	48.87	45.91
30	39.74	41.25	50.45	50.40	46.45	39.90	40.94	48.67	49.15	49.07
40	39.92	41.19	50.71	47.49	44.56	39.35	40.16	46.65	48.13	46.18
50	38.84	40.16	46.60	44.60	42.55	39.30	40.32	46.66	48.57	48.15
60	38.58	40.00	48.45	46.53	43.79	38.63	39.52	44.89	46.81	46.41
70	38.19	39.08	44.87	44.14	42.25	37.90	38.87	43.33	46.20	47.12
80	37.51	38.56	43.47	43.01	41.26	38.14	38.58	42.98	44.59	45.94
90	38.36	39.19	43.93	42.07	40.48	38.26	38.65	42.40	44.13	44.75
100	38.36	39.25	42.65	41.25	39.50	38.15	38.54	40.96	42.70	42.76
200	38.01	37.66	35.52	34.13	33.46	37.29	36.95	34.57	33.54	33.09
300	32.20	32.07	31.43	31.08	30.87	31.50	31.35	30.72	30.34	30.19
400	29.51	29.33	28.45	28.11	27.83	29.29	29.02	28.19	27.96	27.86
500	27.23	27.11	26.32	25.80	25.56	27.01	26.84	26.04	25.55	25.26
600	25.40	25.28	24.52	24.25	24.18	25.17	25.00	24.25	23.96	23.86
700	24.04	23.94	23.15	22.83	22.74	23.83	23.72	22.88	22.60	22.50
800	22.56	22.48	21.90	21.53	21.43	22.37	22.30	21.69	21.30	21.14
900	21.35	21.31	20.81	20.61	20.57	21.11	21.06	20.59	20.35	20.27
1000	20.38	20.32	19.84	19.66	19.63	20.22	20.18	19.72	19.54	19.48
1100	19.43	19.40	19.02	18.78	18.73	19.32	19.30	18.94	18.69	18.62
1200	18.57	18.54	18.30	18.14	18.13	18.41	18.41	18.22	18.05	18.04
1300	17.91	17.91	17.69	17.55	17.53	17.75	17.76	17.62	17.49	17.46
1400	17.22	17.22	17.12	16.99	16.97	17.05	17.08	17.06	16.93	16.90
1500	16.73	16.74	16.72	16.65	16.69	16.51	16.54	16.60	16.55	16.56
1600	16.22	16.26	16.32	16.28	16.28	16.04	16.10	16.24	16.22	16.24
1700	15.80	15.84	16.00	15.97	15.97	15.55	15.60	15.89	15.88	15.88
1800	15.50	15.55	15.78	15.81	15.83	15.22	15.30	15.64	15.69	15.72
1900	15.30	15.35	15.64	15.70	15.71	15.04	15.12	15.51	15.61	15.62
2000	15.17	15.23	15.58	15.65	15.67	14.89	14.98	15.43	15.54	15.56
2100	15.18	15.25	15.62	15.74	15.77	14.88	14.98	15.47	15.62	15.66
2200	15.27	15.33	15.74	15.89	15.92	14.99	15.08	15.60	15.79	15.81
2300	15.44	15.52	16.00	16.17	16.23	15.15	15.26	15.84	16.07	16.13
2400	15.78	15.87	16.37	16.58	16.63	15.51	15.62	16.24	16.50	16.58
2500	16.29	16.37	16.89	17.12	17.16	16.05	16.16	16.81	17.09	17.16
2600	16.94	17.03	17.57	17.79	17.84	16.71	16.83	17.51	17.78	17.86
2700	17.88	17.96	18.47	18.66	18.67	17.72	17.84	18.51	18.76	18.81
2800	19.05	19.10	19.56	19.71	19.72	18.96	19.07	19.72	19.92	19.94
2900	20.45	20.50	20.90	20.95	20.91	20.36	20.48	21.20	21.26	21.31
3000	22.18	22.17	22.30	22.12	21.97	22.09	22.20	22.82	22.64	22.60
3200	24.47	24.24	23.46	22.93	22.67	24.20	24.16	24.08	23.44	23.37
3220	24.42	24.16	23.32	22.80	22.55	24.06	24.03	23.92	23.31	23.23
3500	19.77	19.66	19.32	19.27	19.22	19.17	19.18	19.36	19.28	19.34
4000	14.93	14.96	15.23	15.40	15.45	14.45	14.54	15.07	15.26	15.36
4500	14.67	14.76	15.12	15.19	15.23	14.32	14.40	14.80	14.89	14.95
4550	14.78	14.87	15.23	15.27	15.30	14.45	14.54	14.90	14.96	15.00
6000	22.25	22.54	23.08	23.36	23.48	21.00	21.23	21.85	21.93	21.78
6500	24.39	24.36	25.07	26.98	27.51	21.48	21.84	24.47	26.46	27.08
7000	23.29	23.18	24.03	25.80	26.12	21.90	22.14	24.22	26.61	27.55
7500	20.91	21.02	21.96	22.75	22.89	22.32	22.39	22.56	23.21	23.40
8000	18.89	19.20	20.52	20.88	20.97	21.89	21.91	21.03	20.83	20.68
8500	17.88	18.30	19.76	20.47	20.69	20.00	20.18	19.99	19.82	19.67
9000	17.63	18.20	20.30	22.01	22.28	18.22	18.52	19.21	19.08	18.93
9500	19.49	20.52	22.57	21.24	20.93	16.77	17.14	18.62	18.76	18.75
10000	21.31	21.33	20.42	19.52	19.52	15.87	16.22	18.26	18.78	19.02
10500	19.39	19.55	19.38	19.16	19.25	15.45	15.82	18.27	19.24	19.73
11000	18.91	18.95	19.14	19.20	19.27	15.81	16.12	18.52	19.59	20.21
11500	18.98	18.92	19.14	19.34	19.36	16.68	16.89	18.73	19.63	20.15
12000	19.60	19.44	19.67	19.80	19.71	18.07	18.13	18.99	19.40	19.68
12500	20.37	20.15	20.45	20.22	19.99	19.60	19.49	19.36	19.17	19.22
13000	21.41	21.14	21.43	20.84	20.48	21.79	21.34	19.51	18.63	18.39
13500	22.48	22.17	22.41	21.55	21.09	23.71	22.99	19.44	17.95	17.45
14000	23.27	22.92	22.92	22.17	21.82	25.35	24.47	19.56	17.55	16.85
15000	22.89	22.67	22.77	22.28	22.04	28.16	29.20	25.00	21.12	19.77
16000	23.69	23.62	24.38	24.82	24.85	21.34	22.04	22.06	19.32	18.19
18000	13.78	13.60	12.78	12.19	12.03	14.88	15.06	14.20	12.40	11.58
20000	7.00	7.11	7.74	8.20	8.33	6.21	6.41	8.11	9.65	10.52
22000	9.93	10.33	10.55	10.47	10.60	13.21	13.53	11.01	9.65	9.11
24000	10.28	10.32	10.46	10.86	11.04	7.08	7.51	11.58	11.94	11.30
26000	10.01	9.85	10.22	10.68	10.74	10.63	10.59	11.31	13.19	14.56
28000	10.07	10.47	10.88	10.62	10.60	8.70	9.30	12.30	10.52	9.48
30000	7.46	7.29	7.31	7.79	7.95	7.52	7.49	8.22	10.00	11.48
31000	5.49	5.39	5.51	6.06	6.20	8.70	8.47	5.88	5.63	5.79
32000	4.25	4.27	4.68	5.06	5.16	3.41	3.82	4.61	3.96	3.70
33000	3.64	3.74	4.35	4.53	4.59	1.74	1.99	4.04	4.17	3.92
34000	3.54	3.70	4.38	4.52	4.54	1.56	1.75	3.95	5.68	5.97
35000	3.77	3.94	4.40	4.60	4.77	2.70	2.81	3.76	5.41	6.51

 **Mini-Circuits®**
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

 minicircuits.com

Typical Performance Curves



**Environmental Specifications****ENV80**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C or -40° to 105° C or -55° to 105° C or -45° to 105° C Ambient Environment	Refer to Individual Model Data Sheet
Storage Environment (Die)	-65° to 150°C	Individual Model Data Sheet
Storage Environment(Packaging)	-40° to 70°C and 40 to 60% humidity (In Factory Shipped Package)	