



COAXIAL

# Bias-Tee

# ZABT-250W-63+ ZABT-250W-63X+

50Ω 420 to 6000 MHz Up to 250W

## KEY FEATURES

- Wideband, 420 to 6000 MHz
- High Power Handling, 250 W
- Low Insertion Loss, 0.1 dB Typ


## PRODUCT OVERVIEW

Mini-Circuits' ZABT-250W-63+ is a coaxial bias tee providing high power handling and low insertion loss for applications over a very wide frequency range from 420 to 6000 MHz. It provides 45 dB typical DC-RF isolation and handles up to 4.5A DC current at the DC input. This model features rugged construction with N-Type / SMA connectors.



Generic photo used for illustration purposes only

## FUNCTIONAL DIAGRAM



## ELECTRICAL SPECIFICATIONS AT +25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Units
Frequency Range	-	420	-	6000	MHz
Insertion Loss	420-600	-	0.3	0.7	dB
	600-6000	-	0.1	0.3	
Return Loss (RF Port, (RF & DC Port)	420-600	10	15	-	dB
	600-6000	15	20	-	
Isolation (RF/RF & DC Port to DC Port)	420-6000	35	45	-	dB
DC Resistance (DC to RF & DC Port)	-	-	-	100	mOhm

## ABSOLUTE MAXIMUM RATINGS<sup>1</sup>

Operating Case Temperature	-40 °C to +85 °C
Storage Temperature	-40 °C to +85 °C
Input Power <sup>2</sup>	300 W
Voltage at DC Port	+50 V
Current at DC Port	4.5 A

1. Permanent damage may occur if any of these limits are exceeded.
2. For units without heatsink, maximum thermal resistance of user's external heat sink should not exceed 2.2 °C/W.








COAXIAL

# Bias-Tee

## ZABT-250W-63+ ZABT-250W-63X+

50Ω 420 to 6000 MHz Up to 250W

### TYPICAL PERFORMANCE GRAPHS





COAXIAL

# Bias-Tee


# ZABT-250W-63+ ZABT-250W-63X+

50Ω 420 to 6000 MHz Up to 250W

## COAXIAL CONNECTIONS

Description	RF PORT	RF & DC PORT	DC PORT
Connector Type	N	N	SMA

## CASE STYLE DRAWING



Weight: 450 grams; Without heatsink 321 grams  
 Dimensions are in inches [mm]. Tolerances: 2 PI ±.03; 3 PI ±.015

## PRODUCT MARKING\*: ZABT-250W-63+

\*Marking may contain other features or characters for internal lot control.





COAXIAL

# Bias-Tee

## ZABT-250W-63+ ZABT-250W-63X+

50Ω 420 to 6000 MHz Up to 250W

 Mini-Circuits

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (SXP Files) Data Set (.zip file)
Case Style	VY3240-1
RoHS Status	Compliant
Environmental Ratings	ENV28T23

#### NOTES




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/terms/viewterm.html](http://www.minicircuits.com/terms/viewterm.html)



*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	ISOLATION (dB)		Return Loss (dB)	
		RF-DC	RF&DC-DC	RF	RF&DC
360	0.52	58	56	10	10
380	0.43	59	57	11	11
400	0.41	64	57	12	12
420	0.28	62	61	13	13
440	0.23	62	61	14	14
460	0.20	62	62	15	14
480	0.17	63	62	15	15
500	0.14	63	64	17	16
750	0.05	70	71	25	25
1000	0.03	70	72	34	31
1250	0.04	73	73	36	36
1500	0.04	81	81	38	44
1750	0.04	79	89	47	40
2000	0.05	83	80	38	33
2250	0.05	73	73	31	30
2500	0.06	73	74	28	29
2750	0.06	70	70	27	29
3000	0.06	68	67	28	29
3250	0.06	66	63	32	32
3500	0.06	63	63	33	33
3750	0.07	61	61	28	29
4000	0.08	59	60	26	25
4250	0.09	59	59	24	23
4500	0.09	58	58	24	23
4750	0.09	57	57	24	25
5000	0.08	56	56	25	26
5250	0.09	55	55	26	27
5500	0.09	55	55	28	28
5750	0.09	55	55	33	32
6000	0.09	52	54	31	31
6250	0.11	49	49	26	25
6500	0.15	37	36	23	23
6750	0.50	29	27	14	14
7000	0.29	32	31	15	16

## Typical Performance Curves



ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site




The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)


IF/RF MICROWAVE COMPONENTS

## Outline Dimensions

VY3240-1



**MOUNTING INFORMATION OF MODEL WITHOUT HEATSINK**



Weight: 450 grams; Without heatsink 321 grams

Dimensions are in inches (mm). Tolerances: 2 Pl ±.03; 3 Pl ±.015

**Notes:**

1. Case material: Aluminum.
2. Case finish: Gold plating;
3. Heat sink finish: Black anodize.
4. Refer to the individual model data sheet for the type of connectors available.
5. Shape of connector flange may vary.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-40° to 85° C Ambient Environment	Individual Model Data Sheet
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I