



MMIC REFLECTIONLESS

# Low Pass Filter

XLF-762+

Mini-Circuits

50Ω DC to 7600 MHz

## THE BIG DEAL

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Excellent Power handling
- Temperature sData, up to +105°C
- Small size, 3 x 3 mm
- Protected by US Patent No. 8,392,495



Generic photo used for illustration purposes only

CASE STYLE: DQ1225

+RoHS Compliant

The +Suffix identifies RoHS Compliance.  
See our website for methodologies and qualifications

## APPLICATIONS

- Harmonics Rejection
- Satellite
- Radar
- Military & Space

## PRODUCT OVERVIEW

Mini-Circuits' XLF-762+ reflectionless filter employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. This new capability enables unique applications for filter circuits beyond those suited to traditional approaches. Traditional filters are reflective in the stop band, sending signals back to the source at 100% of the power level. These reflections interact with neighboring components and often result in inter-modulation and other interferences. Reflectionless filters eliminate stop band reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators.

## KEY FEATURES

Features	Advantages
Reflectionless Technology	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range and saving board space.
50Ω Match in Stopband	Reflectionless filters maintain good impedance matching in the stopband, allowing for integration with high gain, wideband amplifiers without the risk of creating out-of-band instabilities.
Excellent RF Performance Repeatability	Fabricated on a GaAs process, X-series filters are inherently repeatable for large-volume production.
Excellent Stability over temperature	With ±0.3 dB variation over temperature, is ideal for use in wide temperature range applications without the need for additional temperature compensation.
Excellent Power Handling in a Compact Package	High power handling extends the usability of these filters to the transmit path for inter-stage filtering.

REV. C  
ECO-020994  
XLF-762+  
MCL NY  
240226



MMIC REFLECTIONLESS

# Low Pass Filter

XLF-762+

Mini-Circuits

## ELECTRICAL SPECIFICATIONS<sup>1</sup> AT +25°C

Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC - F1	DC - 7600	—	1.1	1.6
	Frequency Cut-off	F2	11000	—	3.0	—
	VSWR	DC - F1	DC - 7600	—	1.3	—
Stop Band	Rejection	F3 - F5	13100 - 23000	12	15	—
		F3 - F4	13100 - 20000	—	1.7	—
	VSWR	F4 - F5	20000 - 23000	—	2.7	—

1. Measured on Mini-Circuits Characterization Test Board TB-844-762+

## ABSOLUTE MAXIMUM RATINGS<sup>2</sup>


Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-65°C to +150°C
RF Power Input, Passband (DC-F1) <sup>3</sup>	2 W at +25°C
RF Power Input, Stop band (F2-F5) <sup>4</sup>	100 mW at +25°C

2. Permanent damage may occur if any of these limits are exceeded.

3. Passband rating decreases linearly to 1 W at 105°C ambient

4. Stop band rating decreases linearly to 50 mW at 105°C ambient

## SPECIFICATION DEFINITION







# MMIC REFLECTIONLESS Low Pass Filter

**XLF-762+**

Mini-Circuits

## SIMPLIFIED SCHEMATIC AND PAD DESCRIPTION



Function	Pad Number	Description
RF-IN	2	RF Input Pad
RF-OUT	8	RF Output Pad
GND	1,3,7,9, Paddle	Connected to ground
NC (GND Externally)	4,5,6,10,11,12	No internal connection

## PRODUCT MARKING



Marking may contain other features or characters for internal lot control

Mini-Circuits®

[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 3 OF 6



MMIC REFLECTIONLESS



# Low Pass Filter

**XLF-762+**

Mini-Circuits

**TYPICAL PERFORMANCE DATA AT +25°C**

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10	0.39	1.04
50	0.40	1.02
100	0.38	1.02
200	0.39	1.04
400	0.40	1.08
800	0.45	1.16
1500	0.53	1.27
2500	0.60	1.27
4000	0.65	1.21
6000	0.84	1.30
7600	1.02	1.26
9000	1.45	1.49
11000	2.96	1.57
13100	14.60	1.16
15000	26.17	1.55
17000	19.42	2.05
18500	20.07	1.95
20000	26.26	1.44
21500	21.97	2.57
23000	17.87	3.63

**Mini-Circuits®**[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

PAGE 4 OF 6



MMIC REFLECTIONLESS

# Low Pass Filter

XLF-762+

Mini-Circuits

ADDITIONAL DETAILED TECHNICAL INFORMATION IS AVAILABLE ON OUR DASH BOARD. TO ACCESS [CLICK HERE](#)

Performance Data & Graphs	Data Graphs S-Parameter (S2P Files) Data Set (.zip file)
Case Style	DQ1225 Plastic package, exposed paddle lead finish: matte-tin
Tape & Reel Standard quantities available on reel	F66 7" reels with 20, 50, 100, 200, 500 ,1000, 2000, 3000 devices
Suggested Layout for PCB Design	PL-451
Evaluation Board	TB-844-762+ (without connectors) TB-844-762C+ (with connectors) B20-118-F1+ Connector sold separately
Environmental Ratings	ENV82

**ESD RATING**

Human body model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1-2001

**MSL RATING**

Moisture Sensitivity: MSL1 in accordance with IPC/JEDEC J-STD-020D



MMIC REFLECTIONLESS


# Low Pass Filter

XLF-762+

Mini-Circuits

## REFLECTIONLESS FILTER APPLICATION NOTE

Application Circuit Example: Pairing mixers with reflectionless filters to improve system dynamic range



Test block diagram: IF output reflection spectrum with single input frequency




Figure 1. IF output reflection spectrum without filter





Figure 2. IF output reflection spectrum with conventional filter



An application circuit was assembled to measure the IF reflection spectrum at the output of a mixer when the mixer was paired with a conventional filter versus a reflectionless filter.

While the conventional filter reduces the reflections present when the mixer is used alone (no filter), the reflectionless filter virtually eliminates those reflections altogether.

The reflected signal at marker 1 in the figures above exhibits a reduction of more than 20 dB from -28.7 dBm to -50.3 dBm when the reflectionless filter is used as compared to the conventional filter, thus eliminating unwanted spurious mixing products and improving system dynamic range.

For more information, refer to application note [AN-75-007](#).

### NOTES

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)

Mini-Circuits®

## Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB)					GROUP DELAY (nsec)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	0.38	0.38	0.40	0.41	0.45	0.06	0.06	0.08	0.06	0.09
50	0.34	0.35	0.39	0.41	0.42	0.05	0.06	0.06	0.06	0.07
100	0.33	0.34	0.38	0.41	0.42	0.06	0.05	0.05	0.05	0.05
200	0.33	0.34	0.40	0.42	0.44	0.05	0.05	0.05	0.05	0.05
300	0.33	0.35	0.40	0.44	0.45	0.05	0.05	0.05	0.05	0.04
400	0.32	0.34	0.40	0.43	0.45	0.05	0.05	0.05	0.05	0.04
500	0.33	0.34	0.41	0.45	0.47	0.05	0.05	0.04	0.04	0.04
600	0.33	0.36	0.43	0.47	0.48	0.05	0.05	0.04	0.04	0.04
700	0.34	0.36	0.44	0.49	0.50	0.05	0.05	0.04	0.04	0.04
800	0.35	0.37	0.45	0.49	0.51	0.05	0.05	0.04	0.04	0.04
900	0.35	0.37	0.46	0.51	0.52	0.05	0.05	0.04	0.04	0.04
1000	0.35	0.38	0.47	0.51	0.53	0.05	0.05	0.04	0.04	0.04
1200	0.37	0.39	0.50	0.55	0.56	0.05	0.05	0.04	0.04	0.04
1400	0.38	0.41	0.52	0.58	0.60	0.05	0.05	0.04	0.04	0.04
1600	0.40	0.43	0.54	0.60	0.62	0.05	0.05	0.04	0.04	0.04
1800	0.41	0.44	0.56	0.61	0.63	0.05	0.05	0.04	0.04	0.04
2000	0.42	0.44	0.57	0.63	0.64	0.05	0.05	0.04	0.04	0.04
2500	0.43	0.46	0.60	0.66	0.68	0.05	0.05	0.04	0.04	0.04
3000	0.42	0.46	0.61	0.68	0.69	0.05	0.05	0.04	0.04	0.04
3500	0.42	0.46	0.62	0.70	0.73	0.05	0.05	0.04	0.04	0.04
4000	0.43	0.47	0.65	0.75	0.77	0.05	0.05	0.04	0.04	0.04
4500	0.44	0.49	0.69	0.80	0.84	0.05	0.05	0.05	0.04	0.05
5000	0.46	0.52	0.74	0.86	0.90	0.05	0.05	0.05	0.05	0.05
5500	0.51	0.56	0.79	0.92	0.97	0.05	0.05	0.05	0.05	0.05
6000	0.55	0.61	0.84	0.98	1.02	0.05	0.05	0.05	0.05	0.05
6400	0.57	0.63	0.87	1.02	1.06	0.06	0.05	0.05	0.05	0.05
6800	0.59	0.65	0.91	1.06	1.11	0.06	0.06	0.05	0.05	0.05
7000	0.60	0.66	0.93	1.09	1.15	0.06	0.06	0.05	0.05	0.05
7200	0.60	0.67	0.96	1.13	1.19	0.06	0.06	0.05	0.05	0.05
7400	0.61	0.69	0.98	1.17	1.23	0.06	0.06	0.05	0.06	0.06
7600	0.62	0.69	1.01	1.20	1.27	0.06	0.06	0.06	0.06	0.06
7800	0.65	0.72	1.05	1.26	1.33	0.07	0.06	0.06	0.06	0.06
8000	0.67	0.75	1.10	1.31	1.38	0.07	0.07	0.06	0.06	0.06
8200	0.70	0.79	1.15	1.37	1.45	0.07	0.07	0.06	0.06	0.06
8400	0.75	0.83	1.20	1.44	1.52	0.07	0.07	0.06	0.06	0.06
8600	0.81	0.90	1.27	1.51	1.60	0.07	0.07	0.07	0.06	0.06
8800	0.89	0.97	1.35	1.61	1.69	0.07	0.07	0.07	0.07	0.07
9000	0.98	1.07	1.44	1.69	1.78	0.07	0.07	0.07	0.07	0.07
9200	1.09	1.18	1.55	1.81	1.89	0.08	0.08	0.07	0.07	0.07
9400	1.19	1.30	1.67	1.93	2.01	0.08	0.08	0.07	0.07	0.07
9600	1.31	1.40	1.78	2.05	2.14	0.08	0.08	0.07	0.07	0.08
9800	1.42	1.52	1.91	2.19	2.28	0.08	0.08	0.08	0.08	0.08
10000	1.53	1.63	2.05	2.35	2.44	0.09	0.08	0.08	0.08	0.08
10600	1.86	1.98	2.53	2.90	3.03	0.10	0.10	0.10	0.10	0.10
10800	1.98	2.11	2.71	3.13	3.27	0.11	0.11	0.10	0.10	0.10
11000	2.13	2.28	2.94	3.41	3.56	0.12	0.12	0.11	0.11	0.11
11200	2.35	2.51	3.23	3.75	3.91	0.13	0.13	0.12	0.12	0.12
11400	2.66	2.84	3.60	4.18	4.37	0.14	0.14	0.13	0.13	0.13
11600	3.07	3.26	4.09	4.73	4.94	0.15	0.15	0.14	0.14	0.14
12000	4.33	4.56	5.54	6.34	6.60	0.17	0.17	0.16	0.15	0.15
13000	11.45	11.81	13.32	14.60	15.00	0.17	0.16	0.14	0.13	0.13
13100	12.58	12.96	14.56	15.87	16.28	0.17	0.16	0.13	0.12	0.12
13200	13.79	14.18	15.86	17.19	17.62	0.15	0.15	0.13	0.11	0.10
13300	15.09	15.52	17.22	18.58	19.04	0.14	0.14	0.10	0.09	0.08
14000	25.56	25.68	26.44	27.04	27.21	-0.07	-0.05	-0.04	0.00	0.00
15000	25.53	25.64	26.11	26.51	26.58	0.23	0.22	0.24	0.23	0.23
16000	20.97	21.08	21.51	21.81	21.88	0.17	0.17	0.15	0.13	0.13
17000	19.03	19.10	19.39	19.66	19.75	0.10	0.10	0.10	0.11	0.10
18000	18.45	18.60	19.41	19.85	20.05	0.12	0.12	0.10	0.10	0.10
19000	19.93	20.17	21.32	22.21	22.51	0.14	0.14	0.14	0.13	0.14
20000	24.12	24.41	26.20	27.66	28.28	0.27	0.27	0.29	0.31	0.33
21000	23.55	23.78	24.33	24.91	25.18	0.23	0.23	0.20	0.18	0.15
22000	20.62	20.66	20.33	20.31	20.36	0.06	0.06	0.08	0.09	0.09
23000	17.38	17.53	17.89	17.79	17.69	0.06	0.05	0.05	0.06	0.07
24000	14.81	14.97	16.17	16.50	16.63	0.07	0.07	0.03	0.03	0.04
25000	14.42	14.38	14.46	14.91	15.17	0.04	0.03	0.04	0.04	0.03
26000	13.40	13.43	13.00	13.14	13.23	0.02	0.02	0.05	0.05	0.05
27000	10.72	10.94	11.81	12.09	12.16	0.06	0.07	0.04	0.05	0.05
28000	9.51	9.68	10.83	11.69	11.91	0.07	0.07	0.06	0.05	0.04
29000	10.29	10.35	10.18	10.87	11.28	0.03	0.03	0.05	0.04	0.03
30000	9.96	10.14	10.10	10.27	10.35	0.03	0.03	0.05	0.06	0.05
31000	8.79	9.09	10.50	10.76	10.72	0.07	0.07	0.04	0.05	0.05
32000	9.41	9.60	11.51	12.45	12.71	0.10	0.10	0.01	0.01	0.01
33000	12.08	12.08	11.93	13.19	13.82	0.02	0.01	0.03	0.01	0.00
34000	13.57	13.60	12.50	12.98	13.44	-0.02	-0.02	0.01	0.02	0.01
35000	12.36	12.57	12.91	12.82	12.70	-0.01	0.00	0.01	0.00	0.01

 **Mini-Circuits®**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 **The Design Engineers Search Engine** Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

 [minicircuits.com](http://minicircuits.com)

## Typical Performance Data

FREQ. (MHz)	INPUT RETURN LOSS (dB)					OUTPUT RETURN LOSS (dB)				
	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C	@-55°C	@-40°C	@+25°C	@+85°C	@+105°C
	32.59	33.22	34.70	36.73	36.41	35.37	35.80	37.76	40.07	39.80
50	35.69	35.56	39.16	43.51	44.81	35.87	36.60	38.84	40.48	40.93
100	34.96	35.08	37.84	40.59	41.17	36.29	36.80	37.91	38.31	38.00
200	35.22	35.13	34.02	33.54	33.52	35.28	35.12	34.40	33.38	32.86
300	31.15	31.35	30.92	31.02	31.01	30.88	30.86	30.42	30.14	30.19
400	28.71	28.61	28.04	27.96	27.78	28.93	28.70	28.08	27.72	27.70
500	26.73	26.57	26.11	25.91	25.76	27.08	27.03	26.57	26.16	25.96
600	25.59	25.44	24.72	24.71	24.61	25.80	25.73	24.79	24.66	24.65
700	24.28	24.17	23.50	23.28	23.22	24.23	24.15	23.36	23.11	23.03
800	23.00	22.97	22.43	22.21	22.12	22.99	22.90	22.36	22.05	21.95
900	22.01	21.91	21.48	21.35	21.31	21.96	21.91	21.48	21.28	21.25
1000	21.28	21.22	20.78	20.58	20.53	21.28	21.21	20.75	20.55	20.51
1200	20.02	19.96	19.70	19.53	19.52	19.96	19.92	19.64	19.50	19.48
1400	19.04	19.01	18.86	18.69	18.67	19.01	19.02	18.87	18.79	18.69
1600	18.33	18.33	18.36	18.26	18.27	18.26	18.31	18.40	18.33	18.31
1800	17.97	17.98	18.11	18.07	18.09	17.94	17.99	18.20	18.17	18.16
2000	17.72	17.80	18.05	18.10	18.15	17.70	17.81	18.16	18.25	18.24
2500	18.28	18.30	18.53	18.82	18.91	18.26	18.32	18.70	18.89	18.99
3000	19.35	19.38	19.66	19.92	19.99	19.16	19.25	19.59	19.92	20.02
3500	20.14	20.19	20.35	20.32	20.28	19.97	20.06	20.32	20.42	20.43
4000	20.71	20.69	20.33	19.88	19.76	20.56	20.54	20.24	19.87	19.71
4500	20.49	20.43	19.61	18.92	18.73	20.26	20.18	19.49	18.80	18.58
5000	19.28	19.26	18.65	17.98	17.77	18.78	18.80	18.35	17.75	17.50
5500	17.70	17.77	17.78	17.48	17.43	17.15	17.31	17.68	17.40	17.30
6000	16.68	16.81	17.60	17.90	18.06	15.92	16.14	17.38	17.68	17.81
6400	16.59	16.74	17.80	18.57	18.87	15.85	16.04	17.53	18.31	18.63
6800	16.83	17.00	18.24	19.01	19.25	16.13	16.29	17.86	18.76	19.05
7000	17.23	17.37	18.45	19.04	19.17	16.65	16.81	18.04	18.81	18.99
7200	17.76	17.83	18.64	19.03	19.07	17.15	17.22	18.12	18.68	18.75
7400	18.18	18.26	18.64	18.89	18.86	17.57	17.60	18.10	18.49	18.52
7600	18.61	18.63	18.63	18.66	18.55	17.91	17.92	17.97	18.09	18.02
7800	18.64	18.62	18.23	18.12	17.91	18.18	18.11	17.76	17.64	17.44
8000	18.29	18.26	17.83	17.59	17.28	17.86	17.82	17.29	16.98	16.70
8200	17.68	17.67	17.26	16.95	16.67	17.42	17.37	16.80	16.46	16.15
8400	16.86	16.86	16.51	16.29	16.06	16.58	16.60	16.11	15.86	15.56
8600	15.67	15.71	15.77	15.60	15.45	15.44	15.52	15.44	15.26	15.04
8800	14.54	14.62	14.94	14.91	14.82	14.28	14.46	14.71	14.72	14.58
9000	13.38	13.50	14.12	14.30	14.31	13.07	13.27	14.00	14.28	14.29
9200	12.63	12.76	13.42	13.78	13.85	12.23	12.42	13.36	13.84	13.91
9400	11.91	12.04	12.76	13.21	13.33	11.48	11.69	12.79	13.38	13.54
9600	11.42	11.55	12.28	12.75	12.91	10.98	11.18	12.39	13.08	13.30
9800	11.09	11.20	11.91	12.32	12.48	10.69	10.88	12.04	12.71	12.94
10000	11.00	11.10	11.70	12.08	12.25	10.64	10.82	11.93	12.60	12.86
10600	11.77	11.82	11.94	12.09	12.21	11.65	11.76	12.36	12.88	13.10
10800	12.42	12.45	12.43	12.49	12.55	12.59	12.70	13.01	13.37	13.54
11000	13.25	13.28	13.12	13.16	13.22	13.91	13.99	13.85	14.05	14.11
11200	14.07	14.13	14.03	14.14	14.23	15.32	15.40	14.96	14.95	14.93
11400	14.65	14.78	15.08	15.32	15.44	16.80	16.99	16.37	16.19	16.06
11600	15.10	15.32	16.13	16.64	16.87	17.87	18.17	17.77	17.41	17.13
12000	16.03	16.31	17.94	18.91	19.42	18.91	19.36	19.90	19.51	19.02
13000	23.74	24.20	24.88	23.70	22.95	18.17	18.78	21.85	22.05	21.35
13100	23.20	23.24	22.65	21.27	20.67	19.37	19.82	20.84	19.74	18.97
13200	21.56	21.40	20.58	19.36	18.90	21.24	21.39	19.70	18.05	17.20
13300	19.82	19.66	18.97	17.94	17.61	22.25	21.97	18.66	17.06	16.28
14000	13.23	13.32	13.75	14.08	14.25	13.00	13.38	15.14	15.21	15.05
15000	11.94	12.19	13.23	14.15	14.54	12.02	12.31	13.50	14.70	15.17
16000	10.95	11.11	11.77	12.14	12.18	9.70	9.91	10.44	10.36	10.11
17000	8.71	8.82	9.26	9.56	9.64	6.26	6.52	8.71	10.11	10.72
18000	8.40	8.52	8.91	9.23	9.39	9.21	9.23	9.11	9.60	9.82
19000	10.72	10.90	11.50	12.04	12.32	14.52	14.80	12.37	11.38	10.90
20000	15.42	15.38	14.83	14.11	13.96	15.33	16.15	14.85	11.91	10.83
21000	9.11	9.04	9.04	8.42	8.32	7.11	7.42	8.61	7.73	7.13
22000	6.04	6.03	6.22	5.82	5.86	3.08	3.32	5.63	7.14	7.58
23000	4.50	4.59	4.90	5.16	5.33	3.62	3.72	4.50	5.78	6.57
24000	4.01	4.12	4.60	5.22	5.47	4.69	4.88	4.09	3.89	3.77
25000	3.95	4.07	4.65	5.07	5.19	1.98	2.29	4.14	4.29	4.05
26000	4.22	4.33	4.81	4.94	5.01	1.85	2.09	4.64	6.55	7.11
27000	4.81	4.90	5.20	5.39	5.51	5.28	5.23	5.22	6.14	6.78
28000	5.31	5.41	5.74	6.25	6.36	5.81	6.12	5.61	4.68	4.30
29000	5.62	5.69	6.04	6.08	5.99	2.27	2.58	5.36	5.42	4.92
30000	5.26	5.32	5.76	5.56	5.47	2.29	2.49	4.92	7.18	7.72
31000	4.24	4.30	4.60	5.02	5.23	4.54	4.40	3.98	5.06	5.89
32000	3.36	3.39	3.35	3.83	4.05	3.86	4.11	2.79	2.46	2.43
33000	1.82	1.91	2.19	2.41	2.47	0.20	0.44	2.03	1.91	1.66
34000	1.01	1.11	1.68	1.86	1.90	0.44	0.24	1.69	2.61	2.49
35000	1.34	1.43	1.92	2.14	2.26	0.22	0.41	1.69	3.26	4.07

 Mini-Circuits®

ISO 9001 ISO 14001 AS 9100 CERTIFIED


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 **The Design Engineers Search Engine** Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)  
**IF/RF MICROWAVE COMPONENTS**



# MMIC Reflectionless Low Pass Filter

XLF-762+

## Typical Performance Curves



**Mini-Circuits®**  
ISO 9001 ISO 14001 AS 9100 CERTIFIED



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
[minicircuits.com](http://minicircuits.com)



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

## Outline Dimensions



SUGGESTED LAYOUT,  
TOLERANCE TO BE WITHIN  $\pm .002$

**Weight: .02 Grams**

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .01$ ; 3 Pl.  $\pm .004$

### Notes:

1. Case material: Plastic.
2. Termination finish:
  - For RoHS Case Styles: Tin-Silver alloy plate over Nickel barrier or Matte-Tin. All models, (+) suffix.  
See Data sheet.
  - For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010


INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified

# Tape & Reel Packaging TR-F66

## DEVICE ORIENTATION IN T&R



Tape Width, mm	Device Cavity Pitch, mm	Reel Size, inches	Devices per Reel see note	
8	4	7	Small quantity standard	20
				50
				100
				200
				500
		7	Standard	1000, 2000, 3000

Note: Please consult individual model data sheet to determine device per reel availability.

Mini-Circuits carrier tape materials provide protection from ESD (Electro-Static Discharge) during handling and transportation. Tapes are static dissipative and comply with industry standards EIA-481/EIA-541.

Go to: [www.minicircuits.com/pages/pdfs/tape.pdf](http://www.minicircuits.com/pages/pdfs/tape.pdf)




Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Mini-Circuits ISO 9001 & ISO 14001 Certified


## THIRD ANGLE PROJECTION



## REVISIONS

REV	ECN No.	DESCRIPTION	DATE	DR	AUTH
OR	M152656	NEW RELEASE	09/11/15	ITG	MY

SUGGESTED MOUNTING CONFIGURATION  
FOR DQ1225 CASE STYLE, "12FL02" PIN CODE

NOTES:

1. TRACE WIDTH PARAMETERS ARE SHOWN FOR ROGERS R04350B WITH DIELECTRIC THICKNESS  $.0066'' \pm .0007''$ . COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH AND GAP MAY NEED TO BE MODIFIED.
2. BOTTOM SIDE OF THE PCB IS CONTINUOUS GROUND PLANE.



DENOTES PCB COPPER LAYOUT WITH SMOBC (SOLDER MASK OVER BARE COPPER).



DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK.

## UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ON:

2 PL DECIMALS  $\pm$ 3 PL DECIMALS  $\pm .005$ ANGLES  $\pm$ FRACTIONS  $\pm$ 

## INITIALS

DRAWN ITG 09/10/15

CHECKED GF 09/11/15

APPROVED MY 09/11/15

Mini-Circuits®



Mini-Circuits®

13 Neptune Avenue  
Brooklyn NY 11235

PL, 12FL02, DQ1225, TB-844+


SIZE	CODE IDENT	DRAWING NO:	REV:
A	15542	98-PL-451	OR
FILE:	98PL451	SCALE: 16:1	SHEET: 1 OF 1

THIS DOCUMENT AND ITS CONTENTS ARE THE PROPERTY OF MINI-CIRCUITS.  
EXCEPT FOR USE EXPRESSLY GRANTED, IN WRITING, TO ITS VENDORS, VENDEE  
AND THE UNITED STATES GOVERNMENT, MINI-CIRCUITS RESERVES ALL PROPRIETARY  
DESIGN, USE, MANUFACTURING AND REPRODUCTION RIGHTS THERETO.  
THESE CONTENTS SHALL NOT BE USED, DUPLICATED OR DISCLOSED TO ANY OUTSIDE  
PARTY, IN WHOLE OR IN PART, WITHOUT WRITTEN PERMISSION OF MINI-CIRCUITS.


ASHEET1.DWG REV:A DATE:01/12/95

# Evaluation Board and Circuit

To be used with Mini-Circuits 50 Ohm 2.92 connectors B20-118-F1+.  
Connectors are sold separately.



TB-844-762+




Schematic Diagram

Note:


PCB Material: R04350 or equivalent,  
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**

# Evaluation Board and Circuit



TB-844-762C+



Schematic Diagram

Notes:

1. 50 Ohm 2.92 mm Female connectors.
2. PCB Material: RO4350 or equivalent,  
Dielectric Constant=3.5, Thickness=.0066 inch.

 **Mini-Circuits®**



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-65° to 150° C Ambient Environment	Individual Model Data Sheet
Autoclave	15 psig, 100% RH, 121°C, 96 hours	JESD22-A102-C, Condition C
Temperature Cycling	-65° to 150°C, 100 cycles	JESD22-A104
Temperature Humidity	85°C/ 85% RH, 168 hours	JESD22-113
Solder Reflow Heat	Sn-Pb Eutetic Process: 240°C peak Pb-Free Process: 260°C peak	J-STD-020, Table 4-1, 4-2 and 5-2; Figure 5-1
Moisture Sensitivity: Level 1	Bake at 125°C for 24 hours Soak at 85°C/85% RH for 168 hours, Reflow 3 cycles at 240°C peak (Non-RoHS) or 260°C (RoHS)	J-STD-020C
Solderability	10X magnification, 95% coverage	JESD22-B102, Method 1: Dip and Look Test
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + propylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215