

Coaxial Frequency Mixer

Level 7 (LO Power +7 dBm) 0.025 to 200 MHz

ZAD-3+



Generic photo used for illustration purposes only

CASE STYLE: M22

Connectors Model
BNC ZAD-3+
BRACKET (OPTION "B")
BRACKET (OPTION "BR")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
RF Power	50mW
IF Current	40mA

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

LO	1
RF	3
IF	2


Features

- low conversion loss, 4.61 dB typ.
- high L-R isolation, 45 dB typ.
- rugged shielded case

Applications

- VHF
- FM radio
- instrumentation

Outline Drawing



Outline Dimensions (inch)

A	B	C	D	E	F	G	H
2.25	1.38	1.24	.50	.150	3.100	.138	1.238
57.15	35.05	31.50	12.70	3.81	78.74	3.51	31.45
J	K	L	M	N	P	S	wt
3.25	.10	.40	1.15	1.86	.64	.150	grams
82.55	2.54	10.16	29.21	47.24	16.26	3.81	74.0

Electrical Specifications

FREQUENCY (MHz)		CONVERSION LOSS (dB)				LO-RF ISOLATION (dB)						LO-IF ISOLATION (dB)					
LO/RF f_L - f_U	IF	Mid-Band m		Total Range Max.		L		M		U		L		M		U	
		$\bar{X}$	σ			Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Min.
0.025-200	DC-200	4.61	0.06	7.5	8.5	60	50	45	35	35	25	45	35	40	30	30	20


1 dB COMP.: +1 dBm typ.

L = low range [f_L to $10 f_L$]
m = mid band [$2 f_L$ to $f_U/2$]
M = mid range [$10 f_L$ to $f_U/2$]
U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)		Conversion Loss (dB)	Isolation L-R (dB)	Isolation L-I (dB)	VSWR RF Port (:1)	VSWR LO Port (:1)
RF	LO	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm	LO +7dBm
0.03	30.03	6.94	58.72	53.27	1.16	2.06
0.04	30.04	5.80	55.35	51.43	1.17	2.04
0.05	30.05	5.52	54.61	51.09	1.17	2.01
0.10	30.10	5.16	53.51	50.41	1.16	1.99
0.20	30.20	4.98	53.27	50.18	1.16	2.05
0.50	30.50	4.92	53.12	50.13	1.15	2.08
1.00	31.00	4.82	53.18	50.48	1.15	2.07
2.00	32.00	4.77	53.13	50.55	1.14	2.07
5.00	35.00	4.76	53.42	50.99	1.13	2.05
10.00	40.00	4.81	53.68	51.27	1.11	2.02
20.00	50.00	4.87	53.67	50.52	1.10	2.02
38.48	68.48	4.96	53.25	48.52	1.09	2.02
50.00	80.00	4.94	53.49	47.54	1.09	2.03
69.25	99.25	4.90	53.53	45.77	1.08	2.03
84.63	54.63	4.86	53.31	44.13	1.09	2.05
100.00	70.00	4.81	53.55	42.70	1.11	2.07
123.09	93.09	4.87	55.31	40.58	1.13	2.11
153.85	123.85	4.96	52.97	38.04	1.15	2.13
176.93	146.93	5.19	49.53	38.76	1.18	2.14
200.00	170.00	5.28	45.61	38.31	1.21	2.15

Electrical Schematic









Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. D
M151107
ZAD-3+
DJ/TD/CP
200620
Page 1 of 2



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Typical Performance Data

RF (MHz)	LO (MHz)	CONVERSION LOSS (dB)			LO (MHz)	LO-RF ISOLATION (dB)			LO-IF ISOLATION (dB)		
		@LO (dBm)				@LO (dBm)			@LO (dBm)		
		+4	+7	+10		+4	+7	+10	+4	+7	+10
0.03	30.0	7.21	6.94	6.77	0.03	61.68	58.72	56.56	57.08	53.27	51.07
0.04	30.0	6.05	5.80	5.65	0.04	57.71	55.35	53.96	54.31	51.43	49.68
0.05	30.1	5.74	5.52	5.37	0.05	56.72	54.61	53.34	53.56	51.09	49.47
0.1	30.1	5.32	5.16	4.95	0.1	55.43	53.51	52.62	52.38	50.41	49.13
0.2	30.2	5.21	4.98	4.86	0.2	55.00	53.27	52.45	51.97	50.18	49.00
0.5	30.5	5.14	4.92	4.82	0.5	54.58	53.12	52.30	51.86	50.13	48.94
1.0	31.0	5.00	4.82	4.72	1.0	53.86	53.18	52.24	51.81	50.48	49.14
2.0	32.0	4.95	4.77	4.67	2.0	53.82	53.13	52.17	51.42	50.55	49.22
5.0	35.0	4.94	4.76	4.66	5.0	54.18	53.42	52.39	52.01	50.99	49.53
10.0	40.0	5.00	4.81	4.69	10.0	54.39	53.68	52.71	52.35	51.27	49.73
20.0	50.0	5.11	4.87	4.75	20.0	54.46	53.67	52.78	51.61	50.52	49.12
38.5	68.5	5.19	4.96	4.84	38.5	54.62	53.25	52.25	51.07	48.52	46.85
50.0	80.0	5.16	4.94	4.84	50.0	54.76	53.49	52.53	49.96	47.54	45.77
69.2	99.2	5.10	4.90	4.78	69.2	54.38	53.53	52.77	47.69	45.77	44.16
84.6	54.6	5.07	4.86	4.78	84.6	54.10	53.31	52.51	45.33	44.13	42.88
100.0	70.0	4.95	4.81	4.73	100.0	53.91	53.55	52.96	43.50	42.70	41.62
123.1	93.1	5.02	4.87	4.81	123.1	55.23	55.31	55.03	40.89	40.58	39.80
153.9	123.9	5.11	4.96	4.89	153.9	52.25	52.97	52.92	38.71	38.04	37.79
176.9	146.9	5.30	5.19	5.10	176.9	47.72	49.53	51.11	37.78	38.76	38.46
200.0	170.0	5.37	5.28	5.21	200.0	43.90	45.61	47.46	36.16	38.31	40.01

Frequency Mixer

ZAD-3+

Typical Performance Data

RF/LO (MHz)	RF VSWR (:1)			LO VSWR (:1)			IF (MHz)	IF VSWR (:1)			LO/RF (MHz)	max. DC output (mV)	DC Offset (mV)
	@LO (dBm)			@LO (dBm)				@LO (dBm)			@LO (dBm)		
	+4	+7	+10	+4	+7	+10		+4	+7	+10	+7		
5.0	1.28	1.16	1.09	1.39	2.06	2.93	5.0	1.53	1.42	1.33	0.025	-227.8	0.96
10.0	1.29	1.17	1.09	1.38	2.04	2.90	10.0	1.54	1.43	1.33	0.03	-237.3	1.02
16.1	1.29	1.17	1.09	1.36	2.01	2.83	16.1	1.55	1.44	1.34	0.05	-248.9	1.03
20.0	1.29	1.16	1.09	1.34	1.99	2.80	20.0	1.55	1.44	1.34	0.10	-255.2	1.01
27.3	1.28	1.16	1.08	1.39	2.05	2.85	27.3	1.55	1.45	1.35	0.50	-258.7	1.02
38.4	1.27	1.15	1.08	1.43	2.08	2.86	38.4	1.57	1.46	1.36	2.00	-256.8	1.02
44.0	1.27	1.15	1.07	1.42	2.07	2.86	44.0	1.58	1.47	1.37	5.00	-253.4	1.00
50.0	1.26	1.14	1.07	1.42	2.07	2.84	50.0	1.59	1.49	1.39	10.00	-256.8	0.99
60.7	1.25	1.13	1.06	1.41	2.05	2.80	60.7	1.62	1.52	1.42	20.00	-253.0	0.98
77.4	1.23	1.11	1.06	1.41	2.02	2.77	77.4	1.67	1.57	1.47	38.48	-249.2	0.98
94.1	1.21	1.10	1.06	1.42	2.02	2.77	94.1	1.73	1.63	1.53	53.86	-257.1	1.07
100.0	1.20	1.09	1.06	1.42	2.02	2.75	100.0	1.76	1.65	1.55	69.25	-254.5	1.11
110.9	1.18	1.09	1.08	1.44	2.03	2.75	110.9	1.81	1.70	1.61	84.63	-257.0	1.21
122.0	1.17	1.08	1.09	1.45	2.03	2.76	122.0	1.87	1.75	1.64	100.00	-257.9	1.33
138.7	1.16	1.09	1.12	1.47	2.05	2.74	138.7	1.99	1.85	1.76	115.40	-255.2	1.28
149.9	1.15	1.11	1.14	1.51	2.07	2.72	149.9	2.05	1.92	1.81	130.78	-249.2	1.29
166.6	1.15	1.13	1.17	1.53	2.11	2.76	166.6	2.16	2.01	1.91	153.85	-254.9	1.35
177.7	1.16	1.15	1.20	1.56	2.13	2.79	177.7	2.24	2.08	1.98	169.24	-255.8	1.58
188.9	1.17	1.18	1.23	1.59	2.14	2.82	188.9	2.31	2.16	2.05	184.62	-255.3	1.77
200.0	1.19	1.21	1.25	1.61	2.15	2.80	200.0	2.39	2.24	2.11	200.00	-253.6	1.72

REV. X1
ZAD-3+
070509
Page 2 of 2



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Typical Performance Curves


Conversion Loss




LO-RF Isolation




LO-IF Isolation




RF VSWR




LO VSWR



IF VSWR



Max. DC Output



REV. X1

ZAD-3+

070509

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see





Outline Dimensions

M21

M22

M23



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
M21	1.50 (38.10)	1.13 (28.70)	1.00 (25.40)	.50 (12.70)	.155 (3.94)	2.345 (59.56)	.138 (3.51)	.987 (25.07)	2.50 (63.50)	.10 (2.54)	.31 (7.87)	.75 (19.05)	1.19 (30.23)
M22	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)		.150 (3.81)	3.100 (78.74)		1.238 (31.45)	3.25 (82.55)		.40 (10.16)	1.15 (29.21)	1.86 (47.24)
M23	2.25 (57.15)	1.38 (35.05)	1.24 (31.50)		.150 (3.81)	3.100 (78.74)		1.238 (31.45)	3.25 (82.55)		.63 (16.00)	1.06 (26.92)	1.63 (41.40)

CASE#	P	Q	R	S	WT. GRAMS
M21	.66 (16.76)	--	--	.150 (3.81)	40.0
M22	.64 (16.26)	--	--		74.0
M23	.69 (17.53)	--	--		70.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
 - For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
 - For Non-RoHS Case Styles: Yellow hexavalent chrome based conversion coating.

Due to transition from non-RoHS to RoHS, models will be supplied with either case style finish until the non-RoHS case inventory is depleted.
- Mounting bracket available on request. For bracket mounted on connector end add suffix B to part number and add \$5.00 to unit cost. For bracket mounted on the rear, add suffix BR to part number and add \$1.50 to unit cost.



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I