

DC Pass Directional Coupler

ZADC-ED12622/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.




CASE STYLE : CC51-1

ELECTRICAL SPECIFICATIONS 75Ω/50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		850		1450	MHz
Coupling	Nominal		20±1		dB
	Flatness		± 0.63		dB
Mainline Loss **	850-1450 MHz		0.80		dB
Directivity	850-1450 MHz		22		dB
VSWR	850-1450 MHz		1.15		(:1)
RF Power Input	850-1450 MHz			5	W

Note: ** Mainline loss includes theoretical coupled power loss of 0.044dB at 20dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2A

COAXIAL CONNECTIONS	
INPUT (75 OHM, F TYPE)	1
OUTPUT (75 OHM, F-TYPE)	3
COUPLED FORWARD (50 OHM, N-TYPE)	2



* ELECTRICAL SCHEMATIC FOR DIRECTIONAL COUPLER THAT IS DESIGNED WITHOUT INTERNAL TRANSFORMERS.

Directional Coupler

ZADC-ED12622/1





Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	COUPLING (dB)	DIRECTIVITY (dB)	RETURN LOSS		
				IN	OUT	CPL
6.0	0.02	59.66	16.49	53.16	53.19	33.50
8.0	0.02	57.18	16.45	52.83	52.61	33.53
10.0	0.02	55.28	16.52	52.21	52.22	34.03
12.0	0.02	53.68	16.49	51.71	51.56	33.82
14.0	0.02	52.33	16.58	51.23	50.82	33.70
20.0	0.03	49.26	16.46	49.50	49.26	33.58
30.0	0.03	45.74	16.60	46.90	46.61	33.61
50.0	0.04	41.33	16.68	42.72	42.63	33.77
250.0	0.17	27.73	16.98	28.62	28.11	33.60
450.0	0.39	23.28	17.91	23.24	23.24	31.87
650.0	0.60	21.00	19.60	21.07	21.34	30.86
850.0	0.72	19.82	22.46	21.69	21.55	30.53
925.0	0.73	19.58	24.04	22.51	22.06	30.44
950.0	0.73	19.52	24.64	22.92	22.33	30.40
975.0	0.72	19.47	25.30	23.37	22.62	30.71
1000.0	0.72	19.44	26.01	23.82	22.92	30.17
1025.0	0.73	19.41	26.77	24.37	23.28	29.60
1050.0	0.72	19.40	27.57	25.06	23.72	29.68
1075.0	0.72	19.39	28.39	25.83	24.19	29.37
1100.0	0.73	19.40	29.17	26.64	24.65	28.50
1125.0	0.72	19.41	29.88	27.55	25.14	28.16
1150.0	0.73	19.44	30.38	28.66	25.77	28.03
1175.0	0.73	19.47	30.51	29.91	26.49	27.29
1200.0	0.73	19.52	30.24	31.03	27.05	26.70
1225.0	0.74	19.58	29.57	31.99	27.62	26.56
1250.0	0.75	19.65	28.64	32.66	28.24	26.09
1275.0	0.73	19.73	27.55	32.65	28.69	25.47
1300.0	0.76	19.82	26.40	31.94	28.84	25.33
1325.0	0.77	19.92	25.27	30.81	28.90	25.10
1350.0	0.75	20.04	24.16	29.44	28.79	24.48
1375.0	0.75	20.17	23.11	28.15	28.27	24.24
1400.0	0.78	20.31	22.09	27.01	27.62	24.17
1425.0	0.77	20.47	21.13	25.96	27.03	23.64
1450.0	0.74	20.64	20.21	24.99	26.35	23.23
1475.0	0.74	20.83	19.32	24.02	25.53	23.22
1500.0	0.77	21.03	18.47	23.22	24.86	22.95
1600.0	0.74	22.04	15.29	20.49	22.41	22.22
1700.0	0.68	23.44	12.29	18.49	20.43	21.75
1800.0	0.63	25.41	9.20	16.86	18.77	21.63
1900.0	0.58	28.33	5.56	15.40	17.18	21.43
2000.0	0.55	33.18	0.25	14.03	15.51	20.77

Directional Coupler


Typical Performance Curves

ZADC-ED12622/1



Outline Dimensions

CC51-1



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
CC51-1	2.00 (50.80)	2.00 (50.80)	.75 (19.05)	.938 (23.83)	.13 (3.30)	1.750 (44.45)	.125 (3.17)	.38 (9.65)	1.00 (25.40)	1.25 (31.75)	145

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I