

Power Splitter/Combiner

ZAPD-232-75+

2 Way-0° 75Ω 700 to 2450 MHz

Maximum Ratings


Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.5W max.
DC Current	1.0A (500mA for each port)

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Outline Drawing




Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
2.00	2.00	.75	1.00	.13	1.750	.125
50.80	50.80	19.05	25.40	3.30	44.45	3.18

H	J	K	L	wt
.39	1.00	.50	1.00	grams
9.91	25.40	12.70	25.40	170.0

Electrical Schematic



Features

- wideband, 700-2450 MHz
- low insertion loss, 0.5 dB typ.
- good isolation, 25 dB typ.
- excellent output VSWR, 1.15:1 typ.
- excellent input VSWR, 1.25:1 typ.

Applications

- cable TV
- cellular
- GPS
- PCS
- WCDMA
- communication systems
- L-Band




Electrical Specifications at 25°C

Parameter	Frequency (MHz)	Min.	Typ.	Max.	Unit
Frequency Range		700		2450	MHz
Insertion Loss Above 3.0 dB	700 - 2450	—	0.5	1.0	dB
Isolation	700 - 2450	15	20	—	dB
	950 - 2300	20	25	—	dB
Phase Unbalance	700 - 2450	—	1.0	3.0	Degree
Amplitude Unbalance	700 - 2450	—	0.1	0.3	dB
VSWR (Port S)	700 - 2450	—	1.5	1.9	:1
	950 - 2300	—	1.25	1.5	:1
VSWR (Port 1-2)	700 - 2450	—	1.2	1.4	:1
	950 - 2300	—	1.15	1.3	:1

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)	Amp. Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2					
700	3.46	3.45	0.00	17.20	0.61	1.62	1.24
800	3.45	3.45	0.00	19.91	0.77	1.51	1.25
950	3.44	3.41	0.03	23.03	0.81	1.35	1.20
1100	3.39	3.36	0.03	23.51	0.86	1.19	1.08
1200	3.40	3.36	0.04	24.00	0.88	1.11	1.05
1300	3.44	3.40	0.04	25.33	0.78	1.13	1.10
1400	3.45	3.41	0.04	27.02	0.78	1.13	1.15
1500	3.41	3.41	0.01	29.89	1.09	1.21	1.20
1600	3.47	3.44	0.03	29.28	1.13	1.23	1.19
1700	3.61	3.55	0.06	28.71	1.17	1.29	1.16
1800	3.72	3.64	0.08	30.43	1.21	1.35	1.14
1900	3.72	3.62	0.10	38.03	1.19	1.34	1.10
2000	3.66	3.55	0.11	30.29	1.37	1.31	1.08
2150	3.63	3.56	0.08	24.42	1.31	1.19	1.04
2300	3.70	3.59	0.11	24.29	1.12	1.19	1.05
2450	3.75	3.64	0.11	19.47	1.25	1.59	1.15

1. Total Loss = Insertion Loss + 3dB splitter theoretical loss.



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

ZAPD-232-75+

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB) 1-2	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
400	3.55	3.56	0.01	10.38	0.42	400	1.83	1.05	1.04
500	3.54	3.54	0.00	12.34	0.48	500	1.77	1.12	1.10
600	3.51	3.51	0.00	14.54	0.53	600	1.71	1.20	1.18
650	3.49	3.50	0.01	15.83	0.68	650	1.66	1.23	1.22
700	3.46	3.45	0.00	17.20	0.61	700	1.62	1.24	1.23
750	3.48	3.47	0.01	18.35	0.78	750	1.59	1.25	1.24
800	3.45	3.45	0.00	19.91	0.77	800	1.51	1.25	1.24
850	3.45	3.43	0.02	21.05	0.72	850	1.48	1.24	1.22
900	3.46	3.44	0.02	22.12	0.84	900	1.41	1.23	1.21
950	3.44	3.41	0.03	23.03	0.81	950	1.35	1.20	1.18
1000	3.42	3.40	0.03	23.36	0.86	1000	1.32	1.16	1.15
1100	3.39	3.36	0.03	23.51	0.86	1100	1.19	1.08	1.10
1200	3.40	3.36	0.04	24.00	0.88	1200	1.11	1.05	1.04
1300	3.44	3.40	0.04	25.33	0.78	1300	1.13	1.10	1.07
1400	3.45	3.41	0.04	27.02	0.78	1400	1.13	1.15	1.11
1500	3.41	3.41	0.01	29.89	1.09	1500	1.21	1.20	1.16
1600	3.47	3.44	0.03	29.28	1.13	1600	1.23	1.19	1.20
1700	3.61	3.55	0.06	28.71	1.17	1700	1.29	1.16	1.18
1800	3.72	3.64	0.08	30.43	1.21	1800	1.35	1.14	1.14
1900	3.72	3.62	0.10	38.03	1.19	1900	1.34	1.10	1.12
2000	3.66	3.55	0.11	30.29	1.37	2000	1.31	1.08	1.13
2050	3.63	3.55	0.08	29.24	1.44	2050	1.31	1.07	1.10
2100	3.63	3.56	0.07	24.45	1.29	2100	1.26	1.07	1.08
2150	3.63	3.56	0.08	24.42	1.31	2150	1.19	1.04	1.04
2200	3.65	3.56	0.09	23.99	1.27	2200	1.16	1.03	1.03
2300	3.70	3.59	0.11	24.29	1.12	2300	1.19	1.05	1.07
2400	3.78	3.68	0.10	22.89	1.10	2400	1.44	1.17	1.16
2500	4.06	3.92	0.14	19.99	1.34	2500	1.84	1.24	1.28
2600	4.33	4.21	0.12	15.58	1.09	2600	2.32	1.32	1.39
2650	4.57	4.34	0.22	13.90	0.99	2650	2.39	1.38	1.40
2700	4.78	4.63	0.15	12.72	1.08	2700	2.64	1.45	1.42
2750	4.89	4.76	0.13	11.69	0.17	2750	2.89	1.43	1.38
2800	4.99	4.85	0.15	10.96	0.46	2800	2.79	1.47	1.39
2850	4.90	4.86	0.04	10.08	0.36	2850	2.98	1.43	1.37
2900	5.00	4.95	0.05	9.71	0.69	2900	2.87	1.42	1.37
3000	4.85	4.82	0.02	8.80	1.16	3000	2.61	1.35	1.30

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS








REV. OR
 ZAPD-232-75+
 4/27/2015
 Page 1 of 1

2 Way-0° Power Splitter/Combiner

ZAPD-232-75+

Typical Performance Curves




P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZAPD-232-75+
4/27/2015
Page 1 of 1

Outline Dimensions

F53



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
F53	2.00 (50.80)	2.00 (50.80)	.75 (19.05)	1.00 (25.40)	.13 (3.30)	1.750 (44.45)	.125 (3.18)	.39 (9.91)	1.00 (25.40)	.50 (12.70)	1.00 (25.40)	170.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I