

Engineering Development Model

Power Splitter/Combiner

ZAPD-ED12417/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : F14

| ELECTRICAL SPECIFICATIONS 75Ω @ +25°C | | | | | |
|---------------------------------------|----------------|------|-------|------|-------|
| Parameter | | Min. | Typ. | Max. | Units |
| Frequency | | 660 | | 2400 | MHz |
| Isolation | 660 - 2400 MHz | | 20 | | dB |
| Insertion Loss Above 3.0 dB | 660 - 2400 MHz | | 0.30 | | dB |
| Phase Unbalance | 660 - 2400 MHz | | 0.211 | | deg. |
| Amplitude Unbalance | 660 - 2400 MHz | | 0.082 | | dB |
| VSWR | SUM Port | | 1.30 | | (:1) |
| | OUT Ports | | 1.25 | | (:1) |

| MAXIMUM RATINGS | |
|-----------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |

Functional Diagram



2 Way-0° Power Splitter/Combiner

ZAPD-ED12417/1

Typical Performance Data

| FREQ. (MHz) | TOTAL LOSS ¹ (dB) | | AMP. UNBAL. (dB) | ISOLATION (dB) 1-2 | PHASE UNBAL. (deg.) | FREQ. (MHz) | VSWR (:1) | | |
|----------------|---------------------------------|------|------------------------|--------------------------|---------------------------|----------------|--------------|------|------|
| | S-1 | S-2 | | | | | S | 1 | 2 |
| 420.0 | 3.55 | 3.50 | 0.05 | 9.25 | 0.38 | 420.0 | 1.95 | 1.07 | 1.07 |
| 480.0 | 3.56 | 3.50 | 0.06 | 10.33 | 0.31 | 480.0 | 1.91 | 1.04 | 1.05 |
| 540.0 | 3.57 | 3.50 | 0.07 | 11.47 | 0.27 | 540.0 | 1.87 | 1.09 | 1.10 |
| 600.0 | 3.58 | 3.51 | 0.07 | 12.68 | 0.31 | 600.0 | 1.81 | 1.15 | 1.16 |
| 660.0 | 3.55 | 3.49 | 0.06 | 13.96 | 0.27 | 660.0 | 1.75 | 1.20 | 1.20 |
| 720.0 | 3.51 | 3.45 | 0.06 | 15.38 | 0.26 | 720.0 | 1.68 | 1.23 | 1.24 |
| 780.0 | 3.44 | 3.38 | 0.06 | 16.93 | 0.25 | 780.0 | 1.61 | 1.26 | 1.26 |
| 840.0 | 3.35 | 3.28 | 0.07 | 18.66 | 0.25 | 840.0 | 1.55 | 1.28 | 1.28 |
| 900.0 | 3.28 | 3.21 | 0.07 | 20.62 | 0.29 | 900.0 | 1.47 | 1.28 | 1.28 |
| 920.0 | 3.24 | 3.16 | 0.08 | 21.31 | 0.21 | 920.0 | 1.45 | 1.28 | 1.28 |
| 935.0 | 3.21 | 3.14 | 0.07 | 21.84 | 0.19 | 935.0 | 1.43 | 1.28 | 1.28 |
| 950.0 | 3.18 | 3.12 | 0.06 | 22.39 | 0.25 | 950.0 | 1.42 | 1.28 | 1.28 |
| 975.0 | 3.16 | 3.09 | 0.08 | 23.31 | 0.26 | 975.0 | 1.39 | 1.27 | 1.27 |
| 1000.0 | 3.15 | 3.07 | 0.08 | 24.22 | 0.16 | 1000.0 | 1.36 | 1.27 | 1.27 |
| 1100.0 | 3.08 | 3.00 | 0.07 | 26.54 | 0.16 | 1100.0 | 1.25 | 1.24 | 1.24 |
| 1200.0 | 3.09 | 3.01 | 0.09 | 25.46 | 0.20 | 1200.0 | 1.15 | 1.20 | 1.19 |
| 1250.0 | 3.10 | 3.03 | 0.08 | 24.46 | 0.12 | 1250.0 | 1.10 | 1.17 | 1.17 |
| 1300.0 | 3.18 | 3.09 | 0.10 | 23.60 | 0.07 | 1300.0 | 1.06 | 1.15 | 1.15 |
| 1350.0 | 3.21 | 3.10 | 0.11 | 22.90 | 0.07 | 1350.0 | 1.03 | 1.13 | 1.13 |
| 1460.0 | 3.24 | 3.16 | 0.09 | 22.15 | 0.17 | 1460.0 | 1.07 | 1.10 | 1.09 |
| 1575.0 | 3.14 | 3.08 | 0.05 | 22.50 | 0.31 | 1575.0 | 1.12 | 1.08 | 1.05 |
| 1690.0 | 3.07 | 3.05 | 0.02 | 24.22 | 0.12 | 1690.0 | 1.13 | 1.06 | 1.03 |
| 1805.0 | 3.23 | 3.16 | 0.07 | 28.02 | 0.32 | 1805.0 | 1.10 | 1.04 | 1.03 |
| 1860.0 | 3.29 | 3.20 | 0.09 | 30.85 | 0.34 | 1860.0 | 1.06 | 1.03 | 1.04 |
| 1930.0 | 3.28 | 3.19 | 0.09 | 32.77 | 0.18 | 1930.0 | 1.02 | 1.05 | 1.07 |
| 2040.0 | 3.23 | 3.10 | 0.13 | 26.22 | 0.06 | 2040.0 | 1.10 | 1.10 | 1.13 |
| 2150.0 | 3.33 | 3.23 | 0.09 | 21.06 | 0.38 | 2150.0 | 1.25 | 1.16 | 1.20 |
| 2160.0 | 3.37 | 3.23 | 0.14 | 20.69 | 0.23 | 2160.0 | 1.27 | 1.17 | 1.20 |
| 2170.0 | 3.39 | 3.24 | 0.15 | 20.32 | 0.08 | 2170.0 | 1.28 | 1.18 | 1.21 |
| 2180.0 | 3.40 | 3.27 | 0.12 | 19.97 | 0.35 | 2180.0 | 1.30 | 1.18 | 1.21 |
| 2190.0 | 3.39 | 3.31 | 0.07 | 19.63 | 0.42 | 2190.0 | 1.31 | 1.19 | 1.22 |
| 2200.0 | 3.39 | 3.36 | 0.03 | 19.32 | 0.20 | 2200.0 | 1.32 | 1.20 | 1.22 |
| 2250.0 | 3.52 | 3.39 | 0.13 | 17.83 | 0.08 | 2250.0 | 1.41 | 1.23 | 1.25 |
| 2300.0 | 3.55 | 3.46 | 0.09 | 16.53 | 0.08 | 2300.0 | 1.51 | 1.26 | 1.28 |
| 2350.0 | 3.58 | 3.52 | 0.07 | 15.32 | 0.13 | 2350.0 | 1.62 | 1.29 | 1.30 |
| 2400.0 | 3.60 | 3.54 | 0.05 | 14.21 | 0.29 | 2400.0 | 1.73 | 1.31 | 1.32 |
| 2450.0 | 3.67 | 3.56 | 0.10 | 13.25 | 0.30 | 2450.0 | 1.85 | 1.33 | 1.33 |
| 2500.0 | 3.67 | 3.69 | 0.02 | 12.36 | 0.08 | 2500.0 | 1.93 | 1.34 | 1.34 |
| 2550.0 | 3.77 | 3.66 | 0.11 | 11.55 | 0.23 | 2550.0 | 2.00 | 1.36 | 1.36 |
| 2600.0 | 3.66 | 3.65 | 0.02 | 10.90 | 0.84 | 2600.0 | 2.06 | 1.37 | 1.36 |
| 2650.0 | 3.66 | 3.52 | 0.13 | 10.30 | 0.91 | 2650.0 | 2.16 | 1.39 | 1.38 |






¹ Total Loss = Insertion Loss + 3dB Splitter Loss



2 Way-0° Power Splitter/Combiner

ZAPD-ED12417/1

Typical Performance Curves



REV. X2
ZAPD-ED12417/1
100707
Page 1 of 1

Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Outline Dimensions



| CASE # | A | B | C | D | E | F | G | H | J | K | L | WT. GRAM |
|--------|-----------------|-----------------|----------------|-----------------|---------------|------------------|----------------|---------------|-----------------|----------------|-----------------|----------|
| F14 | 2.00 (50.80) | 2.00 (50.80) | .75 (19.05) | 1.00 (25.40) | .25 (6.35) | 1.500 (38.10) | .125 (3.18) | .39 (9.91) | 1.00 (25.40) | .50 (12.70) | 1.00 (25.40) | 170.0 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|--|--------------------------------------|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Barometric Pressure | 100,000 Feet | MIL-STD-202, Method 105, Condition D |
| Humidity | 90% RH, 65°C Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103 |
| Thermal Shock | -65° to 125°C, 5 cycles | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18) | MIL-STD-202, Method 213, Condition I |