

Engineering Development Model

DC Pass

Bi-Directional Coupler

ZABDC20-ED13198

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : DD477-1


ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		700		2100 MHz
Coupling	Nominal		20.3 ± 1	dB
	Flatness		± 1.5	dB
Mainline Loss *	700-2100 MHz		0.25	dB
Directivity	700-2100 MHz		27	dB
VSWR	700-2100 MHz		1.1	(:1)
RF Power Input	700-2100 MHz			50 W
	800-1000 MHz			100

Note: * Mainline loss includes theoretical coupled power loss of 0.041 dB at 20.3 dB coupling.

MAXIMUM RATINGS	
Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
DC Current	2.0 A

COAXIAL CONNECTIONS	
INPUT	1
OUTPUT	4
COUPLED FORWARD	2
COUPLED REVERSE	3

Electrical Schematic



* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITHOUT INTERNAL TRANSFORMERS AND RESISTORS.





Bi-Directional Coupler

ZABDC20-ED13198


Typical Performance Data

FREQ. (MHz)	INSERTION LOSS		COUPLING		DIRECTIVITY		RETURN LOSS			
	(dB)		(dB)		(dB)		(dB)			
	IN-OUT	FWD-REV	IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
500.0	0.13	0.12	24.35	24.36	26.01	26.12	34.59	35.75	34.77	34.15
600.0	0.14	0.13	22.99	23.01	26.23	26.25	32.88	33.81	32.63	32.00
700.0	0.16	0.15	21.92	21.94	26.27	26.35	31.61	32.26	30.98	30.09
800.0	0.17	0.17	21.08	21.10	26.48	26.19	30.98	31.61	29.43	28.43
900.0	0.19	0.19	20.42	20.44	26.46	25.78	30.60	31.10	28.26	27.24
1000.0	0.20	0.20	19.91	19.93	26.39	25.90	30.35	30.95	27.18	26.13
1100.0	0.21	0.22	19.55	19.57	26.67	25.96	30.39	30.81	26.42	25.28
1200.0	0.22	0.23	19.30	19.32	27.18	26.55	30.40	30.67	25.87	24.71
1300.0	0.22	0.24	19.17	19.19	27.96	27.47	30.69	30.65	25.48	24.35
1400.0	0.23	0.24	19.15	19.17	29.44	28.79	31.13	30.80	25.20	24.09
1500.0	0.23	0.25	19.24	19.25	31.56	29.96	32.22	31.59	25.11	24.02
1600.0	0.23	0.25	19.44	19.46	34.00	31.28	34.08	32.70	25.11	24.09
1700.0	0.23	0.25	19.75	19.77	34.30	30.63	36.77	34.05	25.28	24.21
1800.0	0.23	0.25	20.20	20.22	32.66	29.13	41.59	35.13	25.53	24.47
1900.0	0.23	0.25	20.80	20.82	30.27	27.70	47.55	35.92	25.93	24.76
2000.0	0.23	0.25	21.57	21.59	28.19	26.21	43.27	36.15	26.57	25.27
2100.0	0.22	0.24	22.55	22.57	26.26	24.44	38.36	34.71	27.27	25.95
2200.0	0.22	0.24	23.81	23.83	24.33	22.63	34.93	33.32	28.12	26.71
2300.0	0.22	0.24	25.44	25.47	21.60	20.27	33.02	32.36	28.76	27.39
2400.0	0.22	0.24	27.67	27.68	17.92	16.88	32.21	32.13	29.47	28.04
2500.0	0.22	0.24	30.98	30.99	12.55	11.88	31.20	32.13	29.91	28.26

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT, GRAM
DD477-1	2.00 (50.80)	2.00 (50.80)	.88 (22.35)	.90 (22.86)	.156 (3.96)	1.688 (42.88)	.125 (3.18)	.38 (9.65)	-- --	.50 (12.70)	1.00 (25.40)	1.25 (31.75)	225

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I