

Engineering Development Model

Power Splitter/Combiner

2 Way-0°

ZAPD-ED12592C/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : F53

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		200		6400 MHz
Isolation	200 - 2000 MHz		15	dB
	2000 - 3200 MHz		30	dB
	3200 - 6400 MHz		20	dB
Insertion Loss Above 3.0 dB	200 - 2000 MHz		0.40	dB
	2000 - 3200 MHz		0.55	dB
	3200 - 6400 MHz		0.87	dB
Phase Unbalance	200 - 2000 MHz		0.07	deg.
	2000 - 3200 MHz		0.11	deg.
	3200 - 6400 MHz		0.35	deg.
Amplitude Unbalance	200 - 2000 MHz		0.02	dB
	2000 - 3200 MHz		0.03	dB
	3200 - 6400 MHz		0.11	dB
VSWR	SUM Port		1.23	(:1)
	OUT Ports		1.31	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2

Functional Diagram



2 Way-0° Power Splitter/Combiner

ZAPD-ED12592C/1

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
200.0	3.54	3.50	0.02	6.15	0.11	200.0	1.80	1.89	1.88
300.0	3.46	3.42	0.02	7.90	0.02	300.0	1.64	1.77	1.77
400.0	3.38	3.33	0.01	9.50	0.02	400.0	1.46	1.62	1.62
500.0	3.33	3.28	0.00	11.01	0.06	500.0	1.31	1.46	1.47
600.0	3.31	3.26	0.01	12.54	0.05	600.0	1.21	1.33	1.35
700.0	3.33	3.27	0.01	14.21	0.03	700.0	1.20	1.26	1.28
800.0	3.37	3.31	0.02	16.07	0.02	800.0	1.26	1.23	1.26
900.0	3.42	3.35	0.02	18.28	0.00	900.0	1.31	1.24	1.27
1000.0	3.45	3.39	0.02	21.00	0.00	1000.0	1.34	1.25	1.28
1100.0	3.47	3.40	0.02	24.54	0.00	1100.0	1.34	1.25	1.28
1200.0	3.46	3.40	0.01	29.55	0.01	1200.0	1.30	1.24	1.26
1300.0	3.45	3.39	0.01	35.52	0.01	1300.0	1.23	1.22	1.23
1400.0	3.44	3.38	0.01	32.09	0.03	1400.0	1.15	1.19	1.20
1500.0	3.43	3.37	0.01	27.79	0.07	1500.0	1.08	1.16	1.16
1600.0	3.44	3.37	0.01	25.20	0.11	1600.0	1.03	1.13	1.13
1700.0	3.45	3.38	0.02	23.64	0.13	1700.0	1.04	1.11	1.11
1800.0	3.47	3.39	0.04	22.82	0.13	1800.0	1.07	1.10	1.10
1900.0	3.48	3.39	0.05	22.50	0.17	1900.0	1.07	1.10	1.11
2000.0	3.49	3.40	0.05	22.64	0.17	2000.0	1.07	1.12	1.13
2100.0	3.50	3.42	0.06	23.14	0.06	2100.0	1.08	1.14	1.16
2200.0	3.53	3.43	0.06	24.08	0.00	2200.0	1.12	1.18	1.20
2300.0	3.55	3.46	0.05	25.54	0.03	2300.0	1.18	1.22	1.25
2400.0	3.59	3.51	0.04	27.62	0.10	2400.0	1.25	1.26	1.28
2500.0	3.61	3.55	0.02	30.61	0.19	2500.0	1.29	1.29	1.30
2600.0	3.63	3.58	0.01	35.70	0.16	2600.0	1.30	1.30	1.31
2700.0	3.64	3.60	0.01	50.46	0.16	2700.0	1.28	1.29	1.29
2800.0	3.64	3.61	0.02	39.67	0.11	2800.0	1.23	1.26	1.26
2900.0	3.62	3.60	0.03	33.08	0.07	2900.0	1.16	1.22	1.22
3000.0	3.60	3.58	0.03	29.81	0.02	3000.0	1.10	1.17	1.18
3100.0	3.61	3.58	0.03	27.88	0.11	3100.0	1.08	1.14	1.15
3200.0	3.62	3.58	0.02	26.64	0.15	3200.0	1.11	1.11	1.13
3300.0	3.63	3.58	0.01	26.02	0.19	3300.0	1.14	1.08	1.11
3400.0	3.63	3.57	0.00	25.91	0.19	3400.0	1.15	1.06	1.08
3500.0	3.63	3.57	0.01	26.33	0.19	3500.0	1.12	1.02	1.04
3600.0	3.64	3.58	0.01	27.20	0.14	3600.0	1.07	1.04	1.03
3700.0	3.65	3.60	0.00	28.47	0.13	3700.0	1.06	1.10	1.09
3800.0	3.67	3.63	0.02	30.19	0.09	3800.0	1.12	1.17	1.16
3900.0	3.70	3.68	0.04	32.54	0.08	3900.0	1.20	1.23	1.23
4000.0	3.74	3.73	0.07	33.68	0.08	4000.0	1.26	1.28	1.27
4100.0	3.76	3.78	0.09	32.40	0.13	4100.0	1.29	1.30	1.30
4200.0	3.77	3.81	0.11	29.68	0.15	4200.0	1.29	1.28	1.29
4300.0	3.76	3.81	0.13	27.47	0.18	4300.0	1.25	1.25	1.27
4400.0	3.74	3.80	0.13	25.66	0.22	4400.0	1.18	1.20	1.22
4500.0	3.73	3.79	0.13	24.24	0.32	4500.0	1.12	1.15	1.17
4600.0	3.73	3.79	0.12	23.23	0.33	4600.0	1.08	1.11	1.14
4700.0	3.75	3.80	0.12	22.66	0.32	4700.0	1.11	1.11	1.13
4800.0	3.78	3.81	0.11	22.51	0.24	4800.0	1.16	1.12	1.16
4900.0	3.82	3.84	0.09	22.62	0.19	4900.0	1.21	1.14	1.19
5000.0	3.86	3.88	0.10	22.98	0.08	5000.0	1.24	1.18	1.23
5100.0	3.90	3.91	0.09	23.58	0.07	5100.0	1.25	1.24	1.28
5200.0	3.94	3.95	0.09	24.59	0.20	5200.0	1.26	1.31	1.35
5300.0	3.96	3.98	0.10	25.68	0.32	5300.0	1.27	1.40	1.44
5400.0	3.98	4.02	0.12	26.37	0.43	5400.0	1.30	1.49	1.53
5500.0	4.02	4.07	0.14	25.99	0.55	5500.0	1.34	1.57	1.62
5600.0	4.05	4.12	0.17	24.69	0.71	5600.0	1.36	1.63	1.70
5700.0	4.07	4.17	0.20	22.74	0.82	5700.0	1.37	1.68	1.76
5800.0	4.08	4.17	0.21	20.62	0.90	5800.0	1.33	1.69	1.77
5900.0	4.07	4.15	0.23	18.69	0.98	5900.0	1.28	1.69	1.75
6000.0	4.05	4.11	0.22	16.99	1.04	6000.0	1.21	1.66	1.71
6100.0	4.08	4.08	0.18	15.57	0.97	6100.0	1.21	1.65	1.66
6200.0	4.13	4.07	0.14	14.28	0.72	6200.0	1.31	1.64	1.62
6300.0	4.22	4.11	0.10	13.21	0.30	6300.0	1.49	1.66	1.60
6400.0	4.33	4.20	0.06	12.30	0.21	6400.0	1.69	1.70	1.60

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. X2 ZAPD-ED12592C/1






9/15/2010

Page 1 of 1

2 Way-0° Power Splitter/Combiner

ZAPD-ED12592C/1

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

minicircuits.com


P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. X2
ZAPD-ED12592C/1
9/15/2010
Page 1 of 1

Outline Dimensions

F53



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
F53	2.00 (50.80)	2.00 (50.80)	.75 (19.05)	1.00 (25.40)	.13 (3.30)	1.750 (44.45)	.125 (3.18)	.39 (9.91)	1.00 (25.40)	.50 (12.70)	1.00 (25.40)	170.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I