

# Power Splitter/Combiner

## ZB4PD1-2000+

4 Way-0° 50Ω 800 to 2000 MHz


### Maximum Ratings

|                                                                 |                             |
|-----------------------------------------------------------------|-----------------------------|
| Operating Temperature                                           | -55°C to 100°C              |
| Storage Temperature                                             | -55°C to 100°C              |
| Power Input (as a splitter)                                     | 10W max.                    |
| Internal Dissipation                                            | 0.375W max.                 |
| DC Current                                                      | 1.2 A (300mA for each port) |
| Permanent damage may occur if any of these limits are exceeded. |                             |

### Coaxial Connections

|          |   |
|----------|---|
| SUM PORT | S |
| PORT 1   | 1 |
| PORT 2   | 2 |
| PORT 3   | 3 |
| PORT 4   | 4 |

### Outline Drawing



### Outline Dimensions (inch/mm)

|       |       |       |       |       |       |
|-------|-------|-------|-------|-------|-------|
| A     | B     | C     | D     | E     | F     |
| 3.50  | 2.13  | .88   | .150  | 3.350 | 1.06  |
| 88.90 | 54.10 | 22.35 | 3.81  | 85.09 | 26.92 |
| G     | H     | J     | K     |       | wt    |
| .125  | 1.75  | .44   | .89   |       | grams |
| 3.18  | 44.45 | 11.18 | 22.61 |       | 260   |

### Features

- wideband, 800 to 2000 MHz
- good isolation, 25 dB typ.
- excellent output VSWR, 1.1:1 typ.
- up to 10W power input as splitters

### Applications

- cellular
- satellite distribution
- GPS



SMA version shown  
CASE STYLE: UU188

| Connectors | Model          |
|------------|----------------|
| BNC        | ZB4PD1-2000+   |
| SMA        | ZB4PD1-2000-S+ |
| N-TYPE     | ZB4PD1-2000-N+ |

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




### Electrical Specifications

| FREQ. RANGE (MHz) | ISOLATION (dB) |      | INSERTION LOSS (dB) ABOVE 6.0 dB |      | AMPLITUDE UNBALANCE (dB) | PHASE UNBALANCE (deg.) | VSWR (:1) |      |      |      |
|-------------------|----------------|------|----------------------------------|------|--------------------------|------------------------|-----------|------|------|------|
|                   | Typ.           | Min. | Typ.                             | Max. |                          |                        | S         |      | OUT  |      |
| $f_L - f_U$       |                |      |                                  |      | Max.                     | Max.                   | Typ.      | Max. | Typ. | Max. |
| 800-2000          | 25             | 18   | 0.6                              | 1.2  | 0.3                      | 5                      | 1.20      | 1.60 | 1.15 | 1.55 |


### Typical Performance Data

| Freq. (MHz) | Total Loss <sup>1</sup> (dB) |      |      |      | Amp. Unbal. (dB) | Isolation (dB) |       |       | Phase Unbal. (deg.) | VSWR S | VSWR 1 | VSWR 2 | VSWR 3 | VSWR 4 |
|-------------|------------------------------|------|------|------|------------------|----------------|-------|-------|---------------------|--------|--------|--------|--------|--------|
|             | S-1                          | S-2  | S-3  | S-4  |                  | 1-2            | 2-3   | 3-4   |                     |        |        |        |        |        |
| 800.00      | 6.36                         | 6.41 | 6.41 | 6.38 | 0.06             | 32.90          | 26.70 | 32.77 | 0.48                | 1.10   | 1.09   | 1.09   | 1.09   | 1.09   |
| 850.00      | 6.36                         | 6.42 | 6.42 | 6.39 | 0.06             | 32.05          | 28.92 | 32.02 | 0.58                | 1.08   | 1.09   | 1.08   | 1.08   | 1.09   |
| 900.00      | 6.38                         | 6.43 | 6.44 | 6.40 | 0.06             | 29.39          | 31.73 | 29.33 | 0.59                | 1.07   | 1.09   | 1.08   | 1.08   | 1.08   |
| 950.00      | 6.40                         | 6.45 | 6.46 | 6.42 | 0.06             | 27.19          | 35.63 | 27.21 | 0.62                | 1.09   | 1.09   | 1.07   | 1.08   | 1.08   |
| 1000.00     | 6.41                         | 6.48 | 6.47 | 6.43 | 0.07             | 25.70          | 41.89 | 25.69 | 0.68                | 1.12   | 1.09   | 1.06   | 1.07   | 1.07   |
| 1150.00     | 6.49                         | 6.55 | 6.55 | 6.50 | 0.07             | 24.04          | 37.23 | 24.15 | 0.73                | 1.18   | 1.09   | 1.05   | 1.06   | 1.06   |
| 1200.00     | 6.49                         | 6.57 | 6.56 | 6.50 | 0.08             | 24.24          | 34.33 | 24.33 | 0.72                | 1.16   | 1.10   | 1.06   | 1.06   | 1.06   |
| 1300.00     | 6.49                         | 6.57 | 6.57 | 6.50 | 0.08             | 24.95          | 31.35 | 25.08 | 0.77                | 1.08   | 1.11   | 1.07   | 1.07   | 1.08   |
| 1400.00     | 6.51                         | 6.60 | 6.59 | 6.51 | 0.09             | 25.51          | 30.29 | 25.61 | 0.75                | 1.06   | 1.12   | 1.08   | 1.09   | 1.10   |
| 1500.00     | 6.56                         | 6.65 | 6.65 | 6.56 | 0.09             | 25.67          | 30.43 | 25.74 | 0.83                | 1.14   | 1.11   | 1.09   | 1.09   | 1.11   |
| 1600.00     | 6.62                         | 6.70 | 6.70 | 6.61 | 0.10             | 25.54          | 32.04 | 25.62 | 0.87                | 1.17   | 1.09   | 1.07   | 1.08   | 1.10   |
| 1700.00     | 6.63                         | 6.72 | 6.72 | 6.62 | 0.10             | 24.93          | 35.72 | 25.07 | 0.95                | 1.15   | 1.06   | 1.04   | 1.05   | 1.07   |
| 1800.00     | 6.67                         | 6.76 | 6.75 | 6.64 | 0.12             | 24.33          | 45.72 | 24.51 | 0.89                | 1.16   | 1.07   | 1.04   | 1.05   | 1.06   |
| 1900.00     | 6.72                         | 6.81 | 6.80 | 6.68 | 0.13             | 25.35          | 38.36 | 25.59 | 0.91                | 1.19   | 1.08   | 1.05   | 1.05   | 1.06   |
| 2000.00     | 6.76                         | 6.85 | 6.84 | 6.72 | 0.13             | 31.41          | 30.77 | 31.99 | 0.90                | 1.14   | 1.06   | 1.02   | 1.03   | 1.03   |

1. Total Loss = Insertion Loss + 6dB splitter loss.



### electrical schematic



### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



# 4 Way-0° Power Splitter/Combiner

ZB4PD1-2000+

## Typical Performance Data

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      |      |      | AMP.<br>UNBAL.<br>(dB) | ISOLATION<br>(dB) |       |       | PHASE<br>UNBAL.<br>(deg.) | FREQ.<br>(MHz) | VSWR<br>(:1) |      |      |      |      |
|----------------|---------------------------------|------|------|------|------------------------|-------------------|-------|-------|---------------------------|----------------|--------------|------|------|------|------|
|                | S-1                             | S-2  | S-3  | S-4  |                        | 1-2               | 2-3   | 3-4   |                           |                | S            | 1    | 2    | 3    | 4    |
| 800.0          | 6.36                            | 6.41 | 6.41 | 6.38 | 0.06                   | 32.90             | 26.70 | 32.77 | 0.48                      | 800.0          | 1.10         | 1.09 | 1.09 | 1.09 | 1.09 |
| 850.0          | 6.36                            | 6.42 | 6.42 | 6.39 | 0.06                   | 32.05             | 28.92 | 32.02 | 0.58                      | 850.0          | 1.08         | 1.09 | 1.08 | 1.08 | 1.09 |
| 900.0          | 6.38                            | 6.43 | 6.44 | 6.40 | 0.06                   | 29.39             | 31.73 | 29.33 | 0.59                      | 900.0          | 1.07         | 1.09 | 1.08 | 1.08 | 1.08 |
| 950.0          | 6.40                            | 6.45 | 6.46 | 6.42 | 0.06                   | 27.19             | 35.63 | 27.21 | 0.62                      | 950.0          | 1.09         | 1.09 | 1.07 | 1.08 | 1.08 |
| 1000.0         | 6.41                            | 6.48 | 6.47 | 6.43 | 0.07                   | 25.70             | 41.89 | 25.69 | 0.68                      | 1000.0         | 1.12         | 1.09 | 1.06 | 1.07 | 1.07 |
| 1100.0         | 6.47                            | 6.53 | 6.53 | 6.48 | 0.07                   | 24.21             | 42.40 | 24.26 | 0.74                      | 1100.0         | 1.18         | 1.09 | 1.06 | 1.06 | 1.06 |
| 1150.0         | 6.49                            | 6.55 | 6.55 | 6.50 | 0.07                   | 24.04             | 37.23 | 24.15 | 0.73                      | 1150.0         | 1.18         | 1.09 | 1.05 | 1.06 | 1.06 |
| 1200.0         | 6.49                            | 6.57 | 6.56 | 6.50 | 0.08                   | 24.24             | 34.33 | 24.33 | 0.72                      | 1200.0         | 1.16         | 1.10 | 1.06 | 1.06 | 1.06 |
| 1250.0         | 6.49                            | 6.57 | 6.56 | 6.49 | 0.08                   | 24.54             | 32.48 | 24.69 | 0.81                      | 1250.0         | 1.13         | 1.10 | 1.06 | 1.06 | 1.07 |
| 1300.0         | 6.49                            | 6.57 | 6.57 | 6.50 | 0.08                   | 24.95             | 31.35 | 25.08 | 0.77                      | 1300.0         | 1.08         | 1.11 | 1.07 | 1.07 | 1.08 |
| 1350.0         | 6.51                            | 6.57 | 6.58 | 6.50 | 0.08                   | 25.31             | 30.55 | 25.50 | 0.75                      | 1350.0         | 1.04         | 1.11 | 1.08 | 1.08 | 1.09 |
| 1400.0         | 6.51                            | 6.60 | 6.59 | 6.51 | 0.09                   | 25.51             | 30.29 | 25.61 | 0.75                      | 1400.0         | 1.06         | 1.12 | 1.08 | 1.09 | 1.10 |
| 1450.0         | 6.54                            | 6.62 | 6.62 | 6.53 | 0.09                   | 25.60             | 30.20 | 25.74 | 0.78                      | 1450.0         | 1.11         | 1.12 | 1.10 | 1.09 | 1.11 |
| 1500.0         | 6.56                            | 6.65 | 6.65 | 6.56 | 0.09                   | 25.67             | 30.43 | 25.74 | 0.83                      | 1500.0         | 1.14         | 1.11 | 1.09 | 1.09 | 1.11 |
| 1550.0         | 6.59                            | 6.68 | 6.69 | 6.59 | 0.09                   | 25.59             | 31.11 | 25.72 | 0.81                      | 1550.0         | 1.17         | 1.10 | 1.09 | 1.09 | 1.11 |
| 1600.0         | 6.62                            | 6.70 | 6.70 | 6.61 | 0.10                   | 25.54             | 32.04 | 25.62 | 0.87                      | 1600.0         | 1.17         | 1.09 | 1.07 | 1.08 | 1.10 |
| 1650.0         | 6.63                            | 6.72 | 6.72 | 6.62 | 0.10                   | 25.27             | 33.56 | 25.41 | 0.88                      | 1650.0         | 1.16         | 1.07 | 1.06 | 1.07 | 1.08 |
| 1700.0         | 6.63                            | 6.72 | 6.72 | 6.62 | 0.10                   | 24.93             | 35.72 | 25.07 | 0.95                      | 1700.0         | 1.15         | 1.06 | 1.04 | 1.05 | 1.07 |
| 1750.0         | 6.65                            | 6.74 | 6.73 | 6.63 | 0.11                   | 24.57             | 39.18 | 24.75 | 0.89                      | 1750.0         | 1.15         | 1.06 | 1.04 | 1.05 | 1.06 |
| 1800.0         | 6.67                            | 6.76 | 6.75 | 6.64 | 0.12                   | 24.33             | 45.72 | 24.51 | 0.89                      | 1800.0         | 1.16         | 1.07 | 1.04 | 1.05 | 1.06 |
| 1850.0         | 6.70                            | 6.79 | 6.77 | 6.66 | 0.13                   | 24.50             | 45.76 | 24.69 | 0.90                      | 1850.0         | 1.18         | 1.09 | 1.05 | 1.05 | 1.06 |
| 1900.0         | 6.72                            | 6.81 | 6.80 | 6.68 | 0.13                   | 25.35             | 38.36 | 25.59 | 0.91                      | 1900.0         | 1.19         | 1.08 | 1.05 | 1.05 | 1.06 |
| 1950.0         | 6.73                            | 6.82 | 6.81 | 6.69 | 0.13                   | 27.24             | 33.94 | 27.51 | 0.82                      | 1950.0         | 1.16         | 1.07 | 1.04 | 1.03 | 1.05 |
| 2000.0         | 6.76                            | 6.85 | 6.84 | 6.72 | 0.13                   | 31.41             | 30.77 | 31.99 | 0.90                      | 2000.0         | 1.14         | 1.06 | 1.02 | 1.03 | 1.03 |

<sup>1</sup>Total Loss = Insertion Loss + 6dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)








IF/RF MICROWAVE COMPONENTS

REV. X3  
ZB4PD1-2000+  
6/29/2010  
Page 1 of 1

# 4 Way-0° Power Splitter/Combiner


ZB4PD1-2000+

## Typical Performance Curves



## Outline Dimensions

UU188



| CASE# | A               | B               | C              | D              | E                | F               | G              | H               | J              | K              | WT. GRAMS |
|-------|-----------------|-----------------|----------------|----------------|------------------|-----------------|----------------|-----------------|----------------|----------------|-----------|
| UU188 | 3.50<br>(88.90) | 2.13<br>(54.10) | .88<br>(22.35) | .150<br>(3.81) | 3.350<br>(85.09) | 1.06<br>(26.92) | .125<br>(3.18) | 1.75<br>(44.45) | .44<br>(11.18) | .89<br>(22.61) | 260       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

- Case material: Aluminum alloy.
- Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS

UU188 Rev.: AZ (02/25/19) M172688 File: UU188

This document and its contents are the property of Mini-Circuits



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                              | Reference/Spec                       |
|----------------------------|----------------------------------------------------------------------------------------|--------------------------------------|
| Operating Temperature      | -55° to 100°C<br>Ambient Environment                                                   | Individual Model Data Sheet          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                                  | Individual Model Data Sheet          |
| Barometric Pressure        | 100,000 Feet                                                                           | MIL-STD-202, Method 105, Condition D |
| Humidity                   | 90% RH, 65°C<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103              |
| Thermal Shock              | -65° to 125°C, 5 cycles                                                                | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)    | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock           | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)                          | MIL-STD-202, Method 213, Condition I |