

Engineering Development Model

Power Splitter/Combiner with amplifier

2 Way-0°

ZAPD-ED14824/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



CASE STYLE : 99-01-1730

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C

Parameters		Min.	Typ.	Max.	Units
Frequency		400		2300	MHz
Isolation	400-2300 MHz		22		dB
Insertion Loss Above 3dB	400-2300 MHz		0.5		dB
Phase Unbalance	400-2300 MHz		1.0		deg.
Amplitude Unbalance	400-2300 MHz		0.1		dB
VSWR	SUM Port		1.25		(:1)
	OUT Ports		1.25		(:1)

MAXIMUM RATINGS

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS

SUM PORT	S
PORT 1	1
PORT 2	2

Functional Diagram



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site www.minicircuits.com



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X1
ZAPD-ED14824/1
3/29/2012
Page 1 of 1

2 Way-0° Power Splitter/Combiner

ZAPD-ED14824/1

Typical Performance Data

FREQUENCY (MHz)	TOTAL LOSS ¹ (dB)		AMPLITUDE UNBALANCE (dB)	ISOLATION (dB)	PHASE UNBALANCE (deg.)	FREQUENCY (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
300.0	3.42	3.42	0.00	13.56	0.03	300.0	1.66	1.42	1.42
400.0	3.31	3.31	0.00	16.83	0.06	400.0	1.48	1.29	1.29
450.0	3.26	3.26	0.00	18.72	0.07	450.0	1.38	1.22	1.22
500.0	3.22	3.22	0.00	20.96	0.07	500.0	1.29	1.15	1.15
550.0	3.19	3.19	0.00	23.84	0.08	550.0	1.20	1.09	1.09
600.0	3.18	3.18	0.00	27.85	0.09	600.0	1.13	1.03	1.03
650.0	3.18	3.18	0.00	34.07	0.10	650.0	1.07	1.04	1.04
700.0	3.19	3.19	0.00	37.85	0.11	700.0	1.07	1.09	1.09
750.0	3.20	3.21	0.00	31.74	0.12	750.0	1.11	1.14	1.14
800.0	3.23	3.23	0.00	27.99	0.13	800.0	1.16	1.19	1.18
900.0	3.26	3.27	0.00	24.59	0.14	900.0	1.23	1.24	1.24
1000.0	3.28	3.29	0.01	23.87	0.15	1000.0	1.26	1.25	1.25
1100.0	3.27	3.28	0.01	25.16	0.17	1100.0	1.23	1.21	1.22
1200.0	3.26	3.27	0.01	29.18	0.21	1200.0	1.18	1.13	1.14
1300.0	3.26	3.27	0.01	40.04	0.26	1300.0	1.10	1.05	1.06
1350.0	3.26	3.27	0.01	37.07	0.29	1350.0	1.06	1.02	1.02
1400.0	3.27	3.28	0.01	31.13	0.31	1400.0	1.03	1.05	1.02
1500.0	3.30	3.30	0.00	25.44	0.36	1500.0	1.07	1.12	1.10
1600.0	3.33	3.33	0.00	23.20	0.37	1600.0	1.13	1.18	1.15
1700.0	3.35	3.35	0.01	23.02	0.36	1700.0	1.18	1.21	1.18
1800.0	3.37	3.36	0.01	24.88	0.36	1800.0	1.20	1.20	1.18
1900.0	3.37	3.36	0.01	30.31	0.35	1900.0	1.20	1.17	1.16
2000.0	3.37	3.37	0.00	38.41	0.37	2000.0	1.15	1.12	1.12
2025.0	3.37	3.37	0.00	33.82	0.37	2025.0	1.13	1.11	1.11
2050.0	3.38	3.38	0.00	30.39	0.38	2050.0	1.11	1.10	1.10
2075.0	3.38	3.38	0.00	27.82	0.38	2075.0	1.08	1.09	1.09
2100.0	3.39	3.39	0.00	25.76	0.40	2100.0	1.05	1.09	1.09
2120.0	3.39	3.40	0.00	24.39	0.41	2120.0	1.03	1.08	1.08
2140.0	3.40	3.40	0.00	23.20	0.41	2140.0	1.01	1.08	1.08
2160.0	3.41	3.41	0.00	22.14	0.43	2160.0	1.03	1.07	1.07
2180.0	3.42	3.42	0.00	21.20	0.44	2180.0	1.05	1.07	1.07
2200.0	3.50	3.46	0.05	23.34	0.66	2200.0	1.08	1.07	1.06
2220.0	3.53	3.49	0.03	23.10	0.26	2220.0	1.12	1.06	1.06
2240.0	3.57	3.59	0.02	21.31	0.34	2240.0	1.16	1.06	1.06
2260.0	3.63	3.64	0.01	19.89	0.72	2260.0	1.20	1.06	1.06
2280.0	3.67	3.62	0.05	19.90	0.59	2280.0	1.24	1.07	1.06
2300.0	3.65	3.64	0.02	18.61	0.18	2300.0	1.29	1.07	1.06

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS






REV. X1

ZAPD-ED14824/1

3/29/2012

Page 1 of 1

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I