NON-CATALOG

DC Pass

Power Splitter/Combiner

ZB4PD1-8.4+

4 Way-0° 50Ω 6700 to 8400 MHz

SMA version shown

CASE STYLE: UU188

Connectors	Model
SMA	ZB4PD1-8.4-S+
N-TYPE	ZB4PD1-8.4-N+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.375W max.
DC Current	1.6A (400mA for each port)

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

Features

- wideband, 6700 to 8400 MHz
- high isolation, 29 dB typ.
- excellent VSWR
- up to 10W power input as a splitter

Applications

- CATV
- defense communications

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F
3.50	2.13	.88	.150	3.350	1.06
88.90	54.10	22.35	3.81	85.09	26.92

G	H	J	K		wt
.125	1.75	.44	.89		grams
3.18	44.45	11.18	22.61		260

Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 6.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
							S		OUT	
f_L-f_U	Typ.	Min.	Typ.	Max.	Max.	Max.	Typ.	Max.	Typ.	Max.
6700-8400	29	18	0.5	1.3	9	0.9	1.12	1.6	1.27	1.6

Typical Performance Data

Freq. (MHz)	Total Loss[1] (dB)				Amp. Unbal. (dB)	Isolation (dB)			VSWR S	VSWR 1	VSWR 2	VSWR 3	VSWR 4
	S-1	S-2	S-3	S-4		1-2	2-3	3-4					
6675.00	6.67	6.52	6.71	6.68	0.19	26.52	30.49	27.41	1.37	1.35	1.42	1.52	1.37
6750.00	6.70	6.55	6.70	6.67	0.15	28.49	30.14	29.46	1.37	1.37	1.44	1.52	1.39
6825.00	6.75	6.58	6.70	6.67	0.17	30.31	30.23	31.52	1.38	1.38	1.44	1.52	1.41
6975.00	6.78	6.65	6.74	6.67	0.13	33.63	30.34	34.43	1.37	1.38	1.42	1.50	1.42
7125.00	6.66	6.59	6.63	6.52	0.13	32.58	30.92	32.21	1.33	1.33	1.38	1.45	1.38
7275.00	6.52	6.50	6.52	6.35	0.17	30.18	31.21	30.37	1.26	1.27	1.33	1.38	1.33
7425.00	6.46	6.58	6.57	6.31	0.27	27.72	30.64	29.07	1.14	1.21	1.27	1.31	1.27
7575.00	6.52	6.54	6.51	6.36	0.18	26.56	30.19	26.94	1.09	1.17	1.21	1.24	1.22
7725.00	6.53	6.45	6.38	6.38	0.15	26.08	29.79	26.01	1.14	1.13	1.17	1.18	1.17
7875.00	6.57	6.43	6.36	6.40	0.21	25.49	29.40	24.82	1.17	1.09	1.12	1.13	1.14
8025.00	6.59	6.46	6.37	6.44	0.22	25.20	32.73	24.91	1.17	1.08	1.08	1.09	1.13
8175.00	6.67	6.50	6.43	6.49	0.24	27.63	31.20	26.73	1.17	1.12	1.10	1.11	1.15
8250.00	6.71	6.52	6.46	6.52	0.25	28.99	30.46	28.38	1.16	1.14	1.12	1.12	1.16
8325.00	6.71	6.51	6.46	6.52	0.25	30.14	29.71	29.49	1.16	1.16	1.12	1.12	1.17
8400.00	6.72	6.52	6.46	6.53	0.26	29.80	28.69	29.54	1.15	1.16	1.12	1.11	1.17

1. Total Loss = Insertion Loss + 6dB splitter loss.

ZB4PD1-8.4-S+
TOTAL LOSS



ZB4PD1-8.4-S+
ISOLATION



ZB4PD1-8.4-S+
VSWR



electrical schematic



Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

4 Way-0° Power Splitter/Combiner ZB4PD1-8.4+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS[1] (dB)				AMP. UNBAL. (dB)	ISOLATION (dB)		
	S-1	S-2	S-3	S-4		1-2	2-3	3-4
6675.0	6.67	6.52	6.71	6.68	0.19	26.52	30.49	27.41
6750.0	6.70	6.55	6.70	6.67	0.15	28.49	30.14	29.46
6825.0	6.75	6.58	6.70	6.67	0.17	30.31	30.23	31.52
6975.0	6.78	6.65	6.74	6.67	0.13	33.63	30.34	34.43
7125.0	6.66	6.59	6.63	6.52	0.13	32.58	30.92	32.21
7275.0	6.52	6.50	6.52	6.35	0.17	30.18	31.21	30.37
7425.0	6.46	6.58	6.57	6.31	0.27	27.72	30.64	29.07
7575.0	6.52	6.54	6.51	6.36	0.18	26.56	30.19	26.94
7725.0	6.53	6.45	6.38	6.38	0.15	26.08	29.79	26.01
7875.0	6.57	6.43	6.36	6.40	0.21	25.49	29.40	24.82
8025.0	6.59	6.46	6.37	6.44	0.22	25.20	32.73	24.91
8175.0	6.67	6.50	6.43	6.49	0.24	27.63	31.20	26.73
8250.0	6.71	6.52	6.46	6.52	0.25	28.99	30.46	28.38
8325.0	6.71	6.51	6.46	6.52	0.25	30.14	29.71	29.49
8400.0	6.72	6.52	6.46	6.53	0.26	29.80	28.69	29.54

FREQ. (MHz)	VSWR (:1)				
	S	1	2	3	4
6675.0	1.37	1.35	1.42	1.52	1.37
6750.0	1.37	1.37	1.44	1.52	1.39
6825.0	1.38	1.38	1.44	1.52	1.41
6975.0	1.37	1.38	1.42	1.50	1.42
7125.0	1.33	1.33	1.38	1.45	1.38
7275.0	1.26	1.27	1.33	1.38	1.33
7425.0	1.14	1.21	1.27	1.31	1.27
7575.0	1.09	1.17	1.21	1.24	1.22
7725.0	1.14	1.13	1.17	1.18	1.17
7875.0	1.17	1.09	1.12	1.13	1.14
8025.0	1.17	1.08	1.08	1.09	1.13
8175.0	1.17	1.12	1.10	1.11	1.15
8250.0	1.16	1.14	1.12	1.12	1.16
8325.0	1.16	1.16	1.12	1.12	1.17
8400.0	1.15	1.16	1.12	1.11	1.17

[1] Total Loss = Insertion Loss + 6dB Splitter Loss

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

4 Way-0° Power Splitter/Combiner ZB4PD1-8.4+

Typical Performance Curves

Total Loss



Isolation



Amplitude Unbalance



VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Case Style UU

Outline Dimensions UU188



CASE#	A	B	C	D	E	F	G	H	J	K	WT. GRAMS
UU188	3.50 (88.90)	2.13 (54.10)	.88 (22.35)	.150 (3.81)	3.350 (85.09)	1.06 (26.92)	.125 (3.18)	1.75 (44.45)	.44 (11.18)	.89 (22.61)	260

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .03; 3 Pl. ± .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
   For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications ENV28

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.