

Power Splitter/Combiner

8 Way-0° 50Ω 7200 to 8400 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.875W max.
DC Current	1.2A(150mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1,2,3,4,5,6,7,8	1,2,3,4,5,6,7,8

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
7.06	3.13	.88	.250	1.750	5.310	6.810	.250
179.32	79.50	22.35	6.35	44.45	134.87	172.97	6.35

J	K	L	M	N	P	wt
2.875	.144	3.53	.44	.415	.89	grams
73.03	3.66	89.66	11.18	10.54	22.61	800

Features

- wideband, 7200 to 8400 MHz
- low insertion loss 0.9 dB typ.
- good isolation, 25 dB typ.
- up to 10 power input
- rugged shielded case

Applications

- SHF
- defense communication
- cable TV relay
- instrumentation




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 9.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)
$f_c - f_u$	Typ.	Min.	Typ.	Max.	Max.	Max.
7200-8400	25	20	0.9	1.6	15	0.8


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)						Amplitude Unbalance (dB)	Isolation (dB)				VSWR S	VSWR 1	VSWR 8
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-7	3-4	5-7			
7200.00	9.99	9.86	9.89	9.97	9.90	9.96	0.13	27.56	35.97	25.40	36.63	1.32	1.27	1.24
7275.00	10.09	9.98	10.01	10.05	10.01	10.08	0.11	28.39	36.47	25.75	34.71	1.36	1.26	1.23
7350.00	10.09	9.98	10.03	10.02	10.05	10.09	0.12	29.42	37.25	26.64	32.95	1.36	1.25	1.22
7425.00	10.14	10.04	10.09	10.09	10.14	10.19	0.15	30.53	37.66	27.75	31.69	1.33	1.23	1.20
7500.00	9.90	9.80	9.84	9.84	9.91	9.96	0.15	31.30	37.87	28.82	30.49	1.29	1.21	1.18
7575.00	9.90	9.80	9.82	9.82	9.88	9.94	0.14	30.74	39.13	29.46	30.06	1.26	1.19	1.15
7650.00	9.82	9.72	9.74	9.72	9.77	9.86	0.14	29.68	39.20	28.73	29.43	1.24	1.17	1.14
7725.00	9.83	9.73	9.74	9.75	9.74	9.84	0.11	27.93	40.74	27.66	29.46	1.22	1.15	1.10
7800.00	9.91	9.81	9.81	9.81	9.80	9.92	0.14	26.71	41.79	26.33	29.64	1.21	1.13	1.09
7875.00	10.04	9.92	9.91	9.92	9.90	10.03	0.16	25.94	41.90	25.43	29.70	1.21	1.11	1.08
7950.00	10.10	9.99	9.96	9.98	9.95	10.07	0.17	25.75	42.81	24.95	30.40	1.19	1.09	1.07
8025.00	10.12	10.02	9.96	10.00	9.98	10.10	0.17	25.81	43.25	25.16	30.74	1.17	1.07	1.05
8100.00	10.10	10.00	9.95	9.99	9.96	10.12	0.16	26.29	44.56	25.49	30.63	1.15	1.06	1.04
8175.00	10.12	10.01	9.98	10.01	9.96	10.21	0.25	27.52	45.80	26.55	30.81	1.12	1.07	1.03
8400.00	10.23	10.13	10.18	10.29	10.13	10.30	0.18	30.99	45.55	33.14	29.92	1.07	1.11	1.04

1. Total Loss = Insertion Loss + 9dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



ZB8PD-8.4



Generic photo used for illustration purposes only

SMA version shown
 CASE STYLE: Z41

Connectors	Model
SMA	ZB8PD-8.4-S
N-TYPE	ZB8PD-8.4-N

8 Way-0° Power Splitter/Combiner

ZB8PD-8.4

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)						AMP. UNBAL. (dB)	ISOLATION (dB)				FREQ. (MHz)	VSWR (:1)		
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-8	3-4	5-7		S	1	8
7200.0	9.99	9.86	9.89	9.97	9.90	9.96	0.13	27.56	35.97	25.40	36.63	7200.0	1.32	1.27	1.24
7275.0	10.09	9.98	10.01	10.05	10.01	10.08	0.11	28.39	36.47	25.75	34.71	7275.0	1.36	1.26	1.23
7350.0	10.09	9.98	10.03	10.02	10.05	10.09	0.12	29.42	37.25	26.64	32.95	7350.0	1.36	1.25	1.22
7425.0	10.14	10.04	10.09	10.09	10.14	10.19	0.15	30.53	37.66	27.75	31.69	7425.0	1.33	1.23	1.20
7500.0	9.90	9.80	9.84	9.84	9.91	9.96	0.15	31.30	37.87	28.82	30.49	7500.0	1.29	1.21	1.18
7575.0	9.90	9.80	9.82	9.82	9.88	9.94	0.14	30.74	39.13	29.46	30.06	7575.0	1.26	1.19	1.15
7650.0	9.82	9.72	9.74	9.72	9.77	9.86	0.14	29.68	39.20	28.73	29.43	7650.0	1.24	1.17	1.14
7725.0	9.83	9.73	9.74	9.75	9.74	9.84	0.11	27.93	40.74	27.66	29.46	7725.0	1.22	1.15	1.10
7800.0	9.91	9.81	9.81	9.81	9.80	9.92	0.14	26.71	41.79	26.33	29.64	7800.0	1.21	1.13	1.09
7875.0	10.04	9.92	9.91	9.92	9.90	10.03	0.16	25.94	41.90	25.43	29.70	7875.0	1.21	1.11	1.08
7950.0	10.10	9.99	9.96	9.98	9.95	10.07	0.17	25.75	42.81	24.95	30.40	7950.0	1.19	1.09	1.07
8025.0	10.12	10.02	9.96	10.00	9.98	10.10	0.17	25.81	43.25	25.16	30.74	8025.0	1.17	1.07	1.05
8100.0	10.10	10.00	9.95	9.99	9.96	10.12	0.16	26.29	44.56	25.49	30.63	8100.0	1.15	1.06	1.04
8175.0	10.12	10.01	9.98	10.01	9.96	10.21	0.25	27.52	45.80	26.55	30.81	8175.0	1.12	1.07	1.03
8400.0	10.23	10.13	10.18	10.29	10.13	10.30	0.18	30.99	45.55	33.14	29.92	8400.0	1.07	1.11	1.04





¹ Total Loss = Insertion Loss+ 9dB Splitter Loss

REV. X2
ZB8PD-8.4
100627
Page 1 of 1


8 Way-0° Power Splitter/Combiner

ZB8PD-8.4

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Z41	7.06 (179.32)	3.13 (79.50)	.88 (22.35)	.250 (6.35)	1.750 (44.45)	5.310 (134.87)	6.810 (172.97)	.250 (6.35)	2.875 (73.03)	.144 (3.66)	3.53 (89.66)	.44 (11.18)	.415 (10.54)

CASE#	P	WT.GRAMS
Z41	.89 (22.61)	800

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B