Engineering Development Model

Power Splitter/Combiner ZB2PD-ED10774/1

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-954

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		**Min.**	**Typ.**	**Max.**	**Units**
Frequency		0.2		600	MHz
Isolation	**0.2 - 2 MHz**		30		dB
	2 - 300 MHz		22		dB
	300 - 600 MHz		13		dB
Insertion Loss Above 3.0 dB	**0.2 - 2 MHz**		0.20		dB
	2 - 300 MHz		0.30		dB
	300 - 600 MHz		0.70		dB
Phase Unbalance	**0.2 - 2 MHz**		0.020		deg.
	2 - 300 MHz		0.033		deg.
	300 - 600 MHz		0.167		deg.
Amplitude Unbalance	**0.2 - 2 MHz**		0.002		dB
	2 - 300 MHz		0.005		dB
	300 - 600 MHz		0.044		dB
VSWR	**SUM Port**		1.40		(:1)
	OUT Ports		1.10		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	1
PORT 1	2
PORT 2	3

Functional Diagram

2 Way-0° Power Splitter/Combiner ZB2PD-ED10774/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS[1] (dB) S-1	TOTAL LOSS[1] (dB) S-2	AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1) S	VSWR (:1) 1	VSWR (:1) 2
0.2	3.21	3.21	0.00	20.33	0.01	0.2	1.29	1.55	1.55
0.3	3.20	3.20	0.00	23.50	0.02	0.3	1.19	1.34	1.34
0.4	3.20	3.20	0.00	25.58	0.03	0.4	1.15	1.25	1.25
0.5	3.20	3.20	0.00	27.03	0.01	0.5	1.12	1.20	1.20
0.6	3.20	3.20	0.00	28.05	0.01	0.6	1.11	1.17	1.17
0.7	3.20	3.20	0.00	28.80	0.00	0.7	1.10	1.15	1.15
0.8	3.20	3.20	0.00	29.36	0.03	0.8	1.09	1.14	1.14
0.9	3.20	3.20	0.00	29.82	0.03	0.9	1.09	1.13	1.13
1.0	3.20	3.20	0.00	30.19	0.01	1.0	1.08	1.12	1.12
2.0	3.18	3.18	0.00	32.38	0.03	2.0	1.07	1.08	1.08
3.0	3.16	3.16	0.00	33.55	0.02	3.0	1.06	1.07	1.07
5.0	3.15	3.15	0.00	34.55	0.04	5.0	1.05	1.05	1.05
7.0	3.15	3.14	0.01	34.81	0.01	7.0	1.05	1.05	1.05
9.0	3.15	3.15	0.00	34.79	0.01	9.0	1.05	1.04	1.04
10.0	3.15	3.15	0.00	34.73	0.02	10.0	1.05	1.04	1.04
12.0	3.15	3.15	0.00	34.55	0.01	12.0	1.05	1.04	1.04
14.0	3.15	3.16	0.01	34.33	0.01	14.0	1.05	1.04	1.04
16.0	3.15	3.16	0.00	34.08	0.02	16.0	1.05	1.04	1.04
18.0	3.16	3.16	0.00	33.80	0.00	18.0	1.05	1.04	1.04
20.0	3.16	3.16	0.00	33.60	0.01	20.0	1.05	1.04	1.04
48.0	3.20	3.20	0.00	30.01	0.04	48.0	1.08	1.04	1.04
76.0	3.23	3.22	0.01	27.33	0.06	76.0	1.11	1.05	1.05
104.0	3.26	3.26	0.00	25.25	0.09	104.0	1.14	1.05	1.05
132.0	3.30	3.29	0.00	23.57	0.10	132.0	1.18	1.06	1.06
160.0	3.33	3.33	0.00	22.18	0.11	160.0	1.21	1.06	1.07
188.0	3.36	3.36	0.00	21.00	0.15	188.0	1.25	1.07	1.07
216.0	3.40	3.39	0.00	19.98	0.15	216.0	1.29	1.08	1.08
244.0	3.44	3.43	0.01	19.09	0.14	244.0	1.32	1.09	1.09
272.0	3.47	3.47	0.00	18.29	0.17	272.0	1.36	1.10	1.10
300.0	3.52	3.52	0.00	17.58	0.20	300.0	1.40	1.10	1.11
336.0	3.58	3.58	0.00	16.77	0.19	336.0	1.45	1.12	1.12
372.0	3.62	3.62	0.00	16.05	0.25	372.0	1.50	1.13	1.13
408.0	3.69	3.70	0.00	15.42	0.26	408.0	1.55	1.14	1.14
444.0	3.74	3.74	0.00	14.83	0.29	444.0	1.59	1.16	1.16
480.0	3.81	3.82	0.00	14.33	0.29	480.0	1.64	1.17	1.17
500.0	3.86	3.86	0.00	14.07	0.32	500.0	1.67	1.18	1.18
520.0	3.88	3.88	0.00	13.81	0.30	520.0	1.70	1.19	1.19
540.0	3.91	3.91	0.00	13.56	0.35	540.0	1.73	1.20	1.20
560.0	3.96	3.96	0.00	13.35	0.33	560.0	1.75	1.21	1.21
580.0	4.01	4.01	0.00	13.14	0.36	580.0	1.78	1.22	1.22
600.0	4.04	4.04	0.00	12.92	0.35	600.0	1.81	1.23	1.23

[1] Total Loss = Insertion Loss + 3dB Splitter Loss

Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

2 Way-0° Power Splitter/Combiner ZB2PD-ED10774/1

Typical Performance Curves

Total Loss



Isolation



Amplitude Unbalance



Phase Unbalance



VSWR



Mini-Circuits®
IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see minicircuits.com

Mini-Circuits

Environmental Specifications **ENV28T5**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.