

Engineering Development Model


Power Splitter/Combiner

ZB2PD-ED12121/4

2 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : BV278

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		Min.	Typ.	Max.	Units
Frequency		1750		2300	MHz
Isolation	1750 - 2300 MHz		25		dB
Insertion Loss Above 3.0 dB	1750 - 2300 MHz		0.20		dB
Phase Unbalance	1750 - 2300 MHz		0.025		deg.
Amplitude Unbalance	1750 - 2300 MHz		0.012		dB
VSWR	SUM Port		1.10		(:1)
	OUT Ports		1.10		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 55°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	3
PORT 1	1
PORT 2	5

Functional Diagram



2 Way-0° Power Splitter/Combiner ZB2PD-ED12121/4

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB) 1-2	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
1600.0	3.30	3.31	0.01	10.21	0.02	1600.0	1.38	1.38	1.60
1620.0	3.27	3.28	0.01	10.74	0.00	1620.0	1.34	1.34	1.48
1640.0	3.25	3.26	0.01	11.35	0.02	1640.0	1.30	1.30	1.43
1660.0	3.23	3.24	0.01	12.03	0.02	1660.0	1.27	1.27	1.40
1680.0	3.21	3.22	0.01	12.79	0.02	1680.0	1.24	1.24	1.38
1700.0	3.20	3.21	0.01	13.64	0.02	1700.0	1.21	1.21	1.34
1720.0	3.19	3.20	0.01	14.59	0.02	1720.0	1.19	1.18	1.28
1740.0	3.18	3.19	0.01	15.66	0.03	1740.0	1.17	1.16	1.22
1750.0	3.17	3.19	0.01	16.23	0.04	1750.0	1.16	1.16	1.19
1760.0	3.17	3.18	0.01	16.83	0.02	1760.0	1.15	1.15	1.18
1780.0	3.16	3.18	0.01	18.16	0.03	1780.0	1.14	1.13	1.17
1800.0	3.17	3.18	0.01	19.65	0.02	1800.0	1.13	1.12	1.12
1820.0	3.16	3.17	0.01	21.35	0.03	1820.0	1.12	1.11	1.08
1840.0	3.16	3.17	0.01	23.31	0.02	1840.0	1.11	1.11	1.07
1860.0	3.16	3.18	0.01	25.63	0.03	1860.0	1.11	1.10	1.03
1880.0	3.17	3.18	0.01	28.46	0.02	1880.0	1.10	1.10	1.11
1900.0	3.17	3.18	0.01	32.12	0.03	1900.0	1.10	1.10	1.16
1920.0	3.16	3.18	0.01	37.35	0.03	1920.0	1.10	1.10	1.09
1940.0	3.17	3.19	0.01	44.95	0.02	1940.0	1.10	1.10	1.05
1960.0	3.18	3.19	0.01	41.82	0.04	1960.0	1.10	1.10	1.07
1980.0	3.17	3.19	0.01	36.84	0.02	1980.0	1.10	1.10	1.12
2000.0	3.18	3.19	0.01	34.05	0.03	2000.0	1.10	1.10	1.17
2020.0	3.18	3.19	0.01	32.35	0.03	2020.0	1.10	1.10	1.19
2040.0	3.18	3.19	0.01	31.28	0.03	2040.0	1.10	1.09	1.13
2060.0	3.17	3.18	0.01	30.61	0.02	2060.0	1.09	1.09	1.06
2070.0	3.17	3.19	0.01	30.37	0.03	2070.0	1.09	1.09	1.07
2080.0	3.18	3.19	0.01	30.16	0.02	2080.0	1.09	1.09	1.10
2090.0	3.18	3.20	0.01	29.96	0.02	2090.0	1.09	1.09	1.14
2100.0	3.19	3.20	0.01	29.76	0.03	2100.0	1.09	1.09	1.18
2110.0	3.18	3.20	0.01	29.53	0.02	2110.0	1.09	1.09	1.19
2120.0	3.18	3.20	0.01	29.25	0.02	2120.0	1.09	1.09	1.17
2140.0	3.18	3.19	0.01	28.50	0.02	2140.0	1.09	1.08	1.08
2160.0	3.19	3.20	0.01	27.41	0.01	2160.0	1.08	1.08	1.03
2180.0	3.19	3.21	0.02	26.04	0.02	2180.0	1.08	1.08	1.05
2200.0	3.20	3.21	0.01	24.53	0.02	2200.0	1.08	1.08	1.06
2220.0	3.20	3.21	0.02	22.96	0.03	2220.0	1.08	1.08	1.05
2240.0	3.21	3.23	0.02	21.42	0.03	2240.0	1.08	1.08	1.05
2260.0	3.23	3.24	0.02	19.97	0.03	2260.0	1.08	1.08	1.13
2270.0	3.23	3.25	0.02	19.28	0.03	2270.0	1.08	1.09	1.17
2280.0	3.24	3.25	0.02	18.62	0.03	2280.0	1.09	1.09	1.19
2290.0	3.24	3.26	0.02	17.98	0.03	2290.0	1.09	1.09	1.19
2300.0	3.25	3.27	0.02	17.37	0.04	2300.0	1.09	1.09	1.18
2310.0	3.26	3.28	0.02	16.79	0.03	2310.0	1.10	1.10	1.17
2320.0	3.27	3.29	0.02	16.23	0.03	2320.0	1.10	1.10	1.19
2330.0	3.29	3.30	0.02	15.71	0.04	2330.0	1.10	1.11	1.22
2340.0	3.30	3.32	0.02	15.21	0.03	2340.0	1.11	1.11	1.26
2350.0	3.31	3.33	0.02	14.73	0.04	2350.0	1.11	1.12	1.31
2360.0	3.32	3.34	0.02	14.29	0.04	2360.0	1.12	1.12	1.35
2370.0	3.32	3.34	0.02	13.86	0.04	2370.0	1.12	1.13	1.39
2380.0	3.34	3.36	0.02	13.47	0.05	2380.0	1.13	1.13	1.42
2390.0	3.35	3.37	0.02	13.09	0.06	2390.0	1.14	1.14	1.45
2400.0	3.36	3.38	0.02	12.75	0.04	2400.0	1.14	1.15	1.47






¹Total Loss = Insertion Loss + 3dB Splitter Loss



2 Way-0° Power Splitter/Combiner

ZB2PD-ED12121/4

Typical Performance Curves



REV. X2
ZB2PD-ED12121/4
100707
Page 1 of 1

Mini-Circuits®


IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0006 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, instantly • For detailed performance specs & shopping online see



Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K
BV278	6.00 (152.40)	4.50 (114.30)	1.38 (35.05)	.15 (3.81)	5.700 (144.78)	.15 (3.81)	4.200 (106.68)	.38 (9.65)	2.25 (57.15)	.75 (19.05)

CASE #	L	M	WT. GRAMS
BV278	.75 (19.05)	.156 (3.96)	960

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black Anodize.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B