Engineering Development Model

Power Splitter/Combiner ZB8PD1-ED13816

8 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : Z41

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C					
Parameter		**Min.**	**Typ.**	**Max.**	**Units**
Frequency		600		3580	MHz
Isolation	**600-3580 MHz**		31.00		dB
Insertion Loss Above 9.0 dB	**600-3580 MHz**		1.00		dB
Phase Unbalance	**600-3580 MHz**		2.25		deg.
Amplitude Unbalance	**600-3580 MHz**		0.15		dB
VSWR	**SUM Port**		1.30		(:1)
	OUT Ports		1.12		(:1)

MAXIMUM RATINGS	
Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8

Functional Diagram

8 Way-0° Power Splitter/Combiner ZB8PD1-ED13816

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS[1] (dB)						AMP. UNBAL. (dB)	ISOLATION (dB)				PHASE UNBAL. (deg.)
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-8	3-4	6-7	
600.0	9.45	9.42	9.37	9.41	9.38	9.43	0.09	18.36	28.86	18.28	24.90	0.67
650.0	9.55	9.51	9.45	9.50	9.47	9.52	0.10	21.42	30.59	21.39	25.75	0.76
700.0	9.65	9.61	9.55	9.60	9.58	9.61	0.10	23.88	32.66	24.06	27.25	0.81
750.0	9.66	9.62	9.57	9.60	9.58	9.61	0.08	25.67	35.13	26.13	29.53	0.90
840.0	9.53	9.50	9.45	9.47	9.46	9.48	0.08	29.93	40.62	31.18	36.95	1.05
870.0	9.50	9.47	9.44	9.44	9.44	9.45	0.08	32.09	42.37	33.89	40.78	1.09
900.0	9.51	9.48	9.44	9.45	9.45	9.46	0.08	34.58	43.36	37.22	44.39	1.08
950.0	9.56	9.52	9.50	9.50	9.50	9.50	0.08	40.04	42.20	43.05	44.55	1.08
1050.0	9.61	9.58	9.55	9.54	9.55	9.56	0.08	32.54	37.75	30.52	45.27	1.21
1150.0	9.61	9.57	9.57	9.54	9.56	9.56	0.07	23.75	35.19	23.01	37.88	1.18
1250.0	9.77	9.73	9.74	9.70	9.72	9.71	0.07	21.16	34.16	20.72	31.24	1.29
1350.0	9.73	9.68	9.66	9.66	9.66	9.64	0.08	21.52	34.01	21.30	28.78	1.32
1450.0	9.63	9.60	9.56	9.58	9.58	9.55	0.08	22.45	34.71	22.31	29.07	1.40
1550.0	9.72	9.68	9.65	9.67	9.67	9.64	0.08	23.71	36.54	23.67	30.70	1.50
1650.0	9.72	9.69	9.68	9.68	9.69	9.65	0.07	25.92	39.70	26.51	31.21	1.64
1750.0	9.75	9.71	9.72	9.71	9.73	9.68	0.07	26.85	45.93	27.93	31.88	1.68
1950.0	9.84	9.81	9.80	9.79	9.81	9.75	0.09	28.84	45.70	27.01	35.17	1.85
2050.0	10.01	10.00	10.00	10.01	10.01	9.91	0.12	25.49	41.12	24.10	30.61	2.18
2150.0	9.96	9.92	9.92	9.92	9.94	9.86	0.11	26.84	39.24	25.62	28.87	1.97
2250.0	9.86	9.81	9.82	9.81	9.82	9.76	0.11	29.08	38.41	25.80	28.95	1.91
2350.0	9.94	9.88	9.91	9.88	9.89	9.82	0.12	25.75	38.57	23.09	29.19	1.98
2450.0	10.02	9.96	10.00	9.98	9.97	9.88	0.13	23.17	39.35	21.49	28.97	1.96
2550.0	10.07	10.00	10.06	10.01	10.02	9.93	0.14	22.63	40.79	21.24	30.39	1.96
2650.0	10.06	10.00	10.04	9.98	10.03	9.92	0.14	25.05	43.00	24.44	35.91	2.21
2750.0	10.03	9.96	10.00	9.92	9.99	9.87	0.17	32.49	44.95	33.10	43.91	2.38
2850.0	10.08	10.00	10.04	9.99	10.02	9.90	0.19	31.40	45.82	28.26	34.54	2.38
2950.0	10.16	10.08	10.13	10.07	10.09	9.96	0.21	30.30	46.94	26.48	31.53	2.44
3050.0	10.15	10.07	10.13	10.06	10.09	9.93	0.21	34.72	48.90	28.67	29.65	2.60
3150.0	10.16	10.08	10.19	10.12	10.16	9.95	0.24	27.95	51.40	27.64	28.85	2.77
3250.0	10.31	10.22	10.31	10.24	10.29	10.07	0.24	22.65	46.35	21.98	31.35	2.90
3300.0	10.34	10.26	10.34	10.23	10.32	10.10	0.24	22.11	42.98	21.17	35.34	2.90
3330.0	10.35	10.27	10.33	10.22	10.32	10.11	0.24	22.48	40.94	21.43	40.17	3.05
3360.0	10.33	10.24	10.31	10.17	10.30	10.09	0.24	23.34	39.49	22.27	51.34	2.98
3390.0	10.33	10.24	10.29	10.15	10.28	10.09	0.24	24.96	37.75	23.83	42.73	3.08
3420.0	10.34	10.25	10.30	10.15	10.30	10.12	0.22	27.16	36.54	26.10	36.26	3.03
3450.0	10.39	10.27	10.31	10.20	10.32	10.18	0.21	29.33	35.54	28.82	32.58	3.11
3460.0	10.40	10.28	10.32	10.21	10.33	10.20	0.20	29.60	35.21	29.51	31.60	3.16
3470.0	10.40	10.28	10.32	10.21	10.32	10.21	0.19	29.39	34.86	29.79	30.71	3.17
3480.0	10.40	10.28	10.31	10.21	10.32	10.20	0.20	28.77	34.52	29.52	29.93	3.16
3490.0	10.40	10.28	10.31	10.22	10.31	10.20	0.21	27.89	34.16	28.80	29.26	3.13
3500.0	10.42	10.29	10.31	10.23	10.32	10.20	0.22	26.88	33.77	27.85	28.66	3.14
3510.0	10.44	10.31	10.32	10.26	10.33	10.21	0.24	25.87	33.36	26.84	28.15	3.19
3520.0	10.47	10.33	10.35	10.28	10.35	10.22	0.25	24.93	33.01	25.86	27.71	3.27
3530.0	10.48	10.36	10.37	10.30	10.37	10.23	0.25	24.09	32.72	24.93	27.32	3.32
3540.0	10.49	10.37	10.38	10.31	10.38	10.24	0.25	23.33	32.48	24.08	26.98	3.31
3550.0	10.50	10.38	10.39	10.32	10.39	10.24	0.26	22.63	32.27	23.31	26.67	3.24
3560.0	10.51	10.38	10.40	10.33	10.39	10.23	0.27	21.97	32.04	22.62	26.37	3.20
3580.0	10.54	10.40	10.42	10.37	10.41	10.23	0.31	20.83	31.49	21.44	25.90	3.26

FREQ. (MHz)	VSWR (:1)		
	S	1	8
600.0	1.25	1.05	1.04
650.0	1.41	1.06	1.06
700.0	1.56	1.09	1.09
750.0	1.55	1.12	1.12
840.0	1.27	1.15	1.14
870.0	1.18	1.15	1.14
900.0	1.15	1.16	1.14
950.0	1.22	1.16	1.14
1050.0	1.24	1.12	1.11
1150.0	1.24	1.04	1.03
1250.0	1.52	1.09	1.07
1350.0	1.38	1.13	1.11
1450.0	1.05	1.13	1.11
1550.0	1.28	1.12	1.12
1650.0	1.22	1.10	1.11
1750.0	1.24	1.11	1.12
1950.0	1.23	1.02	1.01
2050.0	1.41	1.13	1.11
2150.0	1.40	1.15	1.14
2250.0	1.06	1.12	1.12
2350.0	1.24	1.14	1.14
2450.0	1.32	1.19	1.18
2550.0	1.36	1.21	1.21
2650.0	1.31	1.15	1.17
2750.0	1.09	1.03	1.05
2850.0	1.19	1.10	1.07
2950.0	1.26	1.15	1.14
3050.0	1.16	1.13	1.14
3150.0	1.08	1.13	1.13
3250.0	1.36	1.20	1.20
3300.0	1.40	1.23	1.22
3330.0	1.37	1.23	1.23
3360.0	1.30	1.23	1.22
3390.0	1.19	1.21	1.21
3420.0	1.11	1.18	1.18
3450.0	1.15	1.14	1.15
3460.0	1.19	1.13	1.14
3470.0	1.22	1.12	1.13
3480.0	1.26	1.11	1.11
3490.0	1.30	1.10	1.10
3500.0	1.34	1.08	1.09
3510.0	1.38	1.07	1.08
3520.0	1.42	1.06	1.06
3530.0	1.45	1.05	1.05
3540.0	1.47	1.05	1.04
3550.0	1.49	1.04	1.03
3560.0	1.50	1.04	1.03
3580.0	1.50	1.04	1.02

[1]Total Loss = Insertion Loss + 9dB Splitter Loss

8 Way-0° Power Splitter/Combiner ZB8PD1-ED13816

Typical Performance Curves

Total Loss



Isolation



Amplitude Unbalance



Phase Unbalance



VSWR



Case Style Z

Z41

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Z41	7.06 (179.32)	3.13 (79.50)	.88 (22.35)	.250 (6.35)	1.750 (44.45)	5.310 (134.87)	6.810 (172.97)	.250 (6.35)	2.875 (73.03)	.144 (3.66)	3.53 (89.66)	.44 (11.18)	.415 (10.54)

CASE#	P	WT.GRAMS
Z41	.89 (22.61)	800

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .03; 3 Pl. ± .015

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
   For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.

Mini-Circuits®
INTERNET http://www.minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications **ENV28T5**

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I

This document and its contents are the property of Mini-Circuits.