

Engineering Development Model

Power Splitter/Combiner ZB3PD1-ED10394/1

3 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-920

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		1090		1900 MHz
Isolation	1090 - 1900 MHz		29	
Insertion Loss Above 4.8 dB	1090 - 1900 MHz		0.25	
Phase Unbalance	1090 - 1900 MHz		9.80	
Amplitude Unbalance	1090 - 1900 MHz		0.25	
VSWR	SUM Port		1.15	(:1)
	OUT Ports		1.15	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

PIN CONNECTIONS	
SUM PORT	IN, N FEMALE
PORT 1	2, SMA
PORT 2	3, SMA
PORT 3	4, SMA

Functional Diagram



3 Way-0° Power Splitter/Combiner

ZB3PD1-ED10394/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹			AMP. UNBAL. (dB)	ISOLATION			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)			
	S-1	S-2	S-3		1-2	1-3	2-3			S	1	2	3
1090.0	5.08	4.92	5.24	0.32	29.20	31.95	32.63	6.66	1090.0	1.03	1.18	1.11	1.10
1120.0	5.06	4.88	5.19	0.31	27.98	30.45	34.76	6.75	1120.0	1.02	1.17	1.10	1.10
1150.0	5.06	4.86	5.18	0.31	27.04	29.37	36.88	6.98	1150.0	1.02	1.16	1.09	1.09
1180.0	5.03	4.85	5.15	0.29	26.30	28.59	38.19	7.27	1180.0	1.02	1.14	1.08	1.09
1210.0	5.02	4.85	5.14	0.29	25.75	28.05	38.12	7.54	1210.0	1.04	1.14	1.07	1.09
1240.0	4.98	4.82	5.11	0.29	25.35	27.70	36.92	7.62	1240.0	1.06	1.13	1.06	1.09
1270.0	5.00	4.82	5.10	0.29	25.09	27.58	35.47	7.81	1270.0	1.07	1.11	1.06	1.09
1300.0	5.00	4.83	5.11	0.27	25.01	27.66	34.16	8.21	1300.0	1.09	1.11	1.05	1.10
1330.0	4.95	4.80	5.08	0.28	25.01	27.85	33.11	8.26	1330.0	1.11	1.10	1.04	1.10
1360.0	4.99	4.79	5.08	0.29	25.17	28.32	32.28	8.49	1360.0	1.12	1.09	1.03	1.10
1390.0	4.99	4.82	5.08	0.25	25.54	28.97	31.74	8.97	1390.0	1.13	1.09	1.03	1.11
1420.0	4.93	4.80	5.06	0.26	25.97	29.75	31.28	8.86	1420.0	1.14	1.09	1.02	1.12
1450.0	4.98	4.79	5.07	0.28	26.62	30.85	31.03	9.09	1450.0	1.14	1.09	1.02	1.13
1480.0	5.01	4.84	5.07	0.23	27.56	32.12	30.98	9.62	1480.0	1.14	1.10	1.02	1.13
1510.0	4.96	4.81	5.05	0.24	28.65	33.13	30.98	9.63	1510.0	1.14	1.10	1.03	1.14
1540.0	4.99	4.81	5.06	0.24	30.09	33.43	31.17	9.88	1540.0	1.13	1.12	1.03	1.15
1545.0	4.99	4.82	5.06	0.24	30.36	33.37	31.19	9.92	1545.0	1.13	1.12	1.04	1.15
1550.0	5.00	4.82	5.05	0.23	30.65	33.26	31.24	9.94	1550.0	1.13	1.12	1.04	1.15
1555.0	5.01	4.83	5.06	0.22	30.96	33.13	31.25	10.02	1555.0	1.13	1.12	1.04	1.15
1560.0	5.01	4.83	5.05	0.22	31.26	32.96	31.30	10.09	1560.0	1.13	1.12	1.04	1.15
1565.0	5.02	4.84	5.05	0.21	31.56	32.73	31.35	10.16	1565.0	1.12	1.13	1.04	1.15
1570.0	5.01	4.83	5.04	0.21	31.88	32.49	31.41	10.16	1570.0	1.12	1.13	1.05	1.15
1575.0	5.01	4.84	5.05	0.21	32.21	32.18	31.44	10.22	1575.0	1.12	1.13	1.05	1.15
1580.0	5.01	4.85	5.06	0.21	32.51	31.93	31.49	10.18	1580.0	1.12	1.13	1.05	1.15
1585.0	5.01	4.84	5.05	0.21	32.83	31.58	31.54	10.20	1585.0	1.12	1.13	1.05	1.15
1590.0	5.01	4.83	5.06	0.22	33.15	31.28	31.58	10.26	1590.0	1.11	1.13	1.06	1.15
1595.0	5.01	4.83	5.05	0.22	33.44	30.93	31.63	10.30	1595.0	1.11	1.14	1.06	1.15
1600.0	5.01	4.83	5.04	0.21	33.76	30.59	31.68	10.36	1600.0	1.11	1.14	1.06	1.15
1605.0	5.02	4.83	5.05	0.22	34.02	30.23	31.75	10.40	1605.0	1.11	1.14	1.06	1.16
1615.0	5.04	4.84	5.05	0.21	34.44	29.56	31.83	10.49	1615.0	1.11	1.14	1.06	1.16
1630.0	5.06	4.87	5.06	0.19	34.76	28.50	31.98	10.69	1630.0	1.10	1.15	1.07	1.16
1645.0	5.06	4.87	5.05	0.18	34.53	27.48	32.12	10.76	1645.0	1.10	1.16	1.08	1.16
1660.0	5.06	4.88	5.06	0.19	33.66	26.50	32.13	10.83	1660.0	1.10	1.16	1.09	1.16
1690.0	5.12	4.91	5.08	0.22	31.26	24.73	32.06	11.15	1690.0	1.11	1.17	1.10	1.16
1720.0	5.19	5.00	5.11	0.18	28.80	23.14	31.71	11.45	1720.0	1.13	1.18	1.12	1.16
1750.0	5.17	4.97	5.11	0.20	26.52	21.61	30.82	11.38	1750.0	1.18	1.20	1.15	1.16
1780.0	5.28	5.02	5.15	0.26	24.66	20.40	29.81	11.80	1780.0	1.23	1.21	1.17	1.15
1810.0	5.38	5.16	5.22	0.22	23.11	19.28	28.67	12.09	1810.0	1.30	1.22	1.20	1.15
1840.0	5.38	5.13	5.23	0.26	21.61	18.15	27.33	12.05	1840.0	1.38	1.24	1.23	1.14
1870.0	5.52	5.22	5.30	0.30	20.41	17.28	26.15	12.51	1870.0	1.47	1.26	1.27	1.13
1900.0	5.66	5.38	5.39	0.28	19.38	16.46	25.05	12.91	1900.0	1.58	1.29	1.30	1.12

¹Total Loss = Insertion Loss + 4.8dB Splitter Loss



REV. X2

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

ZB3PD1-ED10394/1






9/16/2010

Page 1 of 1

3 Way-0° Power Splitter/Combiner

ZB3PD1-ED10394/1

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I