

DC Pass

NON-CATALOG

# High Power Combiner

ZB4CS-960-12W

4 Way-0° 50Ω 820 to 960 MHz

## Maximum Ratings


|                       |                             |
|-----------------------|-----------------------------|
| Operating Temperature | -55°C to 90°C               |
| Storage Temperature   | -55°C to 100°C              |
| DC Current            | 1.0 A (250mA for each port) |

Permanent damage may occur if any of these limits are exceeded.

## Coaxial Connections

|          |   |
|----------|---|
| SUM PORT | S |
| PORT 1   | 1 |
| PORT 2   | 2 |
| PORT 3   | 3 |
| PORT 4   | 4 |

## Outline Drawing



## Outline Dimensions (inch/mm)


|        |       |       |       |        |       |
|--------|-------|-------|-------|--------|-------|
| A      | B     | C     | D     | E      | F     |
| 4.50   | 2.25  | 1.69  | .125  | 4.000  | 1.625 |
| 114.30 | 57.15 | 42.93 | 3.18  | 101.60 | 41.28 |
| G      | H     | J     | K     |        | wt    |
| .144   | .890  | .44   | 3.50  |        | grams |
| 3.66   | 22.61 | 11.18 | 88.90 |        | 500   |

## Features

- high power, up to 12W input power
- low insertion loss, 0.3 dB typ.
- high isolation, 28 dB typ.
- excellent VSWR, 1.18 typ.

## Applications

- cellular
- UHF



CASE STYLE: AW256

Connectors Model  
SMA ZB4CS-960-12W-S

## High Power Combiner Electrical Specifications

| FREQ. RANGE (MHz) | ISOLATION (dB) |      | INSERTION LOSS (dB) ABOVE 6.0 dB |      | PHASE UNBALANCE (Degrees) |      | AMPLITUDE UNBALANCE (dB) |      | POWER INPUT <sup>1</sup> (W)  |                  |
|-------------------|----------------|------|----------------------------------|------|---------------------------|------|--------------------------|------|-------------------------------|------------------|
| $f_L$ - $f_U$     | Typ.           | Min. | Typ.                             | Max. | Typ.                      | Max. | Typ.                     | Max. | as combiner <sup>2</sup> Max. | as splitter Max. |
| 820-960           | 28             | 17   | 0.3                              | 0.8  | 2.0                       | 6.0  | 0.2                      | 0.6  | 12                            | 12               |




1. Over -55°C to +55°C. Derate linearly to 20% of rating at 90°C

2. As a combiner of non-coherent signals, max. power per port is power rating divided by number of ports.


## Typical Performance Data

| Freq. (MHz) | Total Loss <sup>1</sup> (dB) |      |      |      | Amp. Unbal. (dB) | Isolation (dB) |       |       | Phase Unbal. (deg.) | VSWR S | VSWR 1 | VSWR 2 | VSWR 3 | VSWR 4 |
|-------------|------------------------------|------|------|------|------------------|----------------|-------|-------|---------------------|--------|--------|--------|--------|--------|
|             | S-1                          | S-2  | S-3  | S-4  |                  | 1-2            | 2-3   | 3-4   |                     |        |        |        |        |        |
| 820.00      | 6.36                         | 6.43 | 6.37 | 6.29 | 0.14             | 20.41          | 21.61 | 20.77 | 1.48                | 1.16   | 1.14   | 1.20   | 1.19   | 1.13   |
| 830.00      | 6.36                         | 6.44 | 6.36 | 6.28 | 0.16             | 20.98          | 21.88 | 21.36 | 1.52                | 1.15   | 1.14   | 1.20   | 1.18   | 1.13   |
| 840.00      | 6.35                         | 6.43 | 6.36 | 6.27 | 0.16             | 21.58          | 22.14 | 21.98 | 1.57                | 1.15   | 1.13   | 1.20   | 1.18   | 1.12   |
| 855.00      | 6.35                         | 6.43 | 6.35 | 6.27 | 0.16             | 22.60          | 22.52 | 23.05 | 1.47                | 1.16   | 1.12   | 1.19   | 1.17   | 1.12   |
| 865.00      | 6.35                         | 6.44 | 6.36 | 6.26 | 0.18             | 23.36          | 22.78 | 23.79 | 1.59                | 1.16   | 1.10   | 1.18   | 1.17   | 1.11   |
| 875.00      | 6.35                         | 6.45 | 6.36 | 6.30 | 0.16             | 24.14          | 23.00 | 24.62 | 1.55                | 1.15   | 1.09   | 1.17   | 1.17   | 1.11   |
| 882.50      | 6.38                         | 6.45 | 6.37 | 6.29 | 0.16             | 24.78          | 23.21 | 25.29 | 1.56                | 1.14   | 1.08   | 1.17   | 1.17   | 1.11   |
| 890.00      | 6.37                         | 6.46 | 6.38 | 6.29 | 0.17             | 25.51          | 23.46 | 26.05 | 1.53                | 1.13   | 1.07   | 1.16   | 1.17   | 1.11   |
| 897.50      | 6.36                         | 6.44 | 6.36 | 6.29 | 0.15             | 26.23          | 23.69 | 26.85 | 1.43                | 1.13   | 1.06   | 1.16   | 1.18   | 1.11   |
| 905.00      | 6.35                         | 6.45 | 6.38 | 6.28 | 0.17             | 27.05          | 23.92 | 27.71 | 1.40                | 1.12   | 1.05   | 1.16   | 1.18   | 1.11   |
| 912.50      | 6.35                         | 6.45 | 6.38 | 6.27 | 0.17             | 27.96          | 24.17 | 28.69 | 1.50                | 1.12   | 1.04   | 1.16   | 1.18   | 1.12   |
| 920.00      | 6.35                         | 6.46 | 6.39 | 6.28 | 0.18             | 29.03          | 24.44 | 24.32 | 1.51                | 1.11   | 1.03   | 1.16   | 1.17   | 1.12   |
| 935.00      | 6.36                         | 6.45 | 6.39 | 6.27 | 0.17             | 31.72          | 24.99 | 32.67 | 1.40                | 1.10   | 1.02   | 1.17   | 1.17   | 1.12   |
| 950.00      | 6.34                         | 6.45 | 6.38 | 6.27 | 0.18             | 35.51          | 25.58 | 36.85 | 1.45                | 1.09   | 1.02   | 1.17   | 1.17   | 1.12   |
| 960.00      | 6.35                         | 6.45 | 6.39 | 6.27 | 0.18             | 39.62          | 26.00 | 41.10 | 1.40                | 1.08   | 1.03   | 1.17   | 1.17   | 1.12   |

1. Total Loss = Insertion Loss + 6dB splitter loss.



## electrical schematic



### Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.  
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.  
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at [www.minicircuits.com/MCLStore/terms.jsp](http://www.minicircuits.com/MCLStore/terms.jsp)



[www.minicircuits.com](http://www.minicircuits.com) P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 [sales@minicircuits.com](mailto:sales@minicircuits.com)

REV. C  
M151107  
ZB4CS-960-12W  
ED-4455  
HY/TD/CP/AM  
151208

# 4 Way-0° Power Splitter/Combiner

ZB4CS-960-12W

## Typical Performance Data

| FREQ.<br>(MHz) | TOTAL LOSS <sup>1</sup><br>(dB) |      |      |      | AMP.<br>UNBAL.<br>(dB) | ISOLATION<br>(dB) |       |       | PHASE<br>UNBAL.<br>(deg.) | FREQ.<br>(MHz) | VSWR<br>(:1) |      |      |      |      |
|----------------|---------------------------------|------|------|------|------------------------|-------------------|-------|-------|---------------------------|----------------|--------------|------|------|------|------|
|                | S-1                             | S-2  | S-3  | S-4  |                        | 1-2               | 2-3   | 3-4   |                           |                | S            | 1    | 2    | 3    | 4    |
| 820.0          | 6.36                            | 6.43 | 6.37 | 6.29 | 0.14                   | 20.41             | 21.61 | 20.77 | 1.48                      | 820.0          | 1.16         | 1.14 | 1.20 | 1.19 | 1.13 |
| 825.0          | 6.37                            | 6.43 | 6.36 | 6.28 | 0.15                   | 20.69             | 21.75 | 21.04 | 1.56                      | 825.0          | 1.15         | 1.14 | 1.20 | 1.19 | 1.13 |
| 830.0          | 6.36                            | 6.44 | 6.36 | 6.28 | 0.16                   | 20.98             | 21.88 | 21.36 | 1.52                      | 830.0          | 1.15         | 1.14 | 1.20 | 1.18 | 1.13 |
| 835.0          | 6.37                            | 6.42 | 6.37 | 6.29 | 0.14                   | 21.27             | 21.99 | 21.66 | 1.55                      | 835.0          | 1.15         | 1.13 | 1.20 | 1.18 | 1.13 |
| 840.0          | 6.35                            | 6.43 | 6.36 | 6.27 | 0.16                   | 21.58             | 22.14 | 21.98 | 1.57                      | 840.0          | 1.15         | 1.13 | 1.20 | 1.18 | 1.12 |
| 845.0          | 6.35                            | 6.43 | 6.36 | 6.28 | 0.14                   | 21.92             | 22.26 | 22.31 | 1.48                      | 845.0          | 1.15         | 1.13 | 1.20 | 1.18 | 1.12 |
| 850.0          | 6.35                            | 6.43 | 6.35 | 6.28 | 0.15                   | 22.26             | 22.39 | 22.68 | 1.54                      | 850.0          | 1.15         | 1.12 | 1.20 | 1.17 | 1.12 |
| 855.0          | 6.35                            | 6.43 | 6.35 | 6.27 | 0.16                   | 22.60             | 22.52 | 23.05 | 1.47                      | 855.0          | 1.16         | 1.12 | 1.19 | 1.17 | 1.12 |
| 860.0          | 6.35                            | 6.43 | 6.36 | 6.27 | 0.16                   | 22.96             | 22.65 | 23.42 | 1.61                      | 860.0          | 1.16         | 1.11 | 1.19 | 1.17 | 1.12 |
| 862.5          | 6.35                            | 6.44 | 6.36 | 6.28 | 0.16                   | 23.17             | 22.69 | 23.60 | 1.57                      | 862.5          | 1.16         | 1.11 | 1.18 | 1.17 | 1.11 |
| 865.0          | 6.35                            | 6.44 | 6.36 | 6.26 | 0.18                   | 23.36             | 22.78 | 23.79 | 1.59                      | 865.0          | 1.16         | 1.10 | 1.18 | 1.17 | 1.11 |
| 870.0          | 6.35                            | 6.44 | 6.36 | 6.28 | 0.16                   | 23.73             | 22.88 | 24.19 | 1.54                      | 870.0          | 1.16         | 1.10 | 1.18 | 1.17 | 1.11 |
| 872.5          | 6.37                            | 6.44 | 6.37 | 6.30 | 0.14                   | 23.95             | 22.93 | 24.40 | 1.67                      | 872.5          | 1.16         | 1.09 | 1.17 | 1.17 | 1.11 |
| 875.0          | 6.35                            | 6.45 | 6.36 | 6.30 | 0.16                   | 24.14             | 23.00 | 24.62 | 1.55                      | 875.0          | 1.15         | 1.09 | 1.17 | 1.17 | 1.11 |
| 877.5          | 6.36                            | 6.46 | 6.38 | 6.30 | 0.16                   | 24.35             | 23.08 | 24.83 | 1.49                      | 877.5          | 1.15         | 1.09 | 1.17 | 1.17 | 1.11 |
| 880.0          | 6.37                            | 6.45 | 6.38 | 6.30 | 0.16                   | 24.57             | 23.12 | 25.07 | 1.52                      | 880.0          | 1.15         | 1.09 | 1.17 | 1.17 | 1.11 |
| 882.5          | 6.38                            | 6.45 | 6.37 | 6.29 | 0.16                   | 24.78             | 23.21 | 25.29 | 1.56                      | 882.5          | 1.14         | 1.08 | 1.17 | 1.17 | 1.11 |
| 885.0          | 6.36                            | 6.46 | 6.37 | 6.30 | 0.16                   | 25.02             | 23.27 | 25.54 | 1.43                      | 885.0          | 1.14         | 1.08 | 1.17 | 1.17 | 1.11 |
| 887.5          | 6.37                            | 6.45 | 6.37 | 6.29 | 0.16                   | 25.25             | 23.37 | 25.78 | 1.35                      | 887.5          | 1.14         | 1.08 | 1.17 | 1.17 | 1.11 |
| 890.0          | 6.37                            | 6.46 | 6.38 | 6.29 | 0.17                   | 25.51             | 23.46 | 26.05 | 1.53                      | 890.0          | 1.13         | 1.07 | 1.16 | 1.17 | 1.11 |
| 892.5          | 6.36                            | 6.45 | 6.38 | 6.29 | 0.16                   | 25.75             | 23.53 | 26.31 | 1.44                      | 892.5          | 1.13         | 1.07 | 1.16 | 1.18 | 1.11 |
| 895.0          | 6.35                            | 6.44 | 6.37 | 6.29 | 0.15                   | 25.98             | 23.59 | 26.58 | 1.40                      | 895.0          | 1.13         | 1.07 | 1.16 | 1.18 | 1.11 |
| 897.5          | 6.36                            | 6.44 | 6.36 | 6.29 | 0.15                   | 26.23             | 23.69 | 26.85 | 1.43                      | 897.5          | 1.13         | 1.06 | 1.16 | 1.18 | 1.11 |
| 900.0          | 6.36                            | 6.45 | 6.38 | 6.28 | 0.16                   | 26.50             | 23.76 | 27.13 | 1.49                      | 900.0          | 1.12         | 1.06 | 1.16 | 1.18 | 1.11 |
| 902.5          | 6.34                            | 6.44 | 6.37 | 6.28 | 0.16                   | 26.80             | 23.83 | 27.37 | 1.40                      | 902.5          | 1.12         | 1.06 | 1.16 | 1.18 | 1.11 |
| 905.0          | 6.35                            | 6.45 | 6.38 | 6.28 | 0.17                   | 27.05             | 23.92 | 27.71 | 1.40                      | 905.0          | 1.12         | 1.05 | 1.16 | 1.18 | 1.11 |
| 907.5          | 6.35                            | 6.45 | 6.38 | 6.28 | 0.18                   | 27.34             | 24.00 | 27.96 | 1.43                      | 907.5          | 1.12         | 1.05 | 1.16 | 1.18 | 1.12 |
| 910.0          | 6.35                            | 6.46 | 6.37 | 6.28 | 0.18                   | 27.68             | 24.08 | 28.32 | 1.52                      | 910.0          | 1.12         | 1.05 | 1.16 | 1.18 | 1.12 |
| 912.5          | 6.35                            | 6.45 | 6.38 | 6.27 | 0.17                   | 27.96             | 24.17 | 28.69 | 1.50                      | 912.5          | 1.12         | 1.04 | 1.16 | 1.18 | 1.12 |
| 915.0          | 6.34                            | 6.45 | 6.38 | 6.28 | 0.17                   | 28.30             | 24.27 | 29.00 | 1.41                      | 915.0          | 1.12         | 1.04 | 1.16 | 1.18 | 1.12 |
| 917.5          | 6.37                            | 6.46 | 6.39 | 6.27 | 0.18                   | 28.64             | 24.33 | 29.43 | 1.49                      | 917.5          | 1.12         | 1.04 | 1.16 | 1.18 | 1.12 |
| 920.0          | 6.35                            | 6.46 | 6.39 | 6.28 | 0.18                   | 29.03             | 24.44 | 24.32 | 1.51                      | 920.0          | 1.11         | 1.03 | 1.16 | 1.17 | 1.12 |
| 925.0          | 6.36                            | 6.46 | 6.39 | 6.28 | 0.18                   | 29.84             | 24.62 | 30.64 | 1.35                      | 925.0          | 1.11         | 1.03 | 1.16 | 1.17 | 1.12 |
| 930.0          | 6.35                            | 6.44 | 6.38 | 6.28 | 0.17                   | 30.71             | 24.80 | 31.64 | 1.57                      | 930.0          | 1.11         | 1.03 | 1.17 | 1.17 | 1.12 |
| 935.0          | 6.36                            | 6.45 | 6.39 | 6.27 | 0.17                   | 31.72             | 24.99 | 32.67 | 1.40                      | 935.0          | 1.10         | 1.02 | 1.17 | 1.17 | 1.12 |
| 940.0          | 6.36                            | 6.44 | 6.39 | 6.27 | 0.17                   | 32.78             | 25.16 | 33.83 | 1.38                      | 940.0          | 1.10         | 1.02 | 1.17 | 1.17 | 1.12 |
| 945.0          | 6.36                            | 6.46 | 6.39 | 6.28 | 0.18                   | 34.01             | 25.38 | 35.17 | 1.47                      | 945.0          | 1.10         | 1.02 | 1.17 | 1.17 | 1.12 |
| 950.0          | 6.34                            | 6.45 | 6.38 | 6.27 | 0.18                   | 35.51             | 25.58 | 36.85 | 1.45                      | 950.0          | 1.09         | 1.02 | 1.17 | 1.17 | 1.12 |
| 955.0          | 6.34                            | 6.44 | 6.39 | 6.26 | 0.18                   | 37.38             | 25.77 | 38.86 | 1.43                      | 955.0          | 1.08         | 1.03 | 1.17 | 1.17 | 1.12 |
| 960.0          | 6.35                            | 6.45 | 6.39 | 6.27 | 0.18                   | 39.62             | 26.00 | 41.10 | 1.40                      | 960.0          | 1.08         | 1.03 | 1.17 | 1.17 | 1.12 |






<sup>1</sup> Total Loss = Insertion Loss+ 6dB Splitter Loss

REV. X2  
ZB4CS-960-12W  
100627  
Page 1 of 1

# 4 Way-0° Power Splitter/Combiner

ZB4CS-960-12W


## Typical Performance Curves



REV. X2  
ZB4CS-960-12W  
100627  
Page 1 of 1

## Outline Dimensions

AW256



| CASE # | A                | B               | C               | D              | E                 | F                | G              | H               | J              | K               | WT. GRAM |
|--------|------------------|-----------------|-----------------|----------------|-------------------|------------------|----------------|-----------------|----------------|-----------------|----------|
| AW256  | 4.50<br>(114.30) | 2.25<br>(57.15) | 1.69<br>(42.93) | .125<br>(3.18) | 4.000<br>(101.60) | 1.625<br>(41.28) | .144<br>(3.66) | .890<br>(22.61) | .44<br>(11.18) | 3.50<br>(88.90) | 500      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

- Case material: Aluminum alloy.
- Case Finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification              | Test/Inspection Condition                                                              | Reference/Spec                       |
|----------------------------|----------------------------------------------------------------------------------------|--------------------------------------|
| Operating Temperature      | -55° to 90° C<br>Ambient Environment                                                   | Individual Model Data Sheet          |
| Storage Temperature        | -55° to 100° C<br>Ambient Environment                                                  | Individual Model Data Sheet          |
| Barometric Pressure        | 100,000 Feet                                                                           | MIL-STD-202, Method 105, Condition D |
| Humidity                   | 90% RH, 65°C<br>Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103              |
| Thermal Shock              | -65° to 125°C, 5 cycles                                                                | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)    | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock           | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)                          | MIL-STD-202, Method 213, Condition I |