


50Ω Up to 20W 1270 to 2575 MHz

Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
DC Current	2.5A
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

INPUT	J1
OUTPUT	J2
COUPLED (forward)	J4
COUPLED (reverse)	J3

Outline Drawing**Outline Dimensions (inch mm)**

A	B	C	D	E	F
3.75	1.56	.70	.125	3.500	.780
95.25	39.62	17.78	3.18	88.90	19.81
G	H	J	K		
.44	.60	.97	2.78		
11.18	15.24	24.64	70.61		
				wt	grams
					130.0

Features

- wide frequency range, 1270 to 2575 MHz
- good coupling flatness, ± 0.1 dB typ over 1700-2200 MHz
- high directivity, 30 dB typ.
- very good VSWR, 1.05:1 typ.
- high power, 20W
- DC Current through input to output 2.5A Max. at 1.0 watt RF input.

Applications

- GPS
- PCS
- LAB use





Bi-Directional Coupler Electrical Specifications

FREQ. (MHz)	COUPLING (dB)		MAINLINE LOSS ¹ (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT (W)
	Nom.	Flatness	Typ.	Max.	Typ.	Min.		
1270-2575	24.9 $\pm$ 1.1	± 0.8	0.3	0.4	28	20	1.05	20
1700-2200	24.3 $\pm$ 0.5	± 0.3	0.3	0.45	30	24	1.05	20

1. Mainline loss includes theoretical power loss at coupled port.

Typical Performance Data

Frequency (MHz)	Mainline Loss (dB) In-Out	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
		In-Cpl Fwd	Out-Cpl Rev	Out-Cpl Fwd	In-Cpl Rev	In	Out	Cpl Fwd	Cpl Rev
1270.00	0.23	25.70	25.71	25.63	26.48	27.91	27.32	30.41	28.47
1450.00	0.24	25.11	25.13	27.14	28.26	29.10	28.76	30.05	28.31
1600.00	0.26	24.78	24.79	28.20	30.37	30.28	29.78	30.32	28.69
1750.00	0.27	24.58	24.59	29.08	33.25	30.99	30.43	30.52	29.43
1850.00	0.28	24.51	24.53	29.48	35.31	31.05	30.69	31.09	30.11
1950.00	0.29	24.50	24.53	29.90	37.88	31.08	30.44	31.41	30.80
2100.00	0.30	24.59	24.61	29.04	41.38	29.61	29.12	31.92	31.77
2250.00	0.31	24.81	24.82	27.73	41.01	27.68	27.97	31.58	32.17
2400.00	0.32	25.17	25.16	26.36	37.32	25.83	26.47	30.79	32.08
2575.00	0.34	25.77	25.75	24.33	33.99	23.84	24.15	29.24	30.72

**Electrical Schematic**

* ELECTRICAL SCHEMATIC IS FOR BI-DIRECTIONAL COUPLER WITH INTERNAL ATTENUATORS AT COUPLING PORTS.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Bi-Directional Coupler

ZBDC25-2575W+

Typical Performance Data

FREQ. (MHz)	INSERTION LOSS (dB) IN-OUT	COUPLING (dB)		DIRECTIVITY (dB)		RETURN LOSS (dB)			
		IN-FWD	OUT-REV	IN-REV	OUT-FWD	IN	OUT	FWD	REV
100.0	0.03	46.03	46.04	26.39	25.88	46.13	45.45	50.35	49.11
230.0	0.07	38.80	38.81	24.74	24.42	37.40	37.78	46.55	44.80
360.0	0.09	34.96	34.96	24.23	24.11	32.98	33.05	44.99	41.72
490.0	0.11	32.39	32.40	23.85	23.86	30.59	30.23	42.17	38.72
620.0	0.14	30.50	30.52	23.84	23.69	28.97	28.62	39.07	36.12
750.0	0.16	29.05	29.08	23.92	23.84	27.95	27.53	36.73	33.92
880.0	0.18	27.91	27.93	24.21	24.00	27.46	27.03	34.28	31.87
1010.0	0.20	27.00	27.03	24.52	24.51	27.18	26.74	32.72	30.31
1140.0	0.21	26.28	26.29	25.48	24.93	27.50	26.89	31.42	29.17
1270.0	0.23	25.70	25.71	26.48	25.63	27.91	27.32	30.41	28.47
1400.0	0.24	25.25	25.27	27.62	26.71	28.79	28.34	30.04	28.25
1450.0	0.24	25.11	25.13	28.26	27.14	29.10	28.76	30.05	28.31
1500.0	0.25	24.98	25.00	28.83	27.60	29.51	29.14	29.95	28.34
1550.0	0.25	24.87	24.89	29.84	27.97	30.05	29.63	30.22	28.44
1600.0	0.26	24.78	24.79	30.37	28.20	30.28	29.78	30.32	28.69
1650.0	0.26	24.70	24.71	31.68	28.48	30.94	30.11	30.21	28.84
1700.0	0.26	24.63	24.65	32.37	28.63	30.94	30.10	30.62	29.23
1750.0	0.27	24.58	24.59	33.25	29.08	30.99	30.43	30.52	29.43
1800.0	0.27	24.54	24.56	35.10	29.38	31.38	30.65	30.95	29.87
1850.0	0.28	24.51	24.53	35.31	29.48	31.05	30.69	31.09	30.11
1900.0	0.28	24.50	24.52	36.93	29.67	31.14	30.47	31.42	30.57
1950.0	0.29	24.50	24.53	37.88	29.90	31.08	30.44	31.41	30.80
2000.0	0.29	24.52	24.54	38.94	29.53	30.50	29.82	31.68	31.29
2050.0	0.30	24.55	24.56	41.68	29.51	30.53	29.72	31.71	31.46
2100.0	0.30	24.59	24.61	41.38	29.04	29.61	29.12	31.92	31.77
2150.0	0.30	24.65	24.66	41.93	28.85	29.25	28.65	32.15	32.05
2200.0	0.31	24.72	24.74	42.36	28.23	28.70	28.31	31.73	32.08
2250.0	0.31	24.81	24.82	41.01	27.73	27.68	27.97	31.58	32.17
2300.0	0.31	24.91	24.92	40.40	27.21	27.14	27.50	31.46	32.21
2350.0	0.32	25.03	25.04	38.46	26.90	26.30	27.07	31.31	32.11
2400.0	0.32	25.17	25.16	37.32	26.36	25.83	26.47	30.79	32.08
2450.0	0.33	25.31	25.31	36.77	25.94	25.34	25.94	30.35	31.66
2575.0	0.34	25.77	25.75	33.99	24.33	23.84	24.15	29.24	30.72
2700.0	0.35	26.34	26.33	30.89	22.50	22.42	22.50	27.90	29.17
2825.0	0.36	27.07	27.05	27.44	20.56	21.11	21.17	26.39	27.63
2950.0	0.37	27.97	27.95	23.71	18.69	20.23	20.12	24.98	26.15
3075.0	0.37	29.10	29.06	20.26	16.77	19.82	19.56	23.89	24.70
3200.0	0.38	30.53	30.45	16.91	14.36	19.44	19.02	23.07	23.62
3325.0	0.38	32.34	32.20	13.46	11.58	19.27	18.98	22.67	22.99
3450.0	0.38	34.74	34.46	9.61	8.45	19.34	19.22	22.77	22.58

REV. X1

ZBDC25-2575W+

061031

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS9100 CERTIFIED • RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661







The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Bi-Directional Coupler


Typical Performance Curves

ZBDC25-2575W+



Outline Dimensions

HT1180



CASE #	A	B	C	D	E	F	G	H	J	K	WT. GRAM
HT1180	3.75 (95.25)	1.56 (39.62)	.70 (17.78)	.125 (3.18)	3.500 (88.90)	.780 (19.81)	.44 (11.18)	.60 (15.24)	.97 (24.64)	2.78 (70.61)	130.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:

For RoHS Case Styles: Clear Chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I