

Power Splitter/Combiner

ZB4PD-ED17050/1

4 Way-0°

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability. At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.



Please click "Back", and then click "Contact Us" for Applications support.

CASE STYLE : 99-01-1936

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter	Min.	Typ.	Max.	Units
Frequency	5		200	MHz
Isolation		18.0		dB
Insertion Loss Above 6.0 dB		0.35		dB
Phase Unbalance		0.80		deg.
Amplitude Unbalance		0.05		dB
DC Supply Voltage		24		V
DC Supply Current		120		mA
VSWR	SUM PORT	1.25		(:1)
	OUT PORTS	1.40		(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C TO 100°C
Storage Temperature	-55°C TO 100°C
Power Input (as a splitter)	100W

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4

SCHEMATICS



4 Way-0° Power Splitter/Combiner

ZB4PD-ED17050/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹				AMP UNBAL. (dB)	ISOLATION			PHASE UNBAL. (Deg)	FREQ. (MHz)	VSWR				
	S1	S2	S3	S4		1-2	2-3	3-4			S	1	2	3	4
3.0	6.49	6.49	6.48	6.49	0.01	13.12	12.76	13.57	0.05	3.0	1.89	2.15	2.15	2.20	2.20
4.0	6.30	6.30	6.30	6.30	0.00	13.47	12.61	13.94	0.06	4.0	1.62	2.02	2.02	2.07	2.07
5.0	6.21	6.21	6.21	6.21	0.00	13.65	12.57	14.13	0.07	5.0	1.47	1.96	1.96	2.00	2.00
7.0	6.13	6.13	6.13	6.13	0.01	13.86	12.61	14.34	0.10	7.0	1.31	1.88	1.88	1.93	1.93
9.0	6.10	6.10	6.10	6.10	0.01	14.01	12.73	14.49	0.14	9.0	1.23	1.83	1.83	1.87	1.87
10.0	6.09	6.09	6.09	6.10	0.01	14.09	12.81	14.57	0.14	10.0	1.20	1.81	1.81	1.85	1.85
15.0	6.09	6.08	6.08	6.09	0.01	14.54	13.30	15.02	0.22	15.0	1.12	1.72	1.72	1.76	1.76
20.0	6.09	6.09	6.10	6.10	0.01	15.09	13.89	15.58	0.25	20.0	1.08	1.65	1.64	1.68	1.68
25.0	6.11	6.11	6.12	6.12	0.01	15.68	14.52	16.17	0.29	25.0	1.05	1.58	1.58	1.61	1.61
30.0	6.14	6.14	6.15	6.15	0.02	16.24	15.15	16.73	0.34	30.0	1.03	1.53	1.53	1.56	1.56
35.0	6.16	6.16	6.18	6.18	0.02	16.75	15.75	17.24	0.37	35.0	1.02	1.49	1.49	1.51	1.51
40.0	6.18	6.18	6.20	6.19	0.02	17.21	16.29	17.71	0.39	40.0	1.01	1.45	1.45	1.48	1.48
45.0	6.19	6.19	6.21	6.21	0.02	17.63	16.78	18.13	0.42	45.0	1.00	1.42	1.42	1.45	1.45
50.0	6.19	6.19	6.21	6.21	0.02	17.98	17.21	18.48	0.45	50.0	1.00	1.40	1.40	1.42	1.42
55.0	6.20	6.20	6.22	6.22	0.02	18.29	17.59	18.79	0.48	55.0	1.01	1.38	1.38	1.40	1.40
60.0	6.20	6.20	6.22	6.22	0.02	18.54	17.93	19.04	0.52	60.0	1.02	1.36	1.36	1.39	1.38
65.0	6.21	6.21	6.23	6.23	0.02	18.75	18.23	19.25	0.56	65.0	1.03	1.35	1.35	1.37	1.37
70.0	6.21	6.21	6.23	6.23	0.02	18.91	18.50	19.41	0.59	70.0	1.04	1.34	1.34	1.36	1.36
75.0	6.22	6.21	6.24	6.24	0.02	19.03	18.74	19.54	0.61	75.0	1.05	1.33	1.33	1.35	1.35
80.0	6.22	6.22	6.24	6.24	0.02	19.13	18.96	19.63	0.64	80.0	1.06	1.32	1.32	1.34	1.34
85.0	6.22	6.22	6.25	6.24	0.03	19.19	19.14	19.69	0.66	85.0	1.07	1.31	1.31	1.33	1.33
90.0	6.23	6.23	6.25	6.25	0.03	19.23	19.32	19.72	0.69	90.0	1.08	1.31	1.31	1.33	1.33
95.0	6.23	6.23	6.26	6.25	0.03	19.24	19.47	19.73	0.71	95.0	1.09	1.30	1.31	1.33	1.32
100.0	6.24	6.24	6.26	6.26	0.03	19.22	19.61	19.71	0.74	100.0	1.10	1.30	1.30	1.32	1.32
110.0	6.25	6.25	6.28	6.27	0.03	19.13	19.87	19.62	0.78	110.0	1.13	1.30	1.30	1.32	1.32
120.0	6.27	6.27	6.29	6.29	0.02	18.97	20.10	19.45	0.82	120.0	1.16	1.30	1.30	1.32	1.31
130.0	6.29	6.29	6.31	6.31	0.02	18.76	20.31	19.24	0.88	130.0	1.19	1.30	1.30	1.32	1.32
140.0	6.31	6.30	6.33	6.32	0.02	18.51	20.48	18.99	0.95	140.0	1.23	1.30	1.30	1.32	1.32
150.0	6.34	6.32	6.35	6.35	0.03	18.22	20.64	18.71	1.01	150.0	1.27	1.31	1.31	1.32	1.32
160.0	6.37	6.36	6.38	6.37	0.02	17.88	20.81	18.37	1.03	160.0	1.31	1.32	1.32	1.33	1.33
170.0	6.40	6.39	6.41	6.40	0.02	17.50	20.99	17.99	1.02	170.0	1.36	1.33	1.33	1.34	1.34
180.0	6.45	6.43	6.44	6.44	0.01	17.10	21.17	17.60	1.01	180.0	1.41	1.34	1.34	1.35	1.35
190.0	6.50	6.48	6.49	6.48	0.02	16.70	21.33	17.20	1.02	190.0	1.47	1.35	1.35	1.36	1.36
200.0	6.55	6.53	6.53	6.53	0.02	16.27	21.48	16.78	1.06	200.0	1.54	1.37	1.37	1.37	1.37
220.0	6.68	6.66	6.64	6.65	0.04	15.40	21.81	15.92	1.07	220.0	1.69	1.40	1.41	1.40	1.40
240.0	6.85	6.82	6.78	6.79	0.07	14.49	22.19	15.03	1.07	240.0	1.87	1.44	1.45	1.44	1.44
260.0	7.07	7.03	6.97	6.98	0.10	13.58	22.62	14.13	1.03	260.0	2.09	1.49	1.50	1.48	1.48
280.0	7.34	7.29	7.20	7.22	0.14	12.68	23.11	13.24	0.96	280.0	2.37	1.55	1.55	1.53	1.52
300.0	7.68	7.61	7.48	7.51	0.20	11.81	23.67	12.38	0.87	300.0	2.70	1.61	1.62	1.58	1.58

¹Total Loss = Insertion Loss + 6dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
ZB4PD-ED17050/1






8/13/2014

Page 1 of 1

4 Way-0° Power Splitter/Combiner

ZB4PD-ED17050/1

Typical Performance Curves





All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I