

High Power Combiner

ZB6CS-150-12W

6 Way-0° 50Ω 50 to 150 MHz


Maximum Ratings

Operating Temperature	-55°C to 90°C
Storage Temperature	-55°C to 100°C
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	
7.06	3.13	.88	.250	1.750	5.310	6.810	.250	
179.32	79.50	22.35	6.35	44.45	134.87	172.97	6.35	
J	K	L	M	N	P		wt	
2.875	.144	3.53	.44	1.31	.89		grams	
73.03	3.66	89.66	11.18	33.27	22.61		800	

Features

- input power, up to 12W input power
- low insertion loss, 0.5 dB typ.
- high isolation, 32 dB typ.

Applications

- VHF
- instrumentation



BNC version shown
CASE STYLE: Z259

Connectors	Model
BNC	ZB6CS-150-12W
N-TYPE	ZB6CS-150-12W-N
SMA	ZB6CS-150-12W-S

High Power Combiner Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 7.8 dB		PHASE UNBALANCE (Degrees)		AMPLITUDE UNBALANCE (dB)		POWER INPUT ¹ (W)	
f_L - f_U	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	as combiner ² Max.	as splitter Max.
50-150	32	20	0.5	1.2	3.0	9.0	0.15	0.5	12	10




1. Over -55°C to +55°C. Derate linearly to 20% of rating at 90°C

2. As a combiner of non-coherent signals, max. power per port is power rating divided by number of ports.

Typical Performance Data

Freq. (MHz)	Total Loss ¹ (dB)			Amplitude Unbalance (dB)	Isolation (dB)			Phase Unbalance (deg.)	VSWR S	VSWR 1
	S-1	S-3	S-5		1-2	1-3	1-6			
50.00	8.20	8.20	8.22	0.03	22.93	22.96	46.56	1.45	1.49	1.20
56.00	8.21	8.22	8.23	0.04	22.74	22.72	45.60	1.47	1.49	1.18
60.00	8.23	8.22	8.26	0.06	22.64	22.56	44.01	1.62	1.49	1.16
69.00	8.23	8.26	8.25	0.04	22.49	22.30	40.71	1.84	1.50	1.14
76.00	8.25	8.25	8.28	0.05	22.47	22.18	38.91	1.99	1.51	1.13
83.00	8.28	8.31	8.29	0.05	22.53	22.13	37.59	2.26	1.51	1.13
90.00	8.32	8.34	8.33	0.05	22.67	22.13	36.68	2.45	1.51	1.13
99.00	8.35	8.39	8.37	0.07	22.98	22.17	35.84	2.68	1.49	1.13
106.00	8.36	8.39	8.37	0.07	23.32	22.25	35.39	2.90	1.47	1.13
110.00	8.35	8.40	8.38	0.07	23.56	22.30	35.27	2.97	1.47	1.13
119.00	8.38	8.41	8.40	0.08	24.28	22.43	35.13	3.27	1.46	1.14
126.00	8.39	8.44	8.43	0.08	25.01	22.54	35.12	3.59	1.47	1.15
133.00	8.42	8.47	8.46	0.09	25.82	22.60	35.20	3.94	1.48	1.15
140.00	8.47	8.54	8.48	0.11	26.61	22.60	35.36	4.37	1.51	1.16
150.00	8.52	8.59	8.54	0.12	27.29	22.35	35.67	4.63	1.55	1.18

1. Total Loss = Insertion Loss + 7.8dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



6 Way-0° Power Splitter/Combiner

ZB6CS-150-12W

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)						AMP. UNBAL. (dB)	ISOLATION (dB)			PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)	
	S-1	S-2	S-3	S-4	S-5	S-6		1-2	1-3	1-6			S	1
50.0	8.20	8.19	8.20	8.22	8.22	8.20	0.03	22.93	22.96	46.56	1.45	50.0	1.49	1.20
53.0	8.22	8.20	8.22	8.23	8.23	8.21	0.03	22.84	22.84	46.46	1.52	53.0	1.49	1.19
56.0	8.21	8.19	8.22	8.22	8.23	8.20	0.04	22.74	22.72	45.60	1.47	56.0	1.49	1.18
59.0	8.22	8.20	8.22	8.23	8.24	8.22	0.03	22.66	22.60	44.25	1.66	59.0	1.49	1.17
60.0	8.23	8.22	8.22	8.24	8.26	8.20	0.06	22.64	22.56	44.01	1.62	60.0	1.49	1.16
63.0	8.24	8.22	8.25	8.24	8.26	8.22	0.04	22.58	22.48	42.76	1.75	63.0	1.50	1.16
66.0	8.24	8.23	8.25	8.23	8.25	8.21	0.04	22.53	22.40	41.71	1.76	66.0	1.50	1.15
69.0	8.23	8.24	8.26	8.24	8.25	8.22	0.04	22.49	22.30	40.71	1.84	69.0	1.50	1.14
70.0	8.23	8.23	8.24	8.23	8.25	8.21	0.04	22.47	22.29	40.38	1.74	70.0	1.51	1.14
73.0	8.25	8.24	8.26	8.26	8.26	8.24	0.02	22.47	22.24	39.54	1.98	73.0	1.51	1.14
76.0	8.25	8.25	8.25	8.27	8.28	8.23	0.05	22.47	22.18	38.91	1.99	76.0	1.51	1.13
79.0	8.26	8.27	8.28	8.28	8.27	8.25	0.04	22.49	22.16	38.26	2.01	79.0	1.51	1.13
80.0	8.28	8.28	8.29	8.28	8.28	8.25	0.04	22.50	22.15	38.09	2.12	80.0	1.51	1.13
83.0	8.28	8.29	8.31	8.29	8.29	8.26	0.05	22.53	22.13	37.59	2.26	83.0	1.51	1.13
86.0	8.29	8.30	8.33	8.31	8.32	8.27	0.05	22.59	22.11	37.18	2.24	86.0	1.51	1.13
89.0	8.31	8.32	8.33	8.34	8.33	8.28	0.06	22.64	22.12	36.75	2.37	89.0	1.51	1.13
90.0	8.32	8.32	8.34	8.34	8.33	8.30	0.05	22.67	22.13	36.68	2.45	90.0	1.51	1.13
93.0	8.32	8.34	8.35	8.34	8.34	8.30	0.06	22.76	22.12	36.34	2.46	93.0	1.50	1.13
96.0	8.34	8.34	8.39	8.35	8.36	8.30	0.09	22.86	22.13	36.04	2.50	96.0	1.49	1.13
99.0	8.35	8.35	8.39	8.37	8.37	8.31	0.07	22.98	22.17	35.84	2.68	99.0	1.49	1.13
100.0	8.34	8.35	8.37	8.38	8.36	8.31	0.07	23.00	22.17	35.77	2.75	100.0	1.49	1.13
103.0	8.37	8.38	8.39	8.40	8.38	8.33	0.07	23.17	22.20	35.60	2.88	103.0	1.48	1.13
106.0	8.36	8.38	8.39	8.39	8.37	8.32	0.07	23.32	22.25	35.39	2.90	106.0	1.47	1.13
109.0	8.36	8.37	8.39	8.40	8.37	8.32	0.08	23.51	22.28	35.29	2.94	109.0	1.47	1.13
110.0	8.35	8.38	8.40	8.38	8.38	8.33	0.07	23.56	22.30	35.27	2.97	110.0	1.47	1.13
113.0	8.37	8.38	8.41	8.39	8.39	8.34	0.07	23.79	22.36	35.18	3.21	113.0	1.46	1.14
116.0	8.36	8.39	8.41	8.40	8.40	8.34	0.08	24.02	22.38	35.14	3.32	116.0	1.46	1.14
119.0	8.38	8.38	8.41	8.41	8.40	8.34	0.08	24.28	22.43	35.13	3.27	119.0	1.46	1.14
120.0	8.38	8.40	8.43	8.41	8.41	8.36	0.07	24.39	22.46	35.10	3.46	120.0	1.46	1.14
123.0	8.38	8.40	8.43	8.42	8.42	8.37	0.07	24.68	22.51	35.14	3.57	123.0	1.46	1.14
126.0	8.39	8.42	8.44	8.43	8.43	8.37	0.08	25.01	22.54	35.12	3.59	126.0	1.47	1.15
129.0	8.40	8.44	8.47	8.45	8.44	8.39	0.08	25.35	22.58	35.17	3.76	129.0	1.47	1.15
130.0	8.42	8.45	8.47	8.47	8.44	8.38	0.09	25.48	22.59	35.22	3.84	130.0	1.48	1.15
133.0	8.42	8.46	8.47	8.47	8.46	8.38	0.09	25.82	22.60	35.20	3.94	133.0	1.48	1.15
136.0	8.45	8.49	8.50	8.50	8.48	8.42	0.08	26.19	22.62	35.28	4.17	136.0	1.49	1.16
139.0	8.46	8.50	8.51	8.49	8.49	8.41	0.10	26.51	22.61	35.32	4.18	139.0	1.51	1.16
140.0	8.47	8.50	8.54	8.52	8.48	8.43	0.11	26.61	22.60	35.36	4.37	140.0	1.51	1.16
144.0	8.50	8.52	8.56	8.54	8.51	8.46	0.10	27.00	22.53	35.50	4.39	144.0	1.53	1.17
146.0	8.50	8.54	8.57	8.56	8.53	8.47	0.10	27.15	22.49	35.56	4.55	146.0	1.53	1.17
150.0	8.52	8.55	8.59	8.58	8.54	8.48	0.12	27.29	22.35	35.67	4.63	150.0	1.55	1.18






¹ Total Loss = Insertion Loss+ 7.8dB Splitter Loss

REV. X2
ZB6CS-150-12W
100627
Page 1 of 1

6 Way-0° Power Splitter/Combiner


ZB6CS-150-12W

Typical Performance Curves



REV. X2
ZB6CS-150-12W
100627
Page 1 of 1

Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Z259	7.06 (179.32)	3.13 (79.50)	.88 (22.35)	.250 (6.35)	1.750 (44.45)	5.310 (134.87)	6.810 (172.97)	.250 (6.35)	2.875 (73.03)	.144 (3.66)	3.53 (89.66)	.44 (11.18)	1.31 (33.27)

CASE#	P	WT.GRAMS
Z259	.89 (22.61)	800

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish: For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.



Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 90° C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I