

Engineering Development Model

Power Splitter/Combiner

8 Way-0°

ZB8CS-ED13323/1

Important Note

This model has been designed, built and tested in our engineering department. Performance data represents model capability.
At present it is a non-catalog model. On request, we can supply a final specification sheet, part number and price/delivery information.

Please click "Back", and then click "Contact Us" for Applications support.



SMA version shown

CASE STYLE : Z41

ELECTRICAL SPECIFICATIONS 50Ω @ +25°C				
Parameter		Min.	Typ.	Max. Units
Frequency		2200		3100 MHz
Isolation	2200-3100 MHz		31	dB
Insertion Loss Above 9.0 dB	2200-3100 MHz		0.90	dB
Phase Unbalance	2200-3100 MHz		3.20	deg.
Amplitude Unbalance	2200-3100 MHz		0.20	dB
VSWR	SUM Port		1.17	(:1)
	OUT Ports		1.11	(:1)

MAXIMUM RATINGS	
Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

COAXIAL CONNECTIONS	
SUM PORT	S
PORT 1	1
PORT 2	2
PORT 3	3
PORT 4	4
PORT 5	5
PORT 6	6
PORT 7	7
PORT 8	8

Functional Diagram



P.O. Box 350188, Brooklyn, New York 11235-0000 (718) 934-4500 Fax (718) 332-4851 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINICIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS



REV. X1

ZB8CS-ED13323/1

12/16/2008

Page 1 of 1

8 Way-0° Power Splitter/Combiner

ZB8CS-ED13323/1

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)						AMP. UNBAL. (dB)	ISOLATION (dB)				PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2	S-3	S-4	S-6	S-8		1-2	1-8	3-4	6-7			S	1	8
2200.0	9.83	9.85	9.98	9.85	9.93	9.81	0.22	22.21	29.91	22.95	20.50	2.08	2200.0	1.28	1.03	1.04
2250.0	9.76	9.72	9.86	9.78	9.85	9.78	0.16	23.26	32.09	25.04	21.23	2.10	2250.0	1.22	1.05	1.02
2300.0	9.74	9.75	9.83	9.71	9.77	9.76	0.12	25.66	31.12	27.68	22.01	2.03	2300.0	1.20	1.08	1.00
2350.0	9.68	9.69	9.77	9.66	9.77	9.76	0.12	30.73	33.65	31.10	22.95	2.39	2350.0	1.19	1.10	1.01
2400.0	9.75	9.67	9.80	9.71	9.74	9.76	0.12	34.25	32.07	35.01	24.03	2.08	2400.0	1.17	1.11	1.03
2425.0	9.71	9.69	9.77	9.68	9.76	9.76	0.10	34.28	36.45	36.08	24.64	2.20	2425.0	1.16	1.12	1.04
2450.0	9.74	9.71	9.74	9.70	9.73	9.75	0.09	31.62	32.18	35.91	25.32	2.61	2450.0	1.15	1.12	1.04
2475.0	9.80	9.71	9.78	9.75	9.73	9.77	0.10	37.28	30.94	34.80	26.03	2.38	2475.0	1.15	1.13	1.05
2500.0	9.78	9.73	9.79	9.73	9.76	9.78	0.10	34.33	34.59	33.37	26.83	2.16	2500.0	1.15	1.13	1.06
2525.0	9.78	9.77	9.78	9.72	9.78	9.79	0.12	31.09	37.43	32.10	27.75	2.78	2525.0	1.14	1.13	1.07
2550.0	9.86	9.78	9.81	9.79	9.78	9.80	0.14	34.41	33.36	31.17	28.74	2.89	2550.0	1.14	1.13	1.07
2575.0	9.89	9.80	9.84	9.80	9.80	9.82	0.16	34.75	32.66	30.40	29.90	2.52	2575.0	1.14	1.13	1.09
2600.0	9.85	9.85	9.84	9.76	9.83	9.84	0.17	31.18	36.67	29.84	31.24	2.74	2600.0	1.14	1.12	1.10
2625.0	9.91	9.85	9.85	9.82	9.84	9.83	0.14	32.29	40.36	29.60	32.76	3.31	2625.0	1.14	1.12	1.10
2650.0	9.95	9.87	9.91	9.86	9.86	9.88	0.17	38.65	33.60	29.59	34.58	3.04	2650.0	1.13	1.12	1.11
2675.0	9.92	9.89	9.90	9.82	9.89	9.88	0.20	36.72	32.03	29.73	36.79	3.11	2675.0	1.11	1.11	1.12
2700.0	9.92	9.89	9.86	9.85	9.87	9.86	0.14	33.33	35.13	30.19	39.16	3.76	2700.0	1.10	1.11	1.13
2725.0	9.99	9.88	9.89	9.93	9.85	9.88	0.17	35.76	47.29	30.97	41.50	3.43	2725.0	1.10	1.11	1.13
2750.0	9.98	9.91	9.98	9.90	9.92	9.91	0.20	44.50	33.14	31.92	42.34	3.35	2750.0	1.10	1.11	1.14
2775.0	9.92	9.89	9.89	9.85	9.88	9.91	0.22	44.42	30.24	33.24	40.73	3.96	2775.0	1.10	1.10	1.14
2800.0	9.98	9.87	9.82	9.96	9.82	9.89	0.16	35.56	34.21	34.92	38.60	4.10	2800.0	1.09	1.09	1.14
2825.0	9.99	9.90	9.94	9.98	9.89	9.90	0.19	32.62	43.73	36.33	36.75	3.56	2825.0	1.11	1.09	1.14
2850.0	9.96	9.90	10.00	9.94	9.93	9.94	0.25	36.28	31.20	36.35	35.10	4.04	2850.0	1.15	1.08	1.14
2875.0	9.99	9.93	9.91	9.99	9.87	9.99	0.20	36.15	30.21	34.66	33.73	4.60	2875.0	1.19	1.08	1.13
2900.0	10.04	9.94	9.92	10.06	9.87	9.92	0.23	29.33	35.44	32.36	32.72	3.82	2900.0	1.21	1.08	1.13
2950.0	10.06	10.02	10.14	10.08	10.03	10.07	0.31	28.31	30.78	28.18	31.23	4.61	2950.0	1.24	1.09	1.12
3000.0	10.19	10.11	10.18	10.20	10.08	9.99	0.28	24.50	35.50	25.28	30.27	3.93	3000.0	1.29	1.11	1.12
3050.0	10.19	10.21	10.32	10.21	10.16	10.15	0.40	22.17	30.65	23.13	29.72	4.89	3050.0	1.28	1.16	1.15
3100.0	10.34	10.23	10.47	10.33	10.36	10.12	0.45	21.22	32.15	21.74	29.59	4.07	3100.0	1.29	1.22	1.20

¹Total Loss = Insertion Loss + 9dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS




REV. X2
ZB8CS-ED13323/1
9/16/2010
Page 1 of 1

Typical Performance Curves



Outline Dimensions



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
Z41	7.06 (179.32)	3.13 (79.50)	.88 (22.35)	.250 (6.35)	1.750 (44.45)	5.310 (134.87)	6.810 (172.97)	.250 (6.35)	2.875 (73.03)	.144 (3.66)	3.53 (89.66)	.44 (11.18)	.415 (10.54)

CASE#	P	WT.GRAMS
Z41	.89 (22.61)	800

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B