

2 Way-0° 50Ω 800 to 900 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.125W max.
DC Current	400 mA (200mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	
1.26	1.00	.70	.200	.200	.860	.125	
32.00	25.40	17.78	5.08	5.08	21.84	3.18	
H	J	K	L				wt
.35	.63	.38	.50				grams
8.89	16.00	9.65	12.70				24.0

Features

- low insertion loss, 0.1 dB typ.
- high isolation, 30 dB typ.
- up to 10W power input as splitter
- excellent amplitude unbalance, 0.1 dB typ.
- excellent phase unbalance, 0.2 deg. typ.
- rugged shielded case

Applications

- UHF
- cellular
- communication systems
- instrumentation



CASE STYLE: F183

Connectors	Model
SMA	ZC2PD-900-S




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 3.0 dB		PHASE UNBALANCE (Degrees)	AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	Max.	S		OUT	
							Typ.	Max.	Typ.	Max.
800-900	30	20	0.1	0.4	2	0.2	1.10	1.30	1.10	1.30


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
800.00	3.13	3.14	0.02	29.27	0.17	1.17	1.12	1.12
810.00	3.10	3.12	0.02	31.39	0.24	1.14	1.16	1.16
820.00	3.11	3.12	0.01	33.87	0.15	1.13	1.19	1.20
830.00	3.13	3.16	0.02	36.03	0.20	1.14	1.22	1.22
840.00	3.19	3.21	0.02	35.97	0.11	1.15	1.24	1.24
850.00	3.18	3.20	0.02	34.02	0.18	1.17	1.23	1.23
860.00	3.11	3.12	0.02	31.59	0.20	1.16	1.21	1.21
865.00	3.09	3.10	0.01	30.39	0.14	1.16	1.20	1.20
870.00	3.06	3.08	0.02	29.30	0.05	1.14	1.18	1.18
872.50	3.07	3.08	0.01	28.89	0.05	1.14	1.17	1.17
875.00	3.08	3.09	0.02	28.41	0.04	1.13	1.17	1.16
880.00	3.08	3.10	0.02	27.53	0.17	1.11	1.15	1.15
885.00	3.09	3.13	0.04	26.69	0.18	1.09	1.15	1.15
890.00	3.11	3.12	0.01	25.98	0.16	1.07	1.15	1.15
900.00	3.05	3.06	0.02	24.56	0.21	1.05	1.18	1.18

1. Total Loss = Insertion Loss + 3dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



2 Way-0° Power Splitter/Combiner

ZC2PD-900

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)		AMP. UNBAL. (dB)	ISOLATION (dB)	PHASE UNBAL. (deg.)	FREQ. (MHz)	VSWR (:1)		
	S-1	S-2					S	1	2
800.0	3.13	3.14	0.02	29.27	0.17	800.0	1.17	1.12	1.12
802.5	3.12	3.13	0.01	29.72	0.24	802.5	1.16	1.13	1.13
805.0	3.11	3.14	0.02	30.27	0.16	805.0	1.16	1.14	1.14
807.5	3.11	3.12	0.01	30.84	0.10	807.5	1.15	1.15	1.15
810.0	3.10	3.12	0.02	31.39	0.24	810.0	1.14	1.16	1.16
812.5	3.11	3.12	0.01	32.03	0.12	812.5	1.14	1.17	1.17
815.0	3.10	3.12	0.02	32.63	0.16	815.0	1.13	1.18	1.18
817.5	3.10	3.12	0.02	33.28	0.11	817.5	1.13	1.19	1.19
820.0	3.11	3.12	0.01	33.87	0.15	820.0	1.13	1.19	1.20
822.5	3.10	3.13	0.03	34.43	0.11	822.5	1.13	1.20	1.20
825.0	3.12	3.14	0.02	34.99	0.21	825.0	1.13	1.21	1.21
827.5	3.13	3.15	0.02	35.57	0.13	827.5	1.13	1.22	1.22
830.0	3.13	3.16	0.02	36.03	0.20	830.0	1.14	1.22	1.22
832.5	3.15	3.15	0.00	36.23	0.14	832.5	1.14	1.23	1.23
835.0	3.16	3.19	0.02	36.29	0.23	835.0	1.15	1.23	1.23
837.5	3.18	3.20	0.02	36.27	0.17	837.5	1.15	1.24	1.24
840.0	3.19	3.21	0.02	35.97	0.11	840.0	1.15	1.24	1.24
842.5	3.20	3.22	0.02	35.64	0.26	842.5	1.16	1.24	1.24
845.0	3.20	3.21	0.01	35.21	0.14	845.0	1.16	1.24	1.24
847.5	3.20	3.22	0.02	34.62	0.21	847.5	1.16	1.24	1.24
850.0	3.18	3.20	0.02	34.02	0.18	850.0	1.17	1.23	1.23
852.5	3.17	3.18	0.01	33.36	0.16	852.5	1.17	1.23	1.23
855.0	3.15	3.16	0.02	32.81	0.14	855.0	1.17	1.23	1.22
857.5	3.14	3.15	0.01	32.24	0.05	857.5	1.17	1.22	1.22
860.0	3.11	3.12	0.02	31.59	0.20	860.0	1.16	1.21	1.21
862.5	3.09	3.10	0.01	31.00	0.13	862.5	1.16	1.21	1.20
865.0	3.09	3.10	0.01	30.39	0.14	865.0	1.16	1.20	1.20
867.5	3.06	3.10	0.03	29.93	0.07	867.5	1.15	1.19	1.19
870.0	3.06	3.08	0.02	29.30	0.05	870.0	1.14	1.18	1.18
872.5	3.07	3.08	0.01	28.89	0.05	872.5	1.14	1.17	1.17
875.0	3.08	3.09	0.02	28.41	0.04	875.0	1.13	1.17	1.16
877.5	3.08	3.09	0.01	27.99	0.21	877.5	1.12	1.16	1.16
880.0	3.08	3.10	0.02	27.53	0.17	880.0	1.11	1.15	1.15
882.5	3.11	3.12	0.01	27.10	0.16	882.5	1.10	1.15	1.15
885.0	3.09	3.13	0.04	26.69	0.18	885.0	1.09	1.15	1.15
887.5	3.12	3.13	0.01	26.33	0.18	887.5	1.08	1.15	1.15
890.0	3.11	3.12	0.01	25.98	0.16	890.0	1.07	1.15	1.15
892.5	3.10	3.11	0.01	25.59	0.21	892.5	1.06	1.16	1.16
895.0	3.08	3.11	0.03	25.22	0.11	895.0	1.05	1.16	1.16
897.5	3.07	3.08	0.02	24.92	0.19	897.5	1.05	1.17	1.17
900.0	3.05	3.06	0.02	24.56	0.21	900.0	1.05	1.18	1.18






¹ Total Loss = Insertion Loss+ 3dB Splitter Loss

REV. X2
ZC2PD-900
100627
Page 1 of 1

2 Way-0° Power Splitter/Combiner


ZC2PD-900

Typical Performance Curves



Outline Dimensions

F183



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
F183	1.26 (32.00)	1.00 (25.40)	.70 (17.78)	.20 (5.08)	.200 (5.08)	.860 (21.84)	.125 (3.18)	.35 (8.89)	.63 (16.00)	.38 (9.65)	.50 (12.70)	24.0

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I