

DC Pass, High Power

Dual-Directional Coupler

ZDDC-50-521+

50Ω 50dB Coupling 400W* 20 to 520 MHz

The Big Deal

- High power handling, up to 400W
- Low insertion loss, 0.1 dB Typ
- Excellent return loss, 28 dB Typ (In/Out)
- High directivity, 26 dB Typ
- Water resistant, IP67



CASE STYLE: RC2504

Product Overview

Mini-Circuits ZDDC-50-521+ is a coaxial high-power (400W) wide band (20-520 MHz) dual-directional coupler which features low insertion loss (0.1 dB), 50 dB coupling and excellent mainline return loss (28 dB). The Dual directional design allows monitoring forward and reverse power and guarantees good directivity, flatness and coupling accuracy.

The ZDDC-50-521+ supports a wide variety of applications from military to commercial, including GSM transmitters and more. The coupler is constructed in a rugged, compact metal case (3.0 x 2.154 x 0.975") and is splash and water resistant, meeting IP67 immersion standard.

Key Features

Feature	Advantages
High power handling: 400W @ +85°C 300W @ +105°C	Usable in many systems with high-power requirements such as antenna feeds, power amplifiers, and others that require sampling a high power RF signal.
Low mainline loss, 0.1 dB typ.	Used primarily in high power transmission applications, the excellent through-path signal loss maximizes the power transmitted to the antenna.
Excellent return loss, 28 dB typ. (input and output)	Provides excellent matching for 50Ω systems.
High directivity, 26 dB typ	High directivity with 50 dB coupling allows accurate signal sampling through the coupled port with minimal measurement error.
DC current passing up to 4 A	Suitable for use in systems requiring DC voltage on the RF line, such as supplying bias to antenna circuitry via the antenna cable.
Meets IP67 immersion standard	Model can handle immersion in water of up to 1m (3.3 ft) for up to 30 minutes.

*See power derating on page 2



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

DC Pass, High Power

Dual-Directional Coupler

50Ω 50dB Coupling 400W* 20 to 520 MHz

ZDDC-50-521+

Maximum Ratings

Operating Temperature, case**	-55°C to 105°C
Storage Temperature	-55°C to 105°C
Main line DC Current	4A
Main line Power Input*	400W @ +85°C, case

*Derate to 350W at +95°C and 300W at +105°C case temperature
**Case temperature is defined as temperature on base plate.
Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections***

INPUT	4 (N-Type)
OUTPUT	2 (N-Type)
COUPLED FORWARD	1 (SMA)
COUPLED REVERSE	3 (SMA)


***Model is Dual-directional input and output are interchangeable.

Features

- high power, up to 400W
- low insertion loss, 0.1 dB Typ.
- excellent in/out return loss, 28 dB typ
- high directivity, 26 dB Typ.
- DC current pass through input to output
- Water resistant, IP67 standard

Applications

- GSM
- Research and Development Labs
- Defense and Military



CASE STYLE: RC2504


+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications @ +25°C


Parameter	Condition (MHz)	Min.	Typ.	Max.	Units
Frequency Range		20		520	MHz
Insertion Loss	20 - 150	—	0.05	0.1	dB
	150 - 520	—	0.10	0.25	
Coupling	20 - 520	—	50±1	—	dB
Coupling Flatness	20 - 520	—	±0.95	—	dB
Directivity	20 - 150	20	23	—	dB
	150 - 520	20	26	—	
Return Loss (Input)	20 - 150	30	38	—	dB
	150 - 520	22	28	—	
Return Loss (Output)	20 - 150	30	38	—	dB
	150 - 520	22	28	—	
Return Loss (Coupling)	20 - 150	—	8	—	dB
	150 - 520	10	14	—	
Input RF Power (Main line)	20 - 520	@ +85°C, Case	—	400	W
		@ +95°C, Case	—	350	
		@ +105°C, Case	—	300	
Thermal Resistance	20 - 520	—	0.2	—	°C/W

Outline Drawing



Case material - Aluminum alloy.


Case finish - Nickel Plate.



Outline Dimensions (inch mm)

A	B	C	D	E	F	G	H	J	K	L	M	N	wt.
3.000	2.154	.975	.525	1.500	2.780	.750	1.390	.125	.125	1.425	.713	2.500	grams
76.20	54.71	24.76	13.33	38.10	70.61	19.05	35.31	3.18	3.18	36.19	18.11	63.50	230

Electrical Schematic



www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com


REV. OR
M165796
EDR-11613
ZDDC-50-521+
RAV
180305
Page 2 of 3

Typical Performance Data *


FREQUENCY (MHz)	Insertion Loss (dB)			Coupling (dB)		Directivity (dB)						Return Loss (dB)			
	In - Out			In - Cpl Fwd	Out - Cpl Rev	In - Cpl Rev			Out - Cpl Fwd			In	Out	Cpl Fwd	Cpl Rev
	-55°C	+25°C	+105°C			-55°C	+25°C	+105°C	-55°C	+25°C	+105°C				
20.0	0.00	0.00	0.00	51.18	51.21	23.54	23.31	23.16	23.33	22.95	23.02	54.35	52.93	7.50	7.48
55.0	0.00	0.01	0.01	50.34	50.41	23.70	23.17	22.94	23.91	22.92	22.91	44.66	43.56	7.95	8.00
90.0	0.01	0.02	0.01	50.99	51.03	24.17	23.52	22.88	24.73	23.51	22.86	40.07	40.22	10.19	10.30
125.0	0.01	0.02	0.02	51.03	51.05	25.03	23.66	22.84	25.44	23.83	22.88	37.47	38.05	11.69	11.85
160.0	0.01	0.03	0.02	50.86	50.85	25.79	24.30	23.07	26.23	24.06	23.17	35.30	35.38	12.66	12.86
195.0	0.02	0.04	0.03	50.68	50.66	26.87	25.60	23.83	26.80	24.90	24.21	33.90	33.60	13.31	13.55
230.0	0.03	0.04	0.04	50.56	50.53	26.22	26.09	23.93	26.77	25.69	25.15	33.18	33.03	13.79	14.06
265.0	0.03	0.05	0.05	50.56	50.49	26.43	26.95	24.54	26.57	25.50	25.31	32.06	32.01	14.14	14.43
300.0	0.04	0.06	0.06	50.63	50.57	27.23	28.93	26.49	29.37	27.94	28.96	30.82	30.90	14.42	14.72
335.0	0.05	0.07	0.07	50.77	50.71	27.06	29.87	27.29	28.59	26.88	30.18	30.35	30.42	14.66	14.97
370.0	0.06	0.08	0.08	50.99	50.90	27.91	31.72	28.88	30.78	28.86	31.97	29.85	29.70	14.89	15.21
405.0	0.06	0.09	0.09	51.22	51.15	30.46	37.69	32.75	37.77	31.54	51.03	28.95	28.59	15.08	15.42
440.0	0.08	0.10	0.10	51.45	51.39	29.85	38.06	33.74	34.80	29.69	43.04	28.50	28.27	15.29	15.65
475.0	0.09	0.12	0.11	51.67	51.62	30.92	36.58	35.19	39.12	31.37	36.40	28.20	28.35	15.47	15.84
520.0	0.10	0.13	0.12	51.82	51.81	28.43	28.57	29.21	28.91	26.68	28.33	27.71	27.60	15.71	16.09
545.0	0.11	0.14	0.14	51.78	51.81	26.94	26.62	27.45	26.72	25.18	26.52	27.81	27.17	15.87	16.25
580.0	0.13	0.16	0.15	51.61	51.67	25.23	23.91	25.15	24.07	23.06	24.07	27.83	27.07	16.06	16.43
615.0	0.14	0.17	0.16	51.28	51.37	22.80	21.69	22.48	22.48	21.93	22.69	27.34	27.06	16.25	16.63
650.0	0.15	0.19	0.18	50.73	50.88	22.10	21.09	21.54	20.49	20.15	20.86	27.34	27.01	16.48	16.85
685.0	0.16	0.20	0.19	50.04	50.19	20.61	19.53	20.34	20.13	19.92	20.68	27.95	27.20	16.72	17.05
720.0	0.17	0.21	0.20	49.21	49.40	19.59	18.84	19.38	19.05	19.23	19.67	27.95	27.33	16.93	17.25

* Data at +25°C unless specified otherwise.


ZDDC-50-521+
Insertion Loss (dB)




ZDDC-50-521+
Coupling (dB)



ZDDC-50-521+
Directivity (dB)



ZDDC-50-521+
Return Loss (dB)



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Dual-Directional Coupler

ZDDC-50-521+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =+5 dBm @Temperature = -55°C

FREQ. (MHz)	INSERTION LOSS (dB) In - Out	COUPLING (dB)		DIRECTIVITY (dB) In - Rev	RETURN LOSS (dB)			
		In - Fwd	Out - Rev		In	Out	Rev	Fwd
10	0.00	55.20	55.24	23.39	50.50	49.67	11.19	11.21
20	0.00	51.10	51.15	23.33	45.16	44.08	7.40	7.42
30	0.00	50.04	50.09	23.52	42.33	41.11	6.61	6.63
50	0.00	50.21	50.30	23.68	39.48	38.40	7.49	7.55
75	0.01	50.82	50.88	24.37	38.12	37.55	9.23	9.29
100	0.01	51.04	51.09	24.89	37.88	37.78	10.68	10.72
125	0.01	51.02	51.05	25.44	38.94	38.68	11.85	11.84
150	0.01	50.90	50.91	25.78	42.27	40.86	12.78	12.72
175	0.01	50.75	50.75	26.36	50.43	43.05	13.53	13.41
200	0.02	50.64	50.60	27.01	57.32	42.03	14.04	13.93
225	0.02	50.56	50.53	26.99	56.80	40.02	14.34	14.28
250	0.03	50.52	50.48	26.65	49.42	38.24	14.52	14.52
275	0.03	50.53	50.51	27.37	44.97	36.91	14.69	14.71
300	0.04	50.60	50.55	29.37	41.26	35.68	14.81	14.83
325	0.04	50.70	50.64	29.28	37.10	33.77	14.88	14.90
350	0.05	50.85	50.78	29.03	34.02	31.64	14.94	14.94
375	0.06	50.99	50.94	31.91	32.23	30.05	15.05	15.04
400	0.06	51.17	51.10	37.80	31.04	28.94	15.19	15.14
425	0.07	51.33	51.27	35.01	29.62	28.00	15.31	15.24
450	0.08	51.52	51.46	37.05	28.08	27.12	15.38	15.30
475	0.09	51.65	51.61	39.12	27.00	26.37	15.50	15.40
500	0.10	51.74	51.75	31.24	26.40	25.83	15.69	15.51
520	0.10	51.79	51.81	28.91	26.06	25.42	15.83	15.57
550	0.11	51.78	51.81	26.37	25.40	24.87	16.01	15.61
575	0.13	51.65	51.72	24.24	24.93	24.53	16.19	15.68
600	0.13	51.44	51.57	23.27	24.86	24.42	16.42	15.81
625	0.14	51.13	51.30	21.75	25.07	24.54	16.64	15.95
650	0.15	50.73	50.89	20.49	25.45	24.78	16.81	16.05
675	0.16	50.25	50.45	20.14	25.91	25.09	16.99	16.19
700	0.16	49.70	49.93	19.82	26.49	25.40	17.24	16.40
725	0.17	49.09	49.34	18.98	27.05	25.63	17.50	16.62
750	0.18	48.47	48.69	18.79	27.38	25.87	17.74	16.77
775	0.19	47.83	48.05	19.09	27.83	26.35	17.98	16.88
800	0.20	47.15	47.41	18.77	28.67	27.13	18.29	17.03
825	0.20	46.48	46.74	18.12	29.84	28.16	18.61	17.19
850	0.21	45.84	46.04	18.82	30.82	29.20	18.90	17.30
875	0.22	45.18	45.39	19.31	31.65	30.34	19.15	17.37
900	0.23	44.54	44.77	18.15	32.70	31.89	19.46	17.45
925	0.24	43.90	44.14	17.94	34.35	33.48	19.77	17.55
950	0.25	43.29	43.50	18.93	36.11	34.62	20.06	17.64
975	0.25	42.70	42.89	18.92	37.78	35.48	20.35	17.71
1000	0.26	42.13	42.32	17.95	39.96	36.52	20.66	17.79
1025	0.27	41.53	41.76	17.81	42.91	36.28	21.04	17.88
1050	0.28	40.98	41.18	18.55	45.63	34.31	21.43	17.95
1100	0.29	39.96	40.13	18.37	46.48	31.72	22.32	18.09
1150	0.31	38.93	39.12	17.57	41.91	29.71	23.38	18.08
1200	0.33	38.05	38.19	18.35	38.26	27.92	24.76	18.14
1250	0.34	37.11	37.30	16.52	34.29	26.78	26.41	18.22
1300	0.37	36.38	36.48	17.62	31.05	25.46	28.62	18.34
1350	0.37	35.50	35.69	15.48	28.50	24.72	30.87	18.43
1400	0.40	34.88	34.99	16.86	26.77	23.82	29.00	18.56
1450	0.39	34.07	34.29	14.07	25.58	23.05	24.28	18.72
1500	0.43	33.51	33.71	15.99	24.31	22.31	19.35	18.79
1550	0.41	32.75	33.08	12.90	23.81	21.89	14.90	18.81

Dual-Directional Coupler

ZDDC-50-521+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =+5 dBm @Temperature = +25°C

FREQ. (MHz)	INSERTION LOSS	COUPLING		DIRECTIVITY	RETURN LOSS			
	(dB)	(dB)		(dB)	(dB)			
	In - Out	In - Fwd	Out - Rev	In - Rev	In	Out	Rev	Fwd
10	0.00	55.30	55.35	23.16	60.78	59.28	11.22	11.25
20	0.00	51.18	51.23	22.95	54.35	52.93	7.48	7.50
30	0.01	50.07	50.13	23.14	50.43	49.01	6.70	6.70
50	0.01	50.22	50.28	23.01	45.58	44.32	7.64	7.59
75	0.01	50.80	50.86	23.48	41.70	41.33	9.41	9.33
100	0.02	51.03	51.09	23.67	39.24	39.67	10.81	10.69
125	0.02	51.03	51.03	23.83	37.47	38.05	11.85	11.69
150	0.03	50.91	50.93	24.05	35.87	36.08	12.60	12.42
175	0.03	50.77	50.77	24.27	34.59	34.43	13.19	12.97
200	0.04	50.65	50.62	25.18	33.79	33.48	13.63	13.39
225	0.04	50.58	50.52	25.62	33.30	33.11	14.00	13.72
250	0.05	50.54	50.51	25.11	32.62	32.55	14.28	14.00
275	0.06	50.56	50.49	26.15	31.66	31.65	14.52	14.23
300	0.06	50.63	50.55	27.94	30.82	30.90	14.72	14.42
325	0.07	50.72	50.64	27.71	30.40	30.54	14.90	14.59
350	0.08	50.86	50.77	27.16	30.18	30.24	15.08	14.77
375	0.09	51.01	50.93	29.23	29.73	29.55	15.23	14.92
400	0.09	51.19	51.10	31.67	29.08	28.73	15.39	15.06
425	0.10	51.35	51.27	29.97	28.66	28.26	15.55	15.19
450	0.11	51.54	51.45	29.78	28.46	28.30	15.70	15.33
475	0.12	51.67	51.61	31.37	28.20	28.35	15.84	15.47
500	0.13	51.77	51.74	28.40	27.87	28.03	15.98	15.60
520	0.13	51.82	51.77	26.68	27.71	27.60	16.09	15.71
550	0.14	51.78	51.79	25.14	27.82	27.13	16.27	15.90
575	0.16	51.67	51.72	23.42	27.87	27.05	16.41	16.04
600	0.16	51.44	51.56	22.64	27.56	27.07	16.55	16.17
625	0.17	51.11	51.25	21.45	27.25	27.01	16.69	16.32
650	0.19	50.73	50.85	20.15	27.34	27.01	16.85	16.48
675	0.19	50.25	50.40	19.85	27.82	27.14	17.00	16.65
700	0.20	49.69	49.89	19.82	28.06	27.28	17.14	16.81
725	0.22	49.09	49.30	19.17	27.87	27.35	17.28	16.97
750	0.23	48.45	48.65	18.69	27.66	27.38	17.43	17.16
775	0.24	47.82	48.01	19.12	27.97	27.57	17.58	17.35
800	0.24	47.16	47.37	19.06	28.63	28.02	17.72	17.53
825	0.26	46.47	46.71	18.46	29.23	28.54	17.85	17.72
850	0.27	45.84	46.02	18.75	29.55	28.94	18.00	17.94
875	0.28	45.19	45.36	19.77	29.94	29.34	18.12	18.16
900	0.28	44.55	44.75	19.26	30.65	29.94	18.25	18.37
925	0.29	43.92	44.12	18.79	31.62	30.90	18.38	18.58
950	0.31	43.32	43.49	19.85	32.64	32.00	18.50	18.84
975	0.32	42.73	42.88	20.95	33.80	32.85	18.62	19.13
1000	0.32	42.16	42.31	20.52	35.36	33.56	18.71	19.38
1025	0.33	41.59	41.76	20.25	37.53	34.54	18.81	19.63
1050	0.34	41.05	41.18	20.88	39.95	35.43	18.90	19.90
1100	0.36	40.03	40.13	24.29	43.44	34.22	19.04	20.57
1150	0.38	39.03	39.14	22.31	39.20	33.35	19.16	21.25
1200	0.40	38.16	38.20	33.38	35.45	30.24	19.21	21.99
1250	0.41	37.27	37.34	24.92	32.11	28.38	19.26	22.79
1300	0.43	36.55	36.49	34.00	29.31	26.55	19.26	23.50
1350	0.44	35.75	35.75	33.73	27.62	25.08	19.25	23.94
1400	0.47	35.20	35.00	23.82	25.80	24.22	19.17	23.64
1450	0.47	34.50	34.35	23.99	24.95	23.05	19.10	22.24
1500	0.49	34.06	33.69	17.84	24.17	22.54	19.00	19.97
1550	0.48	33.40	33.10	15.06	23.47	21.55	18.90	17.18

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Dual-Directional Coupler

ZDDC-50-521+

Typical Performance Data

TEST CONDITIONS: INPUT POWER =+5 dBm @Temperature = +105°C

FREQ. (MHz)	INSERTION LOSS (dB) In - Out	COUPLING (dB)		DIRECTIVITY (dB) In - Rev	RETURN LOSS (dB)			
		In - Fwd	Out - Rev		In	Out	Rev	Fwd
10	0.00	55.43	55.47	22.94	69.86	68.71	11.21	11.23
20	0.00	51.25	51.29	23.02	62.39	62.03	7.54	7.56
30	0.01	50.08	50.12	23.16	58.51	57.24	6.76	6.76
50	0.01	50.16	50.23	22.99	54.95	51.52	7.70	7.70
75	0.01	50.75	50.80	22.87	66.09	48.19	9.50	9.51
100	0.01	50.98	51.02	22.64	48.01	44.31	10.85	10.90
125	0.02	50.96	51.01	22.88	39.56	38.81	11.78	11.87
150	0.02	50.87	50.89	23.06	35.31	34.76	12.41	12.54
175	0.03	50.74	50.75	23.44	32.97	32.16	12.90	13.02
200	0.03	50.63	50.60	24.11	31.11	30.25	13.26	13.35
225	0.04	50.56	50.52	25.07	29.45	28.81	13.56	13.62
250	0.05	50.51	50.49	25.24	28.28	27.82	13.81	13.86
275	0.06	50.55	50.50	26.04	27.67	27.27	14.09	14.10
300	0.06	50.60	50.55	28.96	27.37	26.99	14.35	14.31
325	0.07	50.68	50.63	30.36	27.12	26.67	14.56	14.50
350	0.07	50.82	50.77	30.24	26.98	26.32	14.75	14.67
375	0.08	50.97	50.93	32.33	27.03	26.07	14.94	14.86
400	0.09	51.12	51.08	42.14	27.13	25.97	15.13	15.03
425	0.09	51.29	51.25	43.64	27.08	25.95	15.31	15.19
450	0.10	51.47	51.42	46.40	26.86	25.92	15.46	15.32
475	0.11	51.58	51.58	36.40	26.69	25.85	15.60	15.47
500	0.12	51.67	51.70	30.20	26.71	25.80	15.76	15.61
520	0.12	51.71	51.75	28.33	26.80	25.71	15.89	15.71
550	0.14	51.68	51.73	26.14	26.80	25.62	16.10	15.82
575	0.15	51.53	51.65	24.30	26.65	25.59	16.26	15.93
600	0.16	51.31	51.47	23.34	26.60	25.58	16.45	16.07
625	0.17	50.99	51.18	22.12	26.70	25.70	16.64	16.20
650	0.18	50.57	50.77	20.86	26.98	25.95	16.85	16.31
675	0.19	50.10	50.31	20.66	27.36	26.33	17.05	16.42
700	0.19	49.55	49.80	20.35	27.74	26.67	17.26	16.57
725	0.20	48.94	49.20	19.41	28.03	26.84	17.49	16.73
750	0.21	48.31	48.55	19.25	28.27	27.01	17.73	16.85
775	0.22	47.67	47.90	19.59	28.72	27.46	17.96	16.94
800	0.23	47.01	47.26	19.22	29.49	28.22	18.21	17.06
825	0.24	46.34	46.59	18.46	30.44	29.10	18.46	17.22
850	0.25	45.70	45.91	19.01	31.26	29.86	18.71	17.37
875	0.26	45.04	45.26	19.62	31.99	30.75	18.96	17.49
900	0.26	44.41	44.63	18.62	32.80	31.98	19.26	17.59
925	0.27	43.77	44.02	18.25	33.98	33.24	19.56	17.70
950	0.29	43.16	43.37	19.30	35.35	34.21	19.86	17.82
975	0.29	42.58	42.77	19.47	37.13	35.18	20.15	17.94
1000	0.30	42.01	42.20	18.47	39.35	36.65	20.47	18.01
1025	0.31	41.43	41.65	18.18	42.16	37.50	20.81	18.09
1050	0.32	40.88	41.07	18.81	45.95	36.27	21.17	18.20
1100	0.34	39.87	40.04	18.83	46.29	34.22	21.94	18.44
1150	0.35	38.84	39.03	17.72	38.40	31.79	22.82	18.54
1200	0.38	37.97	38.10	18.94	35.15	29.31	23.83	18.72
1250	0.38	37.04	37.22	16.51	32.48	27.53	24.90	18.86
1300	0.41	36.30	36.41	18.29	30.21	25.78	25.81	18.97
1350	0.42	35.44	35.63	15.52	28.43	24.92	26.08	19.02
1400	0.44	34.81	34.94	17.43	27.17	23.95	24.51	19.08
1450	0.44	34.02	34.24	14.20	26.34	23.26	21.41	19.21
1500	0.46	33.45	33.66	16.33	25.14	22.55	17.64	19.23
1550	0.45	32.72	33.04	13.00	24.69	22.14	13.77	19.20

Notes


- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp



Dual-Directional Coupler

ZDDC-50-521+

Typical Performance Curves




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Dual-Directional Coupler

ZDDC-50-521+

Typical Performance Curves




Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCStore/terms.jsp

Case Style

RC

Outline Dimensions

RC2504



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT. GRAMS
RC2504	3.000 (76.20)	2.154 (54.71)	.975 (24.76)	.525 (13.33)	1.500 (38.10)	2.780 (70.61)	.750 (19.05)	1.390 (35.31)	.125 (3.18)	.125 (3.18)	1.425 (36.19)	.713 (18.11)	2.500 (63.50)	230

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Aluminum alloy.
- Case finish: Nickel Plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105° C Case Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 240 hours, 50°C	MIL-STD-202, Method 103, Condition A, Except 50°C and end-point electrical test done within 12 hours
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Solder Reflow Heat	Sn-Pb Eutectic Process 225°C peak Pb-Free Process 245° - 250°C peak	J-STD-020C, Table 4-1, 4-2 and 5-2, Figure 5-1
Solderability	10X Magnification	J-STD-002, Para 4.2.5, Test S, 95% Coverage
Vibration (high Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-883, Method 2007.3, Condition A
Mechanical Shock	50g, 11 ms, 1/2-sine, 18 shocks: 3 each direction, each of 3 axes	MIL-STD-202, Method 213, Condition A
Marking Resistance to Solvents	Isopropyl alcohol + mineral spirits at 25°C; terpene defluxer at 25°C; distilled water + proylene glycol monomethyl ether + monoethanolamine at 63°C to 70°C	MIL-STD-202, Method 215