

Power Splitter/Combiner

ZC6PD-1900W-S+

6 Way-0° 50Ω 1500 to 2000 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	10W max.
Internal Dissipation	0.875W max.
DC Current	1.8A(300mA for each port)
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	S
PORT 1,2,3,4,5,6	1,2,3,4,5,6

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F
4.76	3.00	.53	.150	4.610	1.500
120.90	76.20	13.46	3.81	117.09	38.10
G	H	J	K	L	wt
.125	.50	.25	1.13	.50	grams
3.18	12.70	6.35	28.70	12.70	155

Features

- low insertion loss, 0.5 dB typ.
- high isolation, 30 dB typ.
- up to 10W power input as splitters
- rugged shielded case

Applications

- GPS
- PCS
- communication systems
- instrumentation



Generic photo used for illustration purposes only

CASE STYLE: AB185

Connectors Model

SMA ZC6PD-1900W-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications




Electrical Specifications

FREQ. RANGE (MHz)	ISOLATION (dB)		INSERTION LOSS (dB) ABOVE 7.8 dB		AMPLITUDE UNBALANCE (dB)	VSWR (:1)			
f_L - f_U	Typ.	Min.	Typ.	Max.	Max.	S		OUT	
						Typ.	Max.	Typ.	Max.
1500-2000	30	15	0.5	1.0	0.6	1.1	1.68	1.1	1.5


Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)			Amplitude Unbalance (dB)	Isolation (dB)			VSWR S	VSWR 1	VSWR 3
	S-1	S-2	S-3		1-2	1-3	1-6			
1500.00	8.30	8.46	8.31	0.21	20.94	28.46	29.86	1.43	1.16	1.14
1520.00	8.36	8.66	8.39	0.35	21.38	31.08	30.12	1.42	1.16	1.13
1550.00	8.20	8.50	8.33	0.37	22.11	33.34	30.54	1.38	1.16	1.14
1580.00	8.22	8.40	8.36	0.36	23.06	36.14	31.15	1.34	1.16	1.16
1620.00	8.27	8.39	8.34	0.18	24.03	37.71	31.91	1.28	1.17	1.17
1680.00	8.24	8.33	8.26	0.11	25.71	31.69	33.60	1.29	1.18	1.17
1740.00	8.13	8.21	8.20	0.18	28.12	31.33	36.26	1.20	1.18	1.18
1800.00	8.16	8.26	8.11	0.17	31.45	28.35	41.05	1.11	1.18	1.18
1830.00	8.14	8.22	8.14	0.11	32.22	26.76	44.85	1.09	1.18	1.18
1860.00	8.19	8.26	8.11	0.17	34.45	25.19	50.00	1.12	1.18	1.18
1890.00	8.25	8.26	8.05	0.24	36.88	23.95	51.21	1.18	1.18	1.18
1910.00	8.31	8.32	8.14	0.23	38.07	23.29	44.96	1.24	1.18	1.18
1930.00	8.32	8.37	8.19	0.21	38.09	22.88	40.44	1.33	1.19	1.18
1960.00	8.32	8.43	8.18	0.30	36.29	22.57	36.99	1.36	1.19	1.19
2000.00	8.42	8.47	8.28	0.24	33.63	20.59	34.49	1.44	1.22	1.20

1. Total Loss = Insertion Loss + 7.8dB splitter loss.



electrical schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp



6 Way-0° Power Splitter/Combiner

ZC6PD-1900W+

Typical Performance Data

FREQ. (MHz)	TOTAL LOSS ¹ (dB)			AMP. UNBAL. (dB)	ISOLATION (dB)			FREQ. (MHz)	VSWR (:1)		
	S-1	S-3	S-5		1-2	1-3	1-6		S	1	3
1500.0	8.30	8.46	8.31	0.21	20.94	28.46	29.86	1500.0	1.43	1.16	1.14
1510.0	8.33	8.55	8.35	0.27	21.17	30.00	30.02	1510.0	1.43	1.16	1.13
1520.0	8.36	8.66	8.39	0.35	21.38	31.08	30.12	1520.0	1.42	1.16	1.13
1530.0	8.35	8.71	8.43	0.47	21.58	31.86	30.25	1530.0	1.41	1.16	1.12
1540.0	8.29	8.66	8.40	0.56	21.78	32.57	30.40	1540.0	1.40	1.16	1.12
1550.0	8.20	8.50	8.33	0.37	22.11	33.34	30.54	1550.0	1.38	1.16	1.14
1560.0	8.11	8.37	8.28	0.44	22.45	34.19	30.72	1560.0	1.37	1.16	1.15
1570.0	8.09	8.34	8.28	0.49	22.77	35.15	30.92	1570.0	1.36	1.16	1.16
1580.0	8.22	8.40	8.36	0.36	23.06	36.14	31.15	1580.0	1.34	1.16	1.16
1590.0	8.33	8.46	8.42	0.27	23.32	36.83	31.35	1590.0	1.33	1.17	1.16
1600.0	8.37	8.48	8.44	0.22	23.56	37.40	31.53	1600.0	1.32	1.17	1.16
1620.0	8.27	8.39	8.34	0.18	24.03	37.71	31.91	1620.0	1.28	1.17	1.17
1640.0	8.16	8.26	8.24	0.18	24.54	36.90	32.33	1640.0	1.24	1.17	1.17
1660.0	8.15	8.24	8.21	0.16	25.11	34.88	32.93	1660.0	1.21	1.18	1.17
1680.0	8.24	8.33	8.26	0.11	25.71	31.69	33.60	1680.0	1.29	1.18	1.17
1700.0	8.22	8.32	8.24	0.11	26.38	28.60	34.38	1700.0	1.26	1.18	1.18
1720.0	8.14	8.23	8.19	0.13	27.11	30.50	35.23	1720.0	1.24	1.18	1.18
1740.0	8.13	8.21	8.20	0.18	28.12	31.33	36.26	1740.0	1.20	1.18	1.18
1760.0	8.12	8.21	8.14	0.13	29.39	30.55	37.52	1760.0	1.17	1.18	1.18
1780.0	8.11	8.21	8.08	0.15	30.98	29.48	39.10	1780.0	1.14	1.18	1.18
1800.0	8.16	8.26	8.11	0.17	31.45	28.35	41.05	1800.0	1.11	1.18	1.18
1810.0	8.16	8.25	8.13	0.15	31.17	27.78	42.26	1810.0	1.10	1.18	1.18
1820.0	8.16	8.25	8.15	0.12	31.54	27.24	43.45	1820.0	1.09	1.18	1.18
1830.0	8.14	8.22	8.14	0.11	32.22	26.76	44.85	1830.0	1.09	1.18	1.18
1840.0	8.13	8.22	8.14	0.11	32.93	26.20	46.53	1840.0	1.10	1.18	1.18
1850.0	8.14	8.23	8.13	0.13	33.67	25.63	48.17	1850.0	1.10	1.18	1.18
1860.0	8.19	8.26	8.11	0.17	34.45	25.19	50.00	1860.0	1.12	1.18	1.18
1870.0	8.19	8.25	8.07	0.20	35.27	24.73	51.71	1870.0	1.14	1.18	1.18
1880.0	8.21	8.25	8.04	0.23	36.07	24.32	52.67	1880.0	1.16	1.18	1.18
1890.0	8.25	8.26	8.05	0.24	36.88	23.95	51.21	1890.0	1.18	1.18	1.18
1900.0	8.31	8.30	8.10	0.23	37.60	23.60	48.16	1900.0	1.20	1.18	1.18
1910.0	8.31	8.32	8.14	0.23	38.07	23.29	44.96	1910.0	1.24	1.18	1.18
1920.0	8.30	8.34	8.16	0.22	38.25	23.02	42.32	1920.0	1.28	1.18	1.18
1930.0	8.32	8.37	8.19	0.21	38.09	22.88	40.44	1930.0	1.33	1.19	1.18
1940.0	8.34	8.42	8.22	0.24	37.58	23.30	39.02	1940.0	1.36	1.19	1.18
1950.0	8.35	8.45	8.23	0.28	36.95	23.58	37.96	1950.0	1.36	1.19	1.18
1960.0	8.32	8.43	8.18	0.30	36.29	22.57	36.99	1960.0	1.36	1.19	1.19
1970.0	8.25	8.33	8.12	0.29	35.53	21.66	36.25	1970.0	1.38	1.19	1.19
1980.0	8.25	8.31	8.12	0.25	34.83	21.18	35.59	1980.0	1.40	1.20	1.19
1990.0	8.34	8.39	8.21	0.24	34.22	20.86	35.00	1990.0	1.42	1.21	1.19
2000.0	8.42	8.47	8.28	0.24	33.63	20.59	34.49	2000.0	1.44	1.22	1.20





¹ Total Loss = Insertion Loss+ 7.8dB Splitter Loss

REV. X2
ZC6PD-1900W+
100627
Page 1 of 1

6 Way-0° Power Splitter/Combiner


ZC6PD-1900W+

Typical Performance Curves



REV. X2
ZC6PD-1900W+
100627
Page 1 of 1

Outline Dimensions



CASE #	A	B	C	D	E	F	G	H	J	K	L	WT. GRAM
AB185	4.76 (120.90)	3.00 (76.20)	.53 (13.46)	.150 (3.81)	4.610 (117.09)	1.500 (38.10)	.125 (3.18)	.50 (12.70)	.25 (6.35)	1.13 (28.70)	.50 (12.70)	155

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:

For RoHS Case Styles:

Clear chemical conversion coating, non-chrome or trivalent chrome based.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I