

Coaxial

Power Splitter/Combiner

ZESC-2-11+

2 Way-0° 50Ω 10 to 2000 MHz


Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C
Power Input (as a splitter)	1W max.
Internal Dissipation	0.125W max.
Permanent damage may occur if any of these limits are exceeded.	

Coaxial Connections

SUM PORT	3
PORT 1	1
PORT 2	2

Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G
.83	.83	.75	.37	.42	1.25	.10
21.08	21.08	19.05	9.40	10.67	31.75	2.54
H	J	K	L	M	N	wt
1.050	.10	.640	.21	.106	.06	grams
26.67	2.54	16.26	5.33	2.69	1.52	22.0

Features

- wideband, 10 to 2000 MHz
- low insertion loss, 0.5 dB typ.
- good isolation, 19 dB typ.
- rugged shielded case

Applications

- HF/VHF
- instrumentation
- communication systems



Generic photo used for illustration purposes only

CASE STYLE: V37

Connectors	Model
SMA	ZESC-2-11+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications




FREQ. RANGE (MHz)	ISOLATION (dB)						INSERTION LOSS (dB) ABOVE 3.0 dB						PHASE UNBALANCE (Degrees)			AMPLITUDE UNBALANCE (dB)		
	L		M		U		L		M		U		L		M		U	
f_L - f_U	Typ.	Min.	Typ.	Min.	Typ.	Min.	Typ.	Max.	Typ.	Max.	Typ.	Max.	Max.	Max.	Max.	Max.	Max.	Max.
10-2000	19	10	18	13	20	11	0.5	0.9	0.5	1.0	0.6	1.2	1	3	6	0.2	0.3	0.5

L = low range [f_L to $10 f_L$] M = mid range [$10 f_L$ to $f_U/2$] U = upper range [$f_U/2$ to f_U]

Typical Performance Data

Frequency (MHz)	Total Loss ¹ (dB)		Amplitude Unbalance (dB)	Isolation (dB)	Phase Unbalance (deg.)	VSWR S	VSWR 1	VSWR 2
	S-1	S-2						
10.00	3.52	3.52	0.00	17.85	0.03	1.99	1.57	1.58
20.00	3.48	3.48	0.01	18.89	0.05	1.99	1.57	1.58
40.00	3.57	3.58	0.01	18.60	0.03	1.99	1.55	1.56
60.00	3.53	3.51	0.02	18.09	0.02	1.99	1.53	1.53
90.00	3.49	3.49	0.01	17.67	0.07	1.98	1.51	1.51
200.00	3.56	3.57	0.01	17.38	0.05	1.97	1.49	1.49
350.00	3.61	3.62	0.01	17.35	0.03	1.94	1.50	1.50
450.00	3.60	3.61	0.02	17.67	0.02	1.92	1.50	1.51
550.00	3.49	3.50	0.01	18.01	0.05	1.89	1.51	1.52
750.00	3.42	3.43	0.01	18.69	0.11	1.83	1.53	1.54
950.00	3.55	3.60	0.04	19.87	0.07	1.75	1.56	1.56
1150.00	3.30	3.32	0.02	21.03	0.08	1.65	1.57	1.58
1400.00	3.35	3.43	0.08	22.89	0.16	1.50	1.58	1.59
1800.00	3.42	3.55	0.13	21.71	0.05	1.25	1.56	1.59
2000.00	3.33	3.50	0.17	19.39	0.25	1.11	1.54	1.57

1. Total Loss = Insertion Loss + 3dB splitter loss.



Electrical Schematic



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

 REV. D
 M151107
 ZESC-2-11+
 HY/TD/CP/AM
 200828

2 Way-0° Power Splitter/Combiner

ZESC-2-11+

Typical Performance Data

FREQ.	TOTAL LOSS ¹		AMP. UNBAL.	ISOLATION	PHASE UNBAL.	FREQ.	VSWR		
(MHz)	(dB)		(dB)	(dB)	(Deg.)	(MHz)	(:1)		
	S-1	S-2		1-2			S	1	2
10.00	3.52	3.52	0.00	17.85	0.03	10.00	1.99	1.57	1.58
20.00	3.48	3.48	0.01	18.89	0.05	20.00	1.99	1.57	1.58
30.00	3.52	3.53	0.02	18.82	0.10	30.00	1.99	1.56	1.57
40.00	3.57	3.58	0.01	18.60	0.03	40.00	1.99	1.55	1.56
50.00	3.58	3.58	0.00	18.34	0.03	50.00	1.99	1.54	1.54
60.00	3.53	3.51	0.02	18.09	0.02	60.00	1.99	1.53	1.53
70.00	3.44	3.45	0.01	17.86	0.03	70.00	1.99	1.52	1.52
80.00	3.44	3.44	0.00	17.74	0.00	80.00	1.99	1.51	1.52
90.00	3.49	3.49	0.01	17.67	0.07	90.00	1.98	1.51	1.51
100.00	3.56	3.56	0.00	17.65	0.05	100.00	1.98	1.50	1.51
150.00	3.55	3.55	0.00	17.24	0.03	150.00	1.97	1.49	1.49
200.00	3.56	3.57	0.01	17.38	0.05	200.00	1.97	1.49	1.49
250.00	3.56	3.56	0.01	17.13	0.10	250.00	1.96	1.49	1.49
300.00	3.52	3.53	0.01	17.47	0.01	300.00	1.95	1.49	1.49
350.00	3.61	3.62	0.01	17.35	0.03	350.00	1.94	1.50	1.50
400.00	3.49	3.49	0.00	17.59	0.05	400.00	1.93	1.50	1.50
450.00	3.60	3.61	0.02	17.67	0.02	450.00	1.92	1.50	1.51
500.00	3.46	3.48	0.02	17.79	0.00	500.00	1.91	1.51	1.52
550.00	3.49	3.50	0.01	18.01	0.05	550.00	1.89	1.51	1.52
600.00	3.56	3.57	0.01	18.17	0.06	600.00	1.88	1.52	1.53
650.00	3.43	3.44	0.02	18.32	0.05	650.00	1.86	1.52	1.53
700.00	3.58	3.60	0.01	18.65	0.00	700.00	1.85	1.53	1.54
750.00	3.42	3.43	0.01	18.69	0.11	750.00	1.83	1.53	1.54
800.00	3.50	3.51	0.01	19.11	0.02	800.00	1.81	1.54	1.55
850.00	3.53	3.56	0.03	19.27	0.02	850.00	1.79	1.54	1.55
900.00	3.39	3.42	0.02	19.61	0.07	900.00	1.77	1.55	1.56
950.00	3.55	3.60	0.04	19.87	0.07	950.00	1.75	1.56	1.56
1000.00	3.37	3.39	0.02	20.21	0.00	1000.00	1.73	1.56	1.57
1050.00	3.44	3.48	0.04	20.45	0.13	1050.00	1.70	1.56	1.57
1100.00	3.47	3.52	0.05	21.02	0.04	1100.00	1.68	1.56	1.58
1150.00	3.30	3.32	0.02	21.03	0.08	1150.00	1.65	1.57	1.58
1200.00	3.53	3.58	0.05	21.75	0.03	1200.00	1.62	1.57	1.59
1250.00	3.28	3.34	0.06	21.74	0.15	1250.00	1.60	1.57	1.59
1300.00	3.44	3.50	0.06	22.39	0.09	1300.00	1.56	1.58	1.59
1400.00	3.35	3.43	0.08	22.89	0.16	1400.00	1.50	1.58	1.59
1500.00	3.35	3.43	0.09	23.20	0.09	1500.00	1.44	1.58	1.60
1600.00	3.44	3.54	0.10	23.12	0.18	1600.00	1.38	1.57	1.60
1700.00	3.51	3.63	0.12	22.61	0.01	1700.00	1.32	1.57	1.60
1800.00	3.42	3.55	0.13	21.71	0.05	1800.00	1.25	1.56	1.59
1900.00	3.37	3.50	0.14	20.60	0.08	1900.00	1.18	1.55	1.58
2000.00	3.33	3.50	0.17	19.39	0.25	2000.00	1.11	1.54	1.57

¹Total Loss = Insertion Loss + 3dB Splitter Loss



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



IF/RF MICROWAVE COMPONENTS








REV. X2
ZESC-2-11+
8/9/2010
Page 1 of 1

2 Way-90° Power Splitter/Combiner

ZESC-2-11+

Typical Performance Curves



Mini-Circuits®
ISO 9001 ISO 14001 AS 9100 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com




IF/RF MICROWAVE COMPONENTS



REV. X2
ZESC-2-11+
8/9/2010
Page 1 of 1

Outline Dimensions

V37



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N	WT GRAMS
V37	.83 (21.08)	.83 (21.08)	.75 (19.05)	.37 (9.40)	.42 (10.67)	1.25 (31.75)	.10 (2.54)	1.050 (26.67)	.10 (2.54)	.640 (16.26)	.21 (5.33)	.106 (2.69)	.06 (1.52)	22.0

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I