

Coaxial Bias-Tee

50Ω Wideband 0.1 to 6000 MHz

ZFBT-6GW+



Generic photo used for illustration purposes only

CASE STYLE: K18

Connectors Model
SMA ZFBT-6GW+
BRACKET (OPTION "B")

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Maximum Ratings

| | |
|-------------------------------------|----------------|
| Operating Temperature | -55°C to 100°C |
| Storage Temperature | -55°C to 100°C |
| RF Power | 30 dBm max. |
| Voltage at DC port | 30 V max. |
| Input Current | 500 mA |
| DC resistance from DC to RF&DC port | 4.5 ohm typ. |

Permanent damage may occur if any of these limits are exceeded.

Coaxial Connections

| | |
|-------|----------------|
| RF | 1 (SMA female) |
| RF&DC | 2 (SMA male) |
| DC | 3 (SMA female) |

Features

- wideband, 0.1 to 6000 MHz
- low insertion loss, 0.6 dB typ.
- good isolation, 40 dB typ.

Applications

- biasing amplifiers
- biasing of laser diodes
- biasing of active antennas
- DC return
- DC blocking
- test accessory

Bias-Tee Electrical Specifications

| FREQUENCY (MHz) | INSERTION LOSS* (dB) | | | | | | ISOLATION* (dB) (RF port to DC port) (RF&DC port to DC port) | | | | | | VSWR** (:1) | | | | | | |
|-----------------|----------------------|------|------|------|------|------|--------------------------------------------------------------|------|------|------|------|------|-------------|------|------|------|------|------|-----|
| | L | | M | | U | | L | | M | | U | | L | | M | | U | | |
| | Typ. | Max. | Typ. | Max. | Typ. | Max. | Typ. | Min. | Typ. | Min. | Typ. | Min. | Typ. | Max. | Typ. | Max. | Typ. | Max. | |
| f_L | f_U | | | | | | | | | | | | | | | | | | |
| 0.1 | 6000 | 0.15 | 0.8 | 0.6 | 1.4 | 1.0 | 2.2 | 25 | 15 | 40 | 20 | 30 | 17 | 1.06 | 1.6 | 1.13 | 1.3 | 1.13 | 1.5 |

L= low range (f_L to 10 f_L)

M= mid range (10 f_L to $f_U/2$)


U= upper range ($f_U/2$ to f_U)

* Insertion Loss 1 dB Max. and isolation 7dB Min. 0.1 to 0.3 MHz.

Insertion Loss and Isolation are guaranteed up to 20 dBm-RF power and 200mA DC current.

**VSWR measured with open and short at DC port.

Outline Drawing



Outline Dimensions (inch mm)


| A | B | C | D | E | F | G | H |
|-------|-------|-------|-------|------|-------|------|-------|
| 1.25 | 1.25 | .75 | .63 | .38 | 1.00 | .125 | 1.000 |
| 31.75 | 31.75 | 19.05 | 16.00 | 9.65 | 25.40 | 3.18 | 25.40 |

| J | K | L | M | N | P | Q | wt |
|----|----|------|-------|-------|-------|------|-------|
| -- | -- | .125 | 1.688 | 2.18 | .75 | .07 | grams |
| -- | -- | 3.18 | 42.88 | 55.37 | 19.05 | 1.78 | 70.0 |

Typical Performance Data

| Freq. (MHz) | Pin (dBm) | INSERTION LOSS (dB) with Current | | | | | | ISOLATION (dB) (Pin= -10dBm) with current | | | | | | VSWR (:1) |
|-------------|-----------|----------------------------------|-------|------|-------|-------|-------|-------------------------------------------|-------|-------|-------|-------|-------|-----------|
| | | 0mA | 20mA | 50mA | 100mA | 150mA | 200mA | 10mA | 20mA | 50mA | 100mA | 150mA | 200mA | |
| | | 0.10 | 19.80 | 0.17 | 0.17 | 0.16 | 0.17 | 0.20 | 0.24 | 19.46 | 19.04 | 17.83 | 14.58 | |
| 0.27 | 19.80 | 0.13 | 0.13 | 0.13 | 0.14 | 0.14 | 0.15 | 25.86 | 25.53 | 24.52 | 21.43 | 19.31 | 18.16 | 1.07 |
| 0.53 | 19.80 | 0.12 | 0.12 | 0.12 | 0.11 | 0.11 | 0.11 | 29.17 | 28.98 | 28.36 | 26.18 | 24.40 | 23.37 | 1.04 |
| 1.06 | 19.80 | 0.13 | 0.13 | 0.12 | 0.11 | 0.12 | 0.12 | 30.81 | 30.74 | 30.56 | 29.62 | 28.62 | 27.92 | 1.02 |
| 10.00 | 18.50 | 0.16 | 0.17 | 0.17 | 0.16 | 0.16 | 0.16 | 30.06 | 30.07 | 30.07 | 30.20 | 30.38 | 30.56 | 1.04 |
| 114.75 | 19.50 | 0.22 | 0.25 | 0.24 | 0.22 | 0.22 | 0.22 | 34.45 | 34.49 | 34.27 | 33.99 | 33.83 | 33.59 | 1.07 |
| 324.25 | 19.70 | 0.50 | 0.55 | 0.53 | 0.52 | 0.53 | 0.56 | 44.65 | 44.61 | 44.25 | 43.90 | 43.91 | 43.34 | 1.06 |
| 743.25 | 18.70 | 0.28 | 0.31 | 0.30 | 0.29 | 0.29 | 0.29 | 51.19 | 50.50 | 50.16 | 50.65 | 51.69 | 52.47 | 1.06 |
| 952.75 | 18.20 | 0.31 | 0.33 | 0.33 | 0.31 | 0.32 | 0.33 | 40.75 | 40.80 | 40.97 | 40.97 | 40.93 | 40.95 | 1.11 |
| 1581.25 | 18.00 | 0.46 | 0.48 | 0.47 | 0.46 | 0.48 | 0.49 | 42.58 | 42.59 | 43.94 | 43.77 | 44.36 | 44.17 | 1.13 |
| 2000.25 | 17.10 | 0.46 | 0.48 | 0.47 | 0.46 | 0.46 | 0.47 | 45.46 | 45.57 | 45.73 | 45.48 | 46.14 | 45.28 | 1.12 |
| 2524.00 | 14.40 | 0.40 | 0.42 | 0.41 | 0.42 | 0.43 | 0.44 | 53.15 | 53.72 | 52.19 | 53.17 | 52.67 | 53.67 | 1.12 |
| 3047.75 | 14.20 | 0.45 | 0.48 | 0.47 | 0.46 | 0.46 | 0.49 | 52.46 | 52.25 | 51.55 | 51.33 | 51.46 | 50.99 | 1.09 |
| 3676.25 | 15.10 | 0.73 | 0.74 | 0.75 | 0.75 | 0.75 | 0.75 | 46.32 | 47.19 | 46.36 | 45.53 | 46.19 | 45.65 | 1.07 |
| 4200.00 | 17.90 | 1.04 | 1.07 | 1.07 | 1.06 | 1.05 | 1.06 | 28.42 | 28.36 | 28.24 | 28.14 | 28.01 | 27.92 | 1.09 |
| 4502.50 | -0.60 | 1.17 | 1.19 | 1.18 | 1.19 | 1.17 | 1.16 | 28.15 | 28.10 | 28.05 | 27.96 | 27.84 | 27.87 | 1.14 |
| 4802.00 | -0.70 | 1.26 | 1.26 | 1.27 | 1.25 | 1.22 | 1.20 | 37.95 | 38.01 | 38.19 | 37.93 | 37.58 | 37.51 | 1.12 |
| 5251.75 | -1.10 | 1.19 | 1.17 | 1.16 | 1.13 | 1.11 | 1.09 | 49.68 | 51.04 | 49.12 | 49.37 | 49.13 | 48.19 | 1.11 |
| 5550.75 | -2.00 | 1.65 | 1.63 | 1.60 | 1.56 | 1.54 | 1.51 | 38.44 | 38.56 | 38.36 | 38.07 | 37.85 | 38.19 | 1.10 |
| 6000.00 | -2.40 | 1.70 | 1.71 | 1.65 | 1.59 | 1.54 | 1.50 | 34.37 | 34.36 | 34.23 | 34.40 | 34.49 | 34.48 | 1.12 |




Electrical Schematic



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuit's standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/MCLStore/terms.jsp





Notes




- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




Typical Performance Data

| FREQ. (MHz) | INSERTION LOSS with current (RF Port to RF&DC Port) (dB) | | | | | | ISOLATION with current (RF Port to DC Port, RF&DC Port to DC Port) (dB) | | | | | | VSWR (:1) |
|----------------|----------------------------------------------------------------|------|------|-------|-------|-------|-------------------------------------------------------------------------------|-------|-------|-------|-------|-------|--------------|
| | 0mA | 20mA | 50mA | 100mA | 150mA | 200mA | 10mA | 20mA | 50mA | 100mA | 150mA | 200mA | |
| | 0.10 | 0.17 | 0.17 | 0.16 | 0.17 | 0.20 | 0.24 | 19.46 | 19.04 | 17.83 | 14.58 | 12.66 | |
| 0.27 | 0.13 | 0.13 | 0.13 | 0.14 | 0.14 | 0.15 | 25.86 | 25.53 | 24.52 | 21.43 | 19.31 | 18.16 | 1.07 |
| 0.53 | 0.12 | 0.12 | 0.12 | 0.11 | 0.11 | 0.11 | 29.17 | 28.98 | 28.36 | 26.18 | 24.40 | 23.37 | 1.04 |
| 1.06 | 0.13 | 0.13 | 0.12 | 0.11 | 0.12 | 0.12 | 30.81 | 30.74 | 30.56 | 29.62 | 28.62 | 27.92 | 1.02 |
| 10.00 | 0.16 | 0.17 | 0.17 | 0.16 | 0.16 | 0.16 | 30.06 | 30.07 | 30.07 | 30.20 | 30.38 | 30.56 | 1.04 |
| 114.75 | 0.22 | 0.25 | 0.24 | 0.22 | 0.22 | 0.22 | 34.45 | 34.49 | 34.27 | 33.99 | 33.83 | 33.59 | 1.07 |
| 324.25 | 0.50 | 0.55 | 0.53 | 0.52 | 0.53 | 0.56 | 44.65 | 44.61 | 44.25 | 43.90 | 43.91 | 43.34 | 1.06 |
| 743.25 | 0.28 | 0.31 | 0.30 | 0.29 | 0.29 | 0.29 | 51.19 | 50.50 | 50.16 | 50.65 | 51.69 | 52.47 | 1.06 |
| 952.75 | 0.31 | 0.33 | 0.33 | 0.31 | 0.32 | 0.33 | 40.75 | 40.80 | 40.97 | 40.97 | 40.93 | 40.95 | 1.11 |
| 1581.25 | 0.46 | 0.48 | 0.47 | 0.46 | 0.48 | 0.49 | 42.58 | 42.59 | 43.94 | 43.77 | 44.36 | 44.17 | 1.13 |
| 2000.25 | 0.46 | 0.48 | 0.47 | 0.46 | 0.46 | 0.47 | 45.46 | 45.57 | 45.73 | 45.48 | 46.14 | 45.28 | 1.12 |
| 2524.00 | 0.40 | 0.42 | 0.41 | 0.42 | 0.43 | 0.44 | 53.15 | 53.72 | 52.19 | 53.17 | 52.67 | 53.67 | 1.12 |
| 3047.75 | 0.45 | 0.48 | 0.47 | 0.46 | 0.46 | 0.49 | 52.46 | 52.25 | 51.55 | 51.33 | 51.46 | 50.99 | 1.09 |
| 3676.25 | 0.73 | 0.74 | 0.75 | 0.75 | 0.75 | 0.75 | 46.32 | 47.19 | 46.36 | 45.53 | 46.19 | 45.65 | 1.07 |
| 4200.00 | 1.04 | 1.07 | 1.07 | 1.06 | 1.05 | 1.06 | 28.42 | 28.36 | 28.24 | 28.14 | 28.01 | 27.92 | 1.09 |
| 4502.50 | 1.17 | 1.19 | 1.18 | 1.19 | 1.17 | 1.16 | 28.15 | 28.10 | 28.05 | 27.96 | 27.84 | 27.87 | 1.14 |
| 4802.00 | 1.26 | 1.26 | 1.27 | 1.25 | 1.22 | 1.20 | 37.95 | 38.01 | 38.19 | 37.93 | 37.58 | 37.51 | 1.12 |
| 5251.75 | 1.19 | 1.17 | 1.16 | 1.13 | 1.11 | 1.09 | 49.68 | 51.04 | 49.12 | 49.37 | 49.13 | 48.19 | 1.11 |
| 5550.75 | 1.65 | 1.63 | 1.60 | 1.56 | 1.54 | 1.51 | 38.44 | 38.56 | 38.36 | 38.07 | 37.85 | 38.19 | 1.10 |
| 6000.00 | 1.70 | 1.71 | 1.65 | 1.59 | 1.54 | 1.50 | 34.37 | 34.36 | 34.23 | 34.40 | 34.49 | 34.48 | 1.12 |

Typical Performance Curves



Outline Dimensions



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M | N |
|-------|-----------------|-----------------|----------------|----------------|---------------|------------------|----------------|------------------|----|----|----------------|------------------|-----------------|
| K18 | 1.25 (31.75) | 1.25 (31.75) | .75 (19.05) | .63 (16.00) | .38 (9.65) | 1.000 (25.40) | .125 (3.18) | 1.000 (25.40) | -- | -- | .125 (3.18) | 1.688 (42.88) | 2.18 (55.37) |

| CASE# | P | Q | WT. GRAMS |
|-------|----------------|---------------|-----------|
| K18 | .75 (19.05) | .07 (1.78) | 70.0 |

Dimensions are in inches (mm). Tolerances: 2 Pl. \pm .03; 3 Pl. \pm .015

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Mounting bracket available on request. Add suffix B to part number.
- For port marking 1, 2, and 3 see specifications data sheet.
- For bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
- Refer to the individual model data sheet for the type of connectors available.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

| Specification | Test/Inspection Condition | Reference/Spec |
|----------------------------|----------------------------------------------------------------------------------------|--------------------------------------|
| Operating Temperature | -55° to 100°C Ambient Environment | Individual Model Data Sheet |
| Storage Temperature | -55° to 100° C Ambient Environment | Individual Model Data Sheet |
| Barometric Pressure | 100,000 Feet | MIL-STD-202, Method 105, Condition D |
| Humidity | 90% RH, 65°C Units may require bake-out after humidity to restore full performance. | MIL-STD-202, Method 103 |
| Thermal Shock | -65° to 125°C, 5 cycles | MIL-STD-202, Method 107, Condition B |
| Vibration (High Frequency) | 20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36) | MIL-STD-202, Method 204, Condition D |
| Mechanical Shock | 100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18) | MIL-STD-202, Method 213, Condition I |