



Mini-Circuits

LUMPED LC COAXIAL

High Pass Filter

ZFHP-0R055-S+

50Ω

0.07 to 1000 MHz

SMA Female

KEY FEATURES

- Wideband, 0.07 MHz to 1000 MHz
- Good Return Loss, 26 Typ @ Passband.
- High Rejection
- Rugged Shielded Case

APPLICATIONS

- Wire-Line Broadband Access
- Fiber Optics Network
- Receivers / Transmitters
- Lab Use
- Test Equipment


PRODUCT OVERVIEW

Mini-Circuits' ZFHP-0R055-S+ is a High pass filter in a fabricated using connectorized package. This filter offers low insertion loss and good rejection. This will find its applications in transmitter and receivers.



Generic photo used for illustration purposes only

FUNCTIONAL DIAGRAM



ELECTRICAL SPECIFICATIONS AT +25°C


Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Units
Passband	Insertion Loss	F3-F4	0.07 - 1000	—	—	1.6	dB
	Freq. Cut-Off	Fc	0.055	—	3	—	dB
	Return Loss	F3-F4	0.07 - 1000	—	26	—	dB
Stopband	Rejection	DC-F1	DC - 0.04	40	—	—	dB
		DC-F2	DC - 0.044	20	—	—	

ABSOLUTE MAXIMUM RATINGS¹

Parameter	Ratings
Operating Temperature	-40°C to +85°C
Storage Temperature	-55°C to +100°C
Input Power	1m W @ 25°C

1. Permanent damage may occur if any of these limits are exceeded.

TYPICAL FREQUENCY RESPONSE



Mini-Circuits



LUMPED LC COAXIAL

High Pass Filter



ZFHP-0R055-S+

50 Ω

0.07 to 1000 MHz

SMA Female

TYPICAL PERFORMANCE GRAPHS





LUMPED LC COAXIAL

High Pass Filter

ZFHP-0R055-S+

50Ω

0.07 to 1000 MHz


SMA Female

CONNECTOR DESCRIPTION

Function	Connector
RF1 ²	SMA Female
RF2 ²	SMA Female

2. This filter is bi-directional, RF1 and RF2 ports may be interchanged, see S-Parameters for actual performance.

CASE STYLE DRAWING



Weight: 70g

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

PRODUCT MARKING*: ZFHP-0R055-S+

*Marking may contain other features or characters for internal lot control.



LUMPED LC COAXIAL

High Pass Filter

ZFHP-0R055-S+

50Ω

0.07 to 1000 MHz

SMA Female

ADDITIONAL INFORMATION IS AVAILABLE ON OUR DASHBOARD

[CLICK HERE](#)

Performance Data & Graphs	Data
	Graphs
	S-Parameter (S2P Files) Data Set (.zip file)
Case Style	H16
RoHS Status	Compliant
Environmental Ratings	ENV46

NOTES

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the standard terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/terms/viewterm.html



Coaxial High Pass Filter

ZFHP-0R055-S+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
0.009	80.97	0.02
0.012	86.90	0.04
0.015	85.48	0.06
0.020	88.75	0.09
0.040	73.86	0.63
0.042	60.68	1.84
0.043	54.10	2.45
0.044	47.51	3.06
0.045	40.92	3.67
0.046	34.33	4.28
0.048	21.16	5.50
0.049	14.57	6.11
0.050	7.99	6.71
0.052	6.68	12.61
0.055	4.73	21.44
0.057	3.42	27.34
0.058	2.77	30.28
0.060	1.47	36.17
0.065	1.17	32.03
0.070	0.87	27.88
0.080	0.66	19.72
0.100	0.43	20.57
0.200	0.17	22.29
0.500	0.08	23.96
0.800	0.05	27.30
1.000	0.04	29.01
1.500	0.03	32.18
2.000	0.03	34.35
5.000	0.02	40.45
10.000	0.02	42.91
20.000	0.04	43.59
50.000	0.05	38.95
100.000	0.07	31.40
120.000	0.12	28.42
140.000	0.18	28.82
160.000	0.32	25.54
180.000	0.55	26.35
200.000	0.20	39.60
250.000	0.18	30.19
300.000	0.33	28.61
350.000	0.21	29.52
400.000	0.20	26.26
500.000	0.46	22.67
600.000	0.74	21.72
700.000	0.48	26.45
800.000	0.65	22.25
900.000	0.61	22.23
1000.000	0.96	24.10

REV. OR
ZFHP-0R055-S+
200225
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661





The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see



Coaxial High Pass Filter

ZFHP-0R055-S+

Typical Performance Curves



REV. OR

ZFHP-0R055-S+

200225

Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661




The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see




Outline Dimensions

H16

STANDARD



OPTION "B"



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
H16	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT.GRAMS
H16	.750 (19.05)	.06 (1.52)	70

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Mounting bracket available on request. Add suffix B to part number.
4. Bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
5. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 100°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Humidity	90 to 95% RH, 40°C, 96 hours; Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103, Condition B
Thermal Shock	-55° to 100°C, 100 cycles	MIL-STD-202, Method 107, Condition A-3, except +100°C
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	50g, 11ms half-sine, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition A