

Coaxial High Pass Filter

ZFHP-3800-S+

50Ω

3800 to 6000 MHz



Generic photo used for illustration purposes only
CASE STYLE: H16

The Big Deal

- Low insertion loss
- Good rejection
- Connectorized package

Product Overview

ZFHP-3800-S+ is a High pass filter in a fabricated using connectorized package. This filter offers low insertion loss and good rejection. This will find its applications in transmitter and receivers.

Key Features

Feature	Advantages
Low insertion loss	Can be used in high performance applications.
Good rejection	This enables the filter to attenuate spurious signals and reject harmonics till 3GHz.
Connectorized package	The connectorized package is easy to interface with other devices and well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



Coaxial High Pass Filter

50Ω 3800 to 6000 MHz

ZFHP-3800-S+



Generic photo used for illustration purposes only

CASE STYLE: H16

Connectors	Model
SMA-M / F	ZFHP-3800-S+
BRACKET (OPTION "B")	

Features

- Wide band, 3800 MHz to 6000 MHz
- Low insertion loss
- Connectorized package

Applications

- Sub-harmonic rejection
- Transmitter \ receiver
- Lab use

Electrical Specifications at 25°C


Parameter	F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection Loss	DC-F1	10-3170	20	27.3	-
	VSWR	DC-F1	10-3170	-	20	-
Pass Band	Insertion Loss	F2-F3	3800-6000	-	1.0	2
	VSWR	F2-F3	3800-6000	-	1.5	2.5

Maximum Ratings

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power Input	2W max.

Permanent damage may occur if any of these limits are exceeded.


Functional Schematic



Typical Performance Data at 25°C





Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
10.0	105.44	2184.20
450.0	77.87	136.92
550.0	76.20	133.47
1230.0	78.93	123.66
1450.0	68.10	120.30
1910.0	56.12	115.68
2510.0	48.88	96.18
2790.0	50.77	72.36
3150.0	33.01	27.15
3170.0	30.16	24.42
3240.0	20.34	14.97
3300.0	12.25	7.84
3305.0	11.61	7.33
3400.0	3.20	1.96
3435.0	2.16	1.55
3625.0	0.96	1.13
3800.0	0.84	1.38
3950.0	0.74	1.37
5000.0	0.61	1.40
6000.0	0.51	1.22

Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV.B
M171494
ZFHP-3800-S+
EDU2097/1
URJ
200123
Page 2 of 3

Coaxial Connections

PORT - 1	SMA-Male
PORT - 2	SMA-Female

Outline Drawing



Outline Dimensions ($\frac{\text{inch}}{\text{mm}}$)

A	B	C	D	E	F	G	H
1.25	1.25	.75	.63	.38	1.000	.125	1.000
31.75	31.75	19.05	16.00	9.65	25.40	3.18	25.40

J	K	L	M	N	P	Q	wt
--	--	.125	1.688	2.18	.750	.06	grams
--	--	3.18	42.88	55.37	19.05	1.52	70.0

Note: Please refer to case style drawing for details

Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.

B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.

C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp







Typical Performance Data

FREQ.	INSERTION LOSS			INPUT RETURN LOSS			OUTPUT RETURN LOSS		
(MHz)	(dB)			(dB)			(dB)		
	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C	@-40°C	@+25°C	@+85°C
10.0	109.49	105.44	103.09	0.01	0.01	0.01	0.00	0.01	0.01
30.0	98.84	94.45	95.99	0.00	0.01	0.01	0.00	0.01	0.01
50.0	94.04	90.86	92.23	0.02	0.03	0.03	0.01	0.02	0.02
70.0	93.67	90.42	90.55	0.02	0.04	0.04	0.02	0.03	0.03
90.0	89.10	90.41	87.11	0.03	0.05	0.05	0.03	0.04	0.04
110.0	85.29	88.24	87.14	0.04	0.06	0.06	0.04	0.05	0.05
170.0	86.13	83.12	85.57	0.06	0.08	0.08	0.06	0.07	0.07
370.0	78.17	78.44	78.18	0.09	0.14	0.14	0.09	0.12	0.12
450.0	78.53	77.87	77.55	0.10	0.15	0.16	0.09	0.13	0.13
670.0	76.12	77.57	76.34	0.11	0.16	0.18	0.10	0.14	0.15
1130.0	106.16	96.24	89.53	0.11	0.17	0.21	0.10	0.14	0.15
1210.0	80.45	81.29	80.94	0.11	0.17	0.21	0.10	0.14	0.15
1690.0	61.33	60.91	60.62	0.07	0.15	0.21	0.09	0.14	0.16
2210.0	51.57	51.45	51.31	0.05	0.15	0.23	0.08	0.16	0.18
2410.0	49.44	49.34	49.27	0.06	0.16	0.24	0.08	0.16	0.19
3000.0	52.37	51.80	51.45	0.20	0.30	0.36	0.24	0.36	0.41
3105.0	40.64	39.44	38.62	0.27	0.38	0.45	0.40	0.52	0.58
3145.0	34.92	33.73	32.88	0.33	0.44	0.50	0.49	0.62	0.69
3150.0	34.21	33.01	32.16	0.33	0.45	0.51	0.50	0.64	0.71
3155.0	33.50	32.29	31.45	0.34	0.45	0.52	0.51	0.65	0.72
3160.0	32.79	31.58	30.74	0.35	0.47	0.53	0.53	0.67	0.74
3165.0	32.07	30.87	30.02	0.35	0.47	0.55	0.55	0.69	0.77
3170.0	31.36	30.16	29.31	0.36	0.48	0.56	0.57	0.71	0.78
3175.0	30.66	29.45	28.60	0.37	0.49	0.57	0.59	0.74	0.81
3210.0	25.74	24.51	23.64	0.44	0.58	0.66	0.75	0.92	1.02
3250.0	20.22	18.96	18.06	0.58	0.75	0.87	1.04	1.27	1.42
3300.0	13.51	12.25	11.37	1.01	1.32	1.56	1.79	2.23	2.54
3305.0	12.86	11.61	10.74	1.08	1.41	1.67	1.91	2.38	2.73
3320.0	10.97	9.78	8.95	1.36	1.78	2.13	2.35	2.96	3.43
3410.0	3.10	2.82	2.66	6.33	7.60	8.51	9.16	10.88	12.05
3415.0	2.90	2.66	2.52	6.77	8.06	8.96	9.70	11.42	12.55
3445.0	2.04	1.98	1.95	9.42	10.71	11.57	12.62	14.09	14.97
3460.0	1.77	1.77	1.76	10.66	11.96	12.81	13.70	15.08	15.89
3495.0	1.38	1.43	1.46	13.36	14.78	15.75	15.82	17.32	18.35
3515.0	1.23	1.30	1.34	14.93	16.49	17.61	17.13	18.90	20.27
3530.0	1.14	1.22	1.26	16.16	17.82	19.09	18.32	20.40	22.10
3560.0	1.00	1.10	1.15	18.66	20.31	21.48	21.51	24.16	26.76
3565.0	0.98	1.08	1.14	19.06	20.65	21.69	22.13	24.82	27.42
3575.0	0.94	1.05	1.11	19.80	21.18	21.89	23.37	25.99	28.06
3590.0	0.90	1.02	1.08	20.67	21.53	21.63	25.02	26.77	27.10
3595.0	0.89	1.01	1.07	20.87	21.51	21.43	25.54	26.77	26.55
3600.0	0.88	1.00	1.07	21.02	21.45	21.20	25.81	26.49	25.89
3625.0	0.83	0.96	1.03	20.95	20.55	19.81	25.23	23.99	22.71
3650.0	0.79	0.93	1.01	20.04	19.34	18.47	22.69	21.46	20.24
3655.0	0.79	0.92	1.00	19.80	19.09	18.21	22.23	21.05	19.87
3665.0	0.78	0.92	1.00	19.34	18.63	17.76	21.34	20.26	19.21
3725.0	0.74	0.88	0.97	17.23	16.67	16.04	17.87	17.28	16.63
3735.0	0.74	0.88	0.96	17.01	16.49	15.89	17.55	16.98	16.40
3740.0	0.73	0.88	0.96	16.92	16.42	15.83	17.40	16.85	16.31
3750.0	0.73	0.87	0.96	16.76	16.27	15.73	17.13	16.61	16.13
3800.0	0.70	0.84	0.93	16.37	15.96	15.63	16.32	15.94	15.63
3810.0	0.69	0.84	0.92	16.38	15.98	15.67	16.27	15.88	15.63
3855.0	0.66	0.81	0.88	16.51	16.17	16.07	16.08	15.77	15.65
3910.0	0.62	0.77	0.84	16.96	16.72	16.84	16.21	15.99	16.04
3945.0	0.60	0.74	0.81	17.21	17.10	17.33	16.31	16.19	16.28
3980.0	0.58	0.72	0.80	17.37	17.38	17.67	16.36	16.32	16.46
4080.0	0.56	0.70	0.78	16.76	16.95	16.97	15.80	15.93	15.87
4400.0	0.58	0.79	0.91	13.72	12.71	12.05	13.33	12.38	11.81
5000.0	0.42	0.61	0.73	17.87	16.09	15.14	17.05	15.53	14.61
6000.0	0.34	0.51	0.61	19.70	20.33	20.67	20.39	20.09	19.68


Typical Performance Data

FREQ.	GROUP DELAY		
(MHz)	(nsec)		
	@-40°C	@+25°C	@+85°C
3800	0.87	0.85	0.83
3820	0.85	0.83	0.81
3840	0.83	0.81	0.79
3850	0.82	0.80	0.79
3870	0.81	0.79	0.77
3890	0.79	0.77	0.76
3900	0.79	0.77	0.76
3920	0.77	0.75	0.74
3940	0.76	0.74	0.73
3950	0.75	0.73	0.72
3970	0.74	0.72	0.71
3990	0.72	0.71	0.70
4000	0.72	0.70	0.69
4025	0.71	0.69	0.68
4050	0.69	0.68	0.67
4075	0.68	0.67	0.66
4100	0.67	0.65	0.65
4125	0.65	0.64	0.63
4150	0.64	0.63	0.62
4175	0.63	0.62	0.61
4200	0.62	0.61	0.60
4225	0.61	0.60	0.59
4250	0.60	0.59	0.58
4280	0.59	0.58	0.57
4300	0.59	0.57	0.56
4350	0.57	0.56	0.54
4400	0.56	0.54	0.53
4410	0.56	0.54	0.53
4420	0.55	0.54	0.52
4430	0.55	0.53	0.52
4440	0.55	0.53	0.52
4450	0.55	0.53	0.52
4460	0.54	0.53	0.51
4470	0.54	0.52	0.51
4480	0.54	0.52	0.51
4490	0.54	0.52	0.51
4500	0.53	0.52	0.51
4550	0.52	0.51	0.50
4600	0.52	0.50	0.49
4650	0.51	0.49	0.48
4700	0.50	0.48	0.47
4710	0.50	0.48	0.47
4720	0.50	0.48	0.47
4730	0.50	0.48	0.47
4740	0.50	0.48	0.47
4750	0.50	0.48	0.47
4760	0.49	0.48	0.47
4770	0.49	0.48	0.47
4780	0.49	0.48	0.46
4800	0.49	0.47	0.46
4810	0.49	0.47	0.46
4830	0.49	0.47	0.46
4850	0.48	0.47	0.46
4900	0.48	0.46	0.45
4950	0.47	0.46	0.45
5000	0.47	0.46	0.45
5260	0.45	0.44	0.43
5500	0.44	0.43	0.42
5760	0.42	0.41	0.41
6000	0.42	0.41	0.40

Typical Performance Curves




Typical Performance Curves




Outline Dimensions

H16

STANDARD



OPTION "B"



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
H16	1.25 (31.75)	1.25 (31.75)	.75 (19.05)	.63 (16.00)	.38 (9.65)	1.000 (25.40)	.125 (3.18)	1.000 (25.40)	--	--	.125 (3.18)	1.688 (42.88)	2.18 (55.37)

CASE#	P	Q	WT.GRAMS
H16	.750 (19.05)	.06 (1.52)	70

Dimensions are in inches (mm). Tolerances: 2PL. $\pm .03$; 3PL. $\pm .015$

Notes:

1. Case material: Aluminum alloy.
2. Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Mounting bracket available on request. Add suffix B to part number.
4. Bracket version, option B, dimension "C" changes from .75 to .94 inches when connectors are type N.
5. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-40° to 85°C	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I